

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1065807

Luminaire Tested: **NVN-SA1C-735-U-T3BC**

Issue Date: 08/07/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1065807  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 08/07/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: NVN-SA1C-735-U-T3BC  
Description: Navion AREA AND ROADWAY LUMINAIRE 1050mA 1xLight Square PACKAGE  
70CRI 3500K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL  
Light Source: (14) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5579.1 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 50.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1065807

CATALOG NUMBER: NVN-SA1C-735-U-T3BC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6.1 fc  
 Type III - Short - N/A

REPORT NUMBER: P1065807

CATALOG NUMBER: NVN-SA1C-735-U-T3BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1065807

CATALOG NUMBER: NVN-SA1C-735-U-T3BC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 19.8     | 0.0    | 19.8   |
|                    | % Fixture | 0.4      | 0.0    | 0.4    |
| <b>Street Side</b> | Lumens    | 5559.3   | 0.0    | 5559.3 |
|                    | % Fixture | 99.6     | 0.0    | 99.6   |
| <b>Total</b>       | Lumens    | 5579.1   | 0.0    | 5579.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 5.2    | 0.1       |
| 10°-20°   | 61.7   | 1.1       |
| 20°-30°   | 221.6  | 4.0       |
| 30°-40°   | 514.9  | 9.2       |
| 40°-50°   | 877.6  | 15.7      |
| 50°-60°   | 1446.0 | 25.9      |
| 60°-70°   | 1671.9 | 30.0      |
| 70°-80°   | 718.3  | 12.9      |
| 80°-90°   | 62.1   | 1.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5579.1 | 100.0     |
| 0°-180°   | 5579.1 | 100.0     |



REPORT NUMBER: P1065807


CATALOG NUMBER: NVN-SA1C-735-U-T3BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 283.5  | 5.1       |                         |      |         |
| FM   | (30°-60°)   | 2833.6 | 50.8      |                         |      |         |
| FH   | (60°-80°)   | 2380.9 | 42.7      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 61.3   | 1.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 4.9    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 4.8    | 0.1       | B0/220                  |      |         |
| BH   | (60°-80°)   | 9.3    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.8    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short





REPORT NUMBER: P1065807

CATALOG NUMBER: NVN-SA1C-735-U-T3BC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 44°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 35.3   | 35.3   | 35.3   | 35.3   | 35.3   | 35.3   | 35.3   | 35.3   | 35.3   | 35.3   | 35.3   |
| 2.5°  | 45.8   | 45.8   | 44.6   | 43.1   | 42.8   | 41.6   | 41.6   | 40.5   | 39.0   | 37.9   | 36.4   |
| 5°    | 66.4   | 66.0   | 63.0   | 59.3   | 54.4   | 51.4   | 51.4   | 47.3   | 43.5   | 40.1   | 37.1   |
| 7.5°  | 145.2  | 141.8  | 130.9  | 112.9  | 89.3   | 73.5   | 72.4   | 58.9   | 49.9   | 43.1   | 37.5   |
| 10°   | 333.1  | 321.5  | 306.1  | 263.0  | 194.3  | 135.8  | 133.2  | 85.9   | 59.6   | 46.5   | 38.3   |
| 12.5° | 545.8  | 555.2  | 524.4  | 456.5  | 376.3  | 279.9  | 261.1  | 144.8  | 78.8   | 51.0   | 39.0   |
| 15°   | 739.4  | 737.1  | 719.9  | 664.4  | 571.7  | 443.4  | 431.8  | 251.7  | 112.9  | 58.1   | 39.8   |
| 17.5° | 884.2  | 881.6  | 865.1  | 829.4  | 758.2  | 629.9  | 619.7  | 401.4  | 177.1  | 68.3   | 40.5   |
| 20°   | 1036.9 | 1033.5 | 1010.2 | 981.7  | 919.5  | 810.3  | 798.3  | 568.7  | 277.2  | 84.8   | 40.5   |
| 22.5° | 1220.0 | 1213.6 | 1188.8 | 1140.4 | 1074.8 | 979.9  | 969.0  | 739.8  | 401.4  | 111.8  | 42.4   |
| 25°   | 1441.3 | 1430.4 | 1396.3 | 1352.8 | 1273.6 | 1147.6 | 1135.9 | 930.3  | 551.1  | 152.7  | 44.3   |
| 27.5° | 1693.8 | 1695.6 | 1649.5 | 1576.0 | 1469.8 | 1341.1 | 1319.4 | 1101.0 | 706.0  | 211.2  | 46.5   |
| 30°   | 1993.5 | 1974.7 | 1909.8 | 1824.3 | 1721.1 | 1557.2 | 1536.2 | 1271.0 | 880.1  | 297.5  | 50.3   |
| 32.5° | 2274.1 | 2253.8 | 2166.4 | 2058.8 | 1948.1 | 1775.2 | 1757.9 | 1461.9 | 1038.4 | 399.5  | 57.0   |
| 35°   | 2514.9 | 2500.7 | 2378.4 | 2247.1 | 2148.8 | 1994.2 | 1989.0 | 1675.0 | 1224.5 | 509.4  | 64.5   |
| 37.5° | 2726.9 | 2701.0 | 2543.8 | 2407.6 | 2307.9 | 2169.4 | 2158.2 | 1870.1 | 1403.8 | 637.0  | 75.8   |
| 40°   | 2907.7 | 2893.4 | 2701.8 | 2522.8 | 2441.8 | 2318.0 | 2303.7 | 2041.1 | 1589.1 | 785.2  | 89.7   |
| 42.5° | 3101.3 | 3082.5 | 2896.4 | 2695.8 | 2546.4 | 2414.0 | 2404.6 | 2182.2 | 1754.2 | 948.0  | 110.3  |
| 45°   | 3320.0 | 3285.1 | 3121.9 | 2941.8 | 2714.9 | 2513.4 | 2502.9 | 2307.9 | 1923.3 | 1122.8 | 135.4  |
| 47.5° | 3553.7 | 3523.3 | 3391.3 | 3264.8 | 3003.7 | 2677.4 | 2654.9 | 2414.8 | 2091.4 | 1324.6 | 167.3  |
| 50°   | 3791.5 | 3792.3 | 3693.2 | 3632.5 | 3356.7 | 2943.7 | 2911.8 | 2572.0 | 2268.1 | 1540.7 | 214.6  |
| 52.5° | 4068.4 | 4075.5 | 4074.0 | 4029.0 | 3815.2 | 3379.3 | 3336.5 | 2810.5 | 2473.3 | 1792.8 | 279.9  |
| 55°   | 4184.3 | 4197.1 | 4280.0 | 4379.8 | 4321.6 | 3931.5 | 3885.7 | 3222.1 | 2745.3 | 2073.8 | 376.6  |
| 57.5° | 4089.4 | 4103.6 | 4218.1 | 4392.9 | 4526.4 | 4415.0 | 4409.8 | 3757.8 | 3103.5 | 2414.4 | 534.9  |
| 59°   | 3976.5 | 3974.6 | 4092.0 | 4277.3 | 4457.4 | 4529.8 | 4537.3 | 4120.2 | 3415.6 | 2653.4 | 671.5  |
| 60°   | 3901.4 | 3902.9 | 3981.0 | 4171.2 | 4362.5 | 4488.2 | 4517.4 | 4333.6 | 3598.0 | 2825.2 | 788.5  |
| 62.5° | 3611.8 | 3629.1 | 3691.0 | 3867.7 | 4049.3 | 4189.6 | 4239.4 | 4523.8 | 4119.8 | 3231.1 | 1195.6 |
| 65°   | 3297.1 | 3298.2 | 3386.4 | 3537.6 | 3711.6 | 3810.3 | 3841.8 | 4227.8 | 4468.3 | 3644.5 | 1729.4 |
| 67.5° | 2735.5 | 2758.4 | 2858.6 | 3103.5 | 3333.5 | 3458.4 | 3482.4 | 3680.1 | 4323.9 | 3913.8 | 1996.9 |
| 70°   | 1914.3 | 1944.3 | 2087.3 | 2405.0 | 2747.5 | 2952.7 | 2951.2 | 3059.3 | 3805.4 | 3793.8 | 1693.0 |
| 72.5° | 955.9  | 1007.6 | 1124.3 | 1464.5 | 1879.4 | 2201.7 | 2269.6 | 2460.9 | 3057.0 | 3151.2 | 1263.1 |
| 75°   | 422.4  | 425.4  | 491.8  | 663.2  | 934.1  | 1343.4 | 1404.1 | 1953.3 | 2345.4 | 2190.1 | 912.3  |
| 77.5° | 245.7  | 248.0  | 260.0  | 297.9  | 378.5  | 658.4  | 726.6  | 1281.1 | 1657.4 | 1272.8 | 595.0  |
| 80°   | 89.3   | 91.5   | 91.2   | 112.9  | 165.8  | 259.2  | 288.9  | 620.9  | 1105.5 | 670.4  | 311.7  |
| 82.5° | 54.8   | 54.8   | 52.9   | 53.3   | 60.4   | 99.4   | 108.8  | 264.5  | 538.3  | 330.1  | 89.3   |
| 85°   | 27.0   | 28.5   | 30.4   | 34.1   | 40.5   | 49.1   | 52.1   | 75.8   | 181.2  | 79.9   | 21.4   |
| 87.5° | 16.1   | 16.5   | 18.0   | 21.8   | 27.0   | 35.3   | 37.5   | 51.4   | 64.9   | 53.6   | 5.3    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1065807

CATALOG NUMBER: NVN-SA1C-735-U-T3BC

**CANDELA DISTRIBUTION (continued):**

|       | 90°   | 95°  | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|------|------|------|------|------|------|------|------|------|------|
| 0°    | 35.3  | 35.3 | 35.3 | 35.3 | 35.3 | 35.3 | 35.3 | 35.3 | 35.3 | 35.3 | 35.3 |
| 2.5°  | 35.6  | 35.3 | 33.4 | 31.9 | 30.4 | 28.9 | 27.8 | 26.6 | 26.6 | 27.0 | 26.6 |
| 5°    | 35.6  | 34.1 | 31.1 | 28.5 | 26.3 | 24.4 | 22.5 | 21.0 | 20.6 | 20.6 | 21.0 |
| 7.5°  | 35.3  | 33.4 | 29.3 | 25.9 | 22.9 | 20.3 | 18.4 | 16.5 | 16.1 | 16.5 | 16.1 |
| 10°   | 34.9  | 32.6 | 27.8 | 23.6 | 19.5 | 16.9 | 14.3 | 12.4 | 12.4 | 12.4 | 12.8 |
| 12.5° | 34.9  | 31.5 | 26.3 | 21.4 | 16.9 | 13.9 | 11.3 | 9.4  | 9.0  | 9.0  | 9.0  |
| 15°   | 34.5  | 30.8 | 24.8 | 18.8 | 14.3 | 10.5 | 8.3  | 6.4  | 6.4  | 6.4  | 6.4  |
| 17.5° | 33.8  | 29.6 | 22.9 | 16.5 | 11.3 | 7.9  | 5.6  | 3.8  | 3.8  | 4.5  | 4.5  |
| 20°   | 33.0  | 28.5 | 20.6 | 13.5 | 9.4  | 6.0  | 3.8  | 2.3  | 2.3  | 3.4  | 3.8  |
| 22.5° | 33.4  | 28.5 | 19.1 | 12.0 | 7.5  | 4.5  | 3.0  | 1.9  | 1.5  | 2.6  | 3.4  |
| 25°   | 33.8  | 27.8 | 17.3 | 10.5 | 5.6  | 3.4  | 2.3  | 0.8  | 0.4  | 0.8  | 1.1  |
| 27.5° | 33.8  | 27.0 | 15.0 | 8.3  | 4.1  | 2.6  | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  |
| 30°   | 33.4  | 25.9 | 13.1 | 6.8  | 3.0  | 1.5  | 0.4  | 0.0  | 0.0  | 0.0  | 0.0  |
| 32.5° | 33.0  | 24.8 | 12.0 | 5.3  | 2.6  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 35°   | 33.4  | 23.3 | 10.5 | 4.1  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.8  |
| 37.5° | 34.5  | 21.8 | 9.0  | 3.4  | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 40°   | 36.0  | 20.6 | 7.5  | 2.6  | 0.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 42.5° | 39.0  | 20.6 | 6.8  | 1.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 45°   | 42.8  | 20.6 | 5.6  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 47.5° | 47.6  | 21.0 | 4.9  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 50°   | 53.6  | 21.8 | 4.5  | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 52.5° | 58.1  | 21.0 | 4.1  | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 55°   | 66.0  | 20.3 | 3.8  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 57.5° | 76.5  | 19.1 | 3.8  | 0.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 59°   | 87.0  | 17.6 | 3.8  | 0.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 60°   | 99.0  | 16.9 | 3.4  | 0.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 62.5° | 163.6 | 15.0 | 3.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 65°   | 315.9 | 14.3 | 2.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 67.5° | 510.6 | 14.3 | 1.9  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 70°   | 536.8 | 14.3 | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 72.5° | 357.1 | 11.6 | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 75°   | 191.3 | 10.5 | 1.1  | 0.4  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 77.5° | 103.2 | 9.8  | 1.5  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 80°   | 45.4  | 7.1  | 1.9  | 1.1  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 82.5° | 18.0  | 4.9  | 2.3  | 1.9  | 1.5  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 85°   | 8.6   | 3.8  | 3.0  | 2.6  | 1.9  | 1.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 87.5° | 4.1   | 3.8  | 3.4  | 3.0  | 2.6  | 1.9  | 0.4  | 0.0  | 0.0  | 0.0  | 0.0  |
| 90°   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-5  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-735-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 3369     | CRI (Ra): | 70.1 |      |       |
| CIE u':                   | 0.2386   | R1:       | 66.6 | R9:  | -40.2 |
| CIE v':                   | 0.5156   | R2:       | 77.6 | R10: | 49.1  |
| Duv:                      | 0.0013   | R3:       | 88.5 | R11: | 66.3  |
| CIE x:                    | 0.4143   | R4:       | 69.5 | R12: | 45.7  |
| CIE y:                    | 0.3980   | R5:       | 66.4 | R13: | 68.0  |
| CIE z:                    | 0.1877   | R6:       | 69.6 | R14: | 93.4  |
| Peak Wavelength (nm):     | 590      | R7:       | 77.5 | R15: | 57.6  |
| Dominant Wavelength (nm): | 580      | R8:       | 44.9 |      |       |
| Purity:                   | 43.80166 |           |      |      |       |
| Rf:                       | 71.4     |           |      |      |       |
| Rg:                       | 96       |           |      |      |       |



### Test Conditions

Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |



REPORT NUMBER: SP1-2407-184-5

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 119                                  | NR                             | 620               | 778                                  | NR                             | 750               | 19                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 173                                  | NR                             | 625               | 711                                  | NR                             | 755               | 16                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 239                                  | NR                             | 630               | 648                                  | NR                             | 760               | 14                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 313                                  | NR                             | 635               | 582                                  | NR                             | 765               | 12                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 383                                  | NR                             | 640               | 520                                  | NR                             | 770               | 11                                   | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 448                                  | NR                             | 645               | 460                                  | NR                             | 775               | 9                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 2                                    | NR                             | 520               | 500                                  | NR                             | 650               | 406                                  | NR                             | 780               | 8                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 4                                    | NR                             | 525               | 539                                  | NR                             | 655               | 355                                  | NR                             | 785               | 7                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 6                                    | NR                             | 530               | 575                                  | NR                             | 660               | 309                                  | NR                             | 790               | 6                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 11                                   | NR                             | 535               | 606                                  | NR                             | 665               | 269                                  | NR                             | 795               | 5                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 22                                   | NR                             | 540               | 633                                  | NR                             | 670               | 231                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 45                                   | NR                             | 545               | 666                                  | NR                             | 675               | 199                                  | NR                             | 805               | 4                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 96                                   | NR                             | 550               | 701                                  | NR                             | 680               | 171                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 193                                  | NR                             | 555               | 743                                  | NR                             | 685               | 147                                  | NR                             | 815               | 3                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 341                                  | NR                             | 560               | 788                                  | NR                             | 690               | 126                                  | NR                             | 820               | 3                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 547                                  | NR                             | 565               | 837                                  | NR                             | 695               | 107                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 799                                  | NR                             | 570               | 887                                  | NR                             | 700               | 92                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 831                                  | NR                             | 575               | 931                                  | NR                             | 705               | 78                                   | NR                             | 835               | 2                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 461                                  | NR                             | 580               | 967                                  | NR                             | 710               | 67                                   | NR                             | 840               | 2                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 256                                  | NR                             | 585               | 990                                  | NR                             | 715               | 57                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 176                                  | NR                             | 590               | 1000                                 | NR                             | 720               | 49                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 107                                  | NR                             | 595               | 994                                  | NR                             | 725               | 42                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 74                                   | NR                             | 600               | 973                                  | NR                             | 730               | 36                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 67                                   | NR                             | 605               | 938                                  | NR                             | 735               | 31                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 68                                   | NR                             | 610               | 892                                  | NR                             | 740               | 26                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 84                                   | NR                             | 615               | 838                                  | NR                             | 745               | 22                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-5

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.29

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 119                      | NR            | 620    | 778                      | NR            | 750    | 19                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 173                      | NR            | 625    | 711                      | NR            | 755    | 16                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 239                      | NR            | 630    | 648                      | NR            | 760    | 14                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 313                      | NR            | 635    | 582                      | NR            | 765    | 12                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 383                      | NR            | 640    | 520                      | NR            | 770    | 11                       | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 448                      | NR            | 645    | 460                      | NR            | 775    | 9                        | NR            | 905    | 0                        | NR            |
| 390    | 2                        | NR            | 520    | 500                      | NR            | 650    | 406                      | NR            | 780    | 8                        | NR            | 910    | 0                        | NR            |
| 395    | 4                        | NR            | 525    | 539                      | NR            | 655    | 355                      | NR            | 785    | 7                        | NR            | 915    | 0                        | NR            |
| 400    | 6                        | NR            | 530    | 575                      | NR            | 660    | 309                      | NR            | 790    | 6                        | NR            | 920    | 0                        | NR            |
| 405    | 11                       | NR            | 535    | 606                      | NR            | 665    | 269                      | NR            | 795    | 5                        | NR            | 925    | 0                        | NR            |
| 410    | 22                       | NR            | 540    | 633                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 45                       | NR            | 545    | 666                      | NR            | 675    | 199                      | NR            | 805    | 4                        | NR            | 935    | 0                        | NR            |
| 420    | 96                       | NR            | 550    | 701                      | NR            | 680    | 171                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 193                      | NR            | 555    | 743                      | NR            | 685    | 147                      | NR            | 815    | 3                        | NR            | 945    | 0                        | NR            |
| 430    | 341                      | NR            | 560    | 788                      | NR            | 690    | 126                      | NR            | 820    | 3                        | NR            | 950    | 0                        | NR            |
| 435    | 547                      | NR            | 565    | 837                      | NR            | 695    | 107                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 799                      | NR            | 570    | 887                      | NR            | 700    | 92                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 831                      | NR            | 575    | 931                      | NR            | 705    | 78                       | NR            | 835    | 2                        | NR            | 965    | 0                        | NR            |
| 450    | 461                      | NR            | 580    | 967                      | NR            | 710    | 67                       | NR            | 840    | 2                        | NR            | 970    | 0                        | NR            |
| 455    | 256                      | NR            | 585    | 990                      | NR            | 715    | 57                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 176                      | NR            | 590    | 1000                     | NR            | 720    | 49                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 107                      | NR            | 595    | 994                      | NR            | 725    | 42                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 74                       | NR            | 600    | 973                      | NR            | 730    | 36                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 67                       | NR            | 605    | 938                      | NR            | 735    | 31                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 68                       | NR            | 610    | 892                      | NR            | 740    | 26                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 84                       | NR            | 615    | 838                      | NR            | 745    | 22                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-5

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.36


| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 119                         | NR               | 620       | 778                         | NR               | 750       | 19                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 173                         | NR               | 625       | 711                         | NR               | 755       | 16                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 239                         | NR               | 630       | 648                         | NR               | 760       | 14                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 313                         | NR               | 635       | 582                         | NR               | 765       | 12                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 383                         | NR               | 640       | 520                         | NR               | 770       | 11                          | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 448                         | NR               | 645       | 460                         | NR               | 775       | 9                           | NR               | 905       | 0                           | NR               |
| 390       | 2                           | NR               | 520       | 500                         | NR               | 650       | 406                         | NR               | 780       | 8                           | NR               | 910       | 0                           | NR               |
| 395       | 4                           | NR               | 525       | 539                         | NR               | 655       | 355                         | NR               | 785       | 7                           | NR               | 915       | 0                           | NR               |
| 400       | 6                           | NR               | 530       | 575                         | NR               | 660       | 309                         | NR               | 790       | 6                           | NR               | 920       | 0                           | NR               |
| 405       | 11                          | NR               | 535       | 606                         | NR               | 665       | 269                         | NR               | 795       | 5                           | NR               | 925       | 0                           | NR               |
| 410       | 22                          | NR               | 540       | 633                         | NR               | 670       | 231                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 45                          | NR               | 545       | 666                         | NR               | 675       | 199                         | NR               | 805       | 4                           | NR               | 935       | 0                           | NR               |
| 420       | 96                          | NR               | 550       | 701                         | NR               | 680       | 171                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 193                         | NR               | 555       | 743                         | NR               | 685       | 147                         | NR               | 815       | 3                           | NR               | 945       | 0                           | NR               |
| 430       | 341                         | NR               | 560       | 788                         | NR               | 690       | 126                         | NR               | 820       | 3                           | NR               | 950       | 0                           | NR               |
| 435       | 547                         | NR               | 565       | 837                         | NR               | 695       | 107                         | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 799                         | NR               | 570       | 887                         | NR               | 700       | 92                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 831                         | NR               | 575       | 931                         | NR               | 705       | 78                          | NR               | 835       | 2                           | NR               | 965       | 0                           | NR               |
| 450       | 461                         | NR               | 580       | 967                         | NR               | 710       | 67                          | NR               | 840       | 2                           | NR               | 970       | 0                           | NR               |
| 455       | 256                         | NR               | 585       | 990                         | NR               | 715       | 57                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 176                         | NR               | 590       | 1000                        | NR               | 720       | 49                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 107                         | NR               | 595       | 994                         | NR               | 725       | 42                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 74                          | NR               | 600       | 973                         | NR               | 730       | 36                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 67                          | NR               | 605       | 938                         | NR               | 735       | 31                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 68                          | NR               | 610       | 892                         | NR               | 740       | 26                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 84                          | NR               | 615       | 838                         | NR               | 745       | 22                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-5




TM-30-18

### Summary

$R_f = 71.4$   
 $R_g = 96$   
 $CIE R_a = 70.1$   
 $R_g = -40.2$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 57 | CES51 = 84 | CES76 = 50 |
| CES02 = 62 | CES27 = 80 | CES52 = 86 | CES77 = 74 |
| CES03 = 31 | CES28 = 81 | CES53 = 72 | CES78 = 54 |
| CES04 = 70 | CES29 = 50 | CES54 = 79 | CES79 = 81 |
| CES05 = 48 | CES30 = 55 | CES55 = 78 | CES80 = 79 |
| CES06 = 51 | CES31 = 56 | CES56 = 67 | CES81 = 74 |
| CES07 = 40 | CES32 = 54 | CES57 = 65 | CES82 = 91 |
| CES08 = 39 | CES33 = 60 | CES58 = 68 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 85 | CES84 = 89 |
| CES10 = 75 | CES35 = 83 | CES60 = 91 | CES85 = 83 |
| CES11 = 58 | CES36 = 88 | CES61 = 85 | CES86 = 66 |
| CES12 = 64 | CES37 = 78 | CES62 = 78 | CES87 = 77 |
| CES13 = 43 | CES38 = 64 | CES63 = 71 | CES88 = 75 |
| CES14 = 74 | CES39 = 92 | CES64 = 70 | CES89 = 68 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 72 |
| CES16 = 47 | CES41 = 81 | CES66 = 65 | CES91 = 95 |
| CES17 = 50 | CES42 = 79 | CES67 = 63 | CES92 = 62 |
| CES18 = 56 | CES43 = 71 | CES68 = 69 | CES93 = 78 |
| CES19 = 72 | CES44 = 98 | CES69 = 80 | CES94 = 51 |
| CES20 = 65 | CES45 = 80 | CES70 = 60 | CES95 = 70 |
| CES21 = 87 | CES46 = 75 | CES71 = 58 | CES96 = 76 |
| CES22 = 79 | CES47 = 71 | CES72 = 85 | CES97 = 82 |
| CES23 = 92 | CES48 = 61 | CES73 = 51 | CES98 = 72 |
| CES24 = 91 | CES49 = 74 | CES74 = 94 | CES99 = 60 |
| CES25 = 72 | CES50 = 83 | CES75 = 57 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)