

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1066378

Luminaire Tested: **NVN-SA6B-827-U-T4BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1066378
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: NVN-SA6B-827-U-T4BC
Description: Navion AREA AND ROADWAY LUMINAIRE 800mA 6xLight Square PACKAGE
80CRI 2700K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL
Light Source: (84) 2700K CCT, 80 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19600.8 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 211
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1066378

CATALOG NUMBER: NVN-SA6B-827-U-T4BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 21.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P1066378

CATALOG NUMBER: NVN-SA6B-827-U-T4BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1066378

CATALOG NUMBER: NVN-SA6B-827-U-T4BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	60.3	0.0	60.3
	% Fixture	0.3	0.0	0.3
Street Side	Lumens	19540.5	0.0	19540.5
	% Fixture	99.7	0.0	99.7
Total	Lumens	19600.8	0.0	19600.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.6	0.1
10°-20°	241.0	1.2
20°-30°	817.7	4.2
30°-40°	1921.8	9.8
40°-50°	3120.6	15.9
50°-60°	3954.4	20.2
60°-70°	5023.2	25.6
70°-80°	4081.3	20.8
80°-90°	420.2	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19600.8	100.0
0°-180°	19600.8	100.0



REPORT NUMBER: P1066378


CATALOG NUMBER: NVN-SA6B-827-U-T4BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1066.2	5.4			
FM	(30°-60°)	8985.2	45.8			
FH	(60°-80°)	9071.3	46.3			G4/12000
FVH	(80°-90°)	417.7	2.1			G3/500
BL	(0°-30°)	13.1	0.1	B0/110		
BM	(30°-60°)	11.6	0.1	B0/220		
BH	(60°-80°)	33.2	0.2	B0/110		G0/110
BVH	(80°-90°)	2.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type IV Short



REPORT NUMBER: P1066378

CATALOG NUMBER: NVN-SA6B-827-U-T4BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	39°	45°	55°	65°	75°	85°
0°	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4
2.5°	138.4	138.4	138.4	133.0	133.0	127.7	127.7	122.4	117.1	117.1	111.8
5°	260.8	266.1	250.1	218.2	196.9	186.3	175.6	149.0	133.0	122.4	111.8
7.5°	713.1	691.8	659.9	553.4	425.7	361.9	308.7	218.2	159.6	127.7	111.8
10°	1500.7	1442.1	1351.7	1208.0	957.9	856.8	665.2	399.1	223.5	143.7	111.8
12.5°	2203.1	2213.8	2102.0	1963.7	1660.3	1490.0	1229.3	750.3	351.2	170.3	111.8
15°	2735.3	2724.6	2682.1	2570.3	2298.9	2133.9	1899.8	1261.2	590.7	212.9	117.1
17.5°	3155.7	3113.1	3097.1	3049.3	2873.6	2783.2	2527.7	1857.2	936.6	287.4	122.4
20°	3576.1	3565.4	3549.5	3496.3	3379.2	3315.3	3118.4	2458.6	1394.2	409.8	133.0
22.5°	4188.1	4129.5	4140.2	4023.1	3927.3	3815.6	3655.9	3097.1	1921.1	585.4	149.0
25°	4906.5	4901.2	4816.0	4762.8	4603.1	4480.8	4267.9	3714.4	2506.5	846.1	165.0
27.5°	5752.6	5694.1	5656.8	5566.3	5401.4	5263.0	4970.3	4326.4	3139.7	1138.8	186.3
30°	6636.0	6636.0	6566.8	6428.4	6268.8	6098.5	5800.5	4970.3	3767.7	1511.3	212.9
32.5°	7668.4	7689.7	7519.4	7311.8	7104.3	6987.2	6598.7	5699.4	4369.0	1937.0	244.8
35°	8668.8	8642.2	8360.2	8131.3	7977.0	7849.3	7519.4	6497.6	5050.2	2432.0	287.4
37.5°	9626.7	9557.5	9089.2	8764.6	8695.4	8610.3	8280.3	7295.9	5726.0	2980.1	340.6
40°	10313.2	10206.7	9722.5	9275.5	9174.4	9126.5	8871.0	8019.6	6439.1	3592.1	409.8
42.5°	10611.2	10488.8	10153.5	9791.7	9568.2	9456.4	9232.9	8610.3	7152.2	4273.2	510.9
45°	10669.7	10573.9	10334.5	10249.3	9946.0	9775.7	9472.4	9030.7	7817.4	4949.0	649.2
47.5°	10456.9	10414.3	10270.6	10451.5	10297.2	10063.1	9695.9	9344.7	8408.1	5768.6	840.8
50°	9935.3	9903.4	9972.6	10446.2	10552.6	10286.6	9940.7	9589.4	8918.9	6614.7	1112.2
52.5°	9232.9	9227.6	9552.2	10307.9	10664.4	10499.4	10180.1	9834.2	9323.4	7434.2	1495.4
55°	8466.6	8557.1	9126.5	10180.1	10728.3	10653.8	10414.3	10052.4	9685.2	8195.2	2112.7
57.5°	8402.7	8365.5	8913.6	10126.9	10765.5	10808.1	10648.4	10281.2	9993.9	8817.8	2937.5
60°	9041.3	8956.2	9163.7	10238.7	10930.5	11005.0	10882.6	10456.9	10302.5	9307.4	4023.1
62.5°	9781.0	9701.2	9807.6	10669.7	11255.1	11361.5	11207.2	10637.8	10552.6	9648.0	5188.5
65°	10371.7	10307.9	10510.1	11313.6	11707.4	11797.9	11691.5	10973.1	10664.4	9924.7	6135.8
67.5°	10467.5	10387.7	10808.1	11744.7	12165.1	12228.9	12143.8	11297.7	10627.1	9946.0	6353.9
70°	10196.1	10126.9	10728.3	11883.0	12362.0	12415.2	12143.8	11143.3	10121.6	9403.2	5193.8
72.5°	9360.6	9413.8	10190.8	11547.8	12090.6	11845.8	11271.1	10366.4	9467.1	7971.7	3645.3
75°	8062.2	8120.7	9153.1	10627.1	10669.7	10371.7	10063.1	9536.2	8471.9	5252.4	2527.7
77.5°	5731.3	5523.8	7067.0	8775.2	8620.9	8812.5	8839.1	7934.4	7093.6	2735.3	1692.3
80°	564.1	478.9	888.7	2517.1	5561.0	6215.6	6471.0	6114.5	5231.1	1224.0	888.7
82.5°	122.4	122.4	133.0	143.7	223.5	335.3	1537.9	3767.7	3379.2	622.6	287.4
85°	69.2	69.2	85.1	101.1	133.0	149.0	175.6	234.1	910.0	223.5	53.2
87.5°	53.2	58.5	69.2	85.1	111.8	122.4	149.0	186.3	228.8	207.5	16.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1066378

CATALOG NUMBER: NVN-SA6B-827-U-T4BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4	106.4
2.5°	111.8	106.4	101.1	95.8	90.5	90.5	85.1	85.1	85.1	85.1	85.1
5°	106.4	101.1	95.8	85.1	79.8	74.5	69.2	69.2	69.2	69.2	69.2
7.5°	106.4	101.1	90.5	79.8	69.2	63.9	58.5	53.2	53.2	58.5	58.5
10°	106.4	95.8	79.8	69.2	58.5	53.2	47.9	42.6	42.6	42.6	42.6
12.5°	101.1	90.5	74.5	63.9	53.2	42.6	31.9	26.6	26.6	26.6	26.6
15°	95.8	85.1	69.2	53.2	37.3	26.6	21.3	16.0	16.0	16.0	16.0
17.5°	95.8	79.8	63.9	47.9	26.6	16.0	10.6	5.3	5.3	5.3	10.6
20°	95.8	79.8	58.5	37.3	16.0	10.6	10.6	5.3	0.0	5.3	5.3
22.5°	95.8	74.5	47.9	26.6	16.0	10.6	5.3	0.0	0.0	0.0	0.0
25°	101.1	74.5	42.6	21.3	10.6	5.3	0.0	0.0	0.0	0.0	0.0
27.5°	101.1	69.2	37.3	16.0	5.3	0.0	0.0	0.0	0.0	0.0	0.0
30°	106.4	69.2	31.9	10.6	5.3	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	106.4	63.9	21.3	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	106.4	58.5	16.0	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	106.4	53.2	16.0	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	111.8	47.9	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	117.1	42.6	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	122.4	37.3	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	138.4	37.3	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	159.6	37.3	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	191.6	37.3	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	250.1	31.9	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	361.9	31.9	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	606.7	31.9	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	1064.3	31.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1798.7	31.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2346.8	37.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1782.7	31.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	851.4	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	377.8	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	165.0	16.0	5.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	63.9	10.6	5.3	5.3	5.3	5.3	0.0	0.0	0.0	0.0	0.0
82.5°	26.6	10.6	5.3	5.3	5.3	5.3	5.3	0.0	0.0	0.0	0.0
85°	16.0	10.6	10.6	10.6	5.3	5.3	5.3	0.0	0.0	0.0	0.0
87.5°	10.6	10.6	10.6	10.6	10.6	5.3	5.3	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-8

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-827-U-5WQ

Data in this report applies to families of products including GSS-SB1A-827-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-827-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI
 2700K CCT 26 LEDS

Spectral Parameters

CCT (K): 2756
 CIE u' : 0.2599
 CIE v' : 0.5271
 Duv: 0.0006
 CIE x: 0.4563
 CIE y: 0.4112
 CIE z: 0.1325
 Peak Wavelength (nm): 609
 Dominant Wavelength (nm): 583
 Purity: 60.41121
 Rf: 82.2
 Rg: 99.9

CRI (Ra): 82.9
 R1: 81.6
 R2: 88.8
 R3: 96.0
 R4: 83.4
 R5: 81.4
 R6: 87.0
 R7: 84.0
 R8: 60.8
 R9: 10.8
 R10: 74.8
 R11: 84.3
 R12: 72.1
 R13: 82.9
 R14: 97.3
 R15: 73.7



Test Conditions

Stabilization Time: 29M
 Operation Time: 1H 29M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-8

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-8

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-8

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	158	NR	620	959	NR	750	35	NR	880	1	NR
365	0	NR	495	211	NR	625	918	NR	755	30	NR	885	1	NR
370	0	NR	500	264	NR	630	873	NR	760	26	NR	890	1	NR
375	0	NR	505	318	NR	635	816	NR	765	22	NR	895	1	NR
380	0	NR	510	363	NR	640	755	NR	770	19	NR	900	1	NR
385	0	NR	515	403	NR	645	689	NR	775	16	NR	905	1	NR
390	0	NR	520	435	NR	650	626	NR	780	14	NR	910	0	NR
395	1	NR	525	459	NR	655	564	NR	785	12	NR	915	0	NR
400	3	NR	530	481	NR	660	503	NR	790	10	NR	920	0	NR
405	6	NR	535	501	NR	665	447	NR	795	9	NR	925	0	NR
410	13	NR	540	519	NR	670	392	NR	800	8	NR	930	0	NR
415	26	NR	545	542	NR	675	343	NR	805	7	NR	935	0	NR
420	51	NR	550	565	NR	680	299	NR	810	6	NR	940	0	NR
425	93	NR	555	593	NR	685	260	NR	815	5	NR	945	0	NR
430	156	NR	560	624	NR	690	225	NR	820	4	NR	950	0	NR
435	250	NR	565	662	NR	695	194	NR	825	4	NR	955	0	NR
440	391	NR	570	707	NR	700	166	NR	830	3	NR	960	0	NR
445	460	NR	575	756	NR	705	143	NR	835	3	NR	965	0	NR
450	293	NR	580	810	NR	710	122	NR	840	2	NR	970	0	NR
455	188	NR	585	860	NR	715	105	NR	845	2	NR	975	0	NR
460	149	NR	590	910	NR	720	90	NR	850	2	NR	980	0	NR
465	103	NR	595	950	NR	725	77	NR	855	2	NR	985	0	NR
470	80	NR	600	980	NR	730	66	NR	860	1	NR	990	0	NR
475	82	NR	605	995	NR	735	56	NR	865	1	NR	995	0	NR
480	92	NR	610	998	NR	740	48	NR	870	1	NR	1000	0	NR
485	116	NR	615	985	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-8

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.2

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	158	NR	620	959	NR	750	35	NR	880	1	NR
365	0	NR	495	211	NR	625	918	NR	755	30	NR	885	1	NR
370	0	NR	500	264	NR	630	873	NR	760	26	NR	890	1	NR
375	0	NR	505	318	NR	635	816	NR	765	22	NR	895	1	NR
380	0	NR	510	363	NR	640	755	NR	770	19	NR	900	1	NR
385	0	NR	515	403	NR	645	689	NR	775	16	NR	905	1	NR
390	0	NR	520	435	NR	650	626	NR	780	14	NR	910	0	NR
395	1	NR	525	459	NR	655	564	NR	785	12	NR	915	0	NR
400	3	NR	530	481	NR	660	503	NR	790	10	NR	920	0	NR
405	6	NR	535	501	NR	665	447	NR	795	9	NR	925	0	NR
410	13	NR	540	519	NR	670	392	NR	800	8	NR	930	0	NR
415	26	NR	545	542	NR	675	343	NR	805	7	NR	935	0	NR
420	51	NR	550	565	NR	680	299	NR	810	6	NR	940	0	NR
425	93	NR	555	593	NR	685	260	NR	815	5	NR	945	0	NR
430	156	NR	560	624	NR	690	225	NR	820	4	NR	950	0	NR
435	250	NR	565	662	NR	695	194	NR	825	4	NR	955	0	NR
440	391	NR	570	707	NR	700	166	NR	830	3	NR	960	0	NR
445	460	NR	575	756	NR	705	143	NR	835	3	NR	965	0	NR
450	293	NR	580	810	NR	710	122	NR	840	2	NR	970	0	NR
455	188	NR	585	860	NR	715	105	NR	845	2	NR	975	0	NR
460	149	NR	590	910	NR	720	90	NR	850	2	NR	980	0	NR
465	103	NR	595	950	NR	725	77	NR	855	2	NR	985	0	NR
470	80	NR	600	980	NR	730	66	NR	860	1	NR	990	0	NR
475	82	NR	605	995	NR	735	56	NR	865	1	NR	995	0	NR
480	92	NR	610	998	NR	740	48	NR	870	1	NR	1000	0	NR
485	116	NR	615	985	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.16

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	158	NR	620	959	NR	750	35	NR	880	1	NR
365	0	NR	495	211	NR	625	918	NR	755	30	NR	885	1	NR
370	0	NR	500	264	NR	630	873	NR	760	26	NR	890	1	NR
375	0	NR	505	318	NR	635	816	NR	765	22	NR	895	1	NR
380	0	NR	510	363	NR	640	755	NR	770	19	NR	900	1	NR
385	0	NR	515	403	NR	645	689	NR	775	16	NR	905	1	NR
390	0	NR	520	435	NR	650	626	NR	780	14	NR	910	0	NR
395	1	NR	525	459	NR	655	564	NR	785	12	NR	915	0	NR
400	3	NR	530	481	NR	660	503	NR	790	10	NR	920	0	NR
405	6	NR	535	501	NR	665	447	NR	795	9	NR	925	0	NR
410	13	NR	540	519	NR	670	392	NR	800	8	NR	930	0	NR
415	26	NR	545	542	NR	675	343	NR	805	7	NR	935	0	NR
420	51	NR	550	565	NR	680	299	NR	810	6	NR	940	0	NR
425	93	NR	555	593	NR	685	260	NR	815	5	NR	945	0	NR
430	156	NR	560	624	NR	690	225	NR	820	4	NR	950	0	NR
435	250	NR	565	662	NR	695	194	NR	825	4	NR	955	0	NR
440	391	NR	570	707	NR	700	166	NR	830	3	NR	960	0	NR
445	460	NR	575	756	NR	705	143	NR	835	3	NR	965	0	NR
450	293	NR	580	810	NR	710	122	NR	840	2	NR	970	0	NR
455	188	NR	585	860	NR	715	105	NR	845	2	NR	975	0	NR
460	149	NR	590	910	NR	720	90	NR	850	2	NR	980	0	NR
465	103	NR	595	950	NR	725	77	NR	855	2	NR	985	0	NR
470	80	NR	600	980	NR	730	66	NR	860	1	NR	990	0	NR
475	82	NR	605	995	NR	735	56	NR	865	1	NR	995	0	NR
480	92	NR	610	998	NR	740	48	NR	870	1	NR	1000	0	NR
485	116	NR	615	985	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-8

TM-30-18

Summary

$R_f = 82.2$
 $R_g = 99.9$
 $CIE\ R_a = 82.9$
 $R_9 = 10.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 76	CES51 = 89	CES76 = 75
CES02 = 63	CES27 = 89	CES52 = 91	CES77 = 87
CES03 = 31	CES28 = 90	CES53 = 82	CES78 = 76
CES04 = 71	CES29 = 68	CES54 = 88	CES79 = 91
CES05 = 50	CES30 = 69	CES55 = 87	CES80 = 90
CES06 = 52	CES31 = 72	CES56 = 80	CES81 = 74
CES07 = 43	CES32 = 71	CES57 = 78	CES82 = 95
CES08 = 42	CES33 = 71	CES58 = 80	CES83 = 90
CES09 = 29	CES34 = 84	CES59 = 93	CES84 = 94
CES10 = 77	CES35 = 92	CES60 = 96	CES85 = 83
CES11 = 59	CES36 = 92	CES61 = 94	CES86 = 69
CES12 = 66	CES37 = 89	CES62 = 84	CES87 = 85
CES13 = 44	CES38 = 75	CES63 = 79	CES88 = 84
CES14 = 74	CES39 = 93	CES64 = 85	CES89 = 74
CES15 = 72	CES40 = 89	CES65 = 79	CES90 = 81
CES16 = 48	CES41 = 85	CES66 = 83	CES91 = 96
CES17 = 50	CES42 = 88	CES67 = 82	CES92 = 72
CES18 = 57	CES43 = 81	CES68 = 86	CES93 = 84
CES19 = 73	CES44 = 98	CES69 = 92	CES94 = 63
CES20 = 67	CES45 = 87	CES70 = 81	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 81	CES96 = 85
CES22 = 79	CES47 = 76	CES72 = 93	CES97 = 87
CES23 = 92	CES48 = 71	CES73 = 75	CES98 = 82
CES24 = 91	CES49 = 81	CES74 = 91	CES99 = 76
CES25 = 72	CES50 = 88	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)