

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1066103

Luminaire Tested: **NVN-SA3C-760-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1066103
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: NVN-SA3C-760-U-T2BC
Description: Navion AREA AND ROADWAY LUMINAIRE 1050mA 3xLight Square PACKAGE
70CRI 5700K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (42) 5700K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16324.7 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G3

Input Watts (W): 140.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1066103

CATALOG NUMBER: NVN-SA3C-760-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 23.4 fc
 Type II - Short - N/A

REPORT NUMBER: P1066103

CATALOG NUMBER: NVN-SA3C-760-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1066103

CATALOG NUMBER: NVN-SA3C-760-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	66.2	0.0	66.2
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	16258.5	0.0	16258.5
	% Fixture	99.6	0.0	99.6
Total	Lumens	16324.7	0.0	16324.7
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.2	0.1
10°-20°	160.4	1.0
20°-30°	532.8	3.3
30°-40°	1421.7	8.7
40°-50°	3613.5	22.1
50°-60°	5267.7	32.3
60°-70°	4068.8	24.9
70°-80°	1117.4	6.8
80°-90°	126.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16324.7	100.0
0°-180°	16324.7	100.0



REPORT NUMBER: P1066103


CATALOG NUMBER: NVN-SA3C-760-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	694.6	4.3			
FM	(30°-60°)	10281.0	63.0			
FH	(60°-80°)	5159.8	31.6			G3/7500
FVH	(80°-90°)	123.1	0.8			G2/225
BL	(0°-30°)	14.9	0.1	B0/110		
BM	(30°-60°)	21.9	0.1	B0/220		
BH	(60°-80°)	26.4	0.2	B0/110		G0/110
BVH	(80°-90°)	3.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G3

Type II Short



REPORT NUMBER: P1066103

CATALOG NUMBER: NVN-SA3C-760-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8
2.5°	143.8	143.8	143.8	139.3	134.8	134.8	130.3	125.8	125.8	116.8	112.3
5°	220.2	220.2	211.2	202.2	188.7	170.8	152.8	139.3	139.3	125.8	116.8
7.5°	431.4	444.9	404.4	355.0	287.6	242.7	193.2	161.8	157.3	134.8	116.8
10°	934.7	925.7	862.8	741.4	584.2	422.4	269.6	197.7	188.7	143.8	116.8
12.5°	1406.5	1420.0	1352.6	1217.8	1029.0	750.4	462.8	256.1	247.1	157.3	116.8
15°	1810.9	1810.9	1766.0	1698.6	1491.9	1199.8	745.9	382.0	350.5	170.8	112.3
17.5°	2089.5	2085.0	2067.1	2049.1	1927.8	1626.7	1141.4	611.1	539.2	202.2	112.3
20°	2404.1	2390.6	2413.1	2377.1	2282.7	2044.6	1559.3	907.7	840.3	256.1	112.3
22.5°	2732.1	2745.6	2763.6	2727.6	2624.3	2417.6	1999.6	1289.7	1217.8	355.0	116.8
25°	3150.0	3141.0	3181.5	3150.0	3019.7	2777.0	2413.1	1707.6	1604.2	494.3	125.8
27.5°	3662.3	3644.3	3671.3	3590.4	3419.6	3172.5	2781.5	2134.5	2013.1	710.0	143.8
30°	4340.8	4354.3	4233.0	4138.6	3895.9	3567.9	3190.4	2592.8	2467.0	966.1	161.8
32.5°	5410.3	5315.9	5127.2	4745.2	4426.2	4008.3	3599.4	2992.7	2880.4	1294.2	188.7
35°	7077.4	7095.4	6682.0	5738.3	5046.3	4561.0	4048.7	3433.1	3352.2	1667.1	224.7
37.5°	9108.5	9059.1	8695.1	7504.3	5954.0	5248.5	4561.0	3913.9	3797.1	2071.5	269.6
40°	11409.2	11202.5	10991.3	10182.5	7845.8	6111.3	5208.1	4471.1	4381.3	2538.9	341.5
42.5°	13251.6	13197.7	13233.6	12896.6	11000.3	7580.7	6066.3	5154.1	5046.3	3118.6	467.3
45°	14159.3	14082.9	14298.6	14550.2	14064.9	10708.2	7450.4	6025.9	5882.1	3801.6	660.6
47.5°	13916.7	13862.7	14325.6	14819.9	15466.9	14334.6	9710.7	7329.0	7081.9	4677.8	948.1
50°	12721.4	12725.8	13485.3	14406.5	15431.0	16172.4	13058.4	9113.0	8802.9	5841.7	1397.5
52.5°	11557.5	11593.5	12397.8	13741.4	14896.3	16388.1	15997.2	11517.1	11013.8	7212.2	1927.8
55°	10362.2	10380.2	11090.2	12982.0	14644.6	15745.5	17507.0	14613.2	14078.4	8919.8	2444.5
57.5°	9211.9	9211.9	9477.0	11157.6	14370.5	15687.1	17327.3	17444.1	17008.2	10870.0	2826.5
60°	6920.1	6965.1	7625.6	8802.9	12393.3	15772.5	16868.9	18347.3	18347.3	13575.1	3118.6
62.5°	3496.0	3563.4	4385.7	5531.6	8501.9	14595.2	16940.8	17893.5	17965.4	15961.2	3783.6
65°	1640.2	1716.6	2156.9	2965.8	4574.5	10272.3	16194.9	17507.0	17484.6	15507.4	5185.6
67.5°	1177.3	1199.8	1348.1	1730.0	2462.5	4502.6	12361.9	16352.2	16361.2	13175.2	5963.0
70°	1056.0	1056.0	1091.9	1204.3	1482.9	2013.1	6007.9	13242.6	13885.2	10173.5	5527.1
72.5°	1042.5	1033.5	1024.5	1029.0	1002.1	1011.1	2062.6	7477.3	8394.0	7117.8	4408.2
75°	1015.6	1015.6	1006.6	975.1	799.9	651.6	710.0	3024.2	3496.0	4754.2	3271.3
77.5°	804.4	885.2	979.6	921.2	732.5	489.8	413.4	876.3	1105.4	2916.3	2372.6
80°	373.0	377.5	373.0	390.9	467.3	350.5	305.6	426.9	431.4	1617.7	1469.4
82.5°	269.6	274.1	260.6	233.7	206.7	188.7	251.6	314.6	337.0	741.4	548.2
85°	80.9	76.4	89.9	121.3	143.8	166.3	211.2	265.1	278.6	274.1	80.9
87.5°	35.9	35.9	44.9	62.9	85.4	125.8	184.2	242.7	247.1	283.1	22.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1066103

CATALOG NUMBER: NVN-SA3C-760-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8	107.8
2.5°	112.3	107.8	103.4	98.9	94.4	89.9	85.4	85.4	89.9	89.9	89.9
5°	107.8	103.4	94.4	85.4	80.9	76.4	71.9	71.9	76.4	76.4	76.4
7.5°	107.8	98.9	89.9	80.9	71.9	67.4	62.9	62.9	62.9	67.4	67.4
10°	107.8	98.9	85.4	71.9	62.9	58.4	53.9	49.4	53.9	53.9	53.9
12.5°	103.4	94.4	80.9	67.4	53.9	44.9	40.4	40.4	40.4	40.4	40.4
15°	98.9	89.9	76.4	58.4	44.9	35.9	27.0	27.0	27.0	31.5	31.5
17.5°	94.4	85.4	67.4	44.9	31.5	22.5	18.0	18.0	18.0	22.5	22.5
20°	94.4	80.9	58.4	35.9	22.5	13.5	9.0	9.0	9.0	13.5	18.0
22.5°	94.4	80.9	53.9	27.0	13.5	9.0	4.5	4.5	4.5	4.5	4.5
25°	94.4	76.4	49.4	22.5	9.0	4.5	0.0	0.0	4.5	9.0	13.5
27.5°	94.4	71.9	40.4	13.5	9.0	4.5	0.0	4.5	9.0	9.0	9.0
30°	94.4	71.9	35.9	13.5	4.5	0.0	0.0	4.5	9.0	9.0	13.5
32.5°	98.9	67.4	31.5	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	103.4	62.9	27.0	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	112.3	62.9	18.0	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	125.8	67.4	18.0	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	157.3	71.9	13.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	220.2	89.9	13.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	323.5	134.8	13.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	471.8	184.2	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	579.7	184.2	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	575.2	116.8	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	440.4	80.9	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	373.0	58.4	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	449.4	44.9	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	799.9	40.4	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	1285.2	40.4	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1437.9	40.4	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1123.4	35.9	4.5	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	615.6	31.5	4.5	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	310.1	22.5	9.0	4.5	4.5	0.0	0.0	0.0	0.0	0.0	0.0
80°	130.3	18.0	9.0	4.5	4.5	4.5	0.0	0.0	0.0	0.0	0.0
82.5°	44.9	18.0	9.0	9.0	4.5	4.5	0.0	0.0	0.0	0.0	0.0
85°	22.5	13.5	13.5	9.0	9.0	4.5	4.5	0.0	0.0	0.0	0.0
87.5°	13.5	13.5	13.5	9.0	9.0	4.5	4.5	0.0	0.0	0.0	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ

Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-757-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.71

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7


TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $\text{CIE } R_a = 69.9$
 $R_g = -35.4$





Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)