

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1066352

Luminaire Tested: **NVN-SA5D-760-U-T4BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1066352
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: NVN-SA5D-760-U-T4BC
Description: Navion AREA AND ROADWAY LUMINAIRE 1200mA 5xLight Square PACKAGE
70CRI 5700K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL
Light Source: (70) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 30384.9 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G5

Input Watts (W): 269.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1066352

CATALOG NUMBER: NVN-SA5D-760-U-T4BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 33.1 fc
Type IV - Short - N/A

REPORT NUMBER: P1066352

CATALOG NUMBER: NVN-SA5D-760-U-T4BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1066352

CATALOG NUMBER: NVN-SA5D-760-U-T4BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	93.5	0.0	93.5
	% Fixture	0.3	0.0	0.3
Street Side	Lumens	30291.4	0.0	30291.4
	% Fixture	99.7	0.0	99.7
Total	Lumens	30384.9	0.0	30384.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.9	0.1
10°-20°	373.6	1.2
20°-30°	1267.6	4.2
30°-40°	2979.1	9.8
40°-50°	4837.5	15.9
50°-60°	6130.1	20.2
60°-70°	7786.8	25.6
70°-80°	6326.8	20.8
80°-90°	651.4	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	30384.9	100.0
0°-180°	30384.9	100.0



REPORT NUMBER: P1066352


CATALOG NUMBER: NVN-SA5D-760-U-T4BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1652.9	5.4			
FM	(30°-60°)	13928.8	45.8			
FH	(60°-80°)	14062.2	46.3			G5
FVH	(80°-90°)	647.5	2.1			G4/750
BL	(0°-30°)	20.2	0.1	B0/110		
BM	(30°-60°)	18.0	0.1	B0/220		
BH	(60°-80°)	51.4	0.2	B0/110		G0/110
BVH	(80°-90°)	3.9	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G5

Type IV Short





REPORT NUMBER: P1066352

CATALOG NUMBER: NVN-SA5D-760-U-T4BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	39°	45°	55°	65°	75°	85°
0°	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0
2.5°	214.5	214.5	214.5	206.2	206.2	198.0	198.0	189.7	181.5	181.5	173.2
5°	404.2	412.5	387.7	338.2	305.2	288.7	272.2	231.0	206.2	189.7	173.2
7.5°	1105.4	1072.4	1022.9	857.9	660.0	561.0	478.5	338.2	247.5	198.0	173.2
10°	2326.3	2235.6	2095.4	1872.6	1484.9	1328.2	1031.2	618.7	346.5	222.7	173.2
12.5°	3415.3	3431.8	3258.5	3044.0	2573.8	2309.8	1905.6	1163.2	544.5	264.0	173.2
15°	4240.2	4223.7	4157.7	3984.5	3563.8	3308.0	2945.0	1955.1	915.7	330.0	181.5
17.5°	4891.9	4825.9	4801.2	4726.9	4454.7	4314.4	3918.5	2879.0	1451.9	445.5	189.7
20°	5543.6	5527.1	5502.4	5419.9	5238.4	5139.4	4834.2	3811.2	2161.3	635.2	206.2
22.5°	6492.3	6401.6	6418.1	6236.6	6088.1	5914.8	5667.4	4801.2	2978.0	907.4	231.0
25°	7606.0	7597.7	7465.7	7383.2	7135.8	6946.0	6616.0	5758.1	3885.5	1311.7	255.7
27.5°	8917.6	8826.9	8769.1	8628.9	8373.2	8158.7	7705.0	6706.8	4867.2	1765.4	288.7
30°	10287.0	10287.0	10179.8	9965.3	9717.8	9453.8	8991.9	7705.0	5840.6	2342.8	330.0
32.5°	11887.4	11920.4	11656.4	11334.7	11013.0	10831.5	10229.3	8835.1	6772.8	3002.8	379.5
35°	13438.3	13397.1	12959.8	12605.1	12365.9	12167.9	11656.4	10072.5	7828.7	3770.0	445.5
37.5°	14923.2	14816.0	14090.0	13586.8	13479.6	13347.6	12836.1	11310.0	8876.4	4619.7	528.0
40°	15987.4	15822.4	15071.7	14378.7	14222.0	14147.8	13751.8	12431.9	9981.8	5568.4	635.2
42.5°	16449.4	16259.6	15739.9	15178.9	14832.5	14659.2	14312.8	13347.6	11087.2	6624.3	791.9
45°	16540.1	16391.6	16020.4	15888.4	15418.2	15154.2	14684.0	13999.3	12118.4	7672.0	1006.4
47.5°	16210.1	16144.1	15921.4	16201.9	15962.6	15599.7	15030.5	14486.0	13034.1	8942.4	1303.4
50°	15401.7	15352.2	15459.4	16193.6	16358.6	15946.1	15409.9	14865.5	13826.0	10254.0	1724.1
52.5°	14312.8	14304.5	14807.7	15979.1	16531.8	16276.1	15781.2	15244.9	14453.0	11524.4	2318.1
55°	13124.8	13265.1	14147.8	15781.2	16630.8	16515.4	16144.1	15583.2	15014.0	12704.1	3275.0
57.5°	13025.8	12968.1	13817.8	15698.7	16688.6	16754.6	16507.1	15937.9	15492.4	13669.3	4553.7
60°	14015.8	13883.8	14205.5	15871.9	16944.3	17059.8	16870.1	16210.1	15970.9	14428.2	6236.6
62.5°	15162.4	15038.7	15203.7	16540.1	17447.5	17612.5	17373.3	16490.6	16358.6	14956.2	8043.2
65°	16078.1	15979.1	16292.6	17538.3	18148.7	18289.0	18124.0	17010.3	16531.8	15385.2	9511.6
67.5°	16226.6	16102.9	16754.6	18206.5	18858.2	18957.2	18825.2	17513.5	16474.1	15418.2	9849.8
70°	15805.9	15698.7	16630.8	18421.0	19163.4	19245.9	18825.2	17274.3	15690.4	14576.7	8051.4
72.5°	14510.7	14593.2	15797.7	17901.3	18742.7	18363.2	17472.3	16069.9	14675.7	12357.6	5650.9
75°	12497.9	12588.6	14189.0	16474.1	16540.1	16078.1	15599.7	14783.0	13133.1	8142.2	3918.5
77.5°	8884.6	8562.9	10955.2	13603.3	13364.1	13661.0	13702.3	12299.9	10996.5	4240.2	2623.3
80°	874.4	742.4	1377.7	3902.0	8620.7	9635.3	10031.3	9478.6	8109.2	1897.4	1377.7
82.5°	189.7	189.7	206.2	222.7	346.5	519.7	2384.1	5840.6	5238.4	965.2	445.5
85°	107.2	107.2	132.0	156.7	206.2	231.0	272.2	363.0	1410.7	346.5	82.5
87.5°	82.5	90.7	107.2	132.0	173.2	189.7	231.0	288.7	354.7	321.7	24.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1066352

CATALOG NUMBER: NVN-SA5D-760-U-T4BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0	165.0
2.5°	173.2	165.0	156.7	148.5	140.2	140.2	132.0	132.0	132.0	132.0	132.0
5°	165.0	156.7	148.5	132.0	123.7	115.5	107.2	107.2	107.2	107.2	107.2
7.5°	165.0	156.7	140.2	123.7	107.2	99.0	90.7	82.5	82.5	90.7	90.7
10°	165.0	148.5	123.7	107.2	90.7	82.5	74.2	66.0	66.0	66.0	66.0
12.5°	156.7	140.2	115.5	99.0	82.5	66.0	49.5	41.2	41.2	41.2	41.2
15°	148.5	132.0	107.2	82.5	57.7	41.2	33.0	24.7	24.7	24.7	24.7
17.5°	148.5	123.7	99.0	74.2	41.2	24.7	16.5	8.2	8.2	8.2	16.5
20°	148.5	123.7	90.7	57.7	24.7	16.5	16.5	8.2	0.0	8.2	8.2
22.5°	148.5	115.5	74.2	41.2	24.7	16.5	8.2	0.0	0.0	0.0	0.0
25°	156.7	115.5	66.0	33.0	16.5	8.2	0.0	0.0	0.0	0.0	0.0
27.5°	156.7	107.2	57.7	24.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0
30°	165.0	107.2	49.5	16.5	8.2	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	165.0	99.0	33.0	16.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	165.0	90.7	24.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	165.0	82.5	24.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	173.2	74.2	16.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	181.5	66.0	16.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	189.7	57.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	214.5	57.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	247.5	57.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	297.0	57.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	387.7	49.5	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	561.0	49.5	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	940.4	49.5	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	1649.9	49.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	2788.3	49.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	3638.0	57.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	2763.6	49.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1319.9	33.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	585.7	33.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	255.7	24.7	8.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	99.0	16.5	8.2	8.2	8.2	8.2	0.0	0.0	0.0	0.0	0.0
82.5°	41.2	16.5	8.2	8.2	8.2	8.2	8.2	0.0	0.0	0.0	0.0
85°	24.7	16.5	16.5	16.5	8.2	8.2	8.2	0.0	0.0	0.0	0.0
87.5°	16.5	16.5	16.5	16.5	16.5	8.2	8.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-757-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7


TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $CIE R_a = 69.9$
 $R_g = -35.4$







Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)