

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1066115

Luminaire Tested: **NVN-SA6C-760-U-T2BC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1066115
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: NVN-SA6C-760-U-T2BC
Description: Navion AREA AND ROADWAY LUMINAIRE 1050mA 6xLight Square PACKAGE
70CRI 5700K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (84) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 32636.1 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 279.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1066115

CATALOG NUMBER: NVN-SA6C-760-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 46.8 fc
Type II - Short - N/A

REPORT NUMBER: P1066115

CATALOG NUMBER: NVN-SA6C-760-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1066115

CATALOG NUMBER: NVN-SA6C-760-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	132.3	0.0	132.3
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	32503.8	0.0	32503.8
	% Fixture	99.6	0.0	99.6
Total	Lumens	32636.1	0.0	32636.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.5	0.1
10°-20°	320.7	1.0
20°-30°	1065.2	3.3
30°-40°	2842.2	8.7
40°-50°	7224.1	22.1
50°-60°	10531.2	32.3
60°-70°	8134.3	24.9
70°-80°	2233.8	6.8
80°-90°	252.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	32636.1	100.0
0°-180°	32636.1	100.0



REPORT NUMBER: P1066115


CATALOG NUMBER: NVN-SA6C-760-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1388.6	4.3			
FM	(30°-60°)	20553.6	63.0			
FH	(60°-80°)	10315.4	31.6			G4/12000
FVH	(80°-90°)	246.2	0.8			G3/500
BL	(0°-30°)	29.7	0.1	B0/110		
BM	(30°-60°)	43.8	0.1	B0/220		
BH	(60°-80°)	52.8	0.2	B0/110		G0/110
BVH	(80°-90°)	6.0	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type II Short



REPORT NUMBER: P1066115

CATALOG NUMBER: NVN-SA6C-760-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6
2.5°	287.5	287.5	287.5	278.5	269.5	269.5	260.5	251.5	251.5	233.6	224.6
5°	440.2	440.2	422.2	404.3	377.3	341.4	305.4	278.5	278.5	251.5	233.6
7.5°	862.4	889.4	808.5	709.7	574.9	485.1	386.3	323.4	314.4	269.5	233.6
10°	1868.6	1850.6	1724.8	1482.3	1167.9	844.5	539.0	395.3	377.3	287.5	233.6
12.5°	2811.9	2838.8	2704.0	2434.5	2057.2	1500.3	925.3	512.1	494.1	314.4	233.6
15°	3620.4	3620.4	3530.5	3395.8	2982.5	2398.6	1491.3	763.6	700.7	341.4	224.6
17.5°	4177.3	4168.4	4132.4	4096.5	3853.9	3252.0	2281.8	1221.8	1078.0	404.3	224.6
20°	4806.2	4779.2	4824.2	4752.3	4563.6	4087.5	3117.3	1814.7	1679.9	512.1	224.6
22.5°	5462.0	5488.9	5524.9	5453.0	5246.4	4833.1	3997.7	2578.3	2434.5	709.7	233.6
25°	6297.5	6279.5	6360.4	6297.5	6036.9	5551.8	4824.2	3413.7	3207.1	988.2	251.5
27.5°	7321.6	7285.7	7339.6	7177.9	6836.5	6342.4	5560.8	4267.2	4024.6	1419.4	287.5
30°	8678.1	8705.1	8462.5	8273.8	7788.7	7132.9	6378.3	5183.5	4932.0	1931.5	323.4
32.5°	10816.2	10627.5	10250.2	9486.6	8848.8	8013.3	7195.8	5983.0	5758.5	2587.3	377.3
35°	14149.1	14185.0	13358.5	11472.0	10088.5	9118.3	8094.2	6863.4	6701.7	3332.9	449.2
37.5°	18209.7	18110.8	17383.2	15002.5	11903.2	10492.8	9118.3	7824.7	7591.1	4141.4	539.0
40°	22809.2	22396.0	21973.8	20356.7	15685.3	12217.6	10411.9	8938.6	8759.0	5075.7	682.7
42.5°	26492.5	26384.7	26456.5	25782.8	21991.7	15155.2	12127.8	10304.1	10088.5	6234.6	934.3
45°	28307.2	28154.4	28585.6	29088.7	28118.5	21407.8	14894.7	12046.9	11759.5	7600.1	1320.6
47.5°	27822.0	27714.2	28639.6	29627.7	30921.4	28657.5	19413.4	14652.2	14158.1	9351.9	1895.5
50°	25432.4	25441.4	26959.6	28801.3	30849.5	32331.8	26106.2	18218.6	17598.8	11678.6	2793.9
52.5°	23105.7	23177.6	24785.6	27471.7	29780.5	32763.0	31981.4	23024.8	22018.7	14418.6	3853.9
55°	20716.1	20752.0	22171.4	25953.5	29277.4	31478.4	34999.9	29214.5	28145.5	17832.3	4887.1
57.5°	18416.3	18416.3	18946.3	22306.1	28729.4	31361.6	34640.6	34874.1	34002.7	21731.2	5650.7
60°	13834.7	13924.5	15245.1	17598.8	24776.6	31532.3	33724.2	36679.8	36679.8	27139.3	6234.6
62.5°	6989.2	7124.0	8767.9	11058.7	16996.9	29178.6	33868.0	35772.5	35916.2	31909.6	7564.1
65°	3279.0	3431.7	4312.1	5929.1	9145.3	20536.4	32376.7	34999.9	34955.0	31002.2	10367.0
67.5°	2353.7	2398.6	2695.1	3458.7	4923.0	9001.5	24713.7	32691.1	32709.1	26339.8	11921.2
70°	2111.1	2111.1	2183.0	2407.6	2964.6	4024.6	12011.0	26474.5	27759.2	20338.8	11049.8
72.5°	2084.2	2066.2	2048.2	2057.2	2003.3	2021.3	4123.4	14948.6	16781.3	14229.9	8812.9
75°	2030.3	2030.3	2012.3	1949.4	1599.1	1302.6	1419.4	6045.9	6989.2	9504.6	6540.0
77.5°	1608.1	1769.8	1958.4	1841.6	1464.3	979.2	826.5	1751.8	2210.0	5830.3	4743.3
80°	745.6	754.6	745.6	781.6	934.3	700.7	610.9	853.4	862.4	3234.1	2937.6
82.5°	539.0	548.0	521.0	467.1	413.2	377.3	503.1	628.8	673.8	1482.3	1096.0
85°	161.7	152.7	179.7	242.6	287.5	332.4	422.2	530.0	557.0	548.0	161.7
87.5°	71.9	71.9	89.8	125.8	170.7	251.5	368.3	485.1	494.1	566.0	44.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1066115

CATALOG NUMBER: NVN-SA6C-760-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6	215.6
2.5°	224.6	215.6	206.6	197.6	188.7	179.7	170.7	170.7	179.7	179.7	179.7
5°	215.6	206.6	188.7	170.7	161.7	152.7	143.7	143.7	152.7	152.7	152.7
7.5°	215.6	197.6	179.7	161.7	143.7	134.8	125.8	125.8	125.8	134.8	134.8
10°	215.6	197.6	170.7	143.7	125.8	116.8	107.8	98.8	107.8	107.8	107.8
12.5°	206.6	188.7	161.7	134.8	107.8	89.8	80.9	80.9	80.9	80.9	80.9
15°	197.6	179.7	152.7	116.8	89.8	71.9	53.9	53.9	53.9	62.9	62.9
17.5°	188.7	170.7	134.8	89.8	62.9	44.9	35.9	35.9	35.9	44.9	44.9
20°	188.7	161.7	116.8	71.9	44.9	27.0	18.0	18.0	18.0	27.0	35.9
22.5°	188.7	161.7	107.8	53.9	27.0	18.0	9.0	9.0	9.0	9.0	9.0
25°	188.7	152.7	98.8	44.9	18.0	9.0	0.0	0.0	9.0	18.0	27.0
27.5°	188.7	143.7	80.9	27.0	18.0	9.0	0.0	9.0	18.0	18.0	18.0
30°	188.7	143.7	71.9	27.0	9.0	0.0	0.0	9.0	18.0	18.0	27.0
32.5°	197.6	134.8	62.9	18.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	206.6	125.8	53.9	18.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	224.6	125.8	35.9	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	251.5	134.8	35.9	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	314.4	143.7	27.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	440.2	179.7	27.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	646.8	269.5	27.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	943.3	368.3	18.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	1158.9	368.3	18.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	1149.9	233.6	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	880.4	161.7	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	745.6	116.8	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	898.4	89.8	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1599.1	80.9	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2569.3	80.9	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	2874.7	80.9	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	2245.9	71.9	9.0	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	1230.7	62.9	9.0	9.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	619.9	44.9	18.0	9.0	9.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	260.5	35.9	18.0	9.0	9.0	9.0	0.0	0.0	0.0	0.0	0.0
82.5°	89.8	35.9	18.0	18.0	9.0	9.0	0.0	0.0	0.0	0.0	0.0
85°	44.9	27.0	27.0	18.0	18.0	9.0	9.0	0.0	0.0	0.0	0.0
87.5°	27.0	27.0	27.0	18.0	18.0	9.0	9.0	0.0	0.0	0.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ

Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-757-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.71

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $CIE\ R_a = 69.9$
 $R_g = -35.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)