

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1066854

Luminaire Tested: **NVN-SA5B-827-U-LBC**

Issue Date: 08/07/2025

Test Information

Test Method: LM-79-08
Report Number: P1066854
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/07/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: NVN-SA5B-827-U-LBC
Description: Navion AREA AND ROADWAY LUMINAIRE 800mA 5xLight Square PACKAGE
80CRI 2700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL
Light Source: (70) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14096.1 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G3

Input Watts (W): 178.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1066854

CATALOG NUMBER: NVN-SA5B-827-U-LBC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 41.9 fc
 Type III - Short - N/A

REPORT NUMBER: P1066854

CATALOG NUMBER: NVN-SA5B-827-U-LBC

Luminous Intensity Polar Plot



REPORT NUMBER: P1066854

CATALOG NUMBER: NVN-SA5B-827-U-LBC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	67.9	0.0	67.9
	% Fixture	0.5	0.0	0.5
Street Side	Lumens	14028.2	0.0	14028.2
	% Fixture	99.5	0.0	99.5
Total	Lumens	14096.1	0.0	14096.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.1	0.0
10°-20°	20.6	0.1
20°-30°	262.9	1.9
30°-40°	886.5	6.3
40°-50°	2677.5	19.0
50°-60°	4726.4	33.5
60°-70°	4161.7	29.5
70°-80°	1324.7	9.4
80°-90°	31.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14096.1	100.0
0°-180°	14096.1	100.0



REPORT NUMBER: P1066854


CATALOG NUMBER: NVN-SA5B-827-U-LBC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	280.0	2.0			
FM	(30°-60°)	8262.7	58.6			
FH	(60°-80°)	5455.3	38.7			G3/7500
FVH	(80°-90°)	30.2	0.2			G1/100
BL	(0°-30°)	7.6	0.1	B0/110		
BM	(30°-60°)	27.7	0.2	B0/220		
BH	(60°-80°)	31.1	0.2	B0/110		G0/110
BVH	(80°-90°)	1.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G3

Type III Short



REPORT NUMBER: P1066854

CATALOG NUMBER: NVN-SA5B-827-U-LBC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	42°	45°	55°	65°	75°	85°
0°	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8
2.5°	61.9	61.9	57.5	53.0	48.6	44.2	44.2	44.2	39.8	39.8	35.4
5°	70.7	70.7	66.3	61.9	61.9	57.5	57.5	53.0	48.6	48.6	44.2
7.5°	75.1	75.1	75.1	75.1	70.7	70.7	70.7	66.3	61.9	57.5	53.0
10°	79.6	84.0	88.4	88.4	88.4	88.4	88.4	84.0	75.1	70.7	61.9
12.5°	88.4	92.8	101.7	110.5	110.5	114.9	110.5	106.1	97.2	84.0	70.7
15°	97.2	106.1	119.3	137.0	154.7	159.1	159.1	145.8	128.2	101.7	84.0
17.5°	110.5	123.7	159.1	216.6	278.4	327.1	327.1	291.7	203.3	132.6	97.2
20°	119.3	145.8	256.3	521.5	795.5	998.8	959.1	848.6	455.2	207.7	106.1
22.5°	132.6	185.6	543.6	1370.1	2121.4	2492.7	2404.3	1825.3	1020.9	371.2	128.2
25°	150.3	269.6	1078.4	2567.8	3942.3	4344.5	4287.0	3407.5	1860.7	623.2	163.5
27.5°	185.6	397.8	1728.1	3893.7	5816.2	6160.9	6138.8	4989.7	2974.4	1003.2	212.1
30°	234.2	579.0	2563.4	5290.3	7058.1	7407.2	7296.8	6147.7	4013.0	1533.6	274.0
32.5°	291.7	808.8	3319.1	6320.0	8202.8	8662.4	8529.8	7155.3	4848.3	1984.4	406.6
35°	380.1	1034.2	4066.0	7230.5	9524.2	10107.6	9886.6	8193.9	5568.7	2492.7	490.6
37.5°	424.3	1166.8	4751.1	8220.5	11009.2	11804.7	11636.8	9506.6	6302.3	3142.3	601.1
40°	428.7	1325.9	5462.6	9511.0	13108.5	14527.2	14226.7	11760.6	7668.0	3977.6	773.4
42.5°	442.0	1564.5	6386.3	11711.9	17232.0	19269.5	18929.1	15906.1	10766.1	5652.7	1096.1
45°	503.8	2015.3	8269.1	15826.6	22893.5	25881.2	25487.8	21682.6	15092.9	8803.8	1869.5
47.5°	720.4	3031.8	11570.5	20268.3	28683.2	31065.4	30968.1	26234.7	19013.1	12034.6	3168.9
50°	1157.9	4653.8	15327.2	24002.8	32369.1	34415.4	34172.3	28135.2	21249.4	14239.9	4061.6
52.5°	1546.9	6205.1	17687.2	25377.3	33469.6	35909.2	35613.1	28829.0	21837.2	14889.6	4309.1
55°	1644.1	6766.4	18390.0	25801.6	34198.9	37173.2	36744.5	29293.1	21912.4	14425.6	3898.1
57.5°	1595.5	6236.1	17934.7	26217.1	35215.4	38472.6	37902.5	30199.1	22164.3	13638.9	3244.0
59°	1511.5	5582.0	17651.9	26548.5	35776.7	38675.9	38141.1	30398.0	22332.2	13280.9	2846.2
60°	1414.3	5140.0	17430.9	26765.1	35741.3	38357.7	37805.3	30305.2	22398.5	12971.5	2656.2
62.5°	1091.6	4101.4	17112.7	26610.4	33509.4	35454.0	35140.2	28033.5	21426.2	11981.5	2094.9
65°	848.6	3137.9	15945.9	23733.2	28515.3	29823.5	29726.2	23737.7	18032.0	10328.6	1511.5
67.5°	671.8	2289.4	13484.2	19220.8	22942.1	24802.8	24732.1	19269.5	13687.5	7893.4	1087.2
70°	548.0	1630.8	9245.8	14491.9	18350.2	20692.6	20590.9	15508.4	10143.0	5007.4	791.1
72.5°	464.1	1043.0	5608.5	10925.2	15313.9	16653.0	16356.9	12511.9	7376.3	2726.9	627.6
75°	393.3	640.8	2779.9	6810.6	9122.1	9113.2	8817.1	6625.0	3960.0	1334.7	499.4
77.5°	318.2	450.8	1091.6	1869.5	2877.2	3562.2	3504.7	2346.8	1184.5	388.9	309.4
80°	207.7	212.1	291.7	512.7	791.1	875.1	994.4	716.0	344.7	185.6	128.2
82.5°	92.8	101.7	132.6	167.9	167.9	154.7	137.0	101.7	75.1	61.9	30.9
85°	22.1	30.9	22.1	26.5	22.1	17.7	17.7	8.8	0.0	0.0	0.0
87.5°	4.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1066854

CATALOG NUMBER: NVN-SA5B-827-U-LBC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8
2.5°	35.4	35.4	35.4	30.9	30.9	30.9	26.5	26.5	26.5	22.1	22.1
5°	44.2	39.8	35.4	35.4	30.9	30.9	26.5	22.1	22.1	22.1	17.7
7.5°	48.6	44.2	39.8	35.4	30.9	26.5	26.5	22.1	17.7	17.7	17.7
10°	57.5	53.0	44.2	35.4	30.9	26.5	22.1	22.1	17.7	13.3	13.3
12.5°	66.3	57.5	48.6	39.8	30.9	26.5	22.1	22.1	17.7	13.3	8.8
15°	75.1	66.3	53.0	39.8	30.9	26.5	22.1	22.1	13.3	8.8	4.4
17.5°	84.0	70.7	53.0	44.2	30.9	26.5	22.1	17.7	8.8	4.4	0.0
20°	88.4	75.1	57.5	44.2	30.9	26.5	22.1	13.3	4.4	0.0	0.0
22.5°	97.2	84.0	61.9	44.2	30.9	22.1	13.3	4.4	0.0	0.0	0.0
25°	114.9	88.4	61.9	44.2	30.9	22.1	8.8	0.0	0.0	0.0	0.0
27.5°	128.2	97.2	61.9	44.2	30.9	17.7	4.4	0.0	0.0	0.0	0.0
30°	150.3	106.1	66.3	44.2	30.9	13.3	4.4	0.0	0.0	0.0	0.0
32.5°	185.6	114.9	66.3	44.2	26.5	13.3	0.0	0.0	0.0	0.0	0.0
35°	225.4	132.6	66.3	44.2	26.5	13.3	0.0	0.0	0.0	0.0	0.0
37.5°	229.8	141.4	66.3	44.2	26.5	8.8	0.0	0.0	0.0	0.0	0.0
40°	238.7	132.6	70.7	44.2	26.5	8.8	0.0	0.0	0.0	0.0	0.0
42.5°	274.0	123.7	75.1	44.2	26.5	8.8	0.0	0.0	0.0	0.0	0.0
45°	406.6	128.2	75.1	48.6	26.5	13.3	0.0	0.0	0.0	0.0	0.0
47.5°	707.1	132.6	70.7	48.6	26.5	13.3	0.0	0.0	0.0	0.0	0.0
50°	906.0	154.7	70.7	53.0	30.9	8.8	0.0	0.0	0.0	0.0	0.0
52.5°	963.5	181.2	70.7	57.5	39.8	4.4	0.0	0.0	0.0	0.0	0.0
55°	937.0	212.1	75.1	61.9	48.6	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	866.2	229.8	79.6	66.3	53.0	0.0	0.0	0.0	0.0	0.0	0.0
59°	791.1	243.1	92.8	70.7	53.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	729.2	256.3	97.2	75.1	53.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	587.8	274.0	106.1	88.4	44.2	0.0	0.0	0.0	0.0	0.0	0.0
65°	512.7	287.3	110.5	97.2	39.8	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	468.5	296.1	119.3	101.7	35.4	0.0	0.0	0.0	0.0	0.0	0.0
70°	433.1	291.7	128.2	97.2	30.9	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	393.3	278.4	154.7	88.4	26.5	0.0	0.0	0.0	0.0	0.0	0.0
75°	353.6	251.9	167.9	79.6	17.7	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	256.3	212.1	154.7	70.7	8.8	0.0	0.0	0.0	0.0	0.0	0.0
80°	110.5	114.9	110.5	53.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	22.1	26.5	22.1	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1066854

CATALOG NUMBER: NVN-SA5B-827-U-LBC

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8
2.5°	22.1	22.1	22.1	22.1	26.5	26.5	35.4	44.2	53.0	57.5	57.5
5°	17.7	17.7	17.7	17.7	17.7	22.1	26.5	35.4	48.6	53.0	53.0
7.5°	13.3	13.3	13.3	13.3	13.3	13.3	22.1	30.9	44.2	48.6	53.0
10°	13.3	8.8	8.8	4.4	4.4	8.8	13.3	26.5	39.8	44.2	48.6
12.5°	8.8	4.4	4.4	0.0	0.0	4.4	8.8	22.1	35.4	39.8	44.2
15°	4.4	0.0	0.0	0.0	0.0	0.0	4.4	17.7	30.9	35.4	44.2
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	13.3	26.5	35.4	39.8
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.8	22.1	30.9	35.4
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	17.7	26.5	30.9
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	13.3	17.7	22.1
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.8	13.3	17.7
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.8	13.3	17.7
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8	13.3
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8	13.3
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8	8.8
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	4.4
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	4.4
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
59°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	4.4
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	8.8
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	4.4
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	4.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	4.4	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1066854

CATALOG NUMBER: NVN-SA5B-827-U-LBC

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	318°	325°	335°	345°	355°	360°
0°	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8
2.5°	61.9	61.9	57.5	53.0	53.0	53.0	57.5	61.9	61.9	61.9
5°	57.5	57.5	53.0	53.0	53.0	53.0	57.5	66.3	70.7	70.7
7.5°	57.5	57.5	53.0	53.0	53.0	53.0	57.5	66.3	70.7	75.1
10°	53.0	53.0	53.0	53.0	48.6	53.0	57.5	66.3	79.6	79.6
12.5°	53.0	53.0	53.0	53.0	48.6	53.0	61.9	70.7	84.0	88.4
15°	53.0	53.0	53.0	48.6	48.6	53.0	61.9	75.1	88.4	97.2
17.5°	48.6	53.0	53.0	48.6	48.6	53.0	61.9	75.1	97.2	110.5
20°	44.2	48.6	53.0	48.6	48.6	48.6	61.9	75.1	101.7	119.3
22.5°	39.8	44.2	48.6	48.6	44.2	48.6	61.9	79.6	110.5	132.6
25°	35.4	39.8	39.8	44.2	44.2	48.6	61.9	79.6	114.9	150.3
27.5°	26.5	30.9	35.4	39.8	39.8	48.6	61.9	84.0	123.7	185.6
30°	22.1	26.5	30.9	35.4	39.8	48.6	61.9	84.0	132.6	234.2
32.5°	22.1	26.5	30.9	35.4	39.8	44.2	61.9	88.4	145.8	291.7
35°	17.7	22.1	26.5	35.4	35.4	44.2	61.9	88.4	159.1	380.1
37.5°	17.7	22.1	26.5	35.4	35.4	44.2	61.9	88.4	194.5	424.3
40°	13.3	17.7	22.1	35.4	35.4	44.2	66.3	92.8	198.9	428.7
42.5°	13.3	17.7	22.1	30.9	35.4	44.2	66.3	92.8	185.6	442.0
45°	13.3	17.7	22.1	35.4	39.8	48.6	66.3	97.2	181.2	503.8
47.5°	13.3	17.7	22.1	35.4	44.2	48.6	66.3	97.2	185.6	720.4
50°	13.3	17.7	22.1	35.4	48.6	48.6	66.3	97.2	203.3	1157.9
52.5°	8.8	13.3	17.7	30.9	39.8	53.0	70.7	92.8	216.6	1546.9
55°	8.8	8.8	13.3	26.5	35.4	57.5	75.1	92.8	251.9	1644.1
57.5°	8.8	8.8	13.3	22.1	30.9	61.9	79.6	92.8	291.7	1595.5
59°	8.8	8.8	8.8	22.1	26.5	61.9	79.6	97.2	296.1	1511.5
60°	8.8	8.8	8.8	17.7	26.5	61.9	84.0	101.7	300.5	1414.3
62.5°	4.4	4.4	4.4	17.7	22.1	61.9	92.8	123.7	309.4	1091.6
65°	8.8	8.8	4.4	13.3	22.1	53.0	106.1	132.6	313.8	848.6
67.5°	8.8	8.8	8.8	17.7	22.1	53.0	110.5	137.0	313.8	671.8
70°	8.8	8.8	8.8	17.7	26.5	53.0	110.5	141.4	309.4	548.0
72.5°	8.8	8.8	8.8	17.7	26.5	48.6	101.7	145.8	296.1	464.1
75°	8.8	8.8	8.8	13.3	22.1	44.2	97.2	159.1	269.6	393.3
77.5°	8.8	8.8	8.8	8.8	17.7	35.4	88.4	176.8	238.7	318.2
80°	13.3	8.8	8.8	8.8	13.3	30.9	84.0	172.4	198.9	207.7
82.5°	13.3	8.8	8.8	4.4	8.8	22.1	66.3	132.6	101.7	92.8
85°	8.8	8.8	8.8	4.4	4.4	13.3	30.9	39.8	30.9	22.1
87.5°	8.8	8.8	8.8	4.4	4.4	4.4	4.4	4.4	4.4	4.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-8

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-827-U-5WQ

Data in this report applies to families of products including GSS-SB1A-827-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-827-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI
 2700K CCT 26 LEDS

Spectral Parameters

CCT (K): 2756
 CIE u' : 0.2599
 CIE v' : 0.5271
 Duv: 0.0006
 CIE x: 0.4563
 CIE y: 0.4112
 CIE z: 0.1325
 Peak Wavelength (nm): 609
 Dominant Wavelength (nm): 583
 Purity: 60.41121
 R_f: 82.2
 R_g: 99.9

CRI (Ra): 82.9
 R1: 81.6
 R2: 88.8
 R3: 96.0
 R4: 83.4
 R5: 81.4
 R6: 87.0
 R7: 84.0
 R8: 60.8
 R9: 10.8
 R10: 74.8
 R11: 84.3
 R12: 72.1
 R13: 82.9
 R14: 97.3
 R15: 73.7



Test Conditions


Stabilization Time: 29M
 Operation Time: 1H 29M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-8

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-8

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-8

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	158	NR	620	959	NR	750	35	NR	880	1	NR
365	0	NR	495	211	NR	625	918	NR	755	30	NR	885	1	NR
370	0	NR	500	264	NR	630	873	NR	760	26	NR	890	1	NR
375	0	NR	505	318	NR	635	816	NR	765	22	NR	895	1	NR
380	0	NR	510	363	NR	640	755	NR	770	19	NR	900	1	NR
385	0	NR	515	403	NR	645	689	NR	775	16	NR	905	1	NR
390	0	NR	520	435	NR	650	626	NR	780	14	NR	910	0	NR
395	1	NR	525	459	NR	655	564	NR	785	12	NR	915	0	NR
400	3	NR	530	481	NR	660	503	NR	790	10	NR	920	0	NR
405	6	NR	535	501	NR	665	447	NR	795	9	NR	925	0	NR
410	13	NR	540	519	NR	670	392	NR	800	8	NR	930	0	NR
415	26	NR	545	542	NR	675	343	NR	805	7	NR	935	0	NR
420	51	NR	550	565	NR	680	299	NR	810	6	NR	940	0	NR
425	93	NR	555	593	NR	685	260	NR	815	5	NR	945	0	NR
430	156	NR	560	624	NR	690	225	NR	820	4	NR	950	0	NR
435	250	NR	565	662	NR	695	194	NR	825	4	NR	955	0	NR
440	391	NR	570	707	NR	700	166	NR	830	3	NR	960	0	NR
445	460	NR	575	756	NR	705	143	NR	835	3	NR	965	0	NR
450	293	NR	580	810	NR	710	122	NR	840	2	NR	970	0	NR
455	188	NR	585	860	NR	715	105	NR	845	2	NR	975	0	NR
460	149	NR	590	910	NR	720	90	NR	850	2	NR	980	0	NR
465	103	NR	595	950	NR	725	77	NR	855	2	NR	985	0	NR
470	80	NR	600	980	NR	730	66	NR	860	1	NR	990	0	NR
475	82	NR	605	995	NR	735	56	NR	865	1	NR	995	0	NR
480	92	NR	610	998	NR	740	48	NR	870	1	NR	1000	0	NR
485	116	NR	615	985	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-8

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.2

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	158	NR	620	959	NR	750	35	NR	880	1	NR
365	0	NR	495	211	NR	625	918	NR	755	30	NR	885	1	NR
370	0	NR	500	264	NR	630	873	NR	760	26	NR	890	1	NR
375	0	NR	505	318	NR	635	816	NR	765	22	NR	895	1	NR
380	0	NR	510	363	NR	640	755	NR	770	19	NR	900	1	NR
385	0	NR	515	403	NR	645	689	NR	775	16	NR	905	1	NR
390	0	NR	520	435	NR	650	626	NR	780	14	NR	910	0	NR
395	1	NR	525	459	NR	655	564	NR	785	12	NR	915	0	NR
400	3	NR	530	481	NR	660	503	NR	790	10	NR	920	0	NR
405	6	NR	535	501	NR	665	447	NR	795	9	NR	925	0	NR
410	13	NR	540	519	NR	670	392	NR	800	8	NR	930	0	NR
415	26	NR	545	542	NR	675	343	NR	805	7	NR	935	0	NR
420	51	NR	550	565	NR	680	299	NR	810	6	NR	940	0	NR
425	93	NR	555	593	NR	685	260	NR	815	5	NR	945	0	NR
430	156	NR	560	624	NR	690	225	NR	820	4	NR	950	0	NR
435	250	NR	565	662	NR	695	194	NR	825	4	NR	955	0	NR
440	391	NR	570	707	NR	700	166	NR	830	3	NR	960	0	NR
445	460	NR	575	756	NR	705	143	NR	835	3	NR	965	0	NR
450	293	NR	580	810	NR	710	122	NR	840	2	NR	970	0	NR
455	188	NR	585	860	NR	715	105	NR	845	2	NR	975	0	NR
460	149	NR	590	910	NR	720	90	NR	850	2	NR	980	0	NR
465	103	NR	595	950	NR	725	77	NR	855	2	NR	985	0	NR
470	80	NR	600	980	NR	730	66	NR	860	1	NR	990	0	NR
475	82	NR	605	995	NR	735	56	NR	865	1	NR	995	0	NR
480	92	NR	610	998	NR	740	48	NR	870	1	NR	1000	0	NR
485	116	NR	615	985	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-8

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.16


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	158	NR	620	959	NR	750	35	NR	880	1	NR
365	0	NR	495	211	NR	625	918	NR	755	30	NR	885	1	NR
370	0	NR	500	264	NR	630	873	NR	760	26	NR	890	1	NR
375	0	NR	505	318	NR	635	816	NR	765	22	NR	895	1	NR
380	0	NR	510	363	NR	640	755	NR	770	19	NR	900	1	NR
385	0	NR	515	403	NR	645	689	NR	775	16	NR	905	1	NR
390	0	NR	520	435	NR	650	626	NR	780	14	NR	910	0	NR
395	1	NR	525	459	NR	655	564	NR	785	12	NR	915	0	NR
400	3	NR	530	481	NR	660	503	NR	790	10	NR	920	0	NR
405	6	NR	535	501	NR	665	447	NR	795	9	NR	925	0	NR
410	13	NR	540	519	NR	670	392	NR	800	8	NR	930	0	NR
415	26	NR	545	542	NR	675	343	NR	805	7	NR	935	0	NR
420	51	NR	550	565	NR	680	299	NR	810	6	NR	940	0	NR
425	93	NR	555	593	NR	685	260	NR	815	5	NR	945	0	NR
430	156	NR	560	624	NR	690	225	NR	820	4	NR	950	0	NR
435	250	NR	565	662	NR	695	194	NR	825	4	NR	955	0	NR
440	391	NR	570	707	NR	700	166	NR	830	3	NR	960	0	NR
445	460	NR	575	756	NR	705	143	NR	835	3	NR	965	0	NR
450	293	NR	580	810	NR	710	122	NR	840	2	NR	970	0	NR
455	188	NR	585	860	NR	715	105	NR	845	2	NR	975	0	NR
460	149	NR	590	910	NR	720	90	NR	850	2	NR	980	0	NR
465	103	NR	595	950	NR	725	77	NR	855	2	NR	985	0	NR
470	80	NR	600	980	NR	730	66	NR	860	1	NR	990	0	NR
475	82	NR	605	995	NR	735	56	NR	865	1	NR	995	0	NR
480	92	NR	610	998	NR	740	48	NR	870	1	NR	1000	0	NR
485	116	NR	615	985	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-8



TM-30-18

Summary

$R_f = 82.2$
 $R_g = 99.9$
 $CIE R_a = 82.9$
 $R_9 = 10.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 76	CES51 = 89	CES76 = 75
CES02 = 63	CES27 = 89	CES52 = 91	CES77 = 87
CES03 = 31	CES28 = 90	CES53 = 82	CES78 = 76
CES04 = 71	CES29 = 68	CES54 = 88	CES79 = 91
CES05 = 50	CES30 = 69	CES55 = 87	CES80 = 90
CES06 = 52	CES31 = 72	CES56 = 80	CES81 = 74
CES07 = 43	CES32 = 71	CES57 = 78	CES82 = 95
CES08 = 42	CES33 = 71	CES58 = 80	CES83 = 90
CES09 = 29	CES34 = 84	CES59 = 93	CES84 = 94
CES10 = 77	CES35 = 92	CES60 = 96	CES85 = 83
CES11 = 59	CES36 = 92	CES61 = 94	CES86 = 69
CES12 = 66	CES37 = 89	CES62 = 84	CES87 = 85
CES13 = 44	CES38 = 75	CES63 = 79	CES88 = 84
CES14 = 74	CES39 = 93	CES64 = 85	CES89 = 74
CES15 = 72	CES40 = 89	CES65 = 79	CES90 = 81
CES16 = 48	CES41 = 85	CES66 = 83	CES91 = 96
CES17 = 50	CES42 = 88	CES67 = 82	CES92 = 72
CES18 = 57	CES43 = 81	CES68 = 86	CES93 = 84
CES19 = 73	CES44 = 98	CES69 = 92	CES94 = 63
CES20 = 67	CES45 = 87	CES70 = 81	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 81	CES96 = 85
CES22 = 79	CES47 = 76	CES72 = 93	CES97 = 87
CES23 = 92	CES48 = 71	CES73 = 75	CES98 = 82
CES24 = 91	CES49 = 81	CES74 = 91	CES99 = 76
CES25 = 72	CES50 = 88	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)