

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P360283

Luminaire Tested: NVN-SA3C-727-U-5WQ

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P360283  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA3C-727-U-5WQ  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(3) 70 CRI, 2700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 18727 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G3


Input Watts (W): 166  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P360283  
 CATALOG NUMBER: NVN-SA3C-727-U-5WQ

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.5 fc  
 Type V - Short - N/A

REPORT NUMBER: P360283  
CATALOG NUMBER: NVN-SA3C-727-U-5WQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P360283

CATALOG NUMBER: NVN-SA3C-727-U-5WQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 9363.5   | 0.0    | 9363.5  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 9363.5   | 0.0    | 9363.5  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 18727.0  | 0.0    | 18727.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 143.9   | 0.8       |
| 10°-20°   | 420.2   | 2.2       |
| 20°-30°   | 716.4   | 3.8       |
| 30°-40°   | 1119.4  | 6.0       |
| 40°-50°   | 1897.1  | 10.1      |
| 50°-60°   | 3459.6  | 18.5      |
| 60°-70°   | 5955.9  | 31.8      |
| 70°-80°   | 4668.4  | 24.9      |
| 80°-90°   | 346.2   | 1.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 18727.0 | 100.0     |
| 0°-180°   | 18727.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P360283


CATALOG NUMBER: NVN-SA3C-727-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 640.2  | 3.4       |                         |      |         |
| FM   | (30°-60°)   | 3238.0 | 17.3      |                         |      |         |
| FH   | (60°-80°)   | 5312.1 | 28.4      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 173.1  | 0.9       |                         |      | G2/225  |
| BL   | (0°-30°)    | 640.2  | 3.4       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 3238.0 | 17.3      | B3/5000                 |      |         |
| BH   | (60°-80°)   | 5312.1 | 28.4      | B5                      |      | G3/7500 |
| BVH  | (80°-90°)   | 173.1  | 0.9       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B5-U0-G3**

Type V Short



REPORT NUMBER: P360283

CATALOG NUMBER: NVN-SA3C-727-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1541.2 | 1541.2 | 1541.2 | 1541.2 | 1541.2 | 1541.2 | 1541.2 | 1541.2 | 1541.2 | 1541.2 | 1541.2 |
| 2.5°  | 1534.4 | 1536.3 | 1534.4 | 1535.7 | 1532.6 | 1533.8 | 1533.8 | 1533.8 | 1533.2 | 1533.8 | 1532.6 |
| 5°    | 1520.8 | 1522.0 | 1519.6 | 1520.8 | 1518.9 | 1520.8 | 1521.4 | 1520.8 | 1519.6 | 1520.2 | 1517.7 |
| 7.5°  | 1500.3 | 1501.6 | 1499.7 | 1501.6 | 1499.1 | 1502.2 | 1501.6 | 1499.7 | 1497.9 | 1497.9 | 1495.4 |
| 10°   | 1489.2 | 1489.8 | 1484.9 | 1483.0 | 1477.4 | 1478.7 | 1480.5 | 1482.4 | 1484.2 | 1488.0 | 1487.3 |
| 12.5° | 1489.8 | 1489.8 | 1482.4 | 1474.3 | 1466.3 | 1468.1 | 1471.2 | 1478.0 | 1485.5 | 1492.3 | 1492.9 |
| 15°   | 1496.0 | 1495.4 | 1484.2 | 1471.2 | 1465.7 | 1471.2 | 1473.1 | 1477.4 | 1489.2 | 1501.0 | 1501.6 |
| 17.5° | 1500.3 | 1500.3 | 1483.0 | 1468.1 | 1467.5 | 1476.2 | 1475.6 | 1477.4 | 1490.4 | 1507.8 | 1508.4 |
| 20°   | 1508.4 | 1508.4 | 1486.1 | 1470.0 | 1470.0 | 1479.3 | 1479.9 | 1483.0 | 1496.0 | 1515.2 | 1518.3 |
| 22.5° | 1526.4 | 1527.0 | 1503.4 | 1490.4 | 1491.7 | 1497.3 | 1499.1 | 1504.1 | 1515.8 | 1536.9 | 1540.6 |
| 25°   | 1551.8 | 1553.0 | 1528.8 | 1521.4 | 1525.7 | 1536.3 | 1535.0 | 1538.8 | 1551.8 | 1572.2 | 1575.9 |
| 27.5° | 1587.1 | 1584.0 | 1561.7 | 1558.6 | 1562.9 | 1570.3 | 1569.7 | 1570.3 | 1580.9 | 1599.5 | 1603.8 |
| 30°   | 1632.9 | 1631.7 | 1615.6 | 1617.4 | 1615.6 | 1613.1 | 1613.7 | 1618.7 | 1624.2 | 1639.1 | 1643.4 |
| 32.5° | 1677.5 | 1678.8 | 1668.8 | 1678.1 | 1691.8 | 1701.1 | 1686.8 | 1673.2 | 1667.0 | 1675.0 | 1678.8 |
| 35°   | 1758.0 | 1761.1 | 1745.7 | 1739.5 | 1758.0 | 1785.3 | 1745.0 | 1722.7 | 1735.1 | 1745.7 | 1748.8 |
| 37.5° | 1895.0 | 1896.8 | 1870.8 | 1846.0 | 1832.4 | 1858.4 | 1818.1 | 1820.0 | 1863.4 | 1883.2 | 1882.6 |
| 40°   | 2051.1 | 2051.7 | 2034.3 | 2012.6 | 1989.1 | 1995.3 | 1979.2 | 1984.2 | 2012.6 | 2030.6 | 2035.6 |
| 42.5° | 2236.9 | 2235.0 | 2207.8 | 2176.8 | 2170.0 | 2176.2 | 2148.9 | 2145.2 | 2178.0 | 2210.3 | 2210.9 |
| 45°   | 2477.9 | 2473.5 | 2438.2 | 2404.2 | 2371.3 | 2357.7 | 2350.9 | 2368.8 | 2414.1 | 2443.8 | 2444.4 |
| 47.5° | 2737.4 | 2725.7 | 2707.1 | 2679.8 | 2651.3 | 2637.7 | 2626.5 | 2635.2 | 2668.0 | 2679.8 | 2681.1 |
| 50°   | 3004.4 | 3006.9 | 3010.6 | 3000.1 | 2989.5 | 2985.2 | 2956.1 | 2939.4 | 2949.3 | 2927.6 | 2924.5 |
| 52.5° | 3321.0 | 3325.9 | 3361.8 | 3392.2 | 3410.2 | 3419.5 | 3364.3 | 3306.7 | 3274.5 | 3232.4 | 3220.0 |
| 55°   | 3694.5 | 3702.6 | 3755.2 | 3839.5 | 3926.2 | 3972.0 | 3872.3 | 3764.5 | 3664.8 | 3586.1 | 3560.7 |
| 57.5° | 4110.8 | 4125.0 | 4197.5 | 4359.2 | 4537.0 | 4645.4 | 4476.9 | 4281.1 | 4088.5 | 3975.1 | 3955.3 |
| 60°   | 4598.9 | 4612.6 | 4712.9 | 4944.6 | 5232.6 | 5395.6 | 5140.3 | 4820.1 | 4580.3 | 4471.9 | 4435.4 |
| 62.5° | 5180.0 | 5181.2 | 5304.5 | 5575.2 | 5955.6 | 6182.3 | 5836.6 | 5408.6 | 5161.4 | 5030.7 | 4995.4 |
| 65°   | 5805.0 | 5808.1 | 5935.7 | 6228.1 | 6621.5 | 6868.0 | 6477.8 | 6031.8 | 5729.5 | 5536.8 | 5509.5 |
| 67.5° | 6246.7 | 6259.7 | 6394.1 | 6746.0 | 7114.0 | 7336.4 | 6932.5 | 6428.2 | 6078.8 | 5849.0 | 5826.1 |
| 70°   | 6176.1 | 6226.9 | 6384.8 | 6795.6 | 7307.2 | 7624.4 | 7006.2 | 6381.1 | 5920.2 | 5648.9 | 5629.7 |
| 72.5° | 5386.3 | 5483.5 | 5694.1 | 6233.1 | 7051.4 | 7488.1 | 6604.1 | 5715.2 | 5193.6 | 4962.6 | 4927.9 |
| 75°   | 3667.9 | 3825.8 | 4143.6 | 4921.0 | 6024.3 | 6483.3 | 5559.7 | 4556.8 | 4066.2 | 3746.5 | 3723.0 |
| 77.5° | 1635.4 | 1671.3 | 2074.0 | 2969.1 | 4157.2 | 4655.9 | 4039.5 | 2980.9 | 2237.5 | 1784.7 | 1689.3 |
| 80°   | 455.9  | 461.5  | 615.8  | 1105.7 | 2080.8 | 2735.6 | 2233.8 | 1161.5 | 652.9  | 460.3  | 433.6  |
| 82.5° | 145.0  | 157.3  | 192.0  | 286.8  | 699.4  | 1248.2 | 718.0  | 309.7  | 220.5  | 175.9  | 158.6  |
| 85°   | 70.6   | 70.0   | 97.3   | 116.5  | 178.4  | 276.3  | 190.2  | 143.7  | 125.8  | 83.6   | 75.6   |
| 87.5° | 29.7   | 30.4   | 45.2   | 40.9   | 52.0   | 44.6   | 61.3   | 64.4   | 67.5   | 37.2   | 32.2   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ




### Test Information

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: MCGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 2741   | CRI (Ra): | 71.5 |      |       |
| CIE u':                   | 0.2605 | R1:       | 69.2 | R9:  | -16.1 |
| CIE v':                   | 0.5272 | R2:       | 79.4 | R10: | 51.4  |
| Duv:                      | 0.0005 | R3:       | 87.8 | R11: | 63.1  |
| CIE x:                    | 0.4573 | R4:       | 69.4 | R12: | 42.0  |
| CIE y:                    | 0.4113 | R5:       | 66.4 | R13: | 70.2  |
| CIE z:                    | 0.1313 | R6:       | 69.8 | R14: | 92.4  |
| Peak Wavelength (nm):     | 602    | R7:       | 79.8 |      |       |
| Dominant Wavelength (nm): | 583    | R8:       | 50.1 |      |       |
| Purity:                   | 61.2   |           |      |      |       |
| Rf:                       | 69.9   |           |      |      |       |
| Rg:                       | 98.3   |           |      |      |       |



### Test Conditions


Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**




**Photopic Lumens: 6211.7**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2044             | 0.0              | 490       | 7179             | 1.0              | 620       | 118034           | 30.7             | 750       | 8362             | 0.0              | 880       | 3128             | 0.0              |
| 365       | 2016             | 0.0              | 495       | 10476            | 1.9              | 625       | 111884           | 24.7             | 755       | 7635             | 0.0              | 885       | 3110             | 0.0              |
| 370       | 2020             | 0.0              | 500       | 15549            | 3.4              | 630       | 106119           | 19.2             | 760       | 6582             | 0.0              | 890       | 2632             | 0.0              |
| 375       | 2137             | 0.0              | 505       | 22477            | 6.3              | 635       | 99706            | 15.0             | 765       | 5777             | 0.0              | 895       | 2709             | 0.0              |
| 380       | 2046             | 0.0              | 510       | 30417            | 10.4             | 640       | 92142            | 11.0             | 770       | 5474             | 0.0              | 900       | 2016             | 0.0              |
| 385       | 1925             | 0.0              | 515       | 39274            | 16.3             | 645       | 84987            | 8.2              | 775       | 4977             | 0.0              | 905       | 1748             | 0.0              |
| 390       | 1893             | 0.0              | 520       | 47282            | 22.9             | 650       | 78016            | 5.7              | 780       | 4723             | 0.0              | 910       | 2046             | 0.0              |
| 395       | 1695             | 0.0              | 525       | 55413            | 29.7             | 655       | 71541            | 4.1              | 785       | 4219             | 0.0              | 915       | 1844             | 0.0              |
| 400       | 1633             | 0.0              | 530       | 62377            | 36.7             | 660       | 64863            | 2.7              | 790       | 3969             | 0.0              | 920       | 2734             | 0.0              |
| 405       | 2065             | 0.0              | 535       | 68520            | 42.5             | 665       | 58485            | 1.9              | 795       | 4122             | 0.0              | 925       | 2307             | 0.0              |
| 410       | 3449             | 0.0              | 540       | 73435            | 47.8             | 670       | 51641            | 1.1              | 800       | 2864             | 0.0              | 930       | 2039             | 0.0              |
| 415       | 7117             | 0.0              | 545       | 78677            | 52.4             | 675       | 46030            | 0.8              | 805       | 3151             | 0.0              | 935       | 1784             | 0.0              |
| 420       | 13992            | 0.0              | 550       | 83331            | 56.6             | 680       | 40590            | 0.5              | 810       | 3022             | 0.0              | 940       | 2464             | 0.0              |
| 425       | 25176            | 0.1              | 555       | 89120            | 60.9             | 685       | 35691            | 0.3              | 815       | 3471             | 0.0              | 945       | 2794             | 0.0              |
| 430       | 38151            | 0.3              | 560       | 94613            | 64.3             | 690       | 31631            | 0.2              | 820       | 2749             | 0.0              | 950       | 3090             | 0.0              |
| 435       | 49673            | 0.6              | 565       | 99818            | 66.4             | 695       | 27437            | 0.1              | 825       | 2729             | 0.0              | 955       | 1866             | 0.0              |
| 440       | 57273            | 0.9              | 570       | 106526           | 69.3             | 700       | 24589            | 0.1              | 830       | 2282             | 0.0              | 960       | 3110             | 0.0              |
| 445       | 54802            | 1.1              | 575       | 111610           | 69.4             | 705       | 21832            | 0.0              | 835       | 3140             | 0.0              | 965       | 3880             | 0.0              |
| 450       | 39184            | 1.0              | 580       | 117163           | 69.6             | 710       | 19500            | 0.0              | 840       | 2365             | 0.0              | 970       | 3243             | 0.0              |
| 455       | 22506            | 0.8              | 585       | 122201           | 67.9             | 715       | 17870            | 0.0              | 845       | 3024             | 0.0              | 975       | 2014             | 0.0              |
| 460       | 13692            | 0.6              | 590       | 125662           | 65.0             | 720       | 15924            | 0.0              | 850       | 2510             | 0.0              | 980       | 1688             | 0.0              |
| 465       | 9446             | 0.5              | 595       | 127415           | 60.4             | 725       | 14268            | 0.0              | 855       | 2739             | 0.0              | 985       | 2827             | 0.0              |
| 470       | 6698             | 0.4              | 600       | 129155           | 55.7             | 730       | 12438            | 0.0              | 860       | 3515             | 0.0              | 990       | 4172             | 0.0              |
| 475       | 5328             | 0.4              | 605       | 128057           | 49.6             | 735       | 11255            | 0.0              | 865       | 3600             | 0.0              | 995       | 3177             | 0.0              |
| 480       | 5081             | 0.5              | 610       | 126031           | 43.3             | 740       | 9951             | 0.0              | 870       | 3609             | 0.0              | 1000      | 3241             | 0.0              |
| 485       | 5579             | 0.7              | 615       | 123059           | 37.1             | 745       | 8870             | 0.0              | 875       | 3208             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 6474.3

S/P: 1.04

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2044             | 0.0              | 490       | 7179             | 6.0              | 620       | 118034           | 0.1              | 750       | 8362             | 0.0              | 880       | 3128             | 0.0              |
| 365       | 2016             | 0.0              | 495       | 10476            | 8.6              | 625       | 111884           | 0.1              | 755       | 7635             | 0.0              | 885       | 3110             | 0.0              |
| 370       | 2020             | 0.0              | 500       | 15549            | 12.5             | 630       | 106119           | 0.0              | 760       | 6582             | 0.0              | 890       | 2632             | 0.0              |
| 375       | 2137             | 0.0              | 505       | 22477            | 17.3             | 635       | 99706            | 0.0              | 765       | 5777             | 0.0              | 895       | 2709             | 0.0              |
| 380       | 2046             | 0.0              | 510       | 30417            | 21.8             | 640       | 92142            | 0.0              | 770       | 5474             | 0.0              | 900       | 2016             | 0.0              |
| 385       | 1925             | 0.0              | 515       | 39274            | 25.7             | 645       | 84987            | 0.0              | 775       | 4977             | 0.0              | 905       | 1748             | 0.0              |
| 390       | 1893             | 0.0              | 520       | 47282            | 27.5             | 650       | 78016            | 0.0              | 780       | 4723             | 0.0              | 910       | 2046             | 0.0              |
| 395       | 1695             | 0.0              | 525       | 55413            | 28.1             | 655       | 71541            | 0.0              | 785       | 4219             | 0.0              | 915       | 1844             | 0.0              |
| 400       | 1633             | 0.0              | 530       | 62377            | 27.0             | 660       | 64863            | 0.0              | 790       | 3969             | 0.0              | 920       | 2734             | 0.0              |
| 405       | 2065             | 0.0              | 535       | 68520            | 24.7             | 665       | 58485            | 0.0              | 795       | 4122             | 0.0              | 925       | 2307             | 0.0              |
| 410       | 3449             | 0.1              | 540       | 73435            | 21.5             | 670       | 51641            | 0.0              | 800       | 2864             | 0.0              | 930       | 2039             | 0.0              |
| 415       | 7117             | 0.5              | 545       | 78677            | 18.3             | 675       | 46030            | 0.0              | 805       | 3151             | 0.0              | 935       | 1784             | 0.0              |
| 420       | 13992            | 1.6              | 550       | 83331            | 15.0             | 680       | 40590            | 0.0              | 810       | 3022             | 0.0              | 940       | 2464             | 0.0              |
| 425       | 25176            | 3.9              | 555       | 89120            | 12.0             | 685       | 35691            | 0.0              | 815       | 3471             | 0.0              | 945       | 2794             | 0.0              |
| 430       | 38151            | 8.1              | 560       | 94613            | 9.3              | 690       | 31631            | 0.0              | 820       | 2749             | 0.0              | 950       | 3090             | 0.0              |
| 435       | 49673            | 13.3             | 565       | 99818            | 7.0              | 695       | 27437            | 0.0              | 825       | 2729             | 0.0              | 955       | 1866             | 0.0              |
| 440       | 57273            | 19.1             | 570       | 106526           | 5.2              | 700       | 24589            | 0.0              | 830       | 2282             | 0.0              | 960       | 3110             | 0.0              |
| 445       | 54802            | 21.6             | 575       | 111610           | 3.7              | 705       | 21832            | 0.0              | 835       | 3140             | 0.0              | 965       | 3880             | 0.0              |
| 450       | 39184            | 18.1             | 580       | 117163           | 2.6              | 710       | 19500            | 0.0              | 840       | 2365             | 0.0              | 970       | 3243             | 0.0              |
| 455       | 22506            | 11.8             | 585       | 122201           | 1.8              | 715       | 17870            | 0.0              | 845       | 3024             | 0.0              | 975       | 2014             | 0.0              |
| 460       | 13692            | 8.1              | 590       | 125662           | 1.2              | 720       | 15924            | 0.0              | 850       | 2510             | 0.0              | 980       | 1688             | 0.0              |
| 465       | 9446             | 6.2              | 595       | 127415           | 0.8              | 725       | 14268            | 0.0              | 855       | 2739             | 0.0              | 985       | 2827             | 0.0              |
| 470       | 6698             | 4.8              | 600       | 129155           | 0.5              | 730       | 12438            | 0.0              | 860       | 3515             | 0.0              | 990       | 4172             | 0.0              |
| 475       | 5328             | 4.1              | 605       | 128057           | 0.4              | 735       | 11255            | 0.0              | 865       | 3600             | 0.0              | 995       | 3177             | 0.0              |
| 480       | 5081             | 4.1              | 610       | 126031           | 0.2              | 740       | 9951             | 0.0              | 870       | 3609             | 0.0              | 1000      | 3241             | 0.0              |
| 485       | 5579             | 4.6              | 615       | 123059           | 0.1              | 745       | 8870             | 0.0              | 875       | 3208             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-1908-441-1-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 2145.7 M/P: 0.35**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2044             | 0.0              | 490       | 7179             | 11.1             | 620       | 118034           | 1.5              | 750       | 8362             | 0.0              | 880       | 3128             | 0.0              |
| 365       | 2016             | 0.0              | 495       | 10476            | 16.9             | 625       | 111884           | 0.9              | 755       | 7635             | 0.0              | 885       | 3110             | 0.0              |
| 370       | 2020             | 0.0              | 500       | 15549            | 26.0             | 630       | 106119           | 0.6              | 760       | 6582             | 0.0              | 890       | 2632             | 0.0              |
| 375       | 2137             | 0.0              | 505       | 22477            | 38.2             | 635       | 99706            | 0.4              | 765       | 5777             | 0.0              | 895       | 2709             | 0.0              |
| 380       | 2046             | 0.0              | 510       | 30417            | 51.6             | 640       | 92142            | 0.2              | 770       | 5474             | 0.0              | 900       | 2016             | 0.0              |
| 385       | 1925             | 0.0              | 515       | 39274            | 65.1             | 645       | 84987            | 0.1              | 775       | 4977             | 0.0              | 905       | 1748             | 0.0              |
| 390       | 1893             | 0.0              | 520       | 47282            | 75.2             | 650       | 78016            | 0.1              | 780       | 4723             | 0.0              | 910       | 2046             | 0.0              |
| 395       | 1695             | 0.0              | 525       | 55413            | 82.9             | 655       | 71541            | 0.1              | 785       | 4219             | 0.0              | 915       | 1844             | 0.0              |
| 400       | 1633             | 0.0              | 530       | 62377            | 86.0             | 660       | 64863            | 0.0              | 790       | 3969             | 0.0              | 920       | 2734             | 0.0              |
| 405       | 2065             | 0.1              | 535       | 68520            | 85.4             | 665       | 58485            | 0.0              | 795       | 4122             | 0.0              | 925       | 2307             | 0.0              |
| 410       | 3449             | 0.2              | 540       | 73435            | 81.1             | 670       | 51641            | 0.0              | 800       | 2864             | 0.0              | 930       | 2039             | 0.0              |
| 415       | 7117             | 0.7              | 545       | 78677            | 75.4             | 675       | 46030            | 0.0              | 805       | 3151             | 0.0              | 935       | 1784             | 0.0              |
| 420       | 13992            | 2.3              | 550       | 83331            | 68.1             | 680       | 40590            | 0.0              | 810       | 3022             | 0.0              | 940       | 2464             | 0.0              |
| 425       | 25176            | 6.2              | 555       | 89120            | 60.9             | 685       | 35691            | 0.0              | 815       | 3471             | 0.0              | 945       | 2794             | 0.0              |
| 430       | 38151            | 13.0             | 560       | 94613            | 52.9             | 690       | 31631            | 0.0              | 820       | 2749             | 0.0              | 950       | 3090             | 0.0              |
| 435       | 49673            | 22.2             | 565       | 99818            | 44.8             | 695       | 27437            | 0.0              | 825       | 2729             | 0.0              | 955       | 1866             | 0.0              |
| 440       | 57273            | 32.0             | 570       | 106526           | 37.6             | 700       | 24589            | 0.0              | 830       | 2282             | 0.0              | 960       | 3110             | 0.0              |
| 445       | 54802            | 36.7             | 575       | 111610           | 30.4             | 705       | 21832            | 0.0              | 835       | 3140             | 0.0              | 965       | 3880             | 0.0              |
| 450       | 39184            | 30.4             | 580       | 117163           | 24.1             | 710       | 19500            | 0.0              | 840       | 2365             | 0.0              | 970       | 3243             | 0.0              |
| 455       | 22506            | 19.7             | 585       | 122201           | 18.7             | 715       | 17870            | 0.0              | 845       | 3024             | 0.0              | 975       | 2014             | 0.0              |
| 460       | 13692            | 13.2             | 590       | 125662           | 14.0             | 720       | 15924            | 0.0              | 850       | 2510             | 0.0              | 980       | 1688             | 0.0              |
| 465       | 9446             | 10.0             | 595       | 127415           | 10.2             | 725       | 14268            | 0.0              | 855       | 2739             | 0.0              | 985       | 2827             | 0.0              |
| 470       | 6698             | 7.7              | 600       | 129155           | 7.3              | 730       | 12438            | 0.0              | 860       | 3515             | 0.0              | 990       | 4172             | 0.0              |
| 475       | 5328             | 6.7              | 605       | 128057           | 5.0              | 735       | 11255            | 0.0              | 865       | 3600             | 0.0              | 995       | 3177             | 0.0              |
| 480       | 5081             | 6.9              | 610       | 126031           | 3.4              | 740       | 9951             | 0.0              | 870       | 3609             | 0.0              | 1000      | 3241             | 0.0              |
| 485       | 5579             | 8.1              | 615       | 123059           | 2.3              | 745       | 8870             | 0.0              | 875       | 3208             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-1908-441-1-R4





**TM-30-18**

### Summary

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_g = -16.1$



### Color Vector Graphics




REPORT NUMBER: SP1-1908-441-1-R4

**TM-30-18**

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |








REPORT NUMBER: SP1-1908-441-1-R4

**TM-30-18**



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

**TM-30-18**

**Measure Comparisons**



(END OF REPORT)