

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P359402

Luminaire Tested: NVN-SA4D-740-U-T4W

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P359402  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA4D-740-U-T4W  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(4) 70 CRI, 4000K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 31427 lumens  
Efficiency: N/A  
Efficacy: 121.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5


Input Watts (W): 258  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P359402  
 CATALOG NUMBER: NVN-SA4D-740-U-T4W

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 --- 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 4.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P359402  
CATALOG NUMBER: NVN-SA4D-740-U-T4W

## Luminous Intensity Polar Plot



REPORT NUMBER: P359402

CATALOG NUMBER: NVN-SA4D-740-U-T4W

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 7203.0   | 0.0    | 7203.0  |
|                    | % Fixture | 22.9     | 0.0    | 22.9    |
| <b>Street Side</b> | Lumens    | 24224.0  | 0.0    | 24224.0 |
|                    | % Fixture | 77.1     | 0.0    | 77.1    |
| <b>Total</b>       | Lumens    | 31427.0  | 0.0    | 31427.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 326.4   | 1.0       |
| 10°-20°   | 1087.5  | 3.5       |
| 20°-30°   | 1813.2  | 5.8       |
| 30°-40°   | 2573.1  | 8.2       |
| 40°-50°   | 3784.9  | 12.0      |
| 50°-60°   | 6409.6  | 20.4      |
| 60°-70°   | 9098.4  | 29.0      |
| 70°-80°   | 5527.3  | 17.6      |
| 80°-90°   | 806.6   | 2.6       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 31427.0 | 100.0     |
| 0°-180°   | 31427.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P359402


CATALOG NUMBER: NVN-SA4D-740-U-T4W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1714.8  | 5.5       |                         |      |         |
| FM   | (30°-60°)   | 9451.8  | 30.1      |                         |      |         |
| FH   | (60°-80°)   | 12554.9 | 39.9      |                         |      | G5      |
| FVH  | (80°-90°)   | 502.5   | 1.6       |                         |      | G4/750  |
| BL   | (0°-30°)    | 1512.3  | 4.8       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 3315.7  | 10.6      | B3/5000                 |      |         |
| BH   | (60°-80°)   | 2070.8  | 6.6       | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 304.2   | 1.0       |                         |      | G3/500  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G5**

Type IV Short





REPORT NUMBER: P359402

CATALOG NUMBER: NVN-SA4D-740-U-T4W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 46°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 3201.8  | 3201.8  | 3201.8  | 3201.8  | 3201.8  | 3201.8  | 3201.8  | 3201.8  | 3201.8  | 3201.8  | 3201.8  |
| 2.5°  | 3362.0  | 3364.2  | 3368.5  | 3357.7  | 3327.6  | 3319.0  | 3315.8  | 3284.6  | 3264.2  | 3234.1  | 3208.2  |
| 5°    | 3630.9  | 3633.1  | 3626.6  | 3596.5  | 3529.8  | 3480.4  | 3476.1  | 3405.1  | 3340.5  | 3271.7  | 3220.1  |
| 7.5°  | 3911.6  | 3914.9  | 3894.4  | 3837.4  | 3743.9  | 3657.8  | 3652.4  | 3555.6  | 3457.8  | 3353.4  | 3276.0  |
| 10°   | 4160.1  | 4147.2  | 4113.8  | 4034.2  | 3923.5  | 3818.1  | 3813.8  | 3712.7  | 3599.7  | 3473.9  | 3370.7  |
| 12.5° | 4325.7  | 4315.0  | 4271.9  | 4175.1  | 4053.6  | 3956.8  | 3948.2  | 3854.6  | 3744.9  | 3607.3  | 3483.6  |
| 15°   | 4417.1  | 4424.7  | 4366.6  | 4256.9  | 4138.6  | 4056.8  | 4049.3  | 3982.6  | 3884.7  | 3746.0  | 3604.0  |
| 17.5° | 4429.0  | 4435.4  | 4379.5  | 4270.9  | 4174.1  | 4118.1  | 4114.9  | 4070.8  | 3999.8  | 3866.5  | 3718.0  |
| 20°   | 4360.1  | 4364.4  | 4318.2  | 4228.9  | 4165.5  | 4148.2  | 4147.2  | 4127.8  | 4075.1  | 3956.8  | 3812.7  |
| 22.5° | 4260.1  | 4263.3  | 4230.0  | 4165.5  | 4143.9  | 4170.8  | 4178.4  | 4170.8  | 4133.2  | 4022.4  | 3886.9  |
| 25°   | 4235.4  | 4233.2  | 4198.8  | 4133.2  | 4151.5  | 4208.5  | 4218.2  | 4221.4  | 4195.6  | 4098.8  | 3981.5  |
| 27.5° | 4354.7  | 4347.2  | 4281.6  | 4176.2  | 4188.0  | 4256.9  | 4269.8  | 4301.0  | 4284.8  | 4199.9  | 4089.1  |
| 30°   | 4700.0  | 4687.1  | 4552.6  | 4339.7  | 4281.6  | 4317.1  | 4333.2  | 4382.7  | 4385.9  | 4315.0  | 4232.1  |
| 32.5° | 5282.9  | 5266.8  | 5025.9  | 4645.1  | 4439.7  | 4378.4  | 4393.5  | 4467.7  | 4507.5  | 4452.6  | 4363.3  |
| 35°   | 6019.6  | 6001.4  | 5685.2  | 5164.6  | 4704.3  | 4495.6  | 4506.4  | 4565.5  | 4645.1  | 4567.7  | 4449.4  |
| 37.5° | 6787.5  | 6743.5  | 6439.1  | 5775.5  | 5124.8  | 4746.2  | 4746.2  | 4753.8  | 4791.4  | 4630.1  | 4550.5  |
| 40°   | 7551.2  | 7507.1  | 7231.7  | 6493.9  | 5669.0  | 5140.9  | 5116.2  | 4949.5  | 4919.4  | 4780.6  | 4753.8  |
| 42.5° | 8261.0  | 8248.1  | 8085.7  | 7305.9  | 6307.9  | 5529.2  | 5494.8  | 5211.9  | 5218.4  | 5132.3  | 5133.4  |
| 45°   | 9016.0  | 9016.0  | 8883.7  | 8125.5  | 7052.1  | 6153.0  | 6118.6  | 5702.4  | 5766.9  | 5727.1  | 5822.8  |
| 47.5° | 9632.3  | 9651.6  | 9633.4  | 8979.4  | 7917.9  | 6945.6  | 6883.3  | 6382.1  | 6562.8  | 6699.4  | 6977.9  |
| 50°   | 10261.5 | 10291.6 | 10294.8 | 9916.2  | 8964.4  | 7887.8  | 7816.8  | 7284.4  | 7687.8  | 8079.2  | 8626.7  |
| 52.5° | 11174.6 | 11242.3 | 10972.4 | 10850.8 | 10246.4 | 9006.3  | 8936.4  | 8444.9  | 9118.2  | 9667.8  | 10611.0 |
| 55°   | 12021.0 | 11961.8 | 11769.3 | 11844.6 | 11618.7 | 10279.7 | 10227.0 | 9795.8  | 10712.1 | 11426.2 | 12651.2 |
| 57.5° | 12479.2 | 12474.9 | 12668.4 | 12991.1 | 13098.6 | 11850.0 | 11805.9 | 11386.4 | 12509.3 | 13045.9 | 14566.7 |
| 60°   | 13016.9 | 13024.4 | 13504.1 | 14236.5 | 14679.6 | 13805.3 | 13785.9 | 13467.5 | 14254.8 | 14558.1 | 16069.2 |
| 62.5° | 13092.2 | 13227.7 | 14053.7 | 15314.2 | 16159.6 | 16089.6 | 16132.7 | 15342.2 | 15816.5 | 15764.8 | 17191.0 |
| 65°   | 12226.4 | 12404.9 | 13899.9 | 15640.1 | 17630.9 | 18588.1 | 18627.9 | 17227.5 | 17047.9 | 16796.3 | 17592.1 |
| 67.5° | 10451.8 | 10716.4 | 12340.4 | 14931.3 | 18115.9 | 20434.7 | 20490.6 | 18689.2 | 18069.7 | 17145.8 | 16626.3 |
| 70°   | 7606.0  | 7899.6  | 9534.4  | 12752.3 | 17251.2 | 21025.2 | 21088.6 | 19335.5 | 18108.4 | 16150.9 | 14193.5 |
| 72.5° | 4594.6  | 4824.7  | 6172.4  | 9388.1  | 14560.3 | 19949.7 | 20062.6 | 18516.0 | 16532.8 | 13680.5 | 10480.9 |
| 75°   | 2017.7  | 2168.2  | 2984.5  | 5409.8  | 10423.9 | 16505.9 | 16646.8 | 15848.7 | 13433.1 | 9942.0  | 6194.9  |
| 77.5° | 859.3   | 902.4   | 1223.9  | 2350.0  | 5892.7  | 11278.9 | 11472.5 | 11580.0 | 9113.9  | 5409.8  | 2617.8  |
| 80°   | 535.6   | 552.8   | 692.6   | 1063.7  | 2757.6  | 6334.8  | 6543.4  | 6813.4  | 4525.8  | 1988.6  | 914.2   |
| 82.5° | 325.9   | 345.2   | 460.3   | 643.2   | 1435.8  | 2871.6  | 2971.6  | 3162.0  | 1756.3  | 859.3   | 473.2   |
| 85°   | 195.7   | 209.7   | 281.8   | 406.5   | 817.4   | 1129.3  | 1128.2  | 1247.6  | 827.1   | 552.8   | 249.5   |
| 87.5° | 93.6    | 104.3   | 150.6   | 210.8   | 411.9   | 423.8   | 396.9   | 449.6   | 502.3   | 362.4   | 125.8   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P359402

CATALOG NUMBER: NVN-SA4D-740-U-T4W

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 3201.8  | 3201.8  | 3201.8 | 3201.8 | 3201.8 | 3201.8 | 3201.8 | 3201.8 | 3201.8 | 3201.8 | 3201.8 |
| 2.5°  | 3199.6  | 3195.3  | 3181.4 | 3170.6 | 3168.5 | 3162.0 | 3156.6 | 3159.9 | 3164.2 | 3165.2 | 3165.2 |
| 5°    | 3198.6  | 3186.7  | 3168.5 | 3160.9 | 3170.6 | 3183.5 | 3199.6 | 3221.2 | 3234.1 | 3243.7 | 3250.2 |
| 7.5°  | 3250.2  | 3227.6  | 3207.2 | 3202.9 | 3222.2 | 3256.6 | 3293.2 | 3338.4 | 3369.6 | 3391.1 | 3395.4 |
| 10°   | 3336.2  | 3308.3  | 3287.8 | 3292.1 | 3326.6 | 3376.0 | 3427.7 | 3485.7 | 3533.1 | 3562.1 | 3564.2 |
| 12.5° | 3435.2  | 3408.3  | 3388.9 | 3407.2 | 3464.2 | 3524.4 | 3578.2 | 3628.8 | 3671.8 | 3700.8 | 3700.8 |
| 15°   | 3549.2  | 3529.8  | 3507.2 | 3549.2 | 3626.6 | 3680.4 | 3703.0 | 3727.7 | 3751.4 | 3772.9 | 3768.6 |
| 17.5° | 3658.9  | 3640.6  | 3628.8 | 3678.2 | 3758.9 | 3783.6 | 3768.6 | 3750.3 | 3750.3 | 3762.1 | 3764.3 |
| 20°   | 3753.5  | 3737.4  | 3744.9 | 3793.3 | 3835.3 | 3809.5 | 3753.5 | 3695.5 | 3671.8 | 3678.2 | 3684.7 |
| 22.5° | 3836.3  | 3828.8  | 3851.4 | 3874.0 | 3843.9 | 3753.5 | 3650.3 | 3571.8 | 3542.7 | 3540.6 | 3542.7 |
| 25°   | 3933.1  | 3932.1  | 3960.0 | 3919.2 | 3785.8 | 3619.1 | 3480.4 | 3404.0 | 3387.9 | 3400.8 | 3422.3 |
| 27.5° | 4053.6  | 4065.4  | 4079.4 | 3929.9 | 3667.5 | 3415.8 | 3274.9 | 3222.2 | 3238.4 | 3269.6 | 3290.0 |
| 30°   | 4207.4  | 4239.7  | 4209.5 | 3903.0 | 3497.6 | 3183.5 | 3049.1 | 3034.0 | 3078.1 | 3122.2 | 3143.7 |
| 32.5° | 4356.9  | 4407.4  | 4334.3 | 3833.1 | 3278.2 | 2937.2 | 2832.9 | 2828.6 | 2882.4 | 2925.4 | 2955.5 |
| 35°   | 4477.4  | 4577.4  | 4427.9 | 3694.4 | 3024.3 | 2710.3 | 2633.9 | 2604.9 | 2624.2 | 2674.8 | 2709.2 |
| 37.5° | 4634.4  | 4801.1  | 4492.4 | 3482.5 | 2749.0 | 2523.1 | 2433.9 | 2367.2 | 2350.0 | 2370.4 | 2387.6 |
| 40°   | 4921.5  | 5142.0  | 4522.5 | 3186.7 | 2480.1 | 2336.0 | 2245.7 | 2147.8 | 2080.0 | 2030.6 | 2031.6 |
| 42.5° | 5390.5  | 5586.2  | 4503.2 | 2827.5 | 2231.7 | 2153.2 | 2051.0 | 1938.1 | 1828.4 | 1716.5 | 1707.9 |
| 45°   | 6151.9  | 6246.6  | 4445.1 | 2446.8 | 2013.4 | 1961.7 | 1866.0 | 1753.1 | 1606.8 | 1479.9 | 1468.1 |
| 47.5° | 7370.5  | 7160.8  | 4354.7 | 2114.5 | 1820.8 | 1799.3 | 1711.1 | 1581.0 | 1426.1 | 1324.0 | 1315.3 |
| 50°   | 9032.1  | 8480.4  | 4310.6 | 1849.9 | 1650.9 | 1657.4 | 1585.3 | 1447.6 | 1301.4 | 1226.1 | 1217.5 |
| 52.5° | 11019.7 | 10017.3 | 4395.6 | 1645.5 | 1514.3 | 1536.9 | 1483.1 | 1354.1 | 1231.5 | 1172.3 | 1163.7 |
| 55°   | 13081.4 | 11609.1 | 4487.0 | 1497.1 | 1385.3 | 1429.4 | 1411.1 | 1304.6 | 1193.8 | 1139.0 | 1131.4 |
| 57.5° | 14846.4 | 12797.5 | 4304.2 | 1376.7 | 1270.2 | 1339.0 | 1355.1 | 1273.4 | 1174.5 | 1125.0 | 1116.4 |
| 60°   | 15957.4 | 13276.1 | 3824.5 | 1263.7 | 1178.8 | 1267.0 | 1322.9 | 1264.8 | 1182.0 | 1177.7 | 1171.2 |
| 62.5° | 16484.4 | 13234.2 | 3105.0 | 1174.5 | 1121.8 | 1235.8 | 1346.5 | 1313.2 | 1268.0 | 1306.7 | 1310.0 |
| 65°   | 16247.7 | 12601.8 | 2312.3 | 1115.3 | 1080.9 | 1247.6 | 1417.5 | 1404.6 | 1292.8 | 1331.5 | 1336.9 |
| 67.5° | 14690.4 | 11092.8 | 1712.2 | 1063.7 | 1035.7 | 1280.9 | 1546.6 | 1434.7 | 1244.4 | 1272.3 | 1255.1 |
| 70°   | 11873.6 | 8794.5  | 1320.7 | 1005.6 | 989.5  | 1276.6 | 1604.7 | 1416.4 | 1191.7 | 1198.1 | 1151.9 |
| 72.5° | 8187.9  | 5997.0  | 1074.4 | 951.8  | 922.8  | 1163.7 | 1563.8 | 1371.3 | 1147.6 | 1098.1 | 1036.8 |
| 75°   | 4452.6  | 3219.0  | 913.1  | 895.9  | 805.6  | 1021.7 | 1488.5 | 1339.0 | 1107.8 | 1042.2 | 1007.8 |
| 77.5° | 1752.0  | 1335.8  | 792.7  | 819.5  | 704.5  | 902.4  | 1404.6 | 1277.7 | 1052.9 | 966.9  | 949.7  |
| 80°   | 715.2   | 681.9   | 657.1  | 708.8  | 605.5  | 789.4  | 1303.5 | 1205.6 | 987.3  | 897.0  | 862.6  |
| 82.5° | 405.5   | 423.8   | 510.9  | 559.3  | 491.5  | 727.0  | 1255.1 | 1147.6 | 908.8  | 803.4  | 762.5  |
| 85°   | 207.6   | 248.4   | 356.0  | 401.2  | 361.4  | 618.4  | 1156.2 | 1004.5 | 729.2  | 615.2  | 618.4  |
| 87.5° | 100.0   | 138.7   | 224.8  | 251.7  | 234.5  | 447.4  | 863.6  | 728.1  | 567.9  | 449.6  | 435.6  |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 |      |       |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R9:  | -29.7 |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R10: | 46.2  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R11: | 68.8  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R12: | 45.6  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R13: | 69.5  |
| CIE z:                    | 0.2385  | R6:       | 68.3 | R14: | 90.7  |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



### Test Conditions

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 2.7              | 620       | 97577            | 25.4             | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 4.8              | 625       | 90158            | 19.9             | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 8.0              | 630       | 82240            | 14.9             | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 13.3             | 635       | 74361            | 11.2             | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 20.2             | 640       | 66994            | 8.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 28.5             | 645       | 60405            | 5.8              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 37.4             | 650       | 53806            | 3.9              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 44.9             | 655       | 47610            | 2.7              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 52.6             | 660       | 42018            | 1.8              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 58.4             | 665       | 36742            | 1.2              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.0              | 540       | 96845            | 63.1             | 670       | 32105            | 0.7              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.0              | 545       | 100829           | 67.1             | 675       | 27946            | 0.5              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 0.1              | 550       | 105648           | 71.8             | 680       | 24146            | 0.3              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 0.2              | 555       | 110017           | 75.1             | 685       | 21191            | 0.2              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 0.5              | 560       | 114586           | 77.9             | 690       | 18544            | 0.1              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 1.2              | 565       | 118987           | 79.1             | 695       | 16058            | 0.1              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 2.1              | 570       | 122326           | 79.5             | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 2.9              | 575       | 125968           | 78.4             | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 2.7              | 580       | 127613           | 75.8             | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 2.0              | 585       | 129466           | 71.9             | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 1.5              | 590       | 128813           | 66.6             | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 1.3              | 595       | 126387           | 59.9             | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 1.0              | 600       | 123477           | 53.2             | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 1.1              | 605       | 118718           | 46.0             | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 1.2              | 610       | 112091           | 38.5             | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 1.7              | 615       | 105039           | 31.7             | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8

S/P: 1.47

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 2304                          | 0.0                            | 490               | 19043                         | 29.3                           | 620               | 97577                         | 1.2                            | 750               | 4830                          | 0.0                            | 880               | 3505                          | 0.0                            |
| 365               | 2150                          | 0.0                            | 495               | 26606                         | 43.0                           | 625               | 90158                         | 0.8                            | 755               | 4664                          | 0.0                            | 885               | 2991                          | 0.0                            |
| 370               | 2146                          | 0.0                            | 500               | 36376                         | 60.8                           | 630               | 82240                         | 0.5                            | 760               | 4006                          | 0.0                            | 890               | 2327                          | 0.0                            |
| 375               | 2332                          | 0.0                            | 505               | 47714                         | 81.1                           | 635               | 74361                         | 0.3                            | 765               | 3715                          | 0.0                            | 895               | 2775                          | 0.0                            |
| 380               | 2527                          | 0.0                            | 510               | 58741                         | 99.6                           | 640               | 66994                         | 0.2                            | 770               | 3696                          | 0.0                            | 900               | 2141                          | 0.0                            |
| 385               | 2304                          | 0.0                            | 515               | 68716                         | 113.9                          | 645               | 60405                         | 0.1                            | 775               | 3117                          | 0.0                            | 905               | 2421                          | 0.0                            |
| 390               | 2064                          | 0.0                            | 520               | 77136                         | 122.6                          | 650               | 53806                         | 0.1                            | 780               | 3062                          | 0.0                            | 910               | 2200                          | 0.0                            |
| 395               | 1856                          | 0.0                            | 525               | 83567                         | 125.0                          | 655               | 47610                         | 0.0                            | 785               | 2907                          | 0.0                            | 915               | 2716                          | 0.0                            |
| 400               | 1856                          | 0.0                            | 530               | 89283                         | 123.1                          | 660               | 42018                         | 0.0                            | 790               | 2655                          | 0.0                            | 920               | 2656                          | 0.0                            |
| 405               | 2374                          | 0.1                            | 535               | 94097                         | 117.3                          | 665               | 36742                         | 0.0                            | 795               | 2467                          | 0.0                            | 925               | 2671                          | 0.0                            |
| 410               | 4084                          | 0.2                            | 540               | 96845                         | 107.0                          | 670               | 32105                         | 0.0                            | 800               | 2609                          | 0.0                            | 930               | 3292                          | 0.0                            |
| 415               | 8543                          | 0.9                            | 545               | 100829                        | 96.7                           | 675               | 27946                         | 0.0                            | 805               | 2293                          | 0.0                            | 935               | 3188                          | 0.0                            |
| 420               | 18394                         | 3.0                            | 550               | 105648                        | 86.4                           | 680               | 24146                         | 0.0                            | 810               | 2188                          | 0.0                            | 940               | 1997                          | 0.0                            |
| 425               | 37987                         | 9.3                            | 555               | 110017                        | 75.2                           | 685               | 21191                         | 0.0                            | 815               | 2386                          | 0.0                            | 945               | 2623                          | 0.0                            |
| 430               | 67605                         | 23.0                           | 560               | 114586                        | 64.0                           | 690               | 18544                         | 0.0                            | 820               | 2712                          | 0.0                            | 950               | 2969                          | 0.0                            |
| 435               | 102160                        | 45.7                           | 565               | 118987                        | 53.4                           | 695               | 16058                         | 0.0                            | 825               | 2473                          | 0.0                            | 955               | 2277                          | 0.0                            |
| 440               | 135103                        | 75.5                           | 570               | 122326                        | 43.2                           | 700               | 14133                         | 0.0                            | 830               | 1969                          | 0.0                            | 960               | 4267                          | 0.0                            |
| 445               | 140126                        | 93.8                           | 575               | 125968                        | 34.3                           | 705               | 12309                         | 0.0                            | 835               | 1917                          | 0.0                            | 965               | 2034                          | 0.0                            |
| 450               | 102339                        | 79.3                           | 580               | 127613                        | 26.3                           | 710               | 11142                         | 0.0                            | 840               | 2248                          | 0.0                            | 970               | 3586                          | 0.0                            |
| 455               | 58751                         | 51.3                           | 585               | 129466                        | 19.8                           | 715               | 10143                         | 0.0                            | 845               | 2266                          | 0.0                            | 975               | 2505                          | 0.0                            |
| 460               | 36892                         | 35.6                           | 590               | 128813                        | 14.3                           | 720               | 9072                          | 0.0                            | 850               | 2558                          | 0.0                            | 980               | 2666                          | 0.0                            |
| 465               | 24637                         | 26.0                           | 595               | 126387                        | 10.1                           | 725               | 8130                          | 0.0                            | 855               | 2767                          | 0.0                            | 985               | 2934                          | 0.0                            |
| 470               | 16738                         | 19.3                           | 600               | 123477                        | 7.0                            | 730               | 7149                          | 0.0                            | 860               | 2826                          | 0.0                            | 990               | 4120                          | 0.0                            |
| 475               | 13456                         | 16.8                           | 605               | 118718                        | 4.7                            | 735               | 6311                          | 0.0                            | 865               | 2385                          | 0.0                            | 995               | 3858                          | 0.0                            |
| 480               | 13081                         | 17.7                           | 610               | 112091                        | 3.0                            | 740               | 5711                          | 0.0                            | 870               | 3194                          | 0.0                            | 1000              | 3405                          | 0.0                            |
| 485               | 14734                         | 21.4                           | 615               | 105039                        | 1.9                            | 745               | 5111                          | 0.0                            | 875               | 3189                          | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2101-121-2

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 3927.2**

**M/P: 0.55**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 15.8             | 620       | 97577            | 0.1              | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 22.0             | 625       | 90158            | 0.0              | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 29.2             | 630       | 82240            | 0.0              | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 36.6             | 635       | 74361            | 0.0              | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 42.2             | 640       | 66994            | 0.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 44.9             | 645       | 60405            | 0.0              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 44.9             | 650       | 53806            | 0.0              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 42.4             | 655       | 47610            | 0.0              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 38.6             | 660       | 42018            | 0.0              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 33.9             | 665       | 36742            | 0.0              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.2              | 540       | 96845            | 28.3             | 670       | 32105            | 0.0              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.6              | 545       | 100829           | 23.4             | 675       | 27946            | 0.0              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 2.1              | 550       | 105648           | 19.0             | 680       | 24146            | 0.0              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 5.9              | 555       | 110017           | 14.8             | 685       | 21191            | 0.0              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 14.3             | 560       | 114586           | 11.3             | 690       | 18544            | 0.0              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 27.3             | 565       | 118987           | 8.4              | 695       | 16058            | 0.0              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 45.1             | 570       | 122326           | 6.0              | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 55.3             | 575       | 125968           | 4.2              | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 47.2             | 580       | 127613           | 2.9              | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 30.8             | 585       | 129466           | 1.9              | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 21.7             | 590       | 128813           | 1.3              | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 16.1             | 595       | 126387           | 0.8              | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 12.0             | 600       | 123477           | 0.5              | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 10.3             | 605       | 118718           | 0.3              | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 10.5             | 610       | 112091           | 0.2              | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 12.1             | 615       | 105039           | 0.1              | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

TM-30-18

### Summary

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)