

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P360794

Luminaire Tested: NVN-SA4D-827-U-RW

Issue Date: 3/3/2020

### Test Information

Test Method: LM-79-2019  
Report Number: P360794  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA4D-827-U-RW  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(4) 80 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR  
WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

### Summary

Lumens per Lamp: N/A  
Luminaire Lumens: 23890 lumens  
Efficiency: N/A  
Efficacy: 92.6 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B4 - U0 - G4


Input Watts (W): 258  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P360794  
 CATALOG NUMBER: NVN-SA4D-827-U-RW

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.5 fc  
 Type III - Short - N/A

REPORT NUMBER: P360794  
CATALOG NUMBER: NVN-SA4D-827-U-RW

## Luminous Intensity Polar Plot



REPORT NUMBER: P360794

CATALOG NUMBER: NVN-SA4D-827-U-RW


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 11945.0  | 0.0    | 11945.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 11945.0  | 0.0    | 11945.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 23890.0  | 0.0    | 23890.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 243.2   | 1.0       |
| 10°-20°   | 814.3   | 3.4       |
| 20°-30°   | 1587.7  | 6.6       |
| 30°-40°   | 2667.3  | 11.2      |
| 40°-50°   | 4202.7  | 17.6      |
| 50°-60°   | 5620.4  | 23.5      |
| 60°-70°   | 5463.8  | 22.9      |
| 70°-80°   | 2986.8  | 12.5      |
| 80°-90°   | 303.8   | 1.3       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 23890.0 | 100.0     |
| 0°-180°   | 23890.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P360794


CATALOG NUMBER: NVN-SA4D-827-U-RW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1322.6 | 5.5       |                         |      |         |
| FM   | (30°-60°)   | 6245.2 | 26.1      |                         |      |         |
| FH   | (60°-80°)   | 4225.3 | 17.7      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 151.9  | 0.6       |                         |      | G2/225  |
| BL   | (0°-30°)    | 1322.6 | 5.5       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 6245.2 | 26.1      | B4/8500                 |      |         |
| BH   | (60°-80°)   | 4225.3 | 17.7      | B4/5000                 |      | G4/5000 |
| BVH  | (80°-90°)   | 151.9  | 0.6       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G4**

Type III Short



REPORT NUMBER: P360794

CATALOG NUMBER: NVN-SA4D-827-U-RW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2484.0 | 2484.0 | 2484.0 | 2484.0 | 2484.0 | 2484.0 | 2484.0 | 2484.0 | 2484.0 | 2484.0 | 2484.0 |
| 2.5°  | 2466.4 | 2467.2 | 2471.2 | 2476.0 | 2480.0 | 2490.4 | 2492.8 | 2496.8 | 2498.4 | 2502.4 | 2502.4 |
| 5°    | 2444.7 | 2446.3 | 2456.0 | 2468.8 | 2483.2 | 2508.8 | 2527.3 | 2548.1 | 2558.5 | 2569.7 | 2568.9 |
| 7.5°  | 2442.3 | 2446.3 | 2460.0 | 2480.8 | 2504.8 | 2547.3 | 2585.7 | 2627.4 | 2655.4 | 2681.1 | 2679.4 |
| 10°   | 2467.2 | 2473.6 | 2492.8 | 2524.0 | 2560.1 | 2613.0 | 2669.8 | 2725.9 | 2774.8 | 2814.0 | 2815.6 |
| 12.5° | 2504.8 | 2512.8 | 2543.3 | 2590.5 | 2645.0 | 2713.1 | 2780.4 | 2843.7 | 2910.9 | 2969.4 | 2974.2 |
| 15°   | 2554.5 | 2564.9 | 2610.6 | 2681.1 | 2764.4 | 2845.3 | 2917.4 | 2982.2 | 3059.9 | 3140.8 | 3148.9 |
| 17.5° | 2628.2 | 2642.6 | 2702.7 | 2798.0 | 2907.7 | 2996.7 | 3072.0 | 3120.8 | 3185.7 | 3269.0 | 3284.2 |
| 20°   | 2740.3 | 2758.8 | 2834.8 | 2948.6 | 3082.4 | 3175.3 | 3233.0 | 3243.4 | 3275.4 | 3349.9 | 3367.5 |
| 22.5° | 2886.1 | 2902.1 | 2987.0 | 3122.4 | 3272.2 | 3373.1 | 3403.6 | 3361.9 | 3358.7 | 3418.8 | 3435.6 |
| 25°   | 3048.7 | 3063.1 | 3161.7 | 3313.9 | 3474.9 | 3586.2 | 3585.4 | 3504.5 | 3448.4 | 3494.9 | 3512.5 |
| 27.5° | 3231.4 | 3253.8 | 3348.3 | 3508.5 | 3680.7 | 3790.5 | 3784.1 | 3659.1 | 3552.6 | 3564.6 | 3579.8 |
| 30°   | 3441.2 | 3466.1 | 3558.2 | 3720.8 | 3893.0 | 4000.3 | 3992.3 | 3827.3 | 3667.1 | 3635.1 | 3646.3 |
| 32.5° | 3701.6 | 3731.2 | 3818.5 | 3978.7 | 4130.9 | 4227.8 | 4204.6 | 4010.0 | 3804.9 | 3735.2 | 3745.6 |
| 35°   | 4014.8 | 4032.4 | 4124.5 | 4282.3 | 4405.7 | 4472.2 | 4423.3 | 4221.4 | 3979.5 | 3895.4 | 3895.4 |
| 37.5° | 4332.0 | 4345.6 | 4448.9 | 4601.9 | 4721.3 | 4756.5 | 4661.2 | 4452.9 | 4207.8 | 4088.5 | 4090.9 |
| 40°   | 4636.4 | 4673.2 | 4789.4 | 4946.4 | 5064.1 | 5073.7 | 4947.2 | 4717.3 | 4461.7 | 4338.4 | 4352.8 |
| 42.5° | 4954.4 | 4990.4 | 5129.0 | 5306.8 | 5411.0 | 5427.0 | 5278.8 | 5013.7 | 4748.5 | 4648.4 | 4664.4 |
| 45°   | 5237.9 | 5266.8 | 5427.0 | 5633.7 | 5763.4 | 5805.1 | 5629.6 | 5353.3 | 5058.5 | 4960.8 | 4964.8 |
| 47.5° | 5435.8 | 5473.4 | 5649.7 | 5893.2 | 6082.2 | 6146.3 | 5974.1 | 5684.1 | 5363.7 | 5245.2 | 5255.6 |
| 50°   | 5615.2 | 5635.3 | 5813.9 | 6079.8 | 6320.1 | 6452.3 | 6304.9 | 6010.9 | 5672.1 | 5546.3 | 5557.6 |
| 52.5° | 5715.4 | 5741.0 | 5914.0 | 6191.2 | 6475.5 | 6688.6 | 6598.9 | 6304.9 | 5970.1 | 5847.5 | 5861.1 |
| 55°   | 5645.7 | 5664.9 | 5872.4 | 6216.0 | 6571.7 | 6834.4 | 6848.0 | 6592.5 | 6262.5 | 6155.1 | 6193.6 |
| 57.5° | 5328.5 | 5352.5 | 5605.6 | 6055.8 | 6583.7 | 6932.9 | 7035.5 | 6859.2 | 6535.6 | 6448.3 | 6470.7 |
| 60°   | 4832.6 | 4847.8 | 5117.8 | 5624.0 | 6349.8 | 6973.8 | 7154.8 | 7077.1 | 6803.2 | 6715.8 | 6746.3 |
| 62.5° | 3949.1 | 3971.5 | 4294.3 | 4972.8 | 5855.5 | 6852.8 | 7270.2 | 7257.3 | 7052.3 | 6972.2 | 6999.4 |
| 65°   | 2699.5 | 2738.7 | 3096.0 | 3953.9 | 5093.8 | 6482.7 | 7375.1 | 7467.2 | 7272.6 | 7171.6 | 7207.7 |
| 67.5° | 1630.1 | 1658.9 | 1917.7 | 2610.6 | 3897.8 | 5736.2 | 7267.0 | 7705.9 | 7428.0 | 7265.4 | 7295.0 |
| 68°   | 1457.1 | 1483.5 | 1699.8 | 2355.8 | 3605.4 | 5525.5 | 7168.4 | 7733.2 | 7444.8 | 7263.8 | 7290.2 |
| 70°   | 880.3  | 898.0  | 1042.9 | 1456.3 | 2403.9 | 4383.2 | 6496.4 | 7710.7 | 7552.1 | 7286.2 | 7301.4 |
| 72.5° | 573.5  | 579.1  | 603.2  | 747.4  | 1228.0 | 2451.2 | 4875.9 | 7185.3 | 7713.1 | 7416.7 | 7414.3 |
| 75°   | 476.6  | 473.4  | 475.8  | 492.6  | 605.6  | 1075.0 | 2849.3 | 5676.1 | 7352.7 | 7210.9 | 7160.4 |
| 77.5° | 402.9  | 400.5  | 399.7  | 400.5  | 405.3  | 519.1  | 1236.8 | 3535.8 | 5626.4 | 6378.6 | 6423.5 |
| 80°   | 326.0  | 322.8  | 333.2  | 328.4  | 314.0  | 322.8  | 518.3  | 1470.7 | 2652.2 | 2853.3 | 2673.8 |
| 82.5° | 237.1  | 225.1  | 269.9  | 257.1  | 245.1  | 227.5  | 286.0  | 475.0  | 632.8  | 434.2  | 305.2  |
| 85°   | 182.6  | 169.8  | 205.1  | 197.1  | 168.2  | 116.1  | 169.8  | 232.3  | 256.3  | 146.6  | 115.3  |
| 87.5° | 74.5   | 78.5   | 148.2  | 117.0  | 98.5   | 56.1   | 69.7   | 92.9   | 125.0  | 62.5   | 48.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

### Spectral Parameters

CCT (K): 2764  
 CIE  $u'$ : 0.2591  
 CIE  $v'$ : 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

CRI (Ra): 80.9  
 R1: 78.8  
 R2: 89.9  
 R3: 96.2  
 R4: 79.1  
 R5: 79.1  
 R6: 88.8  
 R7: 81.3  
 R8: 54.3  
 R9: -1.5  
 R10: 77.9  
 R11: 78.9  
 R12: 71.6  
 R13: 81.2  
 R14: 98.5  
 R15: 69.9



### Test Conditions

Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

### Photopic Flux vs. Wavelength



**Photopic Lumens: 4337.9**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 2.6              | 620       | 87426            | 22.8             | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 3.9              | 625       | 83013            | 18.2             | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 5.8              | 630       | 78077            | 14.1             | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 8.5              | 635       | 72080            | 10.7             | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 11.5             | 640       | 66249            | 7.9              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 15.2             | 645       | 59973            | 5.7              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 18.7             | 650       | 53972            | 3.9              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 21.9             | 655       | 48369            | 2.7              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 24.9             | 660       | 42641            | 1.8              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 27.6             | 665       | 37602            | 1.1              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.0              | 540       | 46032            | 30.0             | 670       | 32798            | 0.7              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.0              | 545       | 48553            | 32.5             | 675       | 28558            | 0.5              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 0.0              | 550       | 51408            | 34.9             | 680       | 24782            | 0.3              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 0.0              | 555       | 54711            | 37.4             | 685       | 21386            | 0.2              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 0.0              | 560       | 58847            | 40.0             | 690       | 18413            | 0.1              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 0.1              | 565       | 63386            | 42.4             | 695       | 15721            | 0.1              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 0.2              | 570       | 68196            | 44.3             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 0.6              | 575       | 73613            | 46.0             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 0.9              | 580       | 79207            | 47.1             | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 0.9              | 585       | 84248            | 47.0             | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 0.9              | 590       | 88397            | 45.7             | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 1.0              | 595       | 91428            | 43.4             | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 0.9              | 600       | 93452            | 40.3             | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 1.0              | 605       | 93959            | 36.4             | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 1.3              | 610       | 93079            | 32.0             | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 1.8              | 615       | 90707            | 27.3             | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 75.9             | 620       | 87426            | 0.4              | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 93.2             | 625       | 83013            | 0.2              | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 107.8            | 630       | 78077            | 0.1              | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 118.7            | 635       | 72080            | 0.1              | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 122.2            | 640       | 66249            | 0.1              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 120.8            | 645       | 59973            | 0.0              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 113.9            | 650       | 53972            | 0.0              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 104.1            | 655       | 48369            | 0.0              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 92.4             | 660       | 42641            | 0.0              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 80.5             | 665       | 37602            | 0.0              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.1              | 540       | 46032            | 68.2             | 670       | 32798            | 0.0              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.3              | 545       | 48553            | 57.1             | 675       | 28558            | 0.0              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 1.1              | 550       | 51408            | 46.7             | 680       | 24782            | 0.0              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 2.5              | 555       | 54711            | 37.4             | 685       | 21386            | 0.0              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 5.9              | 560       | 58847            | 29.4             | 690       | 18413            | 0.0              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 12.5             | 565       | 63386            | 22.5             | 695       | 15721            | 0.0              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 26.3             | 570       | 68196            | 16.9             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 55.2             | 575       | 73613            | 12.4             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 85.4             | 580       | 79207            | 9.0              | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 75.1             | 585       | 84248            | 6.3              | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 63.2             | 590       | 88397            | 4.4              | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 63.2             | 595       | 91428            | 3.0              | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 54.2             | 600       | 93452            | 2.0              | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 48.8             | 605       | 93959            | 1.3              | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 54.2             | 610       | 93079            | 0.9              | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 63.3             | 615       | 90707            | 0.5              | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 9797**

**M/P: 2.26**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 0                | 0.0              | 490       | 18018            | 27.7             | 620       | 87426            | 1.1              | 750       | 2680             | 0.0              | 880       | 58               | 0.0              |
| 365       | 0                | 0.0              | 495       | 22295            | 36.0             | 625       | 83013            | 0.7              | 755       | 2287             | 0.0              | 885       | 46               | 0.0              |
| 370       | 0                | 0.0              | 500       | 26478            | 44.2             | 630       | 78077            | 0.4              | 760       | 1944             | 0.0              | 890       | 45               | 0.0              |
| 375       | 0                | 0.0              | 505       | 30524            | 51.8             | 635       | 72080            | 0.3              | 765       | 1653             | 0.0              | 895       | 41               | 0.0              |
| 380       | 0                | 0.0              | 510       | 33611            | 57.0             | 640       | 66249            | 0.2              | 770       | 1413             | 0.0              | 900       | 38               | 0.0              |
| 385       | 0                | 0.0              | 515       | 36490            | 60.5             | 645       | 59973            | 0.1              | 775       | 1198             | 0.0              | 905       | 33               | 0.0              |
| 390       | 0                | 0.0              | 520       | 38610            | 61.4             | 650       | 53972            | 0.1              | 780       | 1025             | 0.0              | 910       | 30               | 0.0              |
| 395       | 0                | 0.0              | 525       | 40511            | 60.6             | 655       | 48369            | 0.0              | 785       | 874              | 0.0              | 915       | 23               | 0.0              |
| 400       | 48               | 0.0              | 530       | 42223            | 58.2             | 660       | 42641            | 0.0              | 790       | 747              | 0.0              | 920       | 24               | 0.0              |
| 405       | 201              | 0.0              | 535       | 44137            | 55.0             | 665       | 37602            | 0.0              | 795       | 639              | 0.0              | 925       | 22               | 0.0              |
| 410       | 457              | 0.0              | 540       | 46032            | 50.9             | 670       | 32798            | 0.0              | 800       | 547              | 0.0              | 930       | 22               | 0.0              |
| 415       | 925              | 0.1              | 545       | 48553            | 46.6             | 675       | 28558            | 0.0              | 805       | 473              | 0.0              | 935       | 17               | 0.0              |
| 420       | 1816             | 0.3              | 550       | 51408            | 42.0             | 680       | 24782            | 0.0              | 810       | 401              | 0.0              | 940       | 13               | 0.0              |
| 425       | 3217             | 0.8              | 555       | 54711            | 37.4             | 685       | 21386            | 0.0              | 815       | 351              | 0.0              | 945       | 6                | 0.0              |
| 430       | 5520             | 1.9              | 560       | 58847            | 32.9             | 690       | 18413            | 0.0              | 820       | 307              | 0.0              | 950       | 10               | 0.0              |
| 435       | 9225             | 4.1              | 565       | 63386            | 28.4             | 695       | 15721            | 0.0              | 825       | 261              | 0.0              | 955       | 11               | 0.0              |
| 440       | 15522            | 8.7              | 570       | 68196            | 24.1             | 700       | 13432            | 0.0              | 830       | 228              | 0.0              | 960       | 8                | 0.0              |
| 445       | 27642            | 18.5             | 575       | 73613            | 20.0             | 705       | 11513            | 0.0              | 835       | 193              | 0.0              | 965       | 12               | 0.0              |
| 450       | 36602            | 28.3             | 580       | 79207            | 16.3             | 710       | 9780             | 0.0              | 840       | 174              | 0.0              | 970       | 3                | 0.0              |
| 455       | 28292            | 24.7             | 585       | 84248            | 12.9             | 715       | 8356             | 0.0              | 845       | 151              | 0.0              | 975       | 8                | 0.0              |
| 460       | 21166            | 20.4             | 590       | 88397            | 9.8              | 720       | 7161             | 0.0              | 850       | 123              | 0.0              | 980       | 2                | 0.0              |
| 465       | 19092            | 20.1             | 595       | 91428            | 7.3              | 725       | 6067             | 0.0              | 855       | 106              | 0.0              | 985       | 13               | 0.0              |
| 470       | 14951            | 17.2             | 600       | 93452            | 5.3              | 730       | 5164             | 0.0              | 860       | 95               | 0.0              | 990       | 16               | 0.0              |
| 475       | 12606            | 15.7             | 605       | 93959            | 3.7              | 735       | 4393             | 0.0              | 865       | 82               | 0.0              | 995       | 20               | 0.0              |
| 480       | 13323            | 18.0             | 610       | 93079            | 2.5              | 740       | 3694             | 0.0              | 870       | 77               | 0.0              | 1000      | 0                | 0.0              |
| 485       | 15164            | 21.9             | 615       | 90707            | 1.7              | 745       | 3157             | 0.0              | 875       | 65               | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2407-157-9

TM-30-18

### Summary

$R_f = 84.7$   
 $R_g = 94.6$   
 $CIE\ R_a = 80.9$   
 $R_g = -1.5$



### Color Vector Graphics




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)