

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P358968

Luminaire Tested: NVN-SA2D-740-U-5WQ

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P358968  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA2D-740-U-5WQ  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(2) 70 CRI, 4000K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V WIDE OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16518 lumens  
Efficiency: N/A  
Efficacy: 128.0 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B4 - U0 - G2


Input Watts (W): 129  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P358968  
 CATALOG NUMBER: NVN-SA2D-740-U-5WQ

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P358968  
CATALOG NUMBER: NVN-SA2D-740-U-5WQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P358968

CATALOG NUMBER: NVN-SA2D-740-U-5WQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 8259.0   | 0.0    | 8259.0  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 8259.0   | 0.0    | 8259.0  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 16518.0  | 0.0    | 16518.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 126.9   | 0.8       |
| 10°-20°   | 370.6   | 2.2       |
| 20°-30°   | 631.9   | 3.8       |
| 30°-40°   | 987.4   | 6.0       |
| 40°-50°   | 1673.3  | 10.1      |
| 50°-60°   | 3051.5  | 18.5      |
| 60°-70°   | 5253.3  | 31.8      |
| 70°-80°   | 4117.8  | 24.9      |
| 80°-90°   | 305.3   | 1.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 16518.0 | 100.0     |
| 0°-180°   | 16518.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P358968


CATALOG NUMBER: NVN-SA2D-740-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 564.7  | 3.4       |                         |      |         |
| FM   | (30°-60°)   | 2856.1 | 17.3      |                         |      |         |
| FH   | (60°-80°)   | 4685.5 | 28.4      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 152.7  | 0.9       |                         |      | G2/225  |
| BL   | (0°-30°)    | 564.7  | 3.4       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 2856.1 | 17.3      | B3/5000                 |      |         |
| BH   | (60°-80°)   | 4685.5 | 28.4      | B4/5000                 |      | G2/5000 |
| BVH  | (80°-90°)   | 152.7  | 0.9       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G2**

Type V Short





REPORT NUMBER: P358968

CATALOG NUMBER: NVN-SA2D-740-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1359.4 | 1359.4 | 1359.4 | 1359.4 | 1359.4 | 1359.4 | 1359.4 | 1359.4 | 1359.4 | 1359.4 | 1359.4 |
| 2.5°  | 1353.4 | 1355.1 | 1353.4 | 1354.5 | 1351.8 | 1352.9 | 1352.9 | 1352.9 | 1352.3 | 1352.9 | 1351.8 |
| 5°    | 1341.4 | 1342.5 | 1340.3 | 1341.4 | 1339.8 | 1341.4 | 1341.9 | 1341.4 | 1340.3 | 1340.9 | 1338.7 |
| 7.5°  | 1323.4 | 1324.5 | 1322.8 | 1324.5 | 1322.3 | 1325.0 | 1324.5 | 1322.8 | 1321.2 | 1321.2 | 1319.0 |
| 10°   | 1313.5 | 1314.1 | 1309.7 | 1308.1 | 1303.2 | 1304.2 | 1305.9 | 1307.5 | 1309.2 | 1312.4 | 1311.9 |
| 12.5° | 1314.1 | 1314.1 | 1307.5 | 1300.4 | 1293.3 | 1295.0 | 1297.7 | 1303.7 | 1310.3 | 1316.3 | 1316.8 |
| 15°   | 1319.5 | 1319.0 | 1309.2 | 1297.7 | 1292.8 | 1297.7 | 1299.3 | 1303.2 | 1313.5 | 1323.9 | 1324.5 |
| 17.5° | 1323.4 | 1323.4 | 1308.1 | 1295.0 | 1294.4 | 1302.1 | 1301.5 | 1303.2 | 1314.6 | 1329.9 | 1330.5 |
| 20°   | 1330.5 | 1330.5 | 1310.8 | 1296.6 | 1296.6 | 1304.8 | 1305.3 | 1308.1 | 1319.5 | 1336.5 | 1339.2 |
| 22.5° | 1346.3 | 1346.9 | 1326.1 | 1314.6 | 1315.7 | 1320.6 | 1322.3 | 1326.6 | 1337.0 | 1355.6 | 1358.9 |
| 25°   | 1368.7 | 1369.8 | 1348.5 | 1341.9 | 1345.8 | 1355.1 | 1354.0 | 1357.2 | 1368.7 | 1386.8 | 1390.0 |
| 27.5° | 1399.9 | 1397.1 | 1377.5 | 1374.7 | 1378.6 | 1385.1 | 1384.6 | 1385.1 | 1394.4 | 1410.8 | 1414.6 |
| 30°   | 1440.3 | 1439.2 | 1425.0 | 1426.6 | 1425.0 | 1422.8 | 1423.4 | 1427.7 | 1432.7 | 1445.8 | 1449.6 |
| 32.5° | 1479.6 | 1480.7 | 1472.0 | 1480.2 | 1492.2 | 1500.4 | 1487.8 | 1475.8 | 1470.4 | 1477.5 | 1480.7 |
| 35°   | 1550.7 | 1553.4 | 1539.7 | 1534.3 | 1550.7 | 1574.7 | 1539.2 | 1519.5 | 1530.5 | 1539.7 | 1542.5 |
| 37.5° | 1671.4 | 1673.1 | 1650.1 | 1628.3 | 1616.2 | 1639.2 | 1603.7 | 1605.3 | 1643.6 | 1661.0 | 1660.5 |
| 40°   | 1809.1 | 1809.7 | 1794.4 | 1775.2 | 1754.5 | 1759.9 | 1745.7 | 1750.1 | 1775.2 | 1791.1 | 1795.5 |
| 42.5° | 1973.0 | 1971.4 | 1947.4 | 1920.0 | 1914.0 | 1919.5 | 1895.4 | 1892.2 | 1921.1 | 1949.5 | 1950.1 |
| 45°   | 2185.6 | 2181.8 | 2150.6 | 2120.6 | 2091.6 | 2079.6 | 2073.6 | 2089.4 | 2129.3 | 2155.5 | 2156.1 |
| 47.5° | 2414.5 | 2404.1 | 2387.8 | 2363.7 | 2338.6 | 2326.6 | 2316.7 | 2324.4 | 2353.3 | 2363.7 | 2364.8 |
| 50°   | 2650.0 | 2652.2 | 2655.5 | 2646.2 | 2636.9 | 2633.1 | 2607.4 | 2592.6 | 2601.4 | 2582.3 | 2579.5 |
| 52.5° | 2929.2 | 2933.6 | 2965.3 | 2992.1 | 3007.9 | 3016.1 | 2967.5 | 2916.7 | 2888.3 | 2851.1 | 2840.2 |
| 55°   | 3258.7 | 3265.8 | 3312.3 | 3386.6 | 3463.1 | 3503.5 | 3415.5 | 3320.4 | 3232.5 | 3163.1 | 3140.7 |
| 57.5° | 3625.9 | 3638.5 | 3702.4 | 3845.0 | 4001.8 | 4097.4 | 3948.8 | 3776.1 | 3606.2 | 3506.2 | 3488.7 |
| 60°   | 4056.4 | 4068.5 | 4157.0 | 4361.3 | 4615.4 | 4759.1 | 4534.0 | 4251.5 | 4040.1 | 3944.4 | 3912.2 |
| 62.5° | 4569.0 | 4570.1 | 4678.8 | 4917.6 | 5253.1 | 5453.0 | 5148.1 | 4770.6 | 4552.6 | 4437.3 | 4406.1 |
| 65°   | 5120.3 | 5123.0 | 5235.6 | 5493.5 | 5840.4 | 6057.9 | 5713.7 | 5320.3 | 5053.6 | 4883.7 | 4859.6 |
| 67.5° | 5509.9 | 5521.3 | 5639.9 | 5950.3 | 6274.8 | 6471.0 | 6114.7 | 5670.0 | 5361.8 | 5159.1 | 5138.9 |
| 70°   | 5447.6 | 5492.4 | 5631.7 | 5994.0 | 6445.3 | 6725.0 | 6179.7 | 5628.4 | 5221.9 | 4982.6 | 4965.6 |
| 72.5° | 4750.9 | 4836.7 | 5022.5 | 5497.8 | 6219.6 | 6604.8 | 5825.1 | 5041.1 | 4581.0 | 4377.2 | 4346.6 |
| 75°   | 3235.2 | 3374.5 | 3654.8 | 4340.6 | 5313.7 | 5718.6 | 4903.9 | 4019.3 | 3586.5 | 3304.6 | 3283.8 |
| 77.5° | 1442.5 | 1474.2 | 1829.3 | 2618.9 | 3666.9 | 4106.7 | 3563.0 | 2629.3 | 1973.6 | 1574.2 | 1490.0 |
| 80°   | 402.1  | 407.1  | 543.1  | 975.3  | 1835.3 | 2412.9 | 1970.3 | 1024.5 | 575.9  | 406.0  | 382.5  |
| 82.5° | 127.9  | 138.8  | 169.4  | 253.0  | 616.9  | 1101.0 | 633.3  | 273.2  | 194.5  | 155.2  | 139.9  |
| 85°   | 62.3   | 61.7   | 85.8   | 102.7  | 157.4  | 243.7  | 167.7  | 126.8  | 110.9  | 73.8   | 66.7   |
| 87.5° | 26.2   | 26.8   | 39.9   | 36.1   | 45.9   | 39.3   | 54.1   | 56.8   | 59.6   | 32.8   | 28.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021


### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 |      |       |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R9:  | -29.7 |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R10: | 46.2  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R11: | 68.8  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R12: | 45.6  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R13: | 69.5  |
| CIE z:                    | 0.2385  | R6:       | 68.3 | R14: | 90.7  |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



### Test Conditions

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 2.7              | 620       | 97577            | 25.4             | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 4.8              | 625       | 90158            | 19.9             | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 8.0              | 630       | 82240            | 14.9             | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 13.3             | 635       | 74361            | 11.2             | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 20.2             | 640       | 66994            | 8.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 28.5             | 645       | 60405            | 5.8              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 37.4             | 650       | 53806            | 3.9              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 44.9             | 655       | 47610            | 2.7              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 52.6             | 660       | 42018            | 1.8              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 58.4             | 665       | 36742            | 1.2              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.0              | 540       | 96845            | 63.1             | 670       | 32105            | 0.7              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.0              | 545       | 100829           | 67.1             | 675       | 27946            | 0.5              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 0.1              | 550       | 105648           | 71.8             | 680       | 24146            | 0.3              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 0.2              | 555       | 110017           | 75.1             | 685       | 21191            | 0.2              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 0.5              | 560       | 114586           | 77.9             | 690       | 18544            | 0.1              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 1.2              | 565       | 118987           | 79.1             | 695       | 16058            | 0.1              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 2.1              | 570       | 122326           | 79.5             | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 2.9              | 575       | 125968           | 78.4             | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 2.7              | 580       | 127613           | 75.8             | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 2.0              | 585       | 129466           | 71.9             | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 1.5              | 590       | 128813           | 66.6             | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 1.3              | 595       | 126387           | 59.9             | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 1.0              | 600       | 123477           | 53.2             | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 1.1              | 605       | 118718           | 46.0             | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 1.2              | 610       | 112091           | 38.5             | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 1.7              | 615       | 105039           | 31.7             | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 10425.8**
**S/P: 1.47**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 2304                          | 0.0                            | 490               | 19043                         | 29.3                           | 620               | 97577                         | 1.2                            | 750               | 4830                          | 0.0                            | 880               | 3505                          | 0.0                            |
| 365               | 2150                          | 0.0                            | 495               | 26606                         | 43.0                           | 625               | 90158                         | 0.8                            | 755               | 4664                          | 0.0                            | 885               | 2991                          | 0.0                            |
| 370               | 2146                          | 0.0                            | 500               | 36376                         | 60.8                           | 630               | 82240                         | 0.5                            | 760               | 4006                          | 0.0                            | 890               | 2327                          | 0.0                            |
| 375               | 2332                          | 0.0                            | 505               | 47714                         | 81.1                           | 635               | 74361                         | 0.3                            | 765               | 3715                          | 0.0                            | 895               | 2775                          | 0.0                            |
| 380               | 2527                          | 0.0                            | 510               | 58741                         | 99.6                           | 640               | 66994                         | 0.2                            | 770               | 3696                          | 0.0                            | 900               | 2141                          | 0.0                            |
| 385               | 2304                          | 0.0                            | 515               | 68716                         | 113.9                          | 645               | 60405                         | 0.1                            | 775               | 3117                          | 0.0                            | 905               | 2421                          | 0.0                            |
| 390               | 2064                          | 0.0                            | 520               | 77136                         | 122.6                          | 650               | 53806                         | 0.1                            | 780               | 3062                          | 0.0                            | 910               | 2200                          | 0.0                            |
| 395               | 1856                          | 0.0                            | 525               | 83567                         | 125.0                          | 655               | 47610                         | 0.0                            | 785               | 2907                          | 0.0                            | 915               | 2716                          | 0.0                            |
| 400               | 1856                          | 0.0                            | 530               | 89283                         | 123.1                          | 660               | 42018                         | 0.0                            | 790               | 2655                          | 0.0                            | 920               | 2656                          | 0.0                            |
| 405               | 2374                          | 0.1                            | 535               | 94097                         | 117.3                          | 665               | 36742                         | 0.0                            | 795               | 2467                          | 0.0                            | 925               | 2671                          | 0.0                            |
| 410               | 4084                          | 0.2                            | 540               | 96845                         | 107.0                          | 670               | 32105                         | 0.0                            | 800               | 2609                          | 0.0                            | 930               | 3292                          | 0.0                            |
| 415               | 8543                          | 0.9                            | 545               | 100829                        | 96.7                           | 675               | 27946                         | 0.0                            | 805               | 2293                          | 0.0                            | 935               | 3188                          | 0.0                            |
| 420               | 18394                         | 3.0                            | 550               | 105648                        | 86.4                           | 680               | 24146                         | 0.0                            | 810               | 2188                          | 0.0                            | 940               | 1997                          | 0.0                            |
| 425               | 37987                         | 9.3                            | 555               | 110017                        | 75.2                           | 685               | 21191                         | 0.0                            | 815               | 2386                          | 0.0                            | 945               | 2623                          | 0.0                            |
| 430               | 67605                         | 23.0                           | 560               | 114586                        | 64.0                           | 690               | 18544                         | 0.0                            | 820               | 2712                          | 0.0                            | 950               | 2969                          | 0.0                            |
| 435               | 102160                        | 45.7                           | 565               | 118987                        | 53.4                           | 695               | 16058                         | 0.0                            | 825               | 2473                          | 0.0                            | 955               | 2277                          | 0.0                            |
| 440               | 135103                        | 75.5                           | 570               | 122326                        | 43.2                           | 700               | 14133                         | 0.0                            | 830               | 1969                          | 0.0                            | 960               | 4267                          | 0.0                            |
| 445               | 140126                        | 93.8                           | 575               | 125968                        | 34.3                           | 705               | 12309                         | 0.0                            | 835               | 1917                          | 0.0                            | 965               | 2034                          | 0.0                            |
| 450               | 102339                        | 79.3                           | 580               | 127613                        | 26.3                           | 710               | 11142                         | 0.0                            | 840               | 2248                          | 0.0                            | 970               | 3586                          | 0.0                            |
| 455               | 58751                         | 51.3                           | 585               | 129466                        | 19.8                           | 715               | 10143                         | 0.0                            | 845               | 2266                          | 0.0                            | 975               | 2505                          | 0.0                            |
| 460               | 36892                         | 35.6                           | 590               | 128813                        | 14.3                           | 720               | 9072                          | 0.0                            | 850               | 2558                          | 0.0                            | 980               | 2666                          | 0.0                            |
| 465               | 24637                         | 26.0                           | 595               | 126387                        | 10.1                           | 725               | 8130                          | 0.0                            | 855               | 2767                          | 0.0                            | 985               | 2934                          | 0.0                            |
| 470               | 16738                         | 19.3                           | 600               | 123477                        | 7.0                            | 730               | 7149                          | 0.0                            | 860               | 2826                          | 0.0                            | 990               | 4120                          | 0.0                            |
| 475               | 13456                         | 16.8                           | 605               | 118718                        | 4.7                            | 735               | 6311                          | 0.0                            | 865               | 2385                          | 0.0                            | 995               | 3858                          | 0.0                            |
| 480               | 13081                         | 17.7                           | 610               | 112091                        | 3.0                            | 740               | 5711                          | 0.0                            | 870               | 3194                          | 0.0                            | 1000              | 3405                          | 0.0                            |
| 485               | 14734                         | 21.4                           | 615               | 105039                        | 1.9                            | 745               | 5111                          | 0.0                            | 875               | 3189                          | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2101-121-2

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 3927.2**

**M/P: 0.55**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 15.8             | 620       | 97577            | 0.1              | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 22.0             | 625       | 90158            | 0.0              | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 29.2             | 630       | 82240            | 0.0              | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 36.6             | 635       | 74361            | 0.0              | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 42.2             | 640       | 66994            | 0.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 44.9             | 645       | 60405            | 0.0              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 44.9             | 650       | 53806            | 0.0              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 42.4             | 655       | 47610            | 0.0              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 38.6             | 660       | 42018            | 0.0              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 33.9             | 665       | 36742            | 0.0              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.2              | 540       | 96845            | 28.3             | 670       | 32105            | 0.0              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.6              | 545       | 100829           | 23.4             | 675       | 27946            | 0.0              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 2.1              | 550       | 105648           | 19.0             | 680       | 24146            | 0.0              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 5.9              | 555       | 110017           | 14.8             | 685       | 21191            | 0.0              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 14.3             | 560       | 114586           | 11.3             | 690       | 18544            | 0.0              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 27.3             | 565       | 118987           | 8.4              | 695       | 16058            | 0.0              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 45.1             | 570       | 122326           | 6.0              | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 55.3             | 575       | 125968           | 4.2              | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 47.2             | 580       | 127613           | 2.9              | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 30.8             | 585       | 129466           | 1.9              | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 21.7             | 590       | 128813           | 1.3              | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 16.1             | 595       | 126387           | 0.8              | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 12.0             | 600       | 123477           | 0.5              | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 10.3             | 605       | 118718           | 0.3              | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 10.5             | 610       | 112091           | 0.2              | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 12.1             | 615       | 105039           | 0.1              | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2



TM-30-18

### Summary

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



### Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2101-121-2

**TM-30-18**

**Measure Comparisons**



(END OF REPORT)