

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P359017

Luminaire Tested: NVN-SA3D-740-U-5MQ

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P359017  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA3D-740-U-5MQ  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(3) 70 CRI, 4000K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V  
MEDIUM OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 25147 lumens  
Efficiency: N/A  
Efficacy: 131.7 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G3


Input Watts (W): 191  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P359017  
 CATALOG NUMBER: NVN-SA3D-740-U-5MQ

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.4 fc  
 Type V - Short - N/A

REPORT NUMBER: P359017  
CATALOG NUMBER: NVN-SA3D-740-U-5MQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P359017

CATALOG NUMBER: NVN-SA3D-740-U-5MQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 12573.5  | 0.0    | 12573.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 12573.5  | 0.0    | 12573.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 25147.0  | 0.0    | 25147.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 260.1   | 1.0       |
| 10°-20°   | 763.6   | 3.0       |
| 20°-30°   | 1300.0  | 5.2       |
| 30°-40°   | 2061.7  | 8.2       |
| 40°-50°   | 3355.1  | 13.3      |
| 50°-60°   | 5531.9  | 22.0      |
| 60°-70°   | 8121.0  | 32.3      |
| 70°-80°   | 3591.1  | 14.3      |
| 80°-90°   | 162.6   | 0.6       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 25147.0 | 100.0     |
| 0°-180°   | 25147.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P359017


CATALOG NUMBER: NVN-SA3D-740-U-5MQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1161.9 | 4.6       |                         |      |         |
| FM   | (30°-60°)   | 5474.3 | 21.8      |                         |      |         |
| FH   | (60°-80°)   | 5856.0 | 23.3      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 81.3   | 0.3       |                         |      | G1/100  |
| BL   | (0°-30°)    | 1161.9 | 4.6       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 5474.3 | 21.8      | B4/8500                 |      |         |
| BH   | (60°-80°)   | 5856.0 | 23.3      | B5                      |      | G3/7500 |
| BVH  | (80°-90°)   | 81.3   | 0.3       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B5-U0-G3**

Type V Short





REPORT NUMBER: P359017

CATALOG NUMBER: NVN-SA3D-740-U-5MQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°     | 45°     | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|---------|---------|--------|--------|--------|--------|--------|
| 0°    | 2746.4 | 2746.4 | 2746.4 | 2746.4 | 2746.4  | 2746.4  | 2746.4 | 2746.4 | 2746.4 | 2746.4 | 2746.4 |
| 2.5°  | 2742.3 | 2739.8 | 2745.6 | 2744.8 | 2739.8  | 2740.6  | 2740.6 | 2743.1 | 2743.1 | 2741.5 | 2741.5 |
| 5°    | 2732.3 | 2730.6 | 2737.3 | 2737.3 | 2732.3  | 2734.0  | 2735.6 | 2738.1 | 2737.3 | 2735.6 | 2734.8 |
| 7.5°  | 2719.8 | 2719.0 | 2725.6 | 2725.6 | 2722.3  | 2724.0  | 2722.3 | 2723.1 | 2721.5 | 2719.8 | 2717.3 |
| 10°   | 2699.0 | 2700.7 | 2706.5 | 2708.2 | 2708.2  | 2709.0  | 2707.3 | 2703.2 | 2700.7 | 2698.2 | 2695.7 |
| 12.5° | 2679.9 | 2679.0 | 2687.4 | 2691.5 | 2698.2  | 2705.7  | 2700.7 | 2689.0 | 2684.0 | 2679.0 | 2677.4 |
| 15°   | 2667.4 | 2668.2 | 2676.5 | 2684.0 | 2695.7  | 2711.5  | 2705.7 | 2687.4 | 2677.4 | 2671.5 | 2669.9 |
| 17.5° | 2664.9 | 2666.5 | 2677.4 | 2690.7 | 2703.2  | 2720.6  | 2717.3 | 2699.0 | 2682.4 | 2671.5 | 2669.0 |
| 20°   | 2670.7 | 2671.5 | 2688.2 | 2707.3 | 2729.0  | 2745.6  | 2738.1 | 2718.1 | 2695.7 | 2679.0 | 2674.9 |
| 22.5° | 2681.5 | 2684.9 | 2705.7 | 2735.6 | 2768.9  | 2791.4  | 2782.2 | 2748.1 | 2713.2 | 2692.3 | 2686.5 |
| 25°   | 2715.7 | 2716.5 | 2744.8 | 2785.6 | 2825.5  | 2851.3  | 2840.5 | 2792.2 | 2747.3 | 2724.0 | 2716.5 |
| 27.5° | 2786.4 | 2788.9 | 2817.2 | 2864.6 | 2898.7  | 2915.4  | 2908.7 | 2869.6 | 2831.3 | 2806.4 | 2808.9 |
| 30°   | 2888.8 | 2892.1 | 2923.7 | 2976.1 | 2997.0  | 3001.1  | 2999.4 | 2981.1 | 2946.2 | 2912.9 | 2915.4 |
| 32.5° | 3013.6 | 3015.3 | 3057.7 | 3105.1 | 3121.8  | 3125.1  | 3121.8 | 3105.1 | 3063.5 | 3018.6 | 3021.1 |
| 35°   | 3174.2 | 3179.2 | 3220.0 | 3265.8 | 3279.1  | 3285.7  | 3279.9 | 3258.3 | 3215.0 | 3170.9 | 3169.2 |
| 37.5° | 3372.3 | 3373.1 | 3415.6 | 3463.0 | 3479.7  | 3481.3  | 3474.7 | 3460.5 | 3406.4 | 3366.5 | 3364.0 |
| 40°   | 3602.0 | 3605.3 | 3655.3 | 3706.0 | 3712.7  | 3705.2  | 3714.4 | 3706.0 | 3650.3 | 3604.5 | 3612.0 |
| 42.5° | 3881.6 | 3889.1 | 3949.1 | 3999.0 | 3979.8  | 3975.7  | 3981.5 | 3984.0 | 3939.1 | 3883.3 | 3878.3 |
| 45°   | 4207.1 | 4213.7 | 4288.6 | 4328.6 | 4316.1  | 4288.6  | 4300.3 | 4320.2 | 4257.8 | 4188.7 | 4195.4 |
| 47.5° | 4578.2 | 4594.9 | 4674.8 | 4712.2 | 4681.4  | 4644.0  | 4666.5 | 4696.4 | 4623.2 | 4537.5 | 4533.3 |
| 50°   | 4991.0 | 5011.8 | 5118.4 | 5170.8 | 5140.0  | 5070.9  | 5108.4 | 5128.4 | 5022.7 | 4912.0 | 4902.8 |
| 52.5° | 5431.3 | 5452.1 | 5586.1 | 5694.3 | 5674.3  | 5567.0  | 5619.4 | 5598.6 | 5477.1 | 5328.1 | 5316.4 |
| 55°   | 5929.8 | 5938.1 | 6083.0 | 6257.7 | 6277.7  | 6198.6  | 6195.3 | 6161.2 | 5981.4 | 5809.1 | 5800.8 |
| 57.5° | 6442.5 | 6448.3 | 6635.6 | 6842.0 | 6936.0  | 6936.0  | 6842.8 | 6770.4 | 6531.5 | 6331.8 | 6311.0 |
| 60°   | 6995.9 | 7016.7 | 7224.0 | 7504.4 | 7724.2  | 7789.1  | 7624.3 | 7427.0 | 7167.4 | 6923.5 | 6899.4 |
| 62.5° | 7488.6 | 7512.8 | 7829.9 | 8247.7 | 8600.5  | 8836.9  | 8434.1 | 8112.8 | 7640.1 | 7248.9 | 7203.2 |
| 65°   | 7551.1 | 7616.0 | 8077.9 | 8834.4 | 9624.2  | 10096.1 | 9323.8 | 8532.3 | 7670.9 | 7127.4 | 7080.8 |
| 67.5° | 6896.1 | 7005.9 | 7630.1 | 8807.8 | 10439.8 | 11452.7 | 9892.2 | 8292.6 | 7118.3 | 6517.4 | 6465.8 |
| 70°   | 5299.0 | 5458.8 | 6178.7 | 7704.2 | 10299.2 | 11889.6 | 9536.0 | 7259.8 | 5934.8 | 5288.2 | 5215.7 |
| 72.5° | 2907.1 | 2972.8 | 3620.3 | 5275.7 | 8256.8  | 10103.6 | 7953.9 | 5368.0 | 3935.7 | 3202.5 | 3081.0 |
| 75°   | 922.1  | 945.4  | 1275.0 | 2158.9 | 4670.6  | 6692.2  | 5052.6 | 2634.9 | 1450.6 | 1069.4 | 1057.0 |
| 77.5° | 409.5  | 412.0  | 461.1  | 630.0  | 1608.8  | 3390.6  | 1932.5 | 717.4  | 494.4  | 431.9  | 446.1  |
| 80°   | 258.8  | 258.8  | 285.5  | 312.1  | 437.8   | 984.6   | 522.7  | 341.2  | 291.3  | 270.5  | 276.3  |
| 82.5° | 124.0  | 137.3  | 185.6  | 199.7  | 240.5   | 331.2   | 268.0  | 223.0  | 194.7  | 144.8  | 134.8  |
| 85°   | 81.6   | 68.2   | 117.3  | 132.3  | 139.8   | 159.0   | 155.6  | 147.3  | 127.3  | 72.4   | 80.7   |
| 87.5° | 36.6   | 35.0   | 60.8   | 55.8   | 52.4    | 39.9    | 59.9   | 74.1   | 71.6   | 35.8   | 35.8   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 |      |       |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R9:  | -29.7 |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R10: | 46.2  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R11: | 68.8  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R12: | 45.6  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R13: | 69.5  |
| CIE z:                    | 0.2385  | R6:       | 68.3 | R14: | 90.7  |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



### Test Conditions

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



CCT = 3905K  
 CIE  $x$  = 0.3841  
 CIE  $y$  = 0.3774  
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 2.7              | 620       | 97577            | 25.4             | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 4.8              | 625       | 90158            | 19.9             | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 8.0              | 630       | 82240            | 14.9             | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 13.3             | 635       | 74361            | 11.2             | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 20.2             | 640       | 66994            | 8.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 28.5             | 645       | 60405            | 5.8              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 37.4             | 650       | 53806            | 3.9              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 44.9             | 655       | 47610            | 2.7              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 52.6             | 660       | 42018            | 1.8              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 58.4             | 665       | 36742            | 1.2              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.0              | 540       | 96845            | 63.1             | 670       | 32105            | 0.7              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.0              | 545       | 100829           | 67.1             | 675       | 27946            | 0.5              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 0.1              | 550       | 105648           | 71.8             | 680       | 24146            | 0.3              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 0.2              | 555       | 110017           | 75.1             | 685       | 21191            | 0.2              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 0.5              | 560       | 114586           | 77.9             | 690       | 18544            | 0.1              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 1.2              | 565       | 118987           | 79.1             | 695       | 16058            | 0.1              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 2.1              | 570       | 122326           | 79.5             | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 2.9              | 575       | 125968           | 78.4             | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 2.7              | 580       | 127613           | 75.8             | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 2.0              | 585       | 129466           | 71.9             | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 1.5              | 590       | 128813           | 66.6             | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 1.3              | 595       | 126387           | 59.9             | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 1.0              | 600       | 123477           | 53.2             | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 1.1              | 605       | 118718           | 46.0             | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 1.2              | 610       | 112091           | 38.5             | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 1.7              | 615       | 105039           | 31.7             | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8

S/P: 1.47

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 2304                          | 0.0                            | 490               | 19043                         | 29.3                           | 620               | 97577                         | 1.2                            | 750               | 4830                          | 0.0                            | 880               | 3505                          | 0.0                            |
| 365               | 2150                          | 0.0                            | 495               | 26606                         | 43.0                           | 625               | 90158                         | 0.8                            | 755               | 4664                          | 0.0                            | 885               | 2991                          | 0.0                            |
| 370               | 2146                          | 0.0                            | 500               | 36376                         | 60.8                           | 630               | 82240                         | 0.5                            | 760               | 4006                          | 0.0                            | 890               | 2327                          | 0.0                            |
| 375               | 2332                          | 0.0                            | 505               | 47714                         | 81.1                           | 635               | 74361                         | 0.3                            | 765               | 3715                          | 0.0                            | 895               | 2775                          | 0.0                            |
| 380               | 2527                          | 0.0                            | 510               | 58741                         | 99.6                           | 640               | 66994                         | 0.2                            | 770               | 3696                          | 0.0                            | 900               | 2141                          | 0.0                            |
| 385               | 2304                          | 0.0                            | 515               | 68716                         | 113.9                          | 645               | 60405                         | 0.1                            | 775               | 3117                          | 0.0                            | 905               | 2421                          | 0.0                            |
| 390               | 2064                          | 0.0                            | 520               | 77136                         | 122.6                          | 650               | 53806                         | 0.1                            | 780               | 3062                          | 0.0                            | 910               | 2200                          | 0.0                            |
| 395               | 1856                          | 0.0                            | 525               | 83567                         | 125.0                          | 655               | 47610                         | 0.0                            | 785               | 2907                          | 0.0                            | 915               | 2716                          | 0.0                            |
| 400               | 1856                          | 0.0                            | 530               | 89283                         | 123.1                          | 660               | 42018                         | 0.0                            | 790               | 2655                          | 0.0                            | 920               | 2656                          | 0.0                            |
| 405               | 2374                          | 0.1                            | 535               | 94097                         | 117.3                          | 665               | 36742                         | 0.0                            | 795               | 2467                          | 0.0                            | 925               | 2671                          | 0.0                            |
| 410               | 4084                          | 0.2                            | 540               | 96845                         | 107.0                          | 670               | 32105                         | 0.0                            | 800               | 2609                          | 0.0                            | 930               | 3292                          | 0.0                            |
| 415               | 8543                          | 0.9                            | 545               | 100829                        | 96.7                           | 675               | 27946                         | 0.0                            | 805               | 2293                          | 0.0                            | 935               | 3188                          | 0.0                            |
| 420               | 18394                         | 3.0                            | 550               | 105648                        | 86.4                           | 680               | 24146                         | 0.0                            | 810               | 2188                          | 0.0                            | 940               | 1997                          | 0.0                            |
| 425               | 37987                         | 9.3                            | 555               | 110017                        | 75.2                           | 685               | 21191                         | 0.0                            | 815               | 2386                          | 0.0                            | 945               | 2623                          | 0.0                            |
| 430               | 67605                         | 23.0                           | 560               | 114586                        | 64.0                           | 690               | 18544                         | 0.0                            | 820               | 2712                          | 0.0                            | 950               | 2969                          | 0.0                            |
| 435               | 102160                        | 45.7                           | 565               | 118987                        | 53.4                           | 695               | 16058                         | 0.0                            | 825               | 2473                          | 0.0                            | 955               | 2277                          | 0.0                            |
| 440               | 135103                        | 75.5                           | 570               | 122326                        | 43.2                           | 700               | 14133                         | 0.0                            | 830               | 1969                          | 0.0                            | 960               | 4267                          | 0.0                            |
| 445               | 140126                        | 93.8                           | 575               | 125968                        | 34.3                           | 705               | 12309                         | 0.0                            | 835               | 1917                          | 0.0                            | 965               | 2034                          | 0.0                            |
| 450               | 102339                        | 79.3                           | 580               | 127613                        | 26.3                           | 710               | 11142                         | 0.0                            | 840               | 2248                          | 0.0                            | 970               | 3586                          | 0.0                            |
| 455               | 58751                         | 51.3                           | 585               | 129466                        | 19.8                           | 715               | 10143                         | 0.0                            | 845               | 2266                          | 0.0                            | 975               | 2505                          | 0.0                            |
| 460               | 36892                         | 35.6                           | 590               | 128813                        | 14.3                           | 720               | 9072                          | 0.0                            | 850               | 2558                          | 0.0                            | 980               | 2666                          | 0.0                            |
| 465               | 24637                         | 26.0                           | 595               | 126387                        | 10.1                           | 725               | 8130                          | 0.0                            | 855               | 2767                          | 0.0                            | 985               | 2934                          | 0.0                            |
| 470               | 16738                         | 19.3                           | 600               | 123477                        | 7.0                            | 730               | 7149                          | 0.0                            | 860               | 2826                          | 0.0                            | 990               | 4120                          | 0.0                            |
| 475               | 13456                         | 16.8                           | 605               | 118718                        | 4.7                            | 735               | 6311                          | 0.0                            | 865               | 2385                          | 0.0                            | 995               | 3858                          | 0.0                            |
| 480               | 13081                         | 17.7                           | 610               | 112091                        | 3.0                            | 740               | 5711                          | 0.0                            | 870               | 3194                          | 0.0                            | 1000              | 3405                          | 0.0                            |
| 485               | 14734                         | 21.4                           | 615               | 105039                        | 1.9                            | 745               | 5111                          | 0.0                            | 875               | 3189                          | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2101-121-2

### Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2

M/P: 0.55

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 15.8             | 620       | 97577            | 0.1              | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 22.0             | 625       | 90158            | 0.0              | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 29.2             | 630       | 82240            | 0.0              | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 36.6             | 635       | 74361            | 0.0              | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 42.2             | 640       | 66994            | 0.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 44.9             | 645       | 60405            | 0.0              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 44.9             | 650       | 53806            | 0.0              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 42.4             | 655       | 47610            | 0.0              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 38.6             | 660       | 42018            | 0.0              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 33.9             | 665       | 36742            | 0.0              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.2              | 540       | 96845            | 28.3             | 670       | 32105            | 0.0              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.6              | 545       | 100829           | 23.4             | 675       | 27946            | 0.0              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 2.1              | 550       | 105648           | 19.0             | 680       | 24146            | 0.0              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 5.9              | 555       | 110017           | 14.8             | 685       | 21191            | 0.0              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 14.3             | 560       | 114586           | 11.3             | 690       | 18544            | 0.0              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 27.3             | 565       | 118987           | 8.4              | 695       | 16058            | 0.0              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 45.1             | 570       | 122326           | 6.0              | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 55.3             | 575       | 125968           | 4.2              | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 47.2             | 580       | 127613           | 2.9              | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 30.8             | 585       | 129466           | 1.9              | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 21.7             | 590       | 128813           | 1.3              | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 16.1             | 595       | 126387           | 0.8              | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 12.0             | 600       | 123477           | 0.5              | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 10.3             | 605       | 118718           | 0.3              | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 10.5             | 610       | 112091           | 0.2              | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 12.1             | 615       | 105039           | 0.1              | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

TM-30-18

### Summary

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)