

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1385281

Luminaire Tested: **VAL-T-SB5C-722-U-SLR-HSS**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



Test Information

Test Method: LM-79-08
 Report Number: P1385281
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 02/18/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: VAL-T-SB5C-722-U-SLR-HSS
 Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 5SQUARE 252W 70CRI
 2200K FIXTURE w/ 90° Spill Light Eliminator RIGHT OPTIC AND HOUSE SIDE
 SHIELD
 Light Source: (130) 2200K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER

Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a | good | reflector |
| b | good | lens |
| c | good | housing |
| d | good | cord |

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 22572.4 lumens
 Efficiency: N/A
 Efficacy: 89.6 lumens/watt
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
 IES Classification: Type III - Short
 BUG Rating: B2 - U0 - G4

Input Watts (W): 252
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: 0.98
 Total Harmonic Distortion (THDi): 7.9%
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 28.75 FT

REPORT NUMBER: P1385281
 CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 12.4 fc
 Type III - Short - N/A

REPORT NUMBER: P1385281
CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P1385281
 CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3648.9 | 0.0 | 3648.9 |
| | % Fixture | 16.2 | 0.0 | 16.2 |
| Street Side | Lumens | 18923.4 | 0.0 | 18923.4 |
| | % Fixture | 83.8 | 0.0 | 83.8 |
| Total | Lumens | 22572.4 | 0.0 | 22572.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 375.0 | 1.7 |
| 10°-20° | 1037.2 | 4.6 |
| 20°-30° | 1485.5 | 6.6 |
| 30°-40° | 1863.3 | 8.3 |
| 40°-50° | 3060.8 | 13.6 |
| 50°-60° | 5523.5 | 24.5 |
| 60°-70° | 6130.0 | 27.2 |
| 70°-80° | 2769.6 | 12.3 |
| 80°-90° | 327.5 | 1.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 22572.4 | 100.0 |
| 0°-180° | 22572.4 | 100.0 |




REPORT NUMBER: P1385281
 CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1933.5 | 8.6 | | | |
| FM (30°-60°) | 8571.3 | 38.0 | | | |
| FH (60°-80°) | 8124.6 | 36.0 | | | G4/12000 |
| FVH (80°-90°) | 294.0 | 1.3 | | | G3/500 |
| BL (0°-30°) | 964.2 | 4.3 | B2/1000 | | |
| BM (30°-60°) | 1876.3 | 8.3 | B2/2500 | | |
| BH (60°-80°) | 774.9 | 3.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 33.5 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G4
 Type III Short





REPORT NUMBER: P1385281

CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 |
| 2.5° | 4401.3 | 4397.2 | 4380.6 | 4276.6 | 4172.6 | 4082.5 | 3992.4 | 3902.3 | 3777.5 | 3680.5 | 3597.3 |
| 5° | 4817.2 | 4795.0 | 4706.3 | 4546.9 | 4373.6 | 4221.1 | 4047.9 | 3881.5 | 3694.4 | 3541.9 | 3382.5 |
| 7.5° | 5101.4 | 5079.2 | 4990.5 | 4727.1 | 4463.7 | 4276.6 | 4089.4 | 3916.2 | 3708.2 | 3507.2 | 3278.5 |
| 10° | 5233.1 | 5208.1 | 5108.3 | 4824.2 | 4519.2 | 4290.4 | 4103.3 | 3943.9 | 3770.6 | 3569.6 | 3285.4 |
| 12.5° | 5323.2 | 5292.7 | 5170.7 | 4844.9 | 4533.0 | 4304.3 | 4110.2 | 3957.7 | 3833.0 | 3715.2 | 3437.9 |
| 15° | 5378.7 | 5350.9 | 5240.0 | 4900.4 | 4540.0 | 4283.5 | 4054.8 | 3909.2 | 3867.6 | 3888.4 | 3756.7 |
| 17.5° | 5461.8 | 5435.5 | 5330.1 | 4969.7 | 4581.6 | 4248.9 | 3937.0 | 3777.5 | 3867.6 | 4054.8 | 4096.4 |
| 20° | 5572.7 | 5545.0 | 5434.1 | 5059.8 | 4616.2 | 4144.9 | 3715.2 | 3562.7 | 3791.4 | 4103.3 | 4318.2 |
| 22.5° | 5697.5 | 5675.3 | 5586.6 | 5163.8 | 4650.9 | 3992.4 | 3424.0 | 3354.7 | 3632.0 | 3964.7 | 4241.9 |
| 25° | 5850.0 | 5829.2 | 5746.0 | 5309.3 | 4685.5 | 3784.5 | 3174.5 | 3188.4 | 3424.0 | 3687.4 | 3971.6 |
| 27.5° | 6057.9 | 6038.5 | 5960.9 | 5489.6 | 4727.1 | 3569.6 | 2973.5 | 3042.8 | 3216.1 | 3396.3 | 3569.6 |
| 30° | 6286.6 | 6271.4 | 6210.4 | 5704.4 | 4810.3 | 3368.6 | 2855.7 | 2897.3 | 3015.1 | 3160.7 | 3264.6 |
| 32.5° | 6598.6 | 6573.6 | 6473.8 | 5905.4 | 4803.4 | 3216.1 | 2800.2 | 2758.6 | 2793.3 | 2911.1 | 3015.1 |
| 35° | 6986.7 | 6967.3 | 6889.7 | 6113.4 | 4678.6 | 3077.5 | 2772.5 | 2626.9 | 2606.2 | 2675.5 | 2779.4 |
| 37.5° | 7555.1 | 7538.4 | 7471.9 | 6453.0 | 4484.5 | 2904.2 | 2703.2 | 2488.3 | 2419.0 | 2467.5 | 2536.8 |
| 40° | 8407.6 | 8364.6 | 8192.7 | 6841.1 | 4269.7 | 2730.9 | 2578.4 | 2322.0 | 2224.9 | 2259.6 | 2335.8 |
| 42.5° | 9565.1 | 9483.3 | 9156.2 | 7361.0 | 3978.5 | 2564.6 | 2391.3 | 2155.6 | 2051.7 | 2072.4 | 2141.8 |
| 45° | 11048.4 | 10925.0 | 10431.5 | 8074.9 | 3673.6 | 2432.9 | 2197.2 | 1982.3 | 1871.4 | 1892.2 | 1968.5 |
| 47.5° | 12781.2 | 12612.1 | 11935.6 | 8823.5 | 3347.8 | 2356.6 | 2044.7 | 1809.1 | 1725.9 | 1774.4 | 1850.6 |
| 50° | 14825.9 | 14655.4 | 13973.4 | 9301.7 | 3084.4 | 2308.1 | 1926.9 | 1649.6 | 1615.0 | 1677.4 | 1739.7 |
| 52.5° | 17057.8 | 16815.2 | 15844.8 | 8996.8 | 2869.5 | 2266.5 | 1885.3 | 1538.7 | 1552.6 | 1601.1 | 1663.5 |
| 55° | 19227.3 | 18688.0 | 16531.0 | 7984.8 | 2592.3 | 2218.0 | 1913.0 | 1455.6 | 1490.2 | 1552.6 | 1601.1 |
| 57.5° | 20641.3 | 19704.2 | 15955.7 | 6432.2 | 2301.2 | 2162.6 | 1933.8 | 1414.0 | 1441.7 | 1511.0 | 1566.5 |
| 60° | 19407.5 | 18464.9 | 14694.3 | 4817.2 | 2051.7 | 2044.7 | 1899.2 | 1400.1 | 1358.5 | 1455.6 | 1504.1 |
| 62.5° | 15900.3 | 15124.0 | 12018.8 | 3077.5 | 1816.0 | 1822.9 | 1822.9 | 1393.2 | 1219.9 | 1344.7 | 1386.3 |
| 65° | 10923.7 | 10438.5 | 8497.7 | 1906.1 | 1483.3 | 1552.6 | 1656.6 | 1351.6 | 1074.3 | 1219.9 | 1261.5 |
| 67.5° | 7180.8 | 6824.5 | 5399.4 | 1178.3 | 1143.7 | 1275.4 | 1434.8 | 1268.4 | 963.4 | 1095.1 | 1122.9 |
| 70° | 3895.4 | 3625.0 | 2543.8 | 776.3 | 748.6 | 998.1 | 1129.8 | 1074.3 | 866.4 | 977.3 | 1005.0 |
| 72.5° | 2571.5 | 2349.7 | 1462.5 | 547.6 | 547.6 | 783.2 | 790.2 | 880.3 | 776.3 | 866.4 | 894.1 |
| 75° | 1933.8 | 1735.6 | 942.7 | 381.2 | 422.8 | 499.1 | 616.9 | 630.7 | 651.5 | 734.7 | 769.4 |
| 77.5° | 887.2 | 779.1 | 346.6 | 228.7 | 311.9 | 346.6 | 471.3 | 402.0 | 485.2 | 547.6 | 561.4 |
| 80° | 512.9 | 449.1 | 194.1 | 152.5 | 201.0 | 221.8 | 388.2 | 235.7 | 291.1 | 388.2 | 408.9 |
| 82.5° | 214.9 | 191.3 | 97.0 | 104.0 | 124.8 | 131.7 | 214.9 | 166.4 | 187.1 | 256.5 | 249.5 |
| 85° | 62.4 | 62.4 | 62.4 | 69.3 | 76.2 | 76.2 | 124.8 | 117.8 | 110.9 | 117.8 | 117.8 |
| 87.5° | 41.6 | 41.6 | 41.6 | 41.6 | 48.5 | 48.5 | 55.5 | 62.4 | 69.3 | 69.3 | 69.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P1385281

CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 |
| 2.5° | 3562.7 | 3514.1 | 3451.8 | 3361.7 | 3347.8 | 3299.3 | 3264.6 | 3299.3 | 3333.9 | 3396.3 | 3403.2 |
| 5° | 3299.3 | 3223.0 | 3077.5 | 2966.6 | 2841.8 | 2779.4 | 2772.5 | 2758.6 | 2800.2 | 2890.3 | 2945.8 |
| 7.5° | 3153.7 | 3029.0 | 2765.6 | 2571.5 | 2398.2 | 2335.8 | 2287.3 | 2328.9 | 2322.0 | 2439.8 | 2488.3 |
| 10° | 3119.1 | 2925.0 | 2557.6 | 2266.5 | 2051.7 | 1968.5 | 1920.0 | 1913.0 | 1926.9 | 1996.2 | 2044.7 |
| 12.5° | 3243.8 | 2994.3 | 2474.5 | 2044.7 | 1795.2 | 1705.1 | 1649.6 | 1601.1 | 1601.1 | 1615.0 | 1677.4 |
| 15° | 3521.1 | 3223.0 | 2523.0 | 1940.8 | 1670.4 | 1552.6 | 1462.5 | 1400.1 | 1351.6 | 1358.5 | 1365.5 |
| 17.5° | 3909.2 | 3555.7 | 2647.7 | 1906.1 | 1594.2 | 1469.4 | 1358.5 | 1296.1 | 1240.7 | 1226.8 | 1226.8 |
| 20° | 4214.2 | 3874.6 | 2744.8 | 1878.4 | 1531.8 | 1372.4 | 1275.4 | 1219.9 | 1171.4 | 1150.6 | 1150.6 |
| 22.5° | 4248.9 | 4006.3 | 2828.0 | 1843.7 | 1455.6 | 1275.4 | 1185.2 | 1136.7 | 1102.1 | 1095.1 | 1095.1 |
| 25° | 4020.1 | 3902.3 | 2800.2 | 1802.1 | 1379.3 | 1185.2 | 1115.9 | 1074.3 | 1039.7 | 1032.8 | 1039.7 |
| 27.5° | 3638.9 | 3576.5 | 2703.2 | 1746.7 | 1316.9 | 1115.9 | 1053.6 | 1018.9 | 984.2 | 977.3 | 984.2 |
| 30° | 3299.3 | 3230.0 | 2536.8 | 1656.6 | 1268.4 | 1060.5 | 991.2 | 956.5 | 921.9 | 921.9 | 928.8 |
| 32.5° | 3022.0 | 2952.7 | 2370.5 | 1552.6 | 1206.0 | 998.1 | 935.7 | 901.1 | 866.4 | 866.4 | 880.3 |
| 35° | 2772.5 | 2717.1 | 2238.8 | 1448.6 | 1143.7 | 942.7 | 873.3 | 845.6 | 817.9 | 811.0 | 824.8 |
| 37.5° | 2557.6 | 2529.9 | 2121.0 | 1337.7 | 1081.3 | 887.2 | 824.8 | 797.1 | 762.4 | 755.5 | 769.4 |
| 40° | 2349.7 | 2335.8 | 1989.3 | 1240.7 | 1005.0 | 831.8 | 769.4 | 741.6 | 700.1 | 700.1 | 713.9 |
| 42.5° | 2155.6 | 2148.7 | 1871.4 | 1178.3 | 935.7 | 776.3 | 707.0 | 679.3 | 644.6 | 644.6 | 658.5 |
| 45° | 2003.1 | 1996.2 | 1760.5 | 1143.7 | 866.4 | 713.9 | 651.5 | 616.9 | 589.2 | 596.1 | 610.0 |
| 47.5° | 1864.5 | 1850.6 | 1642.7 | 1150.6 | 831.8 | 672.3 | 589.2 | 554.5 | 533.7 | 547.6 | 568.4 |
| 50° | 1753.6 | 1739.7 | 1559.5 | 1157.5 | 776.3 | 616.9 | 540.6 | 506.0 | 492.1 | 512.9 | 533.7 |
| 52.5° | 1684.3 | 1670.4 | 1476.4 | 1115.9 | 707.0 | 575.3 | 492.1 | 471.3 | 471.3 | 492.1 | 506.0 |
| 55° | 1615.0 | 1601.1 | 1337.7 | 1025.8 | 630.7 | 533.7 | 457.5 | 443.6 | 443.6 | 464.4 | 478.3 |
| 57.5° | 1573.4 | 1545.7 | 1192.2 | 921.9 | 568.4 | 485.2 | 422.8 | 422.8 | 422.8 | 429.7 | 436.7 |
| 60° | 1511.0 | 1441.7 | 1039.7 | 790.2 | 519.8 | 436.7 | 395.1 | 388.2 | 388.2 | 381.2 | 388.2 |
| 62.5° | 1379.3 | 1261.5 | 873.3 | 672.3 | 464.4 | 395.1 | 360.4 | 353.5 | 332.7 | 311.9 | 318.8 |
| 65° | 1247.6 | 1067.4 | 693.1 | 561.4 | 402.0 | 339.6 | 318.8 | 311.9 | 277.3 | 249.5 | 256.5 |
| 67.5° | 1081.3 | 852.5 | 519.8 | 471.3 | 346.6 | 291.1 | 270.3 | 270.3 | 249.5 | 228.7 | 228.7 |
| 70° | 963.4 | 665.4 | 436.7 | 353.5 | 277.3 | 228.7 | 228.7 | 242.6 | 221.8 | 194.1 | 194.1 |
| 72.5° | 852.5 | 540.6 | 353.5 | 284.2 | 214.9 | 180.2 | 194.1 | 201.0 | 180.2 | 159.4 | 159.4 |
| 75° | 727.8 | 422.8 | 277.3 | 221.8 | 159.4 | 138.6 | 145.6 | 159.4 | 145.6 | 124.8 | 131.7 |
| 77.5° | 526.8 | 291.1 | 187.1 | 145.6 | 117.8 | 104.0 | 110.9 | 110.9 | 104.0 | 97.0 | 97.0 |
| 80° | 367.4 | 194.1 | 124.8 | 97.0 | 83.2 | 76.2 | 76.2 | 69.3 | 69.3 | 76.2 | 76.2 |
| 82.5° | 221.8 | 138.6 | 90.1 | 76.2 | 62.4 | 48.5 | 48.5 | 55.5 | 55.5 | 62.4 | 62.4 |
| 85° | 97.0 | 83.2 | 62.4 | 55.5 | 41.6 | 34.7 | 41.6 | 41.6 | 48.5 | 55.5 | 55.5 |
| 87.5° | 62.4 | 62.4 | 48.5 | 41.6 | 34.7 | 27.7 | 27.7 | 34.7 | 34.7 | 41.6 | 48.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P1385281

CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0° | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 |
| 2.5° | 3431.0 | 3500.3 | 3583.5 | 3701.3 | 3805.3 | 3930.0 | 4054.8 | 4172.6 | 4283.5 | 4297.4 | 4345.9 |
| 5° | 2987.4 | 3119.1 | 3285.4 | 3479.5 | 3715.2 | 3964.7 | 4207.3 | 4463.7 | 4671.7 | 4747.9 | 4858.8 |
| 7.5° | 2529.9 | 2696.3 | 2938.9 | 3236.9 | 3569.6 | 3943.9 | 4318.2 | 4678.6 | 4990.5 | 5136.1 | 5281.6 |
| 10° | 2093.2 | 2252.7 | 2550.7 | 2911.1 | 3340.9 | 3846.8 | 4345.9 | 4831.1 | 5212.3 | 5378.7 | 5517.3 |
| 12.5° | 1698.2 | 1857.6 | 2100.2 | 2516.0 | 3035.9 | 3645.8 | 4304.3 | 4886.5 | 5309.3 | 5482.6 | 5614.3 |
| 15° | 1386.3 | 1517.9 | 1746.7 | 2134.8 | 2682.4 | 3368.6 | 4158.8 | 4844.9 | 5330.1 | 5496.5 | 5593.5 |
| 17.5° | 1219.9 | 1254.6 | 1400.1 | 1753.6 | 2349.7 | 3119.1 | 3971.6 | 4789.5 | 5344.0 | 5496.5 | 5551.9 |
| 20° | 1150.6 | 1150.6 | 1178.3 | 1365.5 | 1947.7 | 2855.7 | 3833.0 | 4754.8 | 5364.8 | 5517.3 | 5510.3 |
| 22.5° | 1088.2 | 1102.1 | 1102.1 | 1143.7 | 1483.3 | 2488.3 | 3687.4 | 4741.0 | 5427.2 | 5545.0 | 5448.0 |
| 25° | 1032.8 | 1053.6 | 1053.6 | 1067.4 | 1164.5 | 2051.7 | 3507.2 | 4768.7 | 5538.1 | 5600.5 | 5406.4 |
| 27.5° | 984.2 | 1005.0 | 1005.0 | 1018.9 | 1039.7 | 1524.9 | 3209.2 | 4775.6 | 5662.8 | 5669.8 | 5350.9 |
| 30° | 935.7 | 956.5 | 970.4 | 970.4 | 984.2 | 1122.9 | 2834.9 | 4734.0 | 5801.5 | 5759.9 | 5344.0 |
| 32.5° | 880.3 | 908.0 | 914.9 | 928.8 | 935.7 | 977.3 | 2349.7 | 4664.7 | 5974.7 | 5884.6 | 5350.9 |
| 35° | 831.8 | 866.4 | 873.3 | 873.3 | 887.2 | 928.8 | 1878.4 | 4588.5 | 6210.4 | 6051.0 | 5378.7 |
| 37.5° | 783.2 | 811.0 | 817.9 | 824.8 | 838.7 | 880.3 | 1490.2 | 4477.6 | 6411.4 | 6258.9 | 5517.3 |
| 40° | 727.8 | 762.4 | 769.4 | 776.3 | 790.2 | 831.8 | 1282.3 | 4339.0 | 6716.4 | 6605.5 | 5725.2 |
| 42.5° | 672.3 | 707.0 | 720.9 | 727.8 | 734.7 | 790.2 | 1171.4 | 4241.9 | 7208.5 | 7090.7 | 6148.0 |
| 45° | 623.8 | 658.5 | 672.3 | 672.3 | 686.2 | 762.4 | 1074.3 | 4456.8 | 7887.8 | 7832.3 | 6716.4 |
| 47.5° | 582.2 | 616.9 | 623.8 | 623.8 | 630.7 | 720.9 | 991.2 | 5032.1 | 8927.5 | 8781.9 | 7603.6 |
| 50° | 547.6 | 575.3 | 589.2 | 575.3 | 582.2 | 686.2 | 1039.7 | 5981.7 | 10258.3 | 10306.8 | 8906.7 |
| 52.5° | 519.8 | 547.6 | 554.5 | 526.8 | 526.8 | 637.7 | 1102.1 | 6758.0 | 11956.4 | 12400.0 | 10972.2 |
| 55° | 485.2 | 512.9 | 519.8 | 485.2 | 485.2 | 561.4 | 956.5 | 6806.5 | 13890.2 | 15318.1 | 13661.5 |
| 57.5° | 450.5 | 478.3 | 478.3 | 450.5 | 443.6 | 485.2 | 776.3 | 6037.1 | 15387.4 | 18624.3 | 17342.0 |
| 60° | 408.9 | 436.7 | 429.7 | 415.9 | 402.0 | 443.6 | 713.9 | 4602.4 | 15186.4 | 20779.9 | 21563.1 |
| 62.5° | 332.7 | 374.3 | 388.2 | 381.2 | 353.5 | 402.0 | 665.4 | 3001.2 | 13141.7 | 18908.5 | 21431.4 |
| 65° | 277.3 | 311.9 | 332.7 | 332.7 | 311.9 | 443.6 | 582.2 | 1580.3 | 10521.6 | 16045.8 | 18894.6 |
| 67.5° | 242.6 | 277.3 | 291.1 | 284.2 | 270.3 | 395.1 | 367.4 | 762.4 | 8068.0 | 13827.8 | 16912.3 |
| 70° | 214.9 | 242.6 | 256.5 | 235.7 | 221.8 | 318.8 | 263.4 | 450.5 | 5399.4 | 11540.5 | 15061.6 |
| 72.5° | 173.3 | 201.0 | 214.9 | 194.1 | 173.3 | 235.7 | 201.0 | 298.0 | 3514.1 | 9835.4 | 13384.2 |
| 75° | 138.6 | 166.4 | 173.3 | 159.4 | 138.6 | 173.3 | 159.4 | 207.9 | 2294.2 | 8137.3 | 11381.1 |
| 77.5° | 104.0 | 117.8 | 131.7 | 124.8 | 104.0 | 124.8 | 110.9 | 145.6 | 1310.0 | 5711.4 | 7984.8 |
| 80° | 83.2 | 90.1 | 90.1 | 90.1 | 83.2 | 76.2 | 76.2 | 97.0 | 589.2 | 2814.1 | 4165.7 |
| 82.5° | 69.3 | 76.2 | 76.2 | 69.3 | 62.4 | 55.5 | 48.5 | 55.5 | 173.3 | 1261.5 | 1920.0 |
| 85° | 62.4 | 69.3 | 55.5 | 48.5 | 41.6 | 34.7 | 20.8 | 20.8 | 48.5 | 201.0 | 374.3 |
| 87.5° | 48.5 | 41.6 | 34.7 | 27.7 | 13.9 | 6.9 | 6.9 | 0.0 | 6.9 | 6.9 | 6.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P1385281

CATALOG NUMBER: VAL-T-SB5C-722-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 | 3902.3 |
| 2.5° | 4422.1 | 4491.5 | 4540.0 | 4581.6 | 4567.7 | 4533.0 | 4463.7 | 4415.2 | 4404.1 | 4401.3 |
| 5° | 5004.4 | 5115.3 | 5212.3 | 5198.4 | 5212.3 | 5108.3 | 5004.4 | 4879.6 | 4829.7 | 4817.2 |
| 7.5° | 5489.6 | 5628.2 | 5746.0 | 5732.1 | 5690.6 | 5572.7 | 5399.4 | 5212.3 | 5123.6 | 5101.4 |
| 10° | 5752.9 | 5912.4 | 6009.4 | 5974.7 | 5905.4 | 5752.9 | 5579.7 | 5357.9 | 5258.0 | 5233.1 |
| 12.5° | 5801.5 | 5905.4 | 5884.6 | 5870.8 | 5856.9 | 5780.7 | 5649.0 | 5448.0 | 5348.2 | 5323.2 |
| 15° | 5676.7 | 5635.1 | 5517.3 | 5489.6 | 5593.5 | 5690.6 | 5662.8 | 5496.5 | 5402.2 | 5378.7 |
| 17.5° | 5468.8 | 5253.9 | 5039.0 | 5011.3 | 5184.6 | 5454.9 | 5669.8 | 5572.7 | 5484.0 | 5461.8 |
| 20° | 5240.0 | 4838.0 | 4602.4 | 4553.8 | 4768.7 | 5170.7 | 5593.5 | 5649.0 | 5588.0 | 5572.7 |
| 22.5° | 4969.7 | 4498.4 | 4248.9 | 4221.1 | 4380.6 | 4851.9 | 5482.6 | 5732.1 | 5704.4 | 5697.5 |
| 25° | 4734.0 | 4200.3 | 3964.7 | 3923.1 | 4131.0 | 4588.5 | 5371.7 | 5870.8 | 5854.1 | 5850.0 |
| 27.5° | 4540.0 | 3985.5 | 3735.9 | 3708.2 | 3909.2 | 4366.7 | 5233.1 | 5988.6 | 6044.1 | 6057.9 |
| 30° | 4387.5 | 3826.1 | 3576.5 | 3541.9 | 3763.7 | 4214.2 | 5136.1 | 6155.0 | 6260.3 | 6286.6 |
| 32.5° | 4269.7 | 3735.9 | 3500.3 | 3479.5 | 3715.2 | 4151.8 | 5080.6 | 6328.2 | 6544.5 | 6598.6 |
| 35° | 4228.1 | 3763.7 | 3604.3 | 3652.8 | 3833.0 | 4214.2 | 5122.2 | 6612.4 | 6911.8 | 6986.7 |
| 37.5° | 4318.2 | 4068.6 | 4179.5 | 4304.3 | 4373.6 | 4512.2 | 5316.3 | 7069.9 | 7458.0 | 7555.1 |
| 40° | 4609.3 | 4886.5 | 5406.4 | 5649.0 | 5621.2 | 5302.4 | 5759.9 | 7714.5 | 8269.0 | 8407.6 |
| 42.5° | 5350.9 | 6252.0 | 7354.1 | 7763.0 | 7527.3 | 6563.9 | 6466.9 | 8775.0 | 9407.1 | 9565.1 |
| 45° | 6453.0 | 7901.6 | 9710.7 | 10632.5 | 9821.6 | 8165.0 | 7582.8 | 10286.0 | 10895.9 | 11048.4 |
| 47.5° | 7555.1 | 9745.3 | 12621.8 | 13716.9 | 12122.8 | 9752.3 | 9045.3 | 12095.0 | 12644.0 | 12781.2 |
| 50° | 8677.9 | 11783.1 | 15526.0 | 16988.5 | 14417.0 | 11367.3 | 10597.9 | 14326.9 | 14726.1 | 14825.9 |
| 52.5° | 9835.4 | 13606.0 | 18728.2 | 19989.7 | 16815.2 | 12614.9 | 12372.3 | 16759.8 | 16998.2 | 17057.8 |
| 55° | 11124.7 | 15331.9 | 21937.4 | 22956.3 | 18998.6 | 13703.1 | 14451.7 | 19303.5 | 19242.5 | 19227.3 |
| 57.5° | 12843.6 | 17147.9 | 24522.8 | 25943.7 | 20980.9 | 15172.5 | 17231.1 | 22131.5 | 20939.3 | 20641.3 |
| 60° | 15844.8 | 19968.9 | 27738.9 | 29284.5 | 23635.6 | 17321.2 | 19275.8 | 22069.1 | 19939.8 | 19407.5 |
| 62.5° | 19324.3 | 22686.0 | 30650.0 | 31953.1 | 26428.9 | 19456.0 | 17647.0 | 18534.2 | 16427.1 | 15900.3 |
| 65° | 16787.5 | 22207.7 | 30740.1 | 32077.8 | 26532.8 | 18152.9 | 13044.6 | 13141.7 | 11367.3 | 10923.7 |
| 67.5° | 14285.3 | 19684.8 | 27995.3 | 29048.9 | 23670.2 | 15006.2 | 8650.2 | 8574.0 | 7459.4 | 7180.8 |
| 70° | 12718.8 | 17245.0 | 24127.7 | 23219.7 | 19899.6 | 12684.2 | 5746.0 | 4761.8 | 4068.6 | 3895.4 |
| 72.5° | 11429.6 | 13682.3 | 19553.1 | 16004.3 | 16510.2 | 10320.6 | 3652.8 | 3243.8 | 2706.0 | 2571.5 |
| 75° | 10348.4 | 11318.7 | 12199.0 | 11062.3 | 11727.7 | 8504.6 | 3098.3 | 2502.2 | 2047.5 | 1933.8 |
| 77.5° | 8234.3 | 8809.6 | 7222.4 | 7014.4 | 8213.5 | 6051.0 | 1538.7 | 1053.6 | 920.5 | 887.2 |
| 80° | 4900.4 | 4165.7 | 4096.4 | 4671.7 | 5468.8 | 3139.9 | 942.7 | 582.2 | 526.8 | 512.9 |
| 82.5° | 2966.6 | 1504.1 | 1635.8 | 2065.5 | 2911.1 | 1427.8 | 561.4 | 249.5 | 221.8 | 214.9 |
| 85° | 499.1 | 408.9 | 630.7 | 603.0 | 568.4 | 305.0 | 152.5 | 69.3 | 63.8 | 62.4 |
| 87.5° | 13.9 | 20.8 | 27.7 | 34.7 | 34.7 | 34.7 | 34.7 | 34.7 | 40.2 | 41.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-722-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 2200K CCT 26 LEDS

Spectral Parameters

CCT (K): 2160
 CIE u': 0.2927
 CIE v': 0.5388
 Duv: 0.0015
 CIE x: 0.5130
 CIE y: 0.4197
 CIE z: 0.0674
 Peak Wavelength (nm): 609
 Dominant Wavelength (nm): 587
 Purity: 79.96089
 Rf: 70.6
 Rg: 97.6

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.9 | | |
| R1: | 68.7 | R9: | -17.8 |
| R2: | 82.6 | R10: | 60.5 |
| R3: | 95.5 | R11: | 60.2 |
| R4: | 66.4 | R12: | 48.2 |
| R5: | 65.4 | R13: | 70.7 |
| R6: | 75.9 | R14: | 96.8 |
| R7: | 77.2 | R15: | 61.8 |
| R8: | 43.5 | | |



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-2


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 27 | NR | 620 | 966 | NR | 750 | 46 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 42 | NR | 625 | 930 | NR | 755 | 39 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 67 | NR | 630 | 888 | NR | 760 | 34 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 101 | NR | 635 | 835 | NR | 765 | 30 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 139 | NR | 640 | 778 | NR | 770 | 26 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 183 | NR | 645 | 717 | NR | 775 | 22 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 224 | NR | 650 | 656 | NR | 780 | 19 | NR | 910 | 1 | NR |
| 395 | 0 | NR | 525 | 262 | NR | 655 | 595 | NR | 785 | 17 | NR | 915 | 1 | NR |
| 400 | 1 | NR | 530 | 299 | NR | 660 | 536 | NR | 790 | 15 | NR | 920 | 1 | NR |
| 405 | 3 | NR | 535 | 332 | NR | 665 | 480 | NR | 795 | 13 | NR | 925 | 1 | NR |
| 410 | 7 | NR | 540 | 365 | NR | 670 | 425 | NR | 800 | 11 | NR | 930 | 1 | NR |
| 415 | 17 | NR | 545 | 400 | NR | 675 | 376 | NR | 805 | 10 | NR | 935 | 0 | NR |
| 420 | 36 | NR | 550 | 437 | NR | 680 | 332 | NR | 810 | 8 | NR | 940 | 0 | NR |
| 425 | 67 | NR | 555 | 479 | NR | 685 | 291 | NR | 815 | 8 | NR | 945 | 0 | NR |
| 430 | 105 | NR | 560 | 525 | NR | 690 | 255 | NR | 820 | 7 | NR | 950 | 0 | NR |
| 435 | 141 | NR | 565 | 579 | NR | 695 | 221 | NR | 825 | 6 | NR | 955 | 0 | NR |
| 440 | 169 | NR | 570 | 639 | NR | 700 | 192 | NR | 830 | 5 | NR | 960 | 0 | NR |
| 445 | 173 | NR | 575 | 703 | NR | 705 | 167 | NR | 835 | 4 | NR | 965 | 0 | NR |
| 450 | 136 | NR | 580 | 769 | NR | 710 | 144 | NR | 840 | 4 | NR | 970 | 0 | NR |
| 455 | 80 | NR | 585 | 832 | NR | 715 | 125 | NR | 845 | 3 | NR | 975 | 0 | NR |
| 460 | 45 | NR | 590 | 890 | NR | 720 | 109 | NR | 850 | 3 | NR | 980 | 0 | NR |
| 465 | 32 | NR | 595 | 937 | NR | 725 | 94 | NR | 855 | 3 | NR | 985 | 0 | NR |
| 470 | 23 | NR | 600 | 972 | NR | 730 | 81 | NR | 860 | 2 | NR | 990 | 0 | NR |
| 475 | 18 | NR | 605 | 992 | NR | 735 | 70 | NR | 865 | 2 | NR | 995 | 0 | NR |
| 480 | 18 | NR | 610 | 998 | NR | 740 | 61 | NR | 870 | 2 | NR | 1000 | 0 | NR |
| 485 | 20 | NR | 615 | 990 | NR | 745 | 53 | NR | 875 | 2 | NR | | | |

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 0.8

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 27 | NR | 620 | 966 | NR | 750 | 46 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 42 | NR | 625 | 930 | NR | 755 | 39 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 67 | NR | 630 | 888 | NR | 760 | 34 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 101 | NR | 635 | 835 | NR | 765 | 30 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 139 | NR | 640 | 778 | NR | 770 | 26 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 183 | NR | 645 | 717 | NR | 775 | 22 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 224 | NR | 650 | 656 | NR | 780 | 19 | NR | 910 | 1 | NR |
| 395 | 0 | NR | 525 | 262 | NR | 655 | 595 | NR | 785 | 17 | NR | 915 | 1 | NR |
| 400 | 1 | NR | 530 | 299 | NR | 660 | 536 | NR | 790 | 15 | NR | 920 | 1 | NR |
| 405 | 3 | NR | 535 | 332 | NR | 665 | 480 | NR | 795 | 13 | NR | 925 | 1 | NR |
| 410 | 7 | NR | 540 | 365 | NR | 670 | 425 | NR | 800 | 11 | NR | 930 | 1 | NR |
| 415 | 17 | NR | 545 | 400 | NR | 675 | 376 | NR | 805 | 10 | NR | 935 | 0 | NR |
| 420 | 36 | NR | 550 | 437 | NR | 680 | 332 | NR | 810 | 8 | NR | 940 | 0 | NR |
| 425 | 67 | NR | 555 | 479 | NR | 685 | 291 | NR | 815 | 8 | NR | 945 | 0 | NR |
| 430 | 105 | NR | 560 | 525 | NR | 690 | 255 | NR | 820 | 7 | NR | 950 | 0 | NR |
| 435 | 141 | NR | 565 | 579 | NR | 695 | 221 | NR | 825 | 6 | NR | 955 | 0 | NR |
| 440 | 169 | NR | 570 | 639 | NR | 700 | 192 | NR | 830 | 5 | NR | 960 | 0 | NR |
| 445 | 173 | NR | 575 | 703 | NR | 705 | 167 | NR | 835 | 4 | NR | 965 | 0 | NR |
| 450 | 136 | NR | 580 | 769 | NR | 710 | 144 | NR | 840 | 4 | NR | 970 | 0 | NR |
| 455 | 80 | NR | 585 | 832 | NR | 715 | 125 | NR | 845 | 3 | NR | 975 | 0 | NR |
| 460 | 45 | NR | 590 | 890 | NR | 720 | 109 | NR | 850 | 3 | NR | 980 | 0 | NR |
| 465 | 32 | NR | 595 | 937 | NR | 725 | 94 | NR | 855 | 3 | NR | 985 | 0 | NR |
| 470 | 23 | NR | 600 | 972 | NR | 730 | 81 | NR | 860 | 2 | NR | 990 | 0 | NR |
| 475 | 18 | NR | 605 | 992 | NR | 735 | 70 | NR | 865 | 2 | NR | 995 | 0 | NR |
| 480 | 18 | NR | 610 | 998 | NR | 740 | 61 | NR | 870 | 2 | NR | 1000 | 0 | NR |
| 485 | 20 | NR | 615 | 990 | NR | 745 | 53 | NR | 875 | 2 | NR | | | |

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 1.21





| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 27 | NR | 620 | 966 | NR | 750 | 46 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 42 | NR | 625 | 930 | NR | 755 | 39 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 67 | NR | 630 | 888 | NR | 760 | 34 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 101 | NR | 635 | 835 | NR | 765 | 30 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 139 | NR | 640 | 778 | NR | 770 | 26 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 183 | NR | 645 | 717 | NR | 775 | 22 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 224 | NR | 650 | 656 | NR | 780 | 19 | NR | 910 | 1 | NR |
| 395 | 0 | NR | 525 | 262 | NR | 655 | 595 | NR | 785 | 17 | NR | 915 | 1 | NR |
| 400 | 1 | NR | 530 | 299 | NR | 660 | 536 | NR | 790 | 15 | NR | 920 | 1 | NR |
| 405 | 3 | NR | 535 | 332 | NR | 665 | 480 | NR | 795 | 13 | NR | 925 | 1 | NR |
| 410 | 7 | NR | 540 | 365 | NR | 670 | 425 | NR | 800 | 11 | NR | 930 | 1 | NR |
| 415 | 17 | NR | 545 | 400 | NR | 675 | 376 | NR | 805 | 10 | NR | 935 | 0 | NR |
| 420 | 36 | NR | 550 | 437 | NR | 680 | 332 | NR | 810 | 8 | NR | 940 | 0 | NR |
| 425 | 67 | NR | 555 | 479 | NR | 685 | 291 | NR | 815 | 8 | NR | 945 | 0 | NR |
| 430 | 105 | NR | 560 | 525 | NR | 690 | 255 | NR | 820 | 7 | NR | 950 | 0 | NR |
| 435 | 141 | NR | 565 | 579 | NR | 695 | 221 | NR | 825 | 6 | NR | 955 | 0 | NR |
| 440 | 169 | NR | 570 | 639 | NR | 700 | 192 | NR | 830 | 5 | NR | 960 | 0 | NR |
| 445 | 173 | NR | 575 | 703 | NR | 705 | 167 | NR | 835 | 4 | NR | 965 | 0 | NR |
| 450 | 136 | NR | 580 | 769 | NR | 710 | 144 | NR | 840 | 4 | NR | 970 | 0 | NR |
| 455 | 80 | NR | 585 | 832 | NR | 715 | 125 | NR | 845 | 3 | NR | 975 | 0 | NR |
| 460 | 45 | NR | 590 | 890 | NR | 720 | 109 | NR | 850 | 3 | NR | 980 | 0 | NR |
| 465 | 32 | NR | 595 | 937 | NR | 725 | 94 | NR | 855 | 3 | NR | 985 | 0 | NR |
| 470 | 23 | NR | 600 | 972 | NR | 730 | 81 | NR | 860 | 2 | NR | 990 | 0 | NR |
| 475 | 18 | NR | 605 | 992 | NR | 735 | 70 | NR | 865 | 2 | NR | 995 | 0 | NR |
| 480 | 18 | NR | 610 | 998 | NR | 740 | 61 | NR | 870 | 2 | NR | 1000 | 0 | NR |
| 485 | 20 | NR | 615 | 990 | NR | 745 | 53 | NR | 875 | 2 | NR | | | |

Summary

$R_f = 70.6$
 $R_g = 97.6$
 CIE $R_a = 71.9$
 $R_9 = -17.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 60 | CES51 = 74 | CES76 = 58 |
| CES02 = 65 | CES27 = 77 | CES52 = 77 | CES77 = 82 |
| CES03 = 32 | CES28 = 85 | CES53 = 65 | CES78 = 65 |
| CES04 = 72 | CES29 = 50 | CES54 = 77 | CES79 = 86 |
| CES05 = 52 | CES30 = 49 | CES55 = 74 | CES80 = 85 |
| CES06 = 53 | CES31 = 55 | CES56 = 64 | CES81 = 61 |
| CES07 = 44 | CES32 = 55 | CES57 = 60 | CES82 = 93 |
| CES08 = 43 | CES33 = 55 | CES58 = 64 | CES83 = 83 |
| CES09 = 29 | CES34 = 75 | CES59 = 84 | CES84 = 93 |
| CES10 = 79 | CES35 = 88 | CES60 = 89 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 55 |
| CES12 = 68 | CES37 = 82 | CES62 = 68 | CES87 = 79 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 86 | CES65 = 66 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 89 |
| CES17 = 51 | CES42 = 83 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 71 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 81 | CES94 = 52 |
| CES20 = 68 | CES45 = 76 | CES70 = 65 | CES95 = 76 |
| CES21 = 89 | CES46 = 68 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 88 | CES97 = 76 |
| CES23 = 92 | CES48 = 47 | CES73 = 59 | CES98 = 71 |
| CES24 = 92 | CES49 = 65 | CES74 = 85 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)