

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1385666

Luminaire Tested: **VAL-T-SB5D-722-U-SLL**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



**Test Information**

Test Method: LM-79-08  
 Report Number: P1385666  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 02/18/2026  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: VAL-T-SB5D-722-U-SLL  
 Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 55 SQUARE 294W 70CRI  
 2200K FIXTURE w/ 90° Spill Light Eliminator LEFT OPTIC  
 Light Source: (130) 2200K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER  
 Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a                 | good             | reflector          |
| b                 | good             | lens               |
| c                 | good             | housing            |
| d                 | good             | cord               |


**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 31387.8 lumens  
 Efficiency: N/A  
 Efficacy: 106.8 lumens/watt  
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
 IES Classification: Type IV - Short  
 BUG Rating: B3 - U0 - G4  
  
 Input Watts (W): 294  
 Input Voltage (V): 120  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: 0.98  
 Total Harmonic Distortion (THDi): --  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 28.75 FT

REPORT NUMBER: P1385666  
 CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 16.6 fc  
 Type IV - Short - N/A

REPORT NUMBER: P1385666  
CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P1385666  
 CATALOG NUMBER: VAL-T-SB5D-722-U-SLL


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 8444.0   | 0.0    | 8444.0  |
|                    | % Fixture | 26.9     | 0.0    | 26.9    |
| <b>Street Side</b> | Lumens    | 22943.8  | 0.0    | 22943.8 |
|                    | % Fixture | 73.1     | 0.0    | 73.1    |
| <b>Total</b>       | Lumens    | 31387.8  | 0.0    | 31387.8 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 494.2   | 1.6       |
| 10°-20°   | 1514.4  | 4.8       |
| 20°-30°   | 2343.8  | 7.5       |
| 30°-40°   | 2908.0  | 9.3       |
| 40°-50°   | 4252.3  | 13.5      |
| 50°-60°   | 6660.8  | 21.2      |
| 60°-70°   | 7903.4  | 25.2      |
| 70°-80°   | 4609.7  | 14.7      |
| 80°-90°   | 701.3   | 2.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 31387.8 | 100.0     |
| 0°-180°   | 31387.8 | 100.0     |




REPORT NUMBER: P1385666  
 CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 2359.1  | 7.5       |                         |      |          |
| FM   | (30°-60°)   | 9548.8  | 30.4      |                         |      |          |
| FH   | (60°-80°)   | 10462.4 | 33.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 573.5   | 1.8       |                         |      | G4/750   |
| BL   | (0°-30°)    | 1993.4  | 6.4       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 4272.2  | 13.6      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 2050.7  | 6.5       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 127.7   | 0.4       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G4**  
 Type IV Short





REPORT NUMBER: P1385666

CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 10°     | 15°     | 20°     | 25°     | 30°     | 35°     | 40°     | 45°     | 50°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  |
| 2.5°  | 5407.8  | 5427.0  | 5446.2  | 5467.0  | 5488.4  | 5500.7  | 5513.0  | 5526.1  | 5538.3  | 5549.9  | 5538.3  |
| 5°    | 5776.3  | 5863.0  | 5949.0  | 6007.4  | 6065.7  | 6110.2  | 6154.7  | 6180.1  | 6206.2  | 6210.0  | 6206.2  |
| 7.5°  | 6148.6  | 6251.5  | 6354.3  | 6443.4  | 6532.4  | 6589.2  | 6646.0  | 6679.0  | 6712.8  | 6724.3  | 6712.8  |
| 10°   | 6382.7  | 6503.2  | 6624.5  | 6710.5  | 6797.2  | 6850.2  | 6902.4  | 6928.5  | 6954.6  | 6962.3  | 6954.6  |
| 12.5° | 6501.7  | 6617.6  | 6733.5  | 6800.3  | 6866.3  | 6900.1  | 6933.1  | 6945.4  | 6956.1  | 6946.9  | 6956.1  |
| 15°   | 6559.3  | 6627.6  | 6695.1  | 6723.5  | 6751.2  | 6735.1  | 6718.2  | 6694.4  | 6670.6  | 6655.2  | 6670.6  |
| 17.5° | 6574.6  | 6598.4  | 6623.0  | 6571.6  | 6520.9  | 6428.8  | 6336.7  | 6267.6  | 6198.5  | 6148.6  | 6198.5  |
| 20°   | 6624.5  | 6586.1  | 6547.8  | 6411.1  | 6275.3  | 6102.5  | 5929.8  | 5813.9  | 5697.2  | 5626.6  | 5697.2  |
| 22.5° | 6678.3  | 6570.0  | 6461.8  | 6232.3  | 6002.7  | 5766.3  | 5530.7  | 5397.1  | 5264.3  | 5189.1  | 5264.3  |
| 25°   | 6762.7  | 6576.9  | 6390.4  | 6080.3  | 5770.9  | 5493.1  | 5215.9  | 5070.9  | 4926.6  | 4843.7  | 4926.6  |
| 27.5° | 6885.5  | 6601.5  | 6317.5  | 5933.7  | 5549.9  | 5249.0  | 4947.3  | 4809.1  | 4670.9  | 4598.0  | 4670.9  |
| 30°   | 7058.2  | 6681.3  | 6303.7  | 5844.6  | 5384.8  | 5070.1  | 4755.4  | 4620.3  | 4484.4  | 4406.1  | 4484.4  |
| 32.5° | 7269.3  | 6793.4  | 6317.5  | 5803.2  | 5288.9  | 4968.0  | 4647.9  | 4518.2  | 4389.2  | 4321.7  | 4389.2  |
| 35°   | 7626.3  | 7023.7  | 6421.1  | 5850.8  | 5281.2  | 4983.4  | 4686.3  | 4591.1  | 4496.7  | 4459.8  | 4496.7  |
| 37.5° | 8079.1  | 7375.2  | 6670.6  | 6083.3  | 5496.1  | 5293.5  | 5090.8  | 5090.8  | 5090.8  | 5120.0  | 5090.8  |
| 40°   | 8747.0  | 7956.3  | 7165.7  | 6609.9  | 6054.9  | 6042.7  | 6031.9  | 6160.9  | 6290.6  | 6348.2  | 6290.6  |
| 42.5° | 9683.5  | 8847.5  | 8012.4  | 7564.1  | 7115.8  | 7384.5  | 7653.1  | 8026.2  | 8399.2  | 8643.3  | 8399.2  |
| 45°   | 10846.4 | 10032.7 | 9219.1  | 8905.9  | 8593.4  | 9191.4  | 9788.6  | 10448.0 | 11107.4 | 11575.6 | 11107.4 |
| 47.5° | 11959.4 | 11274.7 | 10589.2 | 10410.4 | 10232.3 | 11226.4 | 12220.4 | 13186.9 | 14153.3 | 14722.9 | 14153.3 |
| 50°   | 13249.0 | 12633.4 | 12017.0 | 11982.5 | 11947.9 | 13272.1 | 14596.2 | 15843.6 | 17090.9 | 17785.6 | 17090.9 |
| 52.5° | 14903.2 | 14227.0 | 13549.9 | 13577.6 | 13603.7 | 15176.5 | 16749.4 | 18257.7 | 19766.1 | 20549.1 | 19766.1 |
| 55°   | 16879.9 | 16031.6 | 15183.4 | 15178.8 | 15174.2 | 16981.2 | 18789.7 | 20642.7 | 22497.3 | 23542.8 | 22497.3 |
| 57.5° | 18894.8 | 18100.4 | 17305.9 | 17117.0 | 16927.4 | 18817.3 | 20706.4 | 22752.9 | 24800.1 | 25899.3 | 24800.1 |
| 60°   | 20407.0 | 19969.5 | 19532.0 | 19229.5 | 18927.9 | 20868.4 | 22809.7 | 24923.7 | 27036.9 | 28133.1 | 27036.9 |
| 62.5° | 19781.4 | 20563.6 | 21345.8 | 21323.6 | 21301.3 | 23396.1 | 25491.0 | 27689.4 | 29889.4 | 30873.5 | 29889.4 |
| 65°   | 17670.5 | 18917.9 | 20165.2 | 21023.4 | 21880.9 | 24413.2 | 26944.8 | 29235.4 | 31525.9 | 32531.5 | 31525.9 |
| 67.5° | 15690.1 | 16789.3 | 17889.3 | 18591.6 | 19294.0 | 22147.2 | 25001.2 | 27600.4 | 30199.5 | 31234.3 | 30199.5 |
| 70°   | 13794.0 | 15011.5 | 16228.9 | 16730.9 | 17233.0 | 19657.1 | 22080.4 | 24136.9 | 26192.6 | 26597.9 | 26192.6 |
| 72.5° | 11840.5 | 13288.2 | 14736.7 | 14949.3 | 15161.9 | 16925.9 | 18689.9 | 19785.3 | 20880.7 | 19996.4 | 20880.7 |
| 75°   | 9695.0  | 11328.5 | 12961.2 | 13103.2 | 13245.2 | 13794.8 | 14345.2 | 14623.8 | 14903.2 | 14400.5 | 14903.2 |
| 77.5° | 6448.0  | 7861.9  | 9276.6  | 9595.2  | 9913.7  | 10279.9 | 10646.8 | 10627.6 | 10608.4 | 9902.2  | 10608.4 |
| 80°   | 3784.3  | 4890.5  | 5996.6  | 6038.1  | 6079.5  | 6354.3  | 6628.4  | 6908.5  | 7188.7  | 6739.7  | 7188.7  |
| 82.5° | 1892.2  | 2499.4  | 3107.3  | 3201.0  | 3294.6  | 3462.7  | 3630.8  | 3709.1  | 3788.2  | 3408.2  | 3788.2  |
| 85°   | 429.9   | 588.0   | 746.1   | 898.9   | 1051.6  | 1228.2  | 1404.7  | 1384.8  | 1364.8  | 1151.4  | 1364.8  |
| 87.5° | 34.5    | 35.3    | 36.8    | 37.6    | 38.4    | 39.1    | 39.9    | 42.2    | 44.5    | 46.1    | 44.5    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1385666

CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 55°     | 60°     | 65°     | 70°     | 75°     | 80°     | 85°     | 90°     | 95°     | 100°    | 105°   |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|--------|
| 0°    | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8  | 5004.8 |
| 2.5°  | 5526.1  | 5513.0  | 5500.7  | 5488.4  | 5467.0  | 5446.2  | 5427.0  | 5407.8  | 5358.7  | 5310.4  | 5265.8 |
| 5°    | 6180.1  | 6154.7  | 6110.2  | 6065.7  | 6007.4  | 5949.0  | 5863.0  | 5776.3  | 5689.6  | 5603.6  | 5513.0 |
| 7.5°  | 6679.0  | 6646.0  | 6589.2  | 6532.4  | 6443.4  | 6354.3  | 6251.5  | 6148.6  | 6002.7  | 5856.9  | 5719.5 |
| 10°   | 6928.5  | 6902.4  | 6850.2  | 6797.2  | 6710.5  | 6624.5  | 6503.2  | 6382.7  | 6208.5  | 6033.5  | 5863.0 |
| 12.5° | 6945.4  | 6933.1  | 6900.1  | 6866.3  | 6800.3  | 6733.5  | 6617.6  | 6501.7  | 6328.2  | 6154.7  | 5963.6 |
| 15°   | 6694.4  | 6718.2  | 6735.1  | 6751.2  | 6723.5  | 6695.1  | 6627.6  | 6559.3  | 6383.5  | 6208.5  | 6014.3 |
| 17.5° | 6267.6  | 6336.7  | 6428.8  | 6520.9  | 6571.6  | 6623.0  | 6598.4  | 6574.6  | 6410.4  | 6246.9  | 6039.6 |
| 20°   | 5813.9  | 5929.8  | 6102.5  | 6275.3  | 6411.1  | 6547.8  | 6586.1  | 6624.5  | 6458.7  | 6292.9  | 6070.3 |
| 22.5° | 5397.1  | 5530.7  | 5766.3  | 6002.7  | 6232.3  | 6461.8  | 6570.0  | 6678.3  | 6526.3  | 6375.0  | 6130.2 |
| 25°   | 5070.9  | 5215.9  | 5493.1  | 5770.9  | 6080.3  | 6390.4  | 6576.9  | 6762.7  | 6631.4  | 6500.2  | 6233.0 |
| 27.5° | 4809.1  | 4947.3  | 5249.0  | 5549.9  | 5933.7  | 6317.5  | 6601.5  | 6885.5  | 6784.9  | 6684.4  | 6383.5 |
| 30°   | 4620.3  | 4755.4  | 5070.1  | 5384.8  | 5844.6  | 6303.7  | 6681.3  | 7058.2  | 6979.2  | 6900.9  | 6561.6 |
| 32.5° | 4518.2  | 4647.9  | 4968.0  | 5288.9  | 5803.2  | 6317.5  | 6793.4  | 7269.3  | 7220.2  | 7171.1  | 6771.1 |
| 35°   | 4591.1  | 4686.3  | 4983.4  | 5281.2  | 5850.8  | 6421.1  | 7023.7  | 7626.3  | 7564.8  | 7503.4  | 6993.7 |
| 37.5° | 5090.8  | 5090.8  | 5293.5  | 5496.1  | 6083.3  | 6670.6  | 7375.2  | 8079.1  | 8006.2  | 7933.3  | 7265.5 |
| 40°   | 6160.9  | 6031.9  | 6042.7  | 6054.9  | 6609.9  | 7165.7  | 7956.3  | 8747.0  | 8603.4  | 8459.1  | 7576.4 |
| 42.5° | 8026.2  | 7653.1  | 7384.5  | 7115.8  | 7564.1  | 8012.4  | 8847.5  | 9683.5  | 9379.5  | 9074.7  | 7920.3 |
| 45°   | 10448.0 | 9788.6  | 9191.4  | 8593.4  | 8905.9  | 9219.1  | 10032.7 | 10846.4 | 10359.0 | 9871.5  | 8387.0 |
| 47.5° | 13186.9 | 12220.4 | 11226.4 | 10232.3 | 10410.4 | 10589.2 | 11274.7 | 11959.4 | 11342.3 | 10725.1 | 8866.7 |
| 50°   | 15843.6 | 14596.2 | 13272.1 | 11947.9 | 11982.5 | 12017.0 | 12633.4 | 13249.0 | 12412.3 | 11575.6 | 9285.1 |
| 52.5° | 18257.7 | 16749.4 | 15176.5 | 13603.7 | 13577.6 | 13549.9 | 14227.0 | 14903.2 | 13574.5 | 12245.0 | 9483.1 |
| 55°   | 20642.7 | 18789.7 | 16981.2 | 15174.2 | 15178.8 | 15183.4 | 16031.6 | 16879.9 | 14742.0 | 12604.2 | 9430.9 |
| 57.5° | 22752.9 | 20706.4 | 18817.3 | 16927.4 | 17117.0 | 17305.9 | 18100.4 | 18894.8 | 15722.3 | 12550.5 | 9146.1 |
| 60°   | 24923.7 | 22809.7 | 20868.4 | 18927.9 | 19229.5 | 19532.0 | 19969.5 | 20407.0 | 16161.4 | 11914.9 | 8463.7 |
| 62.5° | 27689.4 | 25491.0 | 23396.1 | 21301.3 | 21323.6 | 21345.8 | 20563.6 | 19781.4 | 15187.3 | 10593.1 | 7345.3 |
| 65°   | 29235.4 | 26944.8 | 24413.2 | 21880.9 | 21023.4 | 20165.2 | 18917.9 | 17670.5 | 13099.3 | 8528.2  | 5761.7 |
| 67.5° | 27600.4 | 25001.2 | 22147.2 | 19294.0 | 18591.6 | 17889.3 | 16789.3 | 15690.1 | 11250.2 | 6810.3  | 4483.6 |
| 70°   | 24136.9 | 22080.4 | 19657.1 | 17233.0 | 16730.9 | 16228.9 | 15011.5 | 13794.0 | 9557.6  | 5321.1  | 3435.8 |
| 72.5° | 19785.3 | 18689.9 | 16925.9 | 15161.9 | 14949.3 | 14736.7 | 13288.2 | 11840.5 | 7936.4  | 4031.5  | 2583.0 |
| 75°   | 14623.8 | 14345.2 | 13794.8 | 13245.2 | 13103.2 | 12961.2 | 11328.5 | 9695.0  | 6336.7  | 2978.3  | 1914.4 |
| 77.5° | 10627.6 | 10646.8 | 10279.9 | 9913.7  | 9595.2  | 9276.6  | 7861.9  | 6448.0  | 4157.4  | 1866.8  | 1237.4 |
| 80°   | 6908.5  | 6628.4  | 6354.3  | 6079.5  | 6038.1  | 5996.6  | 4890.5  | 3784.3  | 2383.4  | 982.5   | 683.9  |
| 82.5° | 3709.1  | 3630.8  | 3462.7  | 3294.6  | 3201.0  | 3107.3  | 2499.4  | 1892.2  | 1194.4  | 497.4   | 367.7  |
| 85°   | 1384.8  | 1404.7  | 1228.2  | 1051.6  | 898.9   | 746.1   | 588.0   | 429.9   | 284.0   | 138.2   | 116.7  |
| 87.5° | 42.2    | 39.9    | 39.1    | 38.4    | 37.6    | 36.8    | 35.3    | 34.5    | 33.8    | 32.2    | 31.5   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    |



REPORT NUMBER: P1385666

CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 110°   | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   | 150°   | 155°   | 160°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 |
| 2.5°  | 5221.3 | 5176.8 | 5131.5 | 5088.5 | 5044.8 | 5001.0 | 4962.6 | 4921.2 | 4880.5 | 4848.3 | 4816.8 |
| 5°    | 5423.2 | 5334.9 | 5246.6 | 5163.0 | 5080.1 | 4993.3 | 4918.9 | 4845.2 | 4773.0 | 4713.2 | 4653.3 |
| 7.5°  | 5582.1 | 5459.3 | 5336.5 | 5226.7 | 5116.2 | 5001.0 | 4911.2 | 4821.4 | 4732.3 | 4654.8 | 4576.5 |
| 10°   | 5691.9 | 5540.6 | 5388.7 | 5262.0 | 5135.3 | 5012.5 | 4916.6 | 4822.2 | 4728.5 | 4648.7 | 4568.8 |
| 12.5° | 5772.5 | 5602.8 | 5433.2 | 5293.5 | 5154.5 | 5020.2 | 4926.6 | 4848.3 | 4770.7 | 4714.7 | 4659.4 |
| 15°   | 5820.1 | 5637.4 | 5453.9 | 5296.5 | 5139.2 | 4989.5 | 4906.6 | 4855.9 | 4805.3 | 4800.7 | 4796.1 |
| 17.5° | 5832.3 | 5623.5 | 5415.5 | 5232.1 | 5049.4 | 4874.4 | 4803.7 | 4796.8 | 4789.9 | 4865.9 | 4941.9 |
| 20°   | 5847.7 | 5602.8 | 5358.0 | 5116.9 | 4875.9 | 4644.1 | 4599.5 | 4643.3 | 4686.3 | 4835.2 | 4983.4 |
| 22.5° | 5886.1 | 5586.7 | 5287.3 | 4984.9 | 4682.5 | 4406.1 | 4363.9 | 4428.4 | 4492.1 | 4686.3 | 4880.5 |
| 25°   | 5965.9 | 5585.2 | 5204.4 | 4827.5 | 4450.6 | 4133.6 | 4129.8 | 4199.6 | 4269.5 | 4449.1 | 4628.7 |
| 27.5° | 6083.3 | 5599.8 | 5116.2 | 4666.3 | 4215.7 | 3891.8 | 3911.0 | 3977.8 | 4045.3 | 4178.9 | 4312.5 |
| 30°   | 6221.5 | 5631.2 | 5041.7 | 4525.9 | 4010.8 | 3696.1 | 3716.8 | 3769.0 | 3821.2 | 3917.9 | 4014.6 |
| 32.5° | 6371.2 | 5666.5 | 4962.6 | 4403.0 | 3844.2 | 3554.1 | 3554.1 | 3576.3 | 3598.6 | 3661.5 | 3724.5 |
| 35°   | 6484.8 | 5658.1 | 4832.1 | 4263.3 | 3693.8 | 3469.6 | 3422.0 | 3403.6 | 3385.2 | 3426.6 | 3468.1 |
| 37.5° | 6597.7 | 5634.3 | 4670.9 | 4108.3 | 3546.4 | 3369.8 | 3279.3 | 3230.1 | 3179.5 | 3199.4 | 3217.8 |
| 40°   | 6693.6 | 5580.6 | 4467.5 | 3923.3 | 3379.0 | 3239.3 | 3125.7 | 3052.0 | 2978.3 | 2976.8 | 2974.5 |
| 42.5° | 6764.2 | 5487.7 | 4210.4 | 3703.0 | 3194.8 | 3097.3 | 2956.9 | 2863.2 | 2769.6 | 2759.6 | 2749.6 |
| 45°   | 6902.4 | 5424.0 | 3945.5 | 3478.8 | 3012.9 | 2924.6 | 2784.9 | 2688.2 | 2593.0 | 2577.7 | 2562.3 |
| 47.5° | 7008.3 | 5349.5 | 3690.7 | 3256.2 | 2823.3 | 2721.2 | 2590.7 | 2508.6 | 2425.7 | 2416.5 | 2406.5 |
| 50°   | 6994.5 | 5222.9 | 3450.4 | 3058.2 | 2665.2 | 2525.5 | 2396.5 | 2328.9 | 2260.6 | 2272.1 | 2283.7 |
| 52.5° | 6720.5 | 4963.4 | 3207.1 | 2880.1 | 2554.6 | 2375.8 | 2237.6 | 2186.9 | 2135.5 | 2171.6 | 2206.9 |
| 55°   | 6257.6 | 4619.5 | 2979.9 | 2731.2 | 2480.9 | 2302.8 | 2140.1 | 2083.3 | 2026.5 | 2077.2 | 2127.8 |
| 57.5° | 5741.8 | 4259.5 | 2777.2 | 2605.3 | 2433.3 | 2283.7 | 2084.1 | 2004.2 | 1925.2 | 1975.8 | 2026.5 |
| 60°   | 5012.5 | 3804.3 | 2596.1 | 2475.6 | 2355.0 | 2237.6 | 2038.0 | 1938.2 | 1838.4 | 1872.2 | 1905.2 |
| 62.5° | 4097.5 | 3227.1 | 2356.6 | 2289.0 | 2222.2 | 2172.4 | 1982.0 | 1851.5 | 1721.0 | 1725.6 | 1728.7 |
| 65°   | 2995.2 | 2536.2 | 2076.4 | 2061.8 | 2048.0 | 2034.2 | 1876.8 | 1736.3 | 1596.6 | 1581.3 | 1565.9 |
| 67.5° | 2157.0 | 1939.0 | 1721.0 | 1761.7 | 1802.4 | 1823.1 | 1715.6 | 1592.0 | 1467.7 | 1436.2 | 1404.7 |
| 70°   | 1550.6 | 1473.8 | 1397.1 | 1457.7 | 1518.3 | 1512.2 | 1460.0 | 1386.3 | 1312.6 | 1292.7 | 1272.7 |
| 72.5° | 1134.5 | 1133.0 | 1132.2 | 1178.3 | 1224.3 | 1162.9 | 1195.9 | 1179.1 | 1162.9 | 1148.4 | 1134.5 |
| 75°   | 850.5  | 845.1  | 840.5  | 895.0  | 950.3  | 974.9  | 996.4  | 987.2  | 978.7  | 968.0  | 958.0  |
| 77.5° | 608.0  | 612.6  | 615.6  | 675.5  | 735.4  | 806.0  | 809.8  | 789.9  | 769.2  | 758.4  | 746.1  |
| 80°   | 385.3  | 389.9  | 393.0  | 456.0  | 518.1  | 617.9  | 614.1  | 589.5  | 564.2  | 555.8  | 546.5  |
| 82.5° | 238.0  | 238.7  | 239.5  | 270.2  | 300.9  | 356.9  | 372.3  | 372.3  | 372.3  | 366.9  | 360.8  |
| 85°   | 96.0   | 100.6  | 105.9  | 125.9  | 145.8  | 176.6  | 185.8  | 187.3  | 188.1  | 179.6  | 170.4  |
| 87.5° | 30.7   | 32.2   | 34.5   | 38.4   | 42.2   | 46.1   | 53.7   | 58.3   | 62.9   | 67.6   | 70.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1385666

CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   | 200°   | 205°   | 210°   | 215°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 |
| 2.5°  | 4789.1 | 4760.7 | 4727.7 | 4694.0 | 4670.2 | 4645.6 | 4629.5 | 4613.4 | 4605.7 | 4598.0 | 4591.9 |
| 5°    | 4604.2 | 4553.5 | 4509.0 | 4463.7 | 4428.4 | 4392.3 | 4363.1 | 4333.2 | 4320.9 | 4307.9 | 4299.4 |
| 7.5°  | 4510.5 | 4444.5 | 4389.2 | 4333.2 | 4280.2 | 4228.0 | 4194.2 | 4160.5 | 4140.5 | 4120.6 | 4106.0 |
| 10°   | 4499.0 | 4429.1 | 4356.2 | 4283.3 | 4225.0 | 4166.6 | 4116.0 | 4066.8 | 4038.4 | 4010.8 | 3995.4 |
| 12.5° | 4594.9 | 4530.5 | 4443.7 | 4356.2 | 4277.2 | 4198.9 | 4136.7 | 4074.5 | 4039.2 | 4005.4 | 3982.4 |
| 15°   | 4773.8 | 4751.5 | 4670.9 | 4590.3 | 4481.3 | 4371.6 | 4282.5 | 4192.7 | 4143.6 | 4092.9 | 4064.5 |
| 17.5° | 4985.7 | 5029.4 | 4973.4 | 4916.6 | 4763.1 | 4609.5 | 4476.7 | 4344.7 | 4272.5 | 4200.4 | 4175.1 |
| 20°   | 5101.6 | 5219.8 | 5213.6 | 5208.3 | 5007.9 | 4806.8 | 4632.6 | 4458.3 | 4361.6 | 4266.4 | 4228.0 |
| 22.5° | 5050.9 | 5221.3 | 5265.1 | 5308.1 | 5111.5 | 4914.3 | 4699.3 | 4484.4 | 4370.8 | 4256.4 | 4220.3 |
| 25°   | 4812.2 | 4995.6 | 5077.0 | 5158.4 | 4996.4 | 4834.4 | 4625.6 | 4417.6 | 4297.9 | 4177.4 | 4140.5 |
| 27.5° | 4459.8 | 4607.2 | 4698.6 | 4789.9 | 4690.9 | 4591.9 | 4423.0 | 4254.1 | 4148.2 | 4041.5 | 4002.3 |
| 30°   | 4114.4 | 4214.2 | 4287.1 | 4360.1 | 4294.8 | 4229.6 | 4108.3 | 3987.8 | 3908.7 | 3830.4 | 3805.8 |
| 32.5° | 3798.9 | 3872.6 | 3913.3 | 3953.2 | 3902.6 | 3851.9 | 3772.1 | 3692.2 | 3643.1 | 3594.0 | 3577.9 |
| 35°   | 3528.0 | 3588.6 | 3619.3 | 3650.0 | 3607.8 | 3565.6 | 3494.2 | 3423.6 | 3388.3 | 3352.9 | 3339.9 |
| 37.5° | 3269.3 | 3319.9 | 3363.7 | 3408.2 | 3377.5 | 3346.8 | 3286.2 | 3225.5 | 3184.1 | 3141.1 | 3118.1 |
| 40°   | 3023.6 | 3072.0 | 3127.3 | 3181.8 | 3176.4 | 3170.2 | 3112.7 | 3055.1 | 2995.2 | 2936.1 | 2904.7 |
| 42.5° | 2798.0 | 2846.3 | 2904.7 | 2963.0 | 2974.5 | 2986.0 | 2938.4 | 2890.1 | 2821.0 | 2751.9 | 2703.5 |
| 45°   | 2603.8 | 2646.7 | 2710.4 | 2774.9 | 2801.8 | 2828.7 | 2785.7 | 2741.9 | 2664.4 | 2586.9 | 2529.3 |
| 47.5° | 2450.2 | 2494.7 | 2565.4 | 2636.8 | 2665.2 | 2694.3 | 2665.2 | 2636.8 | 2570.0 | 2502.4 | 2451.8 |
| 50°   | 2332.0 | 2379.6 | 2434.9 | 2490.9 | 2543.9 | 2596.1 | 2590.7 | 2585.3 | 2532.4 | 2479.4 | 2431.8 |
| 52.5° | 2250.6 | 2295.2 | 2352.7 | 2410.3 | 2465.6 | 2521.6 | 2530.1 | 2539.3 | 2500.9 | 2462.5 | 2421.1 |
| 55°   | 2180.8 | 2233.8 | 2287.5 | 2341.2 | 2393.4 | 2444.9 | 2456.4 | 2467.9 | 2440.2 | 2411.8 | 2381.1 |
| 57.5° | 2084.1 | 2141.6 | 2195.4 | 2249.1 | 2309.8 | 2370.4 | 2379.6 | 2388.8 | 2359.6 | 2329.7 | 2306.7 |
| 60°   | 1964.3 | 2022.7 | 2078.7 | 2134.0 | 2195.4 | 2256.8 | 2269.1 | 2281.4 | 2258.3 | 2235.3 | 2213.8 |
| 62.5° | 1795.5 | 1861.5 | 1907.5 | 1953.6 | 2011.9 | 2071.0 | 2088.7 | 2107.1 | 2096.4 | 2086.4 | 2061.8 |
| 65°   | 1628.9 | 1692.6 | 1728.7 | 1765.5 | 1816.2 | 1866.8 | 1884.5 | 1902.1 | 1896.8 | 1892.2 | 1874.5 |
| 67.5° | 1463.1 | 1521.4 | 1551.3 | 1581.3 | 1615.8 | 1650.4 | 1670.3 | 1690.3 | 1680.3 | 1669.6 | 1651.1 |
| 70°   | 1320.3 | 1367.9 | 1394.0 | 1420.1 | 1447.7 | 1475.4 | 1486.1 | 1496.8 | 1481.5 | 1466.1 | 1424.7 |
| 72.5° | 1170.6 | 1206.7 | 1229.0 | 1251.2 | 1277.3 | 1303.4 | 1309.6 | 1316.5 | 1292.7 | 1268.1 | 1219.7 |
| 75°   | 985.6  | 1013.3 | 1030.1 | 1047.8 | 1074.7 | 1101.5 | 1113.0 | 1124.6 | 1090.8 | 1057.8 | 1006.3 |
| 77.5° | 771.5  | 796.8  | 812.9  | 829.0  | 851.3  | 873.5  | 876.6  | 881.2  | 852.1  | 822.9  | 792.2  |
| 80°   | 565.0  | 583.4  | 589.5  | 594.9  | 613.3  | 631.0  | 631.0  | 631.0  | 609.5  | 587.2  | 571.9  |
| 82.5° | 356.9  | 353.1  | 345.4  | 337.8  | 356.2  | 374.6  | 380.7  | 387.6  | 377.7  | 368.5  | 351.6  |
| 85°   | 159.7  | 147.4  | 145.1  | 142.0  | 141.2  | 139.7  | 145.1  | 149.7  | 147.4  | 145.8  | 139.7  |
| 87.5° | 75.2   | 78.3   | 76.0   | 72.9   | 69.9   | 67.6   | 61.4   | 55.3   | 50.7   | 46.1   | 43.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1385666

CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   | 250°   | 255°   | 260°   | 265°   | 270°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 |
| 2.5°  | 4586.5 | 4582.7 | 4586.5 | 4591.9 | 4598.0 | 4605.7 | 4613.4 | 4629.5 | 4645.6 | 4670.2 | 4694.0 |
| 5°    | 4291.0 | 4283.3 | 4291.0 | 4299.4 | 4307.9 | 4320.9 | 4333.2 | 4363.1 | 4392.3 | 4428.4 | 4463.7 |
| 7.5°  | 4091.4 | 4083.7 | 4091.4 | 4106.0 | 4120.6 | 4140.5 | 4160.5 | 4194.2 | 4228.0 | 4280.2 | 4333.2 |
| 10°   | 3980.1 | 3968.6 | 3980.1 | 3995.4 | 4010.8 | 4038.4 | 4066.8 | 4116.0 | 4166.6 | 4225.0 | 4283.3 |
| 12.5° | 3959.4 | 3945.5 | 3959.4 | 3982.4 | 4005.4 | 4039.2 | 4074.5 | 4136.7 | 4198.9 | 4277.2 | 4356.2 |
| 15°   | 4036.1 | 4014.6 | 4036.1 | 4064.5 | 4092.9 | 4143.6 | 4192.7 | 4282.5 | 4371.6 | 4481.3 | 4590.3 |
| 17.5° | 4149.0 | 4137.4 | 4149.0 | 4175.1 | 4200.4 | 4272.5 | 4344.7 | 4476.7 | 4609.5 | 4763.1 | 4916.6 |
| 20°   | 4189.6 | 4175.8 | 4189.6 | 4228.0 | 4266.4 | 4361.6 | 4458.3 | 4632.6 | 4806.8 | 5007.9 | 5208.3 |
| 22.5° | 4183.5 | 4168.1 | 4183.5 | 4220.3 | 4256.4 | 4370.8 | 4484.4 | 4699.3 | 4914.3 | 5111.5 | 5308.1 |
| 25°   | 4102.9 | 4091.4 | 4102.9 | 4140.5 | 4177.4 | 4297.9 | 4417.6 | 4625.6 | 4834.4 | 4996.4 | 5158.4 |
| 27.5° | 3962.4 | 3937.9 | 3962.4 | 4002.3 | 4041.5 | 4148.2 | 4254.1 | 4423.0 | 4591.9 | 4690.9 | 4789.9 |
| 30°   | 3780.5 | 3769.0 | 3780.5 | 3805.8 | 3830.4 | 3908.7 | 3987.8 | 4108.3 | 4229.6 | 4294.8 | 4360.1 |
| 32.5° | 3561.7 | 3554.1 | 3561.7 | 3577.9 | 3594.0 | 3643.1 | 3692.2 | 3772.1 | 3851.9 | 3902.6 | 3953.2 |
| 35°   | 3327.6 | 3316.1 | 3327.6 | 3339.9 | 3352.9 | 3388.3 | 3423.6 | 3494.2 | 3565.6 | 3607.8 | 3650.0 |
| 37.5° | 3095.0 | 3078.1 | 3095.0 | 3118.1 | 3141.1 | 3184.1 | 3225.5 | 3286.2 | 3346.8 | 3377.5 | 3408.2 |
| 40°   | 2872.4 | 2855.5 | 2872.4 | 2904.7 | 2936.1 | 2995.2 | 3055.1 | 3112.7 | 3170.2 | 3176.4 | 3181.8 |
| 42.5° | 2655.9 | 2625.2 | 2655.9 | 2703.5 | 2751.9 | 2821.0 | 2890.1 | 2938.4 | 2986.0 | 2974.5 | 2963.0 |
| 45°   | 2471.7 | 2433.3 | 2471.7 | 2529.3 | 2586.9 | 2664.4 | 2741.9 | 2785.7 | 2828.7 | 2801.8 | 2774.9 |
| 47.5° | 2401.1 | 2364.3 | 2401.1 | 2451.8 | 2502.4 | 2570.0 | 2636.8 | 2665.2 | 2694.3 | 2665.2 | 2636.8 |
| 50°   | 2383.4 | 2348.9 | 2383.4 | 2431.8 | 2479.4 | 2532.4 | 2585.3 | 2590.7 | 2596.1 | 2543.9 | 2490.9 |
| 52.5° | 2379.6 | 2348.9 | 2379.6 | 2421.1 | 2462.5 | 2500.9 | 2539.3 | 2530.1 | 2521.6 | 2465.6 | 2410.3 |
| 55°   | 2350.4 | 2325.9 | 2350.4 | 2381.1 | 2411.8 | 2440.2 | 2467.9 | 2456.4 | 2444.9 | 2393.4 | 2341.2 |
| 57.5° | 2283.7 | 2272.1 | 2283.7 | 2306.7 | 2329.7 | 2359.6 | 2388.8 | 2379.6 | 2370.4 | 2309.8 | 2249.1 |
| 60°   | 2191.5 | 2172.4 | 2191.5 | 2213.8 | 2235.3 | 2258.3 | 2281.4 | 2269.1 | 2256.8 | 2195.4 | 2134.0 |
| 62.5° | 2038.0 | 2011.2 | 2038.0 | 2061.8 | 2086.4 | 2096.4 | 2107.1 | 2088.7 | 2071.0 | 2011.9 | 1953.6 |
| 65°   | 1857.6 | 1826.9 | 1857.6 | 1874.5 | 1892.2 | 1896.8 | 1902.1 | 1884.5 | 1866.8 | 1816.2 | 1765.5 |
| 67.5° | 1633.5 | 1627.3 | 1633.5 | 1651.1 | 1669.6 | 1680.3 | 1690.3 | 1670.3 | 1650.4 | 1615.8 | 1581.3 |
| 70°   | 1383.2 | 1335.7 | 1383.2 | 1424.7 | 1466.1 | 1481.5 | 1496.8 | 1486.1 | 1475.4 | 1447.7 | 1420.1 |
| 72.5° | 1170.6 | 1120.7 | 1170.6 | 1219.7 | 1268.1 | 1292.7 | 1316.5 | 1309.6 | 1303.4 | 1277.3 | 1251.2 |
| 75°   | 955.7  | 921.1  | 955.7  | 1006.3 | 1057.8 | 1090.8 | 1124.6 | 1113.0 | 1101.5 | 1074.7 | 1047.8 |
| 77.5° | 761.5  | 744.6  | 761.5  | 792.2  | 822.9  | 852.1  | 881.2  | 876.6  | 873.5  | 851.3  | 829.0  |
| 80°   | 556.5  | 545.0  | 556.5  | 571.9  | 587.2  | 609.5  | 631.0  | 631.0  | 631.0  | 613.3  | 594.9  |
| 82.5° | 333.9  | 322.4  | 333.9  | 351.6  | 368.5  | 377.7  | 387.6  | 380.7  | 374.6  | 356.2  | 337.8  |
| 85°   | 134.3  | 130.5  | 134.3  | 139.7  | 145.8  | 147.4  | 149.7  | 145.1  | 139.7  | 141.2  | 142.0  |
| 87.5° | 39.9   | 38.4   | 39.9   | 43.0   | 46.1   | 50.7   | 55.3   | 61.4   | 67.6   | 69.9   | 72.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1385666

CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 275°   | 280°   | 285°   | 290°   | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8 |
| 2.5°  | 4727.7 | 4760.7 | 4789.1 | 4816.8 | 4848.3 | 4880.5 | 4921.2 | 4962.6 | 5001.0 | 5044.8 | 5088.5 |
| 5°    | 4509.0 | 4553.5 | 4604.2 | 4653.3 | 4713.2 | 4773.0 | 4845.2 | 4918.9 | 4993.3 | 5080.1 | 5163.0 |
| 7.5°  | 4389.2 | 4444.5 | 4510.5 | 4576.5 | 4654.8 | 4732.3 | 4821.4 | 4911.2 | 5001.0 | 5116.2 | 5226.7 |
| 10°   | 4356.2 | 4429.1 | 4499.0 | 4568.8 | 4648.7 | 4728.5 | 4822.2 | 4916.6 | 5012.5 | 5135.3 | 5262.0 |
| 12.5° | 4443.7 | 4530.5 | 4594.9 | 4659.4 | 4714.7 | 4770.7 | 4848.3 | 4926.6 | 5020.2 | 5154.5 | 5293.5 |
| 15°   | 4670.9 | 4751.5 | 4773.8 | 4796.1 | 4800.7 | 4805.3 | 4855.9 | 4906.6 | 4989.5 | 5139.2 | 5296.5 |
| 17.5° | 4973.4 | 5029.4 | 4985.7 | 4941.9 | 4865.9 | 4789.9 | 4796.8 | 4803.7 | 4874.4 | 5049.4 | 5232.1 |
| 20°   | 5213.6 | 5219.8 | 5101.6 | 4983.4 | 4835.2 | 4686.3 | 4643.3 | 4599.5 | 4644.1 | 4875.9 | 5116.9 |
| 22.5° | 5265.1 | 5221.3 | 5050.9 | 4880.5 | 4686.3 | 4492.1 | 4428.4 | 4363.9 | 4406.1 | 4682.5 | 4984.9 |
| 25°   | 5077.0 | 4995.6 | 4812.2 | 4628.7 | 4449.1 | 4269.5 | 4199.6 | 4129.8 | 4133.6 | 4450.6 | 4827.5 |
| 27.5° | 4698.6 | 4607.2 | 4459.8 | 4312.5 | 4178.9 | 4045.3 | 3977.8 | 3911.0 | 3891.8 | 4215.7 | 4666.3 |
| 30°   | 4287.1 | 4214.2 | 4114.4 | 4014.6 | 3917.9 | 3821.2 | 3769.0 | 3716.8 | 3696.1 | 4010.8 | 4525.9 |
| 32.5° | 3913.3 | 3872.6 | 3798.9 | 3724.5 | 3661.5 | 3598.6 | 3576.3 | 3554.1 | 3554.1 | 3844.2 | 4403.0 |
| 35°   | 3619.3 | 3588.6 | 3528.0 | 3468.1 | 3426.6 | 3385.2 | 3403.6 | 3422.0 | 3469.6 | 3693.8 | 4263.3 |
| 37.5° | 3363.7 | 3319.9 | 3269.3 | 3217.8 | 3199.4 | 3179.5 | 3230.1 | 3279.3 | 3369.8 | 3546.4 | 4108.3 |
| 40°   | 3127.3 | 3072.0 | 3023.6 | 2974.5 | 2976.8 | 2978.3 | 3052.0 | 3125.7 | 3239.3 | 3379.0 | 3923.3 |
| 42.5° | 2904.7 | 2846.3 | 2798.0 | 2749.6 | 2759.6 | 2769.6 | 2863.2 | 2956.9 | 3097.3 | 3194.8 | 3703.0 |
| 45°   | 2710.4 | 2646.7 | 2603.8 | 2562.3 | 2577.7 | 2593.0 | 2688.2 | 2784.9 | 2924.6 | 3012.9 | 3478.8 |
| 47.5° | 2565.4 | 2494.7 | 2450.2 | 2406.5 | 2416.5 | 2425.7 | 2508.6 | 2590.7 | 2721.2 | 2823.3 | 3256.2 |
| 50°   | 2434.9 | 2379.6 | 2332.0 | 2283.7 | 2272.1 | 2260.6 | 2328.9 | 2396.5 | 2525.5 | 2665.2 | 3058.2 |
| 52.5° | 2352.7 | 2295.2 | 2250.6 | 2206.9 | 2171.6 | 2135.5 | 2186.9 | 2237.6 | 2375.8 | 2554.6 | 2880.1 |
| 55°   | 2287.5 | 2233.8 | 2180.8 | 2127.8 | 2077.2 | 2026.5 | 2083.3 | 2140.1 | 2302.8 | 2480.9 | 2731.2 |
| 57.5° | 2195.4 | 2141.6 | 2084.1 | 2026.5 | 1975.8 | 1925.2 | 2004.2 | 2084.1 | 2283.7 | 2433.3 | 2605.3 |
| 60°   | 2078.7 | 2022.7 | 1964.3 | 1905.2 | 1872.2 | 1838.4 | 1938.2 | 2038.0 | 2237.6 | 2355.0 | 2475.6 |
| 62.5° | 1907.5 | 1861.5 | 1795.5 | 1728.7 | 1725.6 | 1721.0 | 1851.5 | 1982.0 | 2172.4 | 2222.2 | 2289.0 |
| 65°   | 1728.7 | 1692.6 | 1628.9 | 1565.9 | 1581.3 | 1596.6 | 1736.3 | 1876.8 | 2034.2 | 2048.0 | 2061.8 |
| 67.5° | 1551.3 | 1521.4 | 1463.1 | 1404.7 | 1436.2 | 1467.7 | 1592.0 | 1715.6 | 1823.1 | 1802.4 | 1761.7 |
| 70°   | 1394.0 | 1367.9 | 1320.3 | 1272.7 | 1292.7 | 1312.6 | 1386.3 | 1460.0 | 1512.2 | 1518.3 | 1457.7 |
| 72.5° | 1229.0 | 1206.7 | 1170.6 | 1134.5 | 1148.4 | 1162.9 | 1179.1 | 1195.9 | 1162.9 | 1224.3 | 1178.3 |
| 75°   | 1030.1 | 1013.3 | 985.6  | 958.0  | 968.0  | 978.7  | 987.2  | 996.4  | 974.9  | 950.3  | 895.0  |
| 77.5° | 812.9  | 796.8  | 771.5  | 746.1  | 758.4  | 769.2  | 789.9  | 809.8  | 806.0  | 735.4  | 675.5  |
| 80°   | 589.5  | 583.4  | 565.0  | 546.5  | 555.8  | 564.2  | 589.5  | 614.1  | 617.9  | 518.1  | 456.0  |
| 82.5° | 345.4  | 353.1  | 356.9  | 360.8  | 366.9  | 372.3  | 372.3  | 372.3  | 356.9  | 300.9  | 270.2  |
| 85°   | 145.1  | 147.4  | 159.7  | 170.4  | 179.6  | 188.1  | 187.3  | 185.8  | 176.6  | 145.8  | 125.9  |
| 87.5° | 76.0   | 78.3   | 75.2   | 70.6   | 67.6   | 62.9   | 58.3   | 53.7   | 46.1   | 42.2   | 38.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1385666  
 CATALOG NUMBER: VAL-T-SB5D-722-U-SLL

**CANDELA DISTRIBUTION (continued):**

|       | 330°   | 335°   | 340°   | 345°   | 350°    | 355°    | 360°    |
|-------|--------|--------|--------|--------|---------|---------|---------|
| 0°    | 5004.8 | 5004.8 | 5004.8 | 5004.8 | 5004.8  | 5004.8  | 5004.8  |
| 2.5°  | 5131.5 | 5176.8 | 5221.3 | 5265.8 | 5310.4  | 5358.7  | 5407.8  |
| 5°    | 5246.6 | 5334.9 | 5423.2 | 5513.0 | 5603.6  | 5689.6  | 5776.3  |
| 7.5°  | 5336.5 | 5459.3 | 5582.1 | 5719.5 | 5856.9  | 6002.7  | 6148.6  |
| 10°   | 5388.7 | 5540.6 | 5691.9 | 5863.0 | 6033.5  | 6208.5  | 6382.7  |
| 12.5° | 5433.2 | 5602.8 | 5772.5 | 5963.6 | 6154.7  | 6328.2  | 6501.7  |
| 15°   | 5453.9 | 5637.4 | 5820.1 | 6014.3 | 6208.5  | 6383.5  | 6559.3  |
| 17.5° | 5415.5 | 5623.5 | 5832.3 | 6039.6 | 6246.9  | 6410.4  | 6574.6  |
| 20°   | 5358.0 | 5602.8 | 5847.7 | 6070.3 | 6292.9  | 6458.7  | 6624.5  |
| 22.5° | 5287.3 | 5586.7 | 5886.1 | 6130.2 | 6375.0  | 6526.3  | 6678.3  |
| 25°   | 5204.4 | 5585.2 | 5965.9 | 6233.0 | 6500.2  | 6631.4  | 6762.7  |
| 27.5° | 5116.2 | 5599.8 | 6083.3 | 6383.5 | 6684.4  | 6784.9  | 6885.5  |
| 30°   | 5041.7 | 5631.2 | 6221.5 | 6561.6 | 6900.9  | 6979.2  | 7058.2  |
| 32.5° | 4962.6 | 5666.5 | 6371.2 | 6771.1 | 7171.1  | 7220.2  | 7269.3  |
| 35°   | 4832.1 | 5658.1 | 6484.8 | 6993.7 | 7503.4  | 7564.8  | 7626.3  |
| 37.5° | 4670.9 | 5634.3 | 6597.7 | 7265.5 | 7933.3  | 8006.2  | 8079.1  |
| 40°   | 4467.5 | 5580.6 | 6693.6 | 7576.4 | 8459.1  | 8603.4  | 8747.0  |
| 42.5° | 4210.4 | 5487.7 | 6764.2 | 7920.3 | 9074.7  | 9379.5  | 9683.5  |
| 45°   | 3945.5 | 5424.0 | 6902.4 | 8387.0 | 9871.5  | 10359.0 | 10846.4 |
| 47.5° | 3690.7 | 5349.5 | 7008.3 | 8866.7 | 10725.1 | 11342.3 | 11959.4 |
| 50°   | 3450.4 | 5222.9 | 6994.5 | 9285.1 | 11575.6 | 12412.3 | 13249.0 |
| 52.5° | 3207.1 | 4963.4 | 6720.5 | 9483.1 | 12245.0 | 13574.5 | 14903.2 |
| 55°   | 2979.9 | 4619.5 | 6257.6 | 9430.9 | 12604.2 | 14742.0 | 16879.9 |
| 57.5° | 2777.2 | 4259.5 | 5741.8 | 9146.1 | 12550.5 | 15722.3 | 18894.8 |
| 60°   | 2596.1 | 3804.3 | 5012.5 | 8463.7 | 11914.9 | 16161.4 | 20407.0 |
| 62.5° | 2356.6 | 3227.1 | 4097.5 | 7345.3 | 10593.1 | 15187.3 | 19781.4 |
| 65°   | 2076.4 | 2536.2 | 2995.2 | 5761.7 | 8528.2  | 13099.3 | 17670.5 |
| 67.5° | 1721.0 | 1939.0 | 2157.0 | 4483.6 | 6810.3  | 11250.2 | 15690.1 |
| 70°   | 1397.1 | 1473.8 | 1550.6 | 3435.8 | 5321.1  | 9557.6  | 13794.0 |
| 72.5° | 1132.2 | 1133.0 | 1134.5 | 2583.0 | 4031.5  | 7936.4  | 11840.5 |
| 75°   | 840.5  | 845.1  | 850.5  | 1914.4 | 2978.3  | 6336.7  | 9695.0  |
| 77.5° | 615.6  | 612.6  | 608.0  | 1237.4 | 1866.8  | 4157.4  | 6448.0  |
| 80°   | 393.0  | 389.9  | 385.3  | 683.9  | 982.5   | 2383.4  | 3784.3  |
| 82.5° | 239.5  | 238.7  | 238.0  | 367.7  | 497.4   | 1194.4  | 1892.2  |
| 85°   | 105.9  | 100.6  | 96.0   | 116.7  | 138.2   | 284.0   | 429.9   |
| 87.5° | 34.5   | 32.2   | 30.7   | 31.5   | 32.2    | 33.8    | 34.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-722-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 2200K CCT 26 LEDS

**Spectral Parameters**

CCT (K): 2160  
 CIE u': 0.2927  
 CIE v': 0.5388  
 Duv: 0.0015  
 CIE x: 0.5130  
 CIE y: 0.4197  
 CIE z: 0.0674  
 Peak Wavelength (nm): 609  
 Dominant Wavelength (nm): 587  
 Purity: 79.96089  
 Rf: 70.6  
 Rg: 97.6

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.9 |      |       |
| R1:       | 68.7 | R9:  | -17.8 |
| R2:       | 82.6 | R10: | 60.5  |
| R3:       | 95.5 | R11: | 60.2  |
| R4:       | 66.4 | R12: | 48.2  |
| R5:       | 65.4 | R13: | 70.7  |
| R6:       | 75.9 | R14: | 96.8  |
| R7:       | 77.2 | R15: | 61.8  |
| R8:       | 43.5 |      |       |



**Test Conditions**


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-2


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-2

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

| $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360               | 0                           | NR                      | 490               | 27                          | NR                      | 620               | 966                         | NR                      | 750               | 46                          | NR                      | 880               | 1                           | NR                      |
| 365               | 0                           | NR                      | 495               | 42                          | NR                      | 625               | 930                         | NR                      | 755               | 39                          | NR                      | 885               | 1                           | NR                      |
| 370               | 0                           | NR                      | 500               | 67                          | NR                      | 630               | 888                         | NR                      | 760               | 34                          | NR                      | 890               | 1                           | NR                      |
| 375               | 0                           | NR                      | 505               | 101                         | NR                      | 635               | 835                         | NR                      | 765               | 30                          | NR                      | 895               | 1                           | NR                      |
| 380               | 0                           | NR                      | 510               | 139                         | NR                      | 640               | 778                         | NR                      | 770               | 26                          | NR                      | 900               | 1                           | NR                      |
| 385               | 0                           | NR                      | 515               | 183                         | NR                      | 645               | 717                         | NR                      | 775               | 22                          | NR                      | 905               | 1                           | NR                      |
| 390               | 0                           | NR                      | 520               | 224                         | NR                      | 650               | 656                         | NR                      | 780               | 19                          | NR                      | 910               | 1                           | NR                      |
| 395               | 0                           | NR                      | 525               | 262                         | NR                      | 655               | 595                         | NR                      | 785               | 17                          | NR                      | 915               | 1                           | NR                      |
| 400               | 1                           | NR                      | 530               | 299                         | NR                      | 660               | 536                         | NR                      | 790               | 15                          | NR                      | 920               | 1                           | NR                      |
| 405               | 3                           | NR                      | 535               | 332                         | NR                      | 665               | 480                         | NR                      | 795               | 13                          | NR                      | 925               | 1                           | NR                      |
| 410               | 7                           | NR                      | 540               | 365                         | NR                      | 670               | 425                         | NR                      | 800               | 11                          | NR                      | 930               | 1                           | NR                      |
| 415               | 17                          | NR                      | 545               | 400                         | NR                      | 675               | 376                         | NR                      | 805               | 10                          | NR                      | 935               | 0                           | NR                      |
| 420               | 36                          | NR                      | 550               | 437                         | NR                      | 680               | 332                         | NR                      | 810               | 8                           | NR                      | 940               | 0                           | NR                      |
| 425               | 67                          | NR                      | 555               | 479                         | NR                      | 685               | 291                         | NR                      | 815               | 8                           | NR                      | 945               | 0                           | NR                      |
| 430               | 105                         | NR                      | 560               | 525                         | NR                      | 690               | 255                         | NR                      | 820               | 7                           | NR                      | 950               | 0                           | NR                      |
| 435               | 141                         | NR                      | 565               | 579                         | NR                      | 695               | 221                         | NR                      | 825               | 6                           | NR                      | 955               | 0                           | NR                      |
| 440               | 169                         | NR                      | 570               | 639                         | NR                      | 700               | 192                         | NR                      | 830               | 5                           | NR                      | 960               | 0                           | NR                      |
| 445               | 173                         | NR                      | 575               | 703                         | NR                      | 705               | 167                         | NR                      | 835               | 4                           | NR                      | 965               | 0                           | NR                      |
| 450               | 136                         | NR                      | 580               | 769                         | NR                      | 710               | 144                         | NR                      | 840               | 4                           | NR                      | 970               | 0                           | NR                      |
| 455               | 80                          | NR                      | 585               | 832                         | NR                      | 715               | 125                         | NR                      | 845               | 3                           | NR                      | 975               | 0                           | NR                      |
| 460               | 45                          | NR                      | 590               | 890                         | NR                      | 720               | 109                         | NR                      | 850               | 3                           | NR                      | 980               | 0                           | NR                      |
| 465               | 32                          | NR                      | 595               | 937                         | NR                      | 725               | 94                          | NR                      | 855               | 3                           | NR                      | 985               | 0                           | NR                      |
| 470               | 23                          | NR                      | 600               | 972                         | NR                      | 730               | 81                          | NR                      | 860               | 2                           | NR                      | 990               | 0                           | NR                      |
| 475               | 18                          | NR                      | 605               | 992                         | NR                      | 735               | 70                          | NR                      | 865               | 2                           | NR                      | 995               | 0                           | NR                      |
| 480               | 18                          | NR                      | 610               | 998                         | NR                      | 740               | 61                          | NR                      | 870               | 2                           | NR                      | 1000              | 0                           | NR                      |
| 485               | 20                          | NR                      | 615               | 990                         | NR                      | 745               | 53                          | NR                      | 875               | 2                           | NR                      |                   |                             |                         |

REPORT NUMBER: SP1-2407-184-2

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 0.8**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 27                       | NR            | 620    | 966                      | NR            | 750    | 46                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 42                       | NR            | 625    | 930                      | NR            | 755    | 39                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 67                       | NR            | 630    | 888                      | NR            | 760    | 34                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 101                      | NR            | 635    | 835                      | NR            | 765    | 30                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 139                      | NR            | 640    | 778                      | NR            | 770    | 26                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 183                      | NR            | 645    | 717                      | NR            | 775    | 22                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 224                      | NR            | 650    | 656                      | NR            | 780    | 19                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 262                      | NR            | 655    | 595                      | NR            | 785    | 17                       | NR            | 915    | 1                        | NR            |
| 400    | 1                        | NR            | 530    | 299                      | NR            | 660    | 536                      | NR            | 790    | 15                       | NR            | 920    | 1                        | NR            |
| 405    | 3                        | NR            | 535    | 332                      | NR            | 665    | 480                      | NR            | 795    | 13                       | NR            | 925    | 1                        | NR            |
| 410    | 7                        | NR            | 540    | 365                      | NR            | 670    | 425                      | NR            | 800    | 11                       | NR            | 930    | 1                        | NR            |
| 415    | 17                       | NR            | 545    | 400                      | NR            | 675    | 376                      | NR            | 805    | 10                       | NR            | 935    | 0                        | NR            |
| 420    | 36                       | NR            | 550    | 437                      | NR            | 680    | 332                      | NR            | 810    | 8                        | NR            | 940    | 0                        | NR            |
| 425    | 67                       | NR            | 555    | 479                      | NR            | 685    | 291                      | NR            | 815    | 8                        | NR            | 945    | 0                        | NR            |
| 430    | 105                      | NR            | 560    | 525                      | NR            | 690    | 255                      | NR            | 820    | 7                        | NR            | 950    | 0                        | NR            |
| 435    | 141                      | NR            | 565    | 579                      | NR            | 695    | 221                      | NR            | 825    | 6                        | NR            | 955    | 0                        | NR            |
| 440    | 169                      | NR            | 570    | 639                      | NR            | 700    | 192                      | NR            | 830    | 5                        | NR            | 960    | 0                        | NR            |
| 445    | 173                      | NR            | 575    | 703                      | NR            | 705    | 167                      | NR            | 835    | 4                        | NR            | 965    | 0                        | NR            |
| 450    | 136                      | NR            | 580    | 769                      | NR            | 710    | 144                      | NR            | 840    | 4                        | NR            | 970    | 0                        | NR            |
| 455    | 80                       | NR            | 585    | 832                      | NR            | 715    | 125                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 45                       | NR            | 590    | 890                      | NR            | 720    | 109                      | NR            | 850    | 3                        | NR            | 980    | 0                        | NR            |
| 465    | 32                       | NR            | 595    | 937                      | NR            | 725    | 94                       | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 23                       | NR            | 600    | 972                      | NR            | 730    | 81                       | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 18                       | NR            | 605    | 992                      | NR            | 735    | 70                       | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 18                       | NR            | 610    | 998                      | NR            | 740    | 61                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 20                       | NR            | 615    | 990                      | NR            | 745    | 53                       | NR            | 875    | 2                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 1.21**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 27                       | NR            | 620    | 966                      | NR            | 750    | 46                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 42                       | NR            | 625    | 930                      | NR            | 755    | 39                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 67                       | NR            | 630    | 888                      | NR            | 760    | 34                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 101                      | NR            | 635    | 835                      | NR            | 765    | 30                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 139                      | NR            | 640    | 778                      | NR            | 770    | 26                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 183                      | NR            | 645    | 717                      | NR            | 775    | 22                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 224                      | NR            | 650    | 656                      | NR            | 780    | 19                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 262                      | NR            | 655    | 595                      | NR            | 785    | 17                       | NR            | 915    | 1                        | NR            |
| 400    | 1                        | NR            | 530    | 299                      | NR            | 660    | 536                      | NR            | 790    | 15                       | NR            | 920    | 1                        | NR            |
| 405    | 3                        | NR            | 535    | 332                      | NR            | 665    | 480                      | NR            | 795    | 13                       | NR            | 925    | 1                        | NR            |
| 410    | 7                        | NR            | 540    | 365                      | NR            | 670    | 425                      | NR            | 800    | 11                       | NR            | 930    | 1                        | NR            |
| 415    | 17                       | NR            | 545    | 400                      | NR            | 675    | 376                      | NR            | 805    | 10                       | NR            | 935    | 0                        | NR            |
| 420    | 36                       | NR            | 550    | 437                      | NR            | 680    | 332                      | NR            | 810    | 8                        | NR            | 940    | 0                        | NR            |
| 425    | 67                       | NR            | 555    | 479                      | NR            | 685    | 291                      | NR            | 815    | 8                        | NR            | 945    | 0                        | NR            |
| 430    | 105                      | NR            | 560    | 525                      | NR            | 690    | 255                      | NR            | 820    | 7                        | NR            | 950    | 0                        | NR            |
| 435    | 141                      | NR            | 565    | 579                      | NR            | 695    | 221                      | NR            | 825    | 6                        | NR            | 955    | 0                        | NR            |
| 440    | 169                      | NR            | 570    | 639                      | NR            | 700    | 192                      | NR            | 830    | 5                        | NR            | 960    | 0                        | NR            |
| 445    | 173                      | NR            | 575    | 703                      | NR            | 705    | 167                      | NR            | 835    | 4                        | NR            | 965    | 0                        | NR            |
| 450    | 136                      | NR            | 580    | 769                      | NR            | 710    | 144                      | NR            | 840    | 4                        | NR            | 970    | 0                        | NR            |
| 455    | 80                       | NR            | 585    | 832                      | NR            | 715    | 125                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 45                       | NR            | 590    | 890                      | NR            | 720    | 109                      | NR            | 850    | 3                        | NR            | 980    | 0                        | NR            |
| 465    | 32                       | NR            | 595    | 937                      | NR            | 725    | 94                       | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 23                       | NR            | 600    | 972                      | NR            | 730    | 81                       | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 18                       | NR            | 605    | 992                      | NR            | 735    | 70                       | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 18                       | NR            | 610    | 998                      | NR            | 740    | 61                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 20                       | NR            | 615    | 990                      | NR            | 745    | 53                       | NR            | 875    | 2                        | NR            |        |                          |               |

**Summary**

$R_f = 70.6$   
 $R_g = 97.6$   
 $CIE R_a = 71.9$   
 $R_g = -17.8$



**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 60 | CES51 = 74 | CES76 = 58 |
| CES02 = 65 | CES27 = 77 | CES52 = 77 | CES77 = 82 |
| CES03 = 32 | CES28 = 85 | CES53 = 65 | CES78 = 65 |
| CES04 = 72 | CES29 = 50 | CES54 = 77 | CES79 = 86 |
| CES05 = 52 | CES30 = 49 | CES55 = 74 | CES80 = 85 |
| CES06 = 53 | CES31 = 55 | CES56 = 64 | CES81 = 61 |
| CES07 = 44 | CES32 = 55 | CES57 = 60 | CES82 = 93 |
| CES08 = 43 | CES33 = 55 | CES58 = 64 | CES83 = 83 |
| CES09 = 29 | CES34 = 75 | CES59 = 84 | CES84 = 93 |
| CES10 = 79 | CES35 = 88 | CES60 = 89 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 55 |
| CES12 = 68 | CES37 = 82 | CES62 = 68 | CES87 = 79 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 86 | CES65 = 66 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 89 |
| CES17 = 51 | CES42 = 83 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 71 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 81 | CES94 = 52 |
| CES20 = 68 | CES45 = 76 | CES70 = 65 | CES95 = 76 |
| CES21 = 89 | CES46 = 68 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 88 | CES97 = 76 |
| CES23 = 92 | CES48 = 47 | CES73 = 59 | CES98 = 71 |
| CES24 = 92 | CES49 = 65 | CES74 = 85 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)