

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1384904

Luminaire Tested: **VAL-T-SB1B-727-U-SLR**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been
influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
 Report Number: P1384904
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 02/18/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: VAL-T-SB1B-727-U-SLR
 Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 15 SQUARE 40W 70CRI
 2700K FIXTURE w/ 90° Spill Light Eliminator RIGHT OPTIC
 Light Source: (26) 2700K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER
 Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
a	good	reflector
b	good	lens
c	good	housing
d	good	cord

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 4517.9 lumens
 Efficiency: N/A
 Efficacy: 112.9 lumens/watt
 Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
 IES Classification: Type IV - Short
 BUG Rating: B1 - U0 - G1

 Input Watts (W): 40
 Input Voltage (V): 120
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: 0.98
 Total Harmonic Distortion (THDi): 5.3%
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 28.75 FT

REPORT NUMBER: P1384904
 CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2.1 fc
 Type IV - Short - N/A

REPORT NUMBER: P1384904
CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1215.4	0.0	1215.4
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	3302.5	0.0	3302.5
	% Fixture	73.1	0.0	73.1
Total	Lumens	4517.9	0.0	4517.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.1	1.6
10°-20°	218.0	4.8
20°-30°	337.4	7.5
30°-40°	418.6	9.3
40°-50°	612.1	13.5
50°-60°	958.7	21.2
60°-70°	1137.6	25.2
70°-80°	663.5	14.7
80°-90°	100.9	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4517.9	100.0
0°-180°	4517.9	100.0

Coefficient of Utilization



REPORT NUMBER: P1384904


CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	339.6	7.5			
FM	(30°-60°)	1374.4	30.4			
FH	(60°-80°)	1505.9	33.3			G1/1800
FVH	(80°-90°)	82.6	1.8			G1/100
BL	(0°-30°)	286.9	6.4	B1/500		
BM	(30°-60°)	614.9	13.6	B1/1000		
BH	(60°-80°)	295.2	6.5	B1/500		G1/500
BVH	(80°-90°)	18.4	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short



REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4
2.5°	778.4	771.3	764.4	758.0	751.5	745.1	738.6	732.4	726.1	719.8	714.3
5°	831.4	818.9	806.6	793.5	780.6	767.9	755.2	743.1	731.2	718.7	708.0
7.5°	885.0	864.0	843.0	823.3	803.5	785.8	768.1	752.3	736.4	719.8	706.9
10°	918.7	893.6	868.4	843.9	819.3	797.5	775.6	757.4	739.2	721.5	707.7
12.5°	935.8	910.9	885.9	858.4	830.9	806.5	782.0	761.9	741.9	722.6	709.1
15°	944.1	918.8	893.6	865.7	837.7	811.4	785.0	762.4	739.7	718.2	706.2
17.5°	946.3	922.7	899.2	869.3	839.5	809.4	779.5	753.1	726.8	701.6	691.4
20°	953.5	929.7	905.8	873.7	841.7	806.5	771.2	736.5	701.8	668.5	662.0
22.5°	961.3	939.4	917.6	882.4	847.2	804.1	761.0	717.5	674.0	634.2	628.1
25°	973.4	954.5	935.6	897.2	858.7	803.9	749.1	694.9	640.6	595.0	594.4
27.5°	991.1	976.6	962.1	918.8	875.6	806.0	736.4	671.7	606.8	560.2	562.9
30°	1015.9	1004.6	993.3	944.5	895.5	810.5	725.7	651.4	577.3	532.0	535.0
32.5°	1046.3	1039.3	1032.2	974.6	917.1	815.6	714.3	633.8	553.3	511.6	511.6
35°	1097.7	1088.9	1080.0	1006.7	933.4	814.4	695.5	613.7	531.7	499.4	492.6
37.5°	1162.9	1152.4	1141.9	1045.8	949.7	811.0	672.3	591.3	510.5	485.0	472.0
40°	1259.0	1238.4	1217.6	1090.5	963.5	803.3	643.0	564.7	486.4	466.3	449.9
42.5°	1393.8	1350.1	1306.2	1140.0	973.6	789.9	606.0	533.0	459.9	445.8	425.6
45°	1561.2	1491.0	1420.9	1207.2	993.5	780.7	567.9	500.7	433.7	421.0	400.9
47.5°	1721.4	1632.6	1543.8	1276.3	1008.8	770.0	531.2	468.7	406.4	391.7	372.9
50°	1907.0	1786.6	1666.2	1336.5	1006.8	751.8	496.6	440.2	383.6	363.5	344.9
52.5°	2145.1	1953.9	1762.5	1365.0	967.3	714.4	461.6	414.6	367.7	342.0	322.1
55°	2429.7	2121.9	1814.2	1357.5	900.7	664.9	428.9	393.1	357.1	331.5	308.0
57.5°	2719.7	2263.0	1806.5	1316.5	826.5	613.1	399.7	375.0	350.2	328.7	300.0
60°	2937.3	2326.2	1715.0	1218.3	721.5	547.6	373.7	356.3	339.0	322.1	293.3
62.5°	2847.3	2186.0	1524.7	1057.3	589.8	464.5	339.2	329.5	319.9	312.7	285.3
65°	2543.5	1885.5	1227.5	829.3	431.1	365.1	298.9	296.8	294.8	292.8	270.1
67.5°	2258.4	1619.3	980.3	645.4	310.5	279.1	247.7	253.6	259.4	262.4	246.9
70°	1985.5	1375.7	765.9	494.5	223.2	212.1	201.1	209.8	218.5	217.7	210.1
72.5°	1704.3	1142.3	580.3	371.8	163.3	163.1	163.0	169.6	176.2	167.4	172.1
75°	1395.5	912.1	428.7	275.6	122.4	121.6	121.0	128.8	136.8	140.3	143.4
77.5°	928.1	598.4	268.7	178.1	87.5	88.2	88.6	97.2	105.8	116.0	116.6
80°	544.7	343.1	141.4	98.4	55.5	56.1	56.6	65.6	74.6	88.9	88.4
82.5°	272.4	171.9	71.6	52.9	34.3	34.4	34.5	38.9	43.3	51.4	53.6
85°	61.9	40.9	19.9	16.8	13.8	14.5	15.2	18.1	21.0	25.4	26.7
87.5°	5.0	4.9	4.6	4.5	4.4	4.6	5.0	5.5	6.1	6.6	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4
2.5°	708.3	702.5	697.8	693.3	689.3	685.3	680.5	675.6	672.2	668.7	666.4
5°	697.4	687.0	678.4	669.8	662.7	655.4	649.0	642.5	637.4	632.2	628.0
7.5°	694.0	681.2	670.0	658.7	649.2	639.7	631.8	623.7	616.1	608.6	603.7
10°	694.1	680.6	669.1	657.6	647.6	637.5	627.0	616.5	608.1	599.7	592.4
12.5°	697.8	686.7	678.6	670.7	661.4	652.1	639.6	627.0	615.6	604.4	595.4
15°	699.0	691.7	691.0	690.3	687.1	683.9	672.3	660.7	645.0	629.2	616.4
17.5°	690.4	689.5	700.4	711.3	717.6	723.9	715.9	707.7	685.6	663.5	644.4
20°	668.3	674.5	696.0	717.3	734.3	751.3	750.4	749.7	720.8	691.9	666.8
22.5°	637.4	646.6	674.5	702.5	727.0	751.5	757.8	764.0	735.7	707.4	676.4
25°	604.5	614.5	640.4	666.2	692.7	719.1	730.8	742.5	719.2	695.9	665.8
27.5°	572.6	582.3	601.5	620.7	641.9	663.2	676.3	689.5	675.2	660.9	636.6
30°	542.5	550.0	563.9	577.9	592.2	606.6	617.1	627.6	618.2	608.8	591.3
32.5°	514.8	518.0	527.0	536.1	546.8	557.4	563.3	569.0	561.7	554.4	542.9
35°	489.9	487.3	493.2	499.2	507.8	516.5	521.0	525.4	519.3	513.2	502.9
37.5°	464.9	457.6	460.5	463.2	470.6	477.9	484.2	490.6	486.2	481.7	473.0
40°	439.3	428.7	428.5	428.1	435.2	442.2	450.1	458.0	457.2	456.3	448.0
42.5°	412.1	398.6	397.2	395.8	402.7	409.7	418.1	426.5	428.1	429.8	423.0
45°	386.9	373.2	371.0	368.8	374.8	381.0	390.1	399.4	403.3	407.2	401.0
47.5°	361.1	349.1	347.8	346.4	352.7	359.1	369.3	379.5	383.6	387.8	383.6
50°	335.2	325.4	327.0	328.7	335.7	342.5	350.5	358.5	366.2	373.7	372.9
52.5°	314.8	307.4	312.6	317.7	324.0	330.4	338.6	346.9	354.9	363.0	364.2
55°	299.9	291.7	299.0	306.3	313.9	321.5	329.3	337.0	344.5	351.9	353.6
57.5°	288.5	277.1	284.4	291.7	300.0	308.3	316.0	323.7	332.5	341.2	342.5
60°	279.0	264.6	269.5	274.2	282.7	291.1	299.2	307.2	316.0	324.8	326.6
62.5°	266.5	247.7	248.4	248.8	258.4	267.9	274.6	281.2	289.6	298.1	300.6
65°	249.9	229.8	227.6	225.4	234.5	243.6	248.8	254.1	261.4	268.7	271.3
67.5°	229.2	211.3	206.7	202.2	210.6	219.0	223.3	227.6	232.6	237.6	240.4
70°	199.5	188.9	186.1	183.2	190.0	196.9	200.6	204.4	208.4	212.4	213.9
72.5°	169.7	167.4	165.3	163.3	168.5	173.7	176.9	180.1	183.9	187.6	188.5
75°	142.1	140.9	139.3	137.9	141.9	145.8	148.3	150.8	154.7	158.6	160.2
77.5°	113.7	110.7	109.2	107.4	111.0	114.7	117.0	119.3	122.5	125.7	126.2
80°	84.9	81.2	80.0	78.7	81.3	84.0	84.9	85.6	88.3	90.8	90.8
82.5°	53.6	53.6	52.8	51.9	51.4	50.8	49.7	48.6	51.3	53.9	54.8
85°	27.0	27.1	25.9	24.5	23.0	21.2	20.9	20.4	20.3	20.1	20.9
87.5°	8.4	9.1	9.7	10.2	10.8	11.3	10.9	10.5	10.1	9.7	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4
2.5°	664.0	662.9	661.8	660.9	660.2	659.6	660.2	660.9	661.8	662.9	664.0
5°	623.7	621.9	620.1	618.8	617.6	616.5	617.6	618.8	620.1	621.9	623.7
7.5°	598.9	596.0	593.1	591.0	588.9	587.8	588.9	591.0	593.1	596.0	598.9
10°	585.4	581.3	577.3	575.1	572.9	571.2	572.9	575.1	577.3	581.3	585.4
12.5°	586.5	581.4	576.5	573.2	569.9	567.9	569.9	573.2	576.5	581.4	586.5
15°	603.5	596.4	589.1	585.0	581.0	577.9	581.0	585.0	589.1	596.4	603.5
17.5°	625.4	615.0	604.6	600.9	597.2	595.5	597.2	600.9	604.6	615.0	625.4
20°	641.7	627.8	614.1	608.6	603.0	601.1	603.0	608.6	614.1	627.8	641.7
22.5°	645.5	629.1	612.7	607.5	602.2	600.0	602.2	607.5	612.7	629.1	645.5
25°	635.9	618.6	601.3	596.0	590.6	588.9	590.6	596.0	601.3	618.6	635.9
27.5°	612.3	597.1	581.7	576.1	570.3	566.8	570.3	576.1	581.7	597.1	612.3
30°	574.0	562.6	551.3	547.8	544.2	542.5	544.2	547.8	551.3	562.6	574.0
32.5°	531.5	524.4	517.3	515.0	512.7	511.6	512.7	515.0	517.3	524.4	531.5
35°	492.8	487.7	482.6	480.7	479.0	477.3	479.0	480.7	482.6	487.7	492.8
37.5°	464.3	458.3	452.1	448.8	445.5	443.1	445.5	448.8	452.1	458.3	464.3
40°	439.7	431.1	422.6	418.1	413.4	411.0	413.4	418.1	422.6	431.1	439.7
42.5°	416.0	406.0	396.1	389.1	382.3	377.9	382.3	389.1	396.1	406.0	416.0
45°	394.7	383.5	372.3	364.1	355.8	350.2	355.8	364.1	372.3	383.5	394.7
47.5°	379.5	369.9	360.2	352.9	345.6	340.3	345.6	352.9	360.2	369.9	379.5
50°	372.1	364.5	356.9	350.0	343.1	338.1	343.1	350.0	356.9	364.5	372.1
52.5°	365.5	360.0	354.4	348.5	342.5	338.1	342.5	348.5	354.4	360.0	365.5
55°	355.2	351.2	347.2	342.7	338.3	334.8	338.3	342.7	347.2	351.2	355.2
57.5°	343.8	339.6	335.3	332.0	328.7	327.0	328.7	332.0	335.3	339.6	343.8
60°	328.4	325.1	321.7	318.7	315.4	312.7	315.4	318.7	321.7	325.1	328.4
62.5°	303.3	301.7	300.3	296.8	293.3	289.5	293.3	296.8	300.3	301.7	303.3
65°	273.8	273.0	272.4	269.8	267.4	263.0	267.4	269.8	272.4	273.0	273.8
67.5°	243.3	241.9	240.3	237.7	235.1	234.2	235.1	237.7	240.3	241.9	243.3
70°	215.5	213.2	211.0	205.1	199.1	192.3	199.1	205.1	211.0	213.2	215.5
72.5°	189.5	186.1	182.5	175.6	168.5	161.3	168.5	175.6	182.5	186.1	189.5
75°	161.9	157.0	152.3	144.9	137.6	132.6	137.6	144.9	152.3	157.0	161.9
77.5°	126.8	122.6	118.4	114.0	109.6	107.2	109.6	114.0	118.4	122.6	126.8
80°	90.8	87.7	84.5	82.3	80.1	78.4	80.1	82.3	84.5	87.7	90.8
82.5°	55.8	54.4	53.0	50.6	48.1	46.4	48.1	50.6	53.0	54.4	55.8
85°	21.5	21.2	21.0	20.1	19.3	18.8	19.3	20.1	21.0	21.2	21.5
87.5°	8.0	7.3	6.6	6.2	5.7	5.5	5.7	6.2	6.6	7.3	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4
2.5°	666.4	668.7	672.2	675.6	680.5	685.3	689.3	693.3	697.8	702.5	708.3
5°	628.0	632.2	637.4	642.5	649.0	655.4	662.7	669.8	678.4	687.0	697.4
7.5°	603.7	608.6	616.1	623.7	631.8	639.7	649.2	658.7	670.0	681.2	694.0
10°	592.4	599.7	608.1	616.5	627.0	637.5	647.6	657.6	669.1	680.6	694.1
12.5°	595.4	604.4	615.6	627.0	639.6	652.1	661.4	670.7	678.6	686.7	697.8
15°	616.4	629.2	645.0	660.7	672.3	683.9	687.1	690.3	691.0	691.7	699.0
17.5°	644.4	663.5	685.6	707.7	715.9	723.9	717.6	711.3	700.4	689.5	690.4
20°	666.8	691.9	720.8	749.7	750.4	751.3	734.3	717.3	696.0	674.5	668.3
22.5°	676.4	707.4	735.7	764.0	757.8	751.5	727.0	702.5	674.5	646.6	637.4
25°	665.8	695.9	719.2	742.5	730.8	719.1	692.7	666.2	640.4	614.5	604.5
27.5°	636.6	660.9	675.2	689.5	676.3	663.2	641.9	620.7	601.5	582.3	572.6
30°	591.3	608.8	618.2	627.6	617.1	606.6	592.2	577.9	563.9	550.0	542.5
32.5°	542.9	554.4	561.7	569.0	563.3	557.4	546.8	536.1	527.0	518.0	514.8
35°	502.9	513.2	519.3	525.4	521.0	516.5	507.8	499.2	493.2	487.3	489.9
37.5°	473.0	481.7	486.2	490.6	484.2	477.9	470.6	463.2	460.5	457.6	464.9
40°	448.0	456.3	457.2	458.0	450.1	442.2	435.2	428.1	428.5	428.7	439.3
42.5°	423.0	429.8	428.1	426.5	418.1	409.7	402.7	395.8	397.2	398.6	412.1
45°	401.0	407.2	403.3	399.4	390.1	381.0	374.8	368.8	371.0	373.2	386.9
47.5°	383.6	387.8	383.6	379.5	369.3	359.1	352.7	346.4	347.8	349.1	361.1
50°	372.9	373.7	366.2	358.5	350.5	342.5	335.7	328.7	327.0	325.4	335.2
52.5°	364.2	363.0	354.9	346.9	338.6	330.4	324.0	317.7	312.6	307.4	314.8
55°	353.6	351.9	344.5	337.0	329.3	321.5	313.9	306.3	299.0	291.7	299.9
57.5°	342.5	341.2	332.5	323.7	316.0	308.3	300.0	291.7	284.4	277.1	288.5
60°	326.6	324.8	316.0	307.2	299.2	291.1	282.7	274.2	269.5	264.6	279.0
62.5°	300.6	298.1	289.6	281.2	274.6	267.9	258.4	248.8	248.4	247.7	266.5
65°	271.3	268.7	261.4	254.1	248.8	243.6	234.5	225.4	227.6	229.8	249.9
67.5°	240.4	237.6	232.6	227.6	223.3	219.0	210.6	202.2	206.7	211.3	229.2
70°	213.9	212.4	208.4	204.4	200.6	196.9	190.0	183.2	186.1	188.9	199.5
72.5°	188.5	187.6	183.9	180.1	176.9	173.7	168.5	163.3	165.3	167.4	169.7
75°	160.2	158.6	154.7	150.8	148.3	145.8	141.9	137.9	139.3	140.9	142.1
77.5°	126.2	125.7	122.5	119.3	117.0	114.7	111.0	107.4	109.2	110.7	113.7
80°	90.8	90.8	88.3	85.6	84.9	84.0	81.3	78.7	80.0	81.2	84.9
82.5°	54.8	53.9	51.3	48.6	49.7	50.8	51.4	51.9	52.8	53.6	53.6
85°	20.9	20.1	20.3	20.4	20.9	21.2	23.0	24.5	25.9	27.1	27.0
87.5°	8.8	9.7	10.1	10.5	10.9	11.3	10.8	10.2	9.7	9.1	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4
2.5°	714.3	719.8	726.1	732.4	738.6	745.1	751.5	758.0	764.4	771.3	778.4
5°	708.0	718.7	731.2	743.1	755.2	767.9	780.6	793.5	806.6	818.9	831.4
7.5°	706.9	719.8	736.4	752.3	768.1	785.8	803.5	823.3	843.0	864.0	885.0
10°	707.7	721.5	739.2	757.4	775.6	797.5	819.3	843.9	868.4	893.6	918.7
12.5°	709.1	722.6	741.9	761.9	782.0	806.5	830.9	858.4	885.9	910.9	935.8
15°	706.2	718.2	739.7	762.4	785.0	811.4	837.7	865.7	893.6	918.8	944.1
17.5°	691.4	701.6	726.8	753.1	779.5	809.4	839.5	869.3	899.2	922.7	946.3
20°	662.0	668.5	701.8	736.5	771.2	806.5	841.7	873.7	905.8	929.7	953.5
22.5°	628.1	634.2	674.0	717.5	761.0	804.1	847.2	882.4	917.6	939.4	961.3
25°	594.4	595.0	640.6	694.9	749.1	803.9	858.7	897.2	935.6	954.5	973.4
27.5°	562.9	560.2	606.8	671.7	736.4	806.0	875.6	918.8	962.1	976.6	991.1
30°	535.0	532.0	577.3	651.4	725.7	810.5	895.5	944.5	993.3	1004.6	1015.9
32.5°	511.6	511.6	553.3	633.8	714.3	815.6	917.1	974.6	1032.2	1039.3	1046.3
35°	492.6	499.4	531.7	613.7	695.5	814.4	933.4	1006.7	1080.0	1088.9	1097.7
37.5°	472.0	485.0	510.5	591.3	672.3	811.0	949.7	1045.8	1141.9	1152.4	1162.9
40°	449.9	466.3	486.4	564.7	643.0	803.3	963.5	1090.5	1217.6	1238.4	1259.0
42.5°	425.6	445.8	459.9	533.0	606.0	789.9	973.6	1140.0	1306.2	1350.1	1393.8
45°	400.9	421.0	433.7	500.7	567.9	780.7	993.5	1207.2	1420.9	1491.0	1561.2
47.5°	372.9	391.7	406.4	468.7	531.2	770.0	1008.8	1276.3	1543.8	1632.6	1721.4
50°	344.9	363.5	383.6	440.2	496.6	751.8	1006.8	1336.5	1666.2	1786.6	1907.0
52.5°	322.1	342.0	367.7	414.6	461.6	714.4	967.3	1365.0	1762.5	1953.9	2145.1
55°	308.0	331.5	357.1	393.1	428.9	664.9	900.7	1357.5	1814.2	2121.9	2429.7
57.5°	300.0	328.7	350.2	375.0	399.7	613.1	826.5	1316.5	1806.5	2263.0	2719.7
60°	293.3	322.1	339.0	356.3	373.7	547.6	721.5	1218.3	1715.0	2326.2	2937.3
62.5°	285.3	312.7	319.9	329.5	339.2	464.5	589.8	1057.3	1524.7	2186.0	2847.3
65°	270.1	292.8	294.8	296.8	298.9	365.1	431.1	829.3	1227.5	1885.5	2543.5
67.5°	246.9	262.4	259.4	253.6	247.7	279.1	310.5	645.4	980.3	1619.3	2258.4
70°	210.1	217.7	218.5	209.8	201.1	212.1	223.2	494.5	765.9	1375.7	1985.5
72.5°	172.1	167.4	176.2	169.6	163.0	163.1	163.3	371.8	580.3	1142.3	1704.3
75°	143.4	140.3	136.8	128.8	121.0	121.6	122.4	275.6	428.7	912.1	1395.5
77.5°	116.6	116.0	105.8	97.2	88.6	88.2	87.5	178.1	268.7	598.4	928.1
80°	88.4	88.9	74.6	65.6	56.6	56.1	55.5	98.4	141.4	343.1	544.7
82.5°	53.6	51.4	43.3	38.9	34.5	34.4	34.3	52.9	71.6	171.9	272.4
85°	26.7	25.4	21.0	18.1	15.2	14.5	13.8	16.8	19.9	40.9	61.9
87.5°	7.7	6.6	6.1	5.5	5.0	4.6	4.4	4.5	4.6	4.9	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4	720.4
2.5°	781.2	783.9	786.9	790.0	791.8	793.5	795.4	797.2	798.8	797.2	795.4
5°	843.9	856.3	864.7	873.1	879.5	885.9	889.5	893.3	893.9	893.3	889.5
7.5°	899.8	914.6	927.4	940.3	948.4	956.6	961.4	966.2	967.9	966.2	961.4
10°	936.1	953.5	965.9	978.4	986.0	993.5	997.3	1001.0	1002.1	1001.0	997.3
12.5°	952.5	969.2	978.8	988.3	993.2	997.9	999.7	1001.3	999.9	1001.3	999.7
15°	954.0	963.7	967.8	971.8	969.4	967.0	963.6	960.1	957.9	960.1	963.6
17.5°	949.8	953.3	945.9	938.6	925.3	912.1	902.1	892.2	885.0	892.2	902.1
20°	948.0	942.5	922.8	903.2	878.4	853.5	836.8	820.0	809.9	820.0	836.8
22.5°	945.7	930.1	897.1	864.0	830.0	796.1	776.8	757.7	746.9	757.7	776.8
25°	946.7	919.8	875.2	830.7	790.7	750.8	729.9	709.1	697.2	709.1	729.9
27.5°	950.2	909.3	854.1	798.8	755.5	712.1	692.2	672.3	661.8	672.3	692.2
30°	961.7	907.3	841.3	775.1	729.8	684.5	665.0	645.5	634.2	645.5	665.0
32.5°	977.8	909.3	835.3	761.3	715.1	669.0	650.3	631.8	622.1	631.8	650.3
35°	1011.0	924.2	842.1	760.2	717.3	674.5	660.8	647.2	641.9	647.2	660.8
37.5°	1061.6	960.1	875.6	791.1	761.9	732.8	732.8	732.8	737.0	732.8	732.8
40°	1145.2	1031.4	951.4	871.5	869.8	868.2	886.8	905.5	913.7	905.5	886.8
42.5°	1273.5	1153.3	1088.8	1024.2	1062.9	1101.6	1155.3	1209.0	1244.1	1209.0	1155.3
45°	1444.1	1327.0	1281.9	1236.9	1323.0	1409.0	1503.9	1598.8	1666.2	1598.8	1503.9
47.5°	1622.9	1524.2	1498.5	1472.8	1615.9	1759.0	1898.1	2037.2	2119.2	2037.2	1898.1
50°	1818.4	1729.7	1724.7	1719.8	1910.4	2100.9	2280.5	2460.0	2560.0	2460.0	2280.5
52.5°	2047.8	1950.4	1954.3	1958.1	2184.5	2410.9	2628.0	2845.1	2957.8	2845.1	2628.0
55°	2307.6	2185.5	2184.8	2184.1	2444.2	2704.5	2971.3	3238.2	3388.7	3238.2	2971.3
57.5°	2605.3	2491.0	2463.8	2436.5	2708.5	2980.4	3275.0	3569.7	3727.9	3569.7	3275.0
60°	2874.4	2811.4	2767.9	2724.4	3003.8	3283.2	3587.5	3891.6	4049.4	3891.6	3587.5
62.5°	2959.9	3072.5	3069.3	3066.1	3367.6	3669.1	3985.6	4302.2	4443.9	4302.2	3985.6
65°	2723.0	2902.5	3026.1	3149.5	3514.0	3878.4	4208.1	4537.8	4682.5	4537.8	4208.1
67.5°	2416.6	2574.9	2676.0	2777.1	3187.8	3598.6	3972.7	4346.9	4495.8	4346.9	3972.7
70°	2160.7	2336.0	2408.2	2480.5	2829.4	3178.2	3474.2	3770.1	3828.4	3770.1	3474.2
72.5°	1912.7	2121.2	2151.8	2182.4	2436.3	2690.2	2847.9	3005.5	2878.2	3005.5	2847.9
75°	1630.6	1865.6	1886.0	1906.5	1985.6	2064.8	2104.9	2145.1	2072.8	2145.1	2104.9
77.5°	1131.6	1335.3	1381.1	1427.0	1479.7	1532.5	1529.7	1527.0	1425.3	1527.0	1529.7
80°	703.9	863.1	869.1	875.1	914.6	954.1	994.4	1034.7	970.1	1034.7	994.4
82.5°	359.8	447.3	460.7	474.2	498.4	522.6	533.9	545.3	490.6	545.3	533.9
85°	84.6	107.4	129.4	151.4	176.8	202.2	199.3	196.4	165.7	196.4	199.3
87.5°	5.1	5.3	5.4	5.5	5.6	5.7	6.1	6.4	6.6	6.4	6.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1384904

CATALOG NUMBER: VAL-T-SB1B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	720.4	720.4	720.4	720.4	720.4	720.4	720.4
2.5°	793.5	791.8	790.0	786.9	783.9	781.2	778.4
5°	885.9	879.5	873.1	864.7	856.3	843.9	831.4
7.5°	956.6	948.4	940.3	927.4	914.6	899.8	885.0
10°	993.5	986.0	978.4	965.9	953.5	936.1	918.7
12.5°	997.9	993.2	988.3	978.8	969.2	952.5	935.8
15°	967.0	969.4	971.8	967.8	963.7	954.0	944.1
17.5°	912.1	925.3	938.6	945.9	953.3	949.8	946.3
20°	853.5	878.4	903.2	922.8	942.5	948.0	953.5
22.5°	796.1	830.0	864.0	897.1	930.1	945.7	961.3
25°	750.8	790.7	830.7	875.2	919.8	946.7	973.4
27.5°	712.1	755.5	798.8	854.1	909.3	950.2	991.1
30°	684.5	729.8	775.1	841.3	907.3	961.7	1015.9
32.5°	669.0	715.1	761.3	835.3	909.3	977.8	1046.3
35°	674.5	717.3	760.2	842.1	924.2	1011.0	1097.7
37.5°	732.8	761.9	791.1	875.6	960.1	1061.6	1162.9
40°	868.2	869.8	871.5	951.4	1031.4	1145.2	1259.0
42.5°	1101.6	1062.9	1024.2	1088.8	1153.3	1273.5	1393.8
45°	1409.0	1323.0	1236.9	1281.9	1327.0	1444.1	1561.2
47.5°	1759.0	1615.9	1472.8	1498.5	1524.2	1622.9	1721.4
50°	2100.9	1910.4	1719.8	1724.7	1729.7	1818.4	1907.0
52.5°	2410.9	2184.5	1958.1	1954.3	1950.4	2047.8	2145.1
55°	2704.5	2444.2	2184.1	2184.8	2185.5	2307.6	2429.7
57.5°	2980.4	2708.5	2436.5	2463.8	2491.0	2605.3	2719.7
60°	3283.2	3003.8	2724.4	2767.9	2811.4	2874.4	2937.3
62.5°	3669.1	3367.6	3066.1	3069.3	3072.5	2959.9	2847.3
65°	3878.4	3514.0	3149.5	3026.1	2902.5	2723.0	2543.5
67.5°	3598.6	3187.8	2777.1	2676.0	2574.9	2416.6	2258.4
70°	3178.2	2829.4	2480.5	2408.2	2336.0	2160.7	1985.5
72.5°	2690.2	2436.3	2182.4	2151.8	2121.2	1912.7	1704.3
75°	2064.8	1985.6	1906.5	1886.0	1865.6	1630.6	1395.5
77.5°	1532.5	1479.7	1427.0	1381.1	1335.3	1131.6	928.1
80°	954.1	914.6	875.1	869.1	863.1	703.9	544.7
82.5°	522.6	498.4	474.2	460.7	447.3	359.8	272.4
85°	202.2	176.8	151.4	129.4	107.4	84.6	61.9
87.5°	5.7	5.6	5.5	5.4	5.3	5.1	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ


Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-727-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672	CRI (Ra):	71.1		
CIE u':	0.2638	R1:	68.3	R9:	-27.8
CIE v':	0.5276	R2:	79.8	R10:	54.4
Duv:	-0.0002	R3:	91.2	R11:	65.8
CIE x:	0.4619	R4:	69.4	R12:	45.6
CIE y:	0.4106	R5:	66.5	R13:	69.8
CIE z:	0.1275	R6:	72.6	R14:	94.5
Peak Wavelength (nm):	601	R7:	77.0	R15:	60.1
Dominant Wavelength (nm):	584	R8:	44.1		
Purity:	61.88407				
Rf:	67.9				
Rg:	98.6				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.02

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.71

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18





Summary

$R_f = 67.9$
 $R_g = 98.6$
 $CIE R_a = 71.1$
 $R_g = -27.8$

Spectral Power Distribution Comparison




Color Vector Graphics







Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)