

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1386041

Luminaire Tested: **VAL-T-SB3C-722-U-SLL-HSS**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



**Test Information**

Test Method: LM-79-08  
 Report Number: P1386041  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 02/18/2026  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: VAL-T-SB3C-722-U-SLL-HSS  
 Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 3SQUARE 150W 70CRI  
 2200K FIXTURE w/ 90° Spill Light Eliminator LETT OPTIC OPTIC AND HOUSE  
 SIDE SHIELD  
 Light Source: (78) 2200K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER

Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a                 | good             | reflector          |
| b                 | good             | lens               |
| c                 | good             | housing            |
| d                 | good             | cord               |

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 13005.1 lumens  
 Efficiency: N/A  
 Efficacy: 86.7 lumens/watt  
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
 IES Classification: Type III - Short  
 BUG Rating: B2 - U0 - G2

Input Watts (W): 150  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: 0.98  
 Total Harmonic Distortion (THDi): 6.3%  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 28.75 FT

REPORT NUMBER: P1386041  
 CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.2 fc  
 Type III - Short - N/A

REPORT NUMBER: P1386041  
CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P1386041  
 CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2925.5   | 0.0    | 2925.5  |
|                    | % Fixture | 22.5     | 0.0    | 22.5    |
| <b>Street Side</b> | Lumens    | 10079.6  | 0.0    | 10079.6 |
|                    | % Fixture | 77.5     | 0.0    | 77.5    |
| <b>Total</b>       | Lumens    | 13005.1  | 0.0    | 13005.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 215.9   | 1.7       |
| 10°-20°   | 597.2   | 4.6       |
| 20°-30°   | 855.4   | 6.6       |
| 30°-40°   | 1073.0  | 8.3       |
| 40°-50°   | 1762.5  | 13.6      |
| 50°-60°   | 3182.3  | 24.5      |
| 60°-70°   | 3532.9  | 27.2      |
| 70°-80°   | 1596.9  | 12.3      |
| 80°-90°   | 189.0   | 1.5       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 13005.1 | 100.0     |
| 0°-180°   | 13005.1 | 100.0     |




REPORT NUMBER: P1386041  
 CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 939.5  | 7.2       |                         |      |         |
| FM (30°-60°)   | 4380.9 | 33.7      |                         |      |         |
| FH (60°-80°)   | 4596.9 | 35.3      |                         |      | G2/5000 |
| FVH (80°-90°)  | 162.3  | 1.2       |                         |      | G2/225  |
| BL (0°-30°)    | 729.0  | 5.6       | B2/1000                 |      |         |
| BM (30°-60°)   | 1636.8 | 12.6      | B2/2500                 |      |         |
| BH (60°-80°)   | 532.9  | 4.1       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 26.7   | 0.2       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**  
 Type III Short





REPORT NUMBER: P1386041

CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 1°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 2246.8  | 2246.8  | 2246.8  | 2246.8  | 2246.8  | 2246.8  | 2246.8  | 2246.8  | 2246.8  | 2246.8  | 2246.8  |
| 2.5°  | 2474.3  | 2506.2  | 2502.2  | 2546.1  | 2586.0  | 2613.9  | 2637.9  | 2629.9  | 2609.9  | 2570.0  | 2542.1  |
| 5°    | 2733.7  | 2757.6  | 2797.5  | 2881.3  | 2945.2  | 3001.0  | 2993.1  | 3001.0  | 2941.2  | 2881.3  | 2809.5  |
| 7.5°  | 2957.1  | 2985.1  | 3040.9  | 3160.7  | 3240.5  | 3308.3  | 3300.3  | 3276.4  | 3208.6  | 3108.8  | 3001.0  |
| 10°   | 3096.8  | 3116.8  | 3176.6  | 3312.3  | 3404.1  | 3460.0  | 3440.0  | 3400.1  | 3312.3  | 3212.5  | 3084.8  |
| 12.5° | 3156.7  | 3180.6  | 3232.5  | 3340.3  | 3400.1  | 3388.1  | 3380.2  | 3372.2  | 3328.3  | 3252.5  | 3136.7  |
| 15°   | 3164.7  | 3180.6  | 3220.5  | 3268.4  | 3244.5  | 3176.6  | 3160.7  | 3220.5  | 3276.4  | 3260.4  | 3164.7  |
| 17.5° | 3164.7  | 3188.6  | 3196.6  | 3148.7  | 3025.0  | 2901.3  | 2885.3  | 2985.1  | 3140.7  | 3264.4  | 3208.6  |
| 20°   | 3176.6  | 3188.6  | 3172.6  | 3017.0  | 2785.5  | 2649.9  | 2621.9  | 2745.6  | 2977.1  | 3220.5  | 3252.5  |
| 22.5° | 3192.6  | 3204.6  | 3136.7  | 2861.4  | 2590.0  | 2446.3  | 2430.4  | 2522.1  | 2793.5  | 3156.7  | 3300.3  |
| 25°   | 3224.5  | 3216.5  | 3112.8  | 2725.7  | 2418.4  | 2282.7  | 2258.8  | 2378.5  | 2641.9  | 3092.8  | 3380.2  |
| 27.5° | 3264.4  | 3228.5  | 3080.9  | 2613.9  | 2294.7  | 2151.0  | 2135.0  | 2250.8  | 2514.2  | 3013.0  | 3448.0  |
| 30°   | 3316.3  | 3280.4  | 3076.9  | 2526.1  | 2202.9  | 2059.2  | 2039.3  | 2167.0  | 2426.4  | 2957.1  | 3543.8  |
| 32.5° | 3388.1  | 3336.3  | 3080.9  | 2458.3  | 2151.0  | 2015.3  | 2003.4  | 2139.0  | 2390.5  | 2925.2  | 3643.5  |
| 35°   | 3483.9  | 3408.1  | 3096.8  | 2434.4  | 2167.0  | 2075.2  | 2103.1  | 2206.9  | 2426.4  | 2949.2  | 3807.2  |
| 37.5° | 3603.6  | 3531.8  | 3176.6  | 2486.2  | 2342.6  | 2406.4  | 2478.3  | 2518.2  | 2598.0  | 3060.9  | 4070.6  |
| 40°   | 3803.2  | 3703.4  | 3296.4  | 2653.8  | 2813.5  | 3112.8  | 3252.5  | 3236.5  | 3052.9  | 3316.3  | 4441.7  |
| 42.5° | 4082.5  | 3990.7  | 3539.8  | 3080.9  | 3599.6  | 4234.2  | 4469.6  | 4333.9  | 3779.2  | 3723.4  | 5052.3  |
| 45°   | 4509.5  | 4357.9  | 3867.0  | 3715.4  | 4549.4  | 5591.0  | 6121.8  | 5654.9  | 4701.1  | 4365.9  | 5922.3  |
| 47.5° | 5056.3  | 4904.6  | 4377.8  | 4349.9  | 5611.0  | 7267.1  | 7897.7  | 6979.8  | 5615.0  | 5207.9  | 6963.8  |
| 50°   | 5934.2  | 5766.6  | 5128.1  | 4996.4  | 6784.3  | 8939.3  | 9781.3  | 8300.7  | 6544.8  | 6101.8  | 8248.9  |
| 52.5° | 7139.4  | 7027.7  | 6317.3  | 5662.9  | 7833.8  | 10783.0 | 11509.3 | 9681.5  | 7263.2  | 7123.5  | 9649.6  |
| 55°   | 8819.5  | 8711.8  | 7865.8  | 6405.1  | 8827.5  | 12630.7 | 13217.3 | 10938.6 | 7889.7  | 8320.7  | 11114.2 |
| 57.5° | 10723.1 | 10902.7 | 9984.8  | 7394.8  | 9873.1  | 14119.2 | 14937.3 | 12080.0 | 8735.7  | 9921.0  | 12742.4 |
| 60°   | 11964.2 | 12530.9 | 12415.2 | 9122.8  | 11497.3 | 15971.0 | 16860.9 | 13608.4 | 9972.9  | 11098.3 | 12706.5 |
| 62.5° | 10886.7 | 11453.4 | 12339.4 | 11126.2 | 13061.7 | 17647.1 | 18397.3 | 15216.7 | 11202.0 | 10160.4 | 10671.2 |
| 65°   | 9238.6  | 9944.9  | 10878.8 | 9665.6  | 12786.3 | 17698.9 | 18469.2 | 15276.6 | 10451.8 | 7510.6  | 7566.4  |
| 67.5° | 7961.5  | 8588.1  | 9737.4  | 8224.9  | 11333.7 | 16118.6 | 16725.2 | 13628.4 | 8640.0  | 4980.4  | 4936.5  |
| 70°   | 6644.6  | 7219.3  | 8671.9  | 7323.0  | 9929.0  | 13891.8 | 13369.0 | 11457.4 | 7303.1  | 3308.3  | 2741.6  |
| 72.5° | 5662.9  | 6193.6  | 7706.1  | 6580.7  | 7877.7  | 11257.9 | 9214.6  | 9505.9  | 5942.2  | 2103.1  | 1867.7  |
| 75°   | 4685.1  | 5172.0  | 6552.8  | 5958.2  | 6516.9  | 7023.7  | 6369.2  | 6752.3  | 4896.6  | 1783.9  | 1440.7  |
| 77.5° | 3288.4  | 3591.7  | 4597.3  | 4741.0  | 5072.2  | 4158.4  | 4038.6  | 4729.0  | 3483.9  | 885.9   | 606.6   |
| 80°   | 1620.2  | 1807.8  | 2398.4  | 2821.5  | 2398.4  | 2358.5  | 2689.8  | 3148.7  | 1807.8  | 542.7   | 335.2   |
| 82.5° | 726.3   | 862.0   | 1105.4  | 1708.0  | 866.0   | 941.8   | 1189.2  | 1676.1  | 822.1   | 323.3   | 143.7   |
| 85°   | 115.7   | 127.7   | 215.5   | 287.3   | 235.5   | 363.2   | 347.2   | 327.2   | 175.6   | 87.8    | 39.9    |
| 87.5° | 4.0     | 4.0     | 4.0     | 8.0     | 12.0    | 16.0    | 20.0    | 20.0    | 20.0    | 20.0    | 20.0    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1386041

CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2246.8  | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 |
| 2.5°  | 2534.1  | 2522.1 | 2462.3 | 2402.4 | 2350.5 | 2298.7 | 2246.8 | 2175.0 | 2119.1 | 2071.2 | 2051.2 |
| 5°    | 2773.6  | 2709.7 | 2617.9 | 2518.2 | 2430.4 | 2330.6 | 2234.8 | 2127.1 | 2039.3 | 1947.5 | 1899.6 |
| 7.5°  | 2937.2  | 2873.3 | 2721.7 | 2570.0 | 2462.3 | 2354.5 | 2254.8 | 2135.0 | 2019.3 | 1887.6 | 1815.8 |
| 10°   | 3013.0  | 2941.2 | 2777.6 | 2602.0 | 2470.3 | 2362.5 | 2270.7 | 2171.0 | 2055.2 | 1891.6 | 1795.8 |
| 12.5° | 3064.9  | 2977.1 | 2789.5 | 2609.9 | 2478.3 | 2366.5 | 2278.7 | 2206.9 | 2139.0 | 1979.4 | 1867.7 |
| 15°   | 3096.8  | 3017.0 | 2821.5 | 2613.9 | 2466.3 | 2334.6 | 2250.8 | 2226.8 | 2238.8 | 2163.0 | 2027.3 |
| 17.5° | 3144.7  | 3068.9 | 2861.4 | 2637.9 | 2446.3 | 2266.7 | 2175.0 | 2226.8 | 2334.6 | 2358.5 | 2250.8 |
| 20°   | 3208.6  | 3128.7 | 2913.2 | 2657.8 | 2386.5 | 2139.0 | 2051.2 | 2182.9 | 2362.5 | 2486.2 | 2426.4 |
| 22.5° | 3280.4  | 3216.5 | 2973.1 | 2677.8 | 2298.7 | 1971.4 | 1931.5 | 2091.1 | 2282.7 | 2442.3 | 2446.3 |
| 25°   | 3368.2  | 3308.3 | 3056.9 | 2697.7 | 2178.9 | 1827.8 | 1835.7 | 1971.4 | 2123.1 | 2286.7 | 2314.6 |
| 27.5° | 3487.9  | 3432.0 | 3160.7 | 2721.7 | 2055.2 | 1712.0 | 1751.9 | 1851.7 | 1955.5 | 2055.2 | 2095.1 |
| 30°   | 3619.6  | 3575.7 | 3284.4 | 2769.6 | 1939.5 | 1644.2 | 1668.1 | 1736.0 | 1819.8 | 1879.6 | 1899.6 |
| 32.5° | 3799.2  | 3727.4 | 3400.1 | 2765.6 | 1851.7 | 1612.3 | 1588.3 | 1608.3 | 1676.1 | 1736.0 | 1740.0 |
| 35°   | 4022.7  | 3966.8 | 3519.8 | 2693.8 | 1771.9 | 1596.3 | 1512.5 | 1500.5 | 1540.4 | 1600.3 | 1596.3 |
| 37.5° | 4349.9  | 4302.0 | 3715.4 | 2582.0 | 1672.1 | 1556.4 | 1432.7 | 1392.8 | 1420.7 | 1460.6 | 1472.6 |
| 40°   | 4840.8  | 4717.1 | 3938.9 | 2458.3 | 1572.4 | 1484.6 | 1336.9 | 1281.0 | 1301.0 | 1344.9 | 1352.9 |
| 42.5° | 5507.2  | 5271.8 | 4238.2 | 2290.7 | 1476.6 | 1376.8 | 1241.1 | 1181.3 | 1193.2 | 1233.1 | 1241.1 |
| 45°   | 6361.2  | 6006.1 | 4649.2 | 2115.1 | 1400.8 | 1265.1 | 1141.4 | 1077.5 | 1089.5 | 1133.4 | 1153.3 |
| 47.5° | 7358.9  | 6872.1 | 5080.2 | 1927.5 | 1356.9 | 1177.3 | 1041.6 | 993.7  | 1021.6 | 1065.5 | 1073.5 |
| 50°   | 8536.2  | 8045.3 | 5355.6 | 1775.9 | 1328.9 | 1109.4 | 949.8  | 929.8  | 965.8  | 1001.7 | 1009.7 |
| 52.5° | 9821.2  | 9122.8 | 5180.0 | 1652.2 | 1305.0 | 1085.5 | 885.9  | 893.9  | 921.9  | 957.8  | 969.8  |
| 55°   | 11070.3 | 9517.9 | 4597.3 | 1492.5 | 1277.0 | 1101.4 | 838.1  | 858.0  | 893.9  | 921.9  | 929.8  |
| 57.5° | 11884.4 | 9186.7 | 3703.4 | 1324.9 | 1245.1 | 1113.4 | 814.1  | 830.1  | 870.0  | 901.9  | 905.9  |
| 60°   | 11174.1 | 8460.4 | 2773.6 | 1181.3 | 1177.3 | 1093.5 | 806.1  | 782.2  | 838.1  | 866.0  | 870.0  |
| 62.5° | 9154.8  | 6919.9 | 1771.9 | 1045.6 | 1049.6 | 1049.6 | 802.1  | 702.4  | 774.2  | 798.1  | 794.2  |
| 65°   | 6289.4  | 4892.7 | 1097.5 | 854.0  | 893.9  | 953.8  | 778.2  | 618.6  | 702.4  | 726.3  | 718.3  |
| 67.5° | 4134.4  | 3108.8 | 678.4  | 658.5  | 734.3  | 826.1  | 730.3  | 554.7  | 630.5  | 646.5  | 622.6  |
| 70°   | 2242.8  | 1464.6 | 447.0  | 431.0  | 574.7  | 650.5  | 618.6  | 498.8  | 562.7  | 578.7  | 554.7  |
| 72.5° | 1480.6  | 842.0  | 315.3  | 315.3  | 451.0  | 454.9  | 506.8  | 447.0  | 498.8  | 514.8  | 490.9  |
| 75°   | 1113.4  | 542.7  | 219.5  | 243.4  | 287.3  | 355.2  | 363.2  | 375.1  | 423.0  | 443.0  | 419.0  |
| 77.5° | 510.8   | 199.5  | 131.7  | 179.6  | 199.5  | 271.4  | 231.5  | 279.4  | 315.3  | 323.3  | 303.3  |
| 80°   | 295.3   | 111.7  | 87.8   | 115.7  | 127.7  | 223.5  | 135.7  | 167.6  | 223.5  | 235.5  | 211.5  |
| 82.5° | 123.7   | 55.9   | 59.9   | 71.8   | 75.8   | 123.7  | 95.8   | 107.8  | 147.7  | 143.7  | 127.7  |
| 85°   | 35.9    | 35.9   | 39.9   | 43.9   | 43.9   | 71.8   | 67.8   | 63.9   | 67.8   | 67.8   | 55.9   |
| 87.5° | 23.9    | 23.9   | 23.9   | 27.9   | 27.9   | 31.9   | 35.9   | 39.9   | 39.9   | 39.9   | 35.9   |
| 90°   | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1386041  
 CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 |
| 2.5°  | 2023.3 | 1987.4 | 1935.5 | 1927.5 | 1899.6 | 1879.6 | 1899.6 | 1919.5 | 1955.5 | 1959.5 | 1975.4 |
| 5°    | 1855.7 | 1771.9 | 1708.0 | 1636.2 | 1600.3 | 1596.3 | 1588.3 | 1612.3 | 1664.1 | 1696.1 | 1720.0 |
| 7.5°  | 1744.0 | 1592.3 | 1480.6 | 1380.8 | 1344.9 | 1316.9 | 1340.9 | 1336.9 | 1404.7 | 1432.7 | 1456.6 |
| 10°   | 1684.1 | 1472.6 | 1305.0 | 1181.3 | 1133.4 | 1105.4 | 1101.4 | 1109.4 | 1149.3 | 1177.3 | 1205.2 |
| 12.5° | 1724.0 | 1424.7 | 1177.3 | 1033.6 | 981.7  | 949.8  | 921.9  | 921.9  | 929.8  | 965.8  | 977.7  |
| 15°   | 1855.7 | 1452.6 | 1117.4 | 961.8  | 893.9  | 842.0  | 806.1  | 778.2  | 782.2  | 786.2  | 798.1  |
| 17.5° | 2047.3 | 1524.5 | 1097.5 | 917.9  | 846.0  | 782.2  | 746.3  | 714.3  | 706.4  | 706.4  | 702.4  |
| 20°   | 2230.8 | 1580.3 | 1081.5 | 882.0  | 790.2  | 734.3  | 702.4  | 674.4  | 662.5  | 662.5  | 662.5  |
| 22.5° | 2306.6 | 1628.2 | 1061.5 | 838.1  | 734.3  | 682.4  | 654.5  | 634.5  | 630.5  | 630.5  | 626.5  |
| 25°   | 2246.8 | 1612.3 | 1037.6 | 794.2  | 682.4  | 642.5  | 618.6  | 598.6  | 594.6  | 598.6  | 594.6  |
| 27.5° | 2059.2 | 1556.4 | 1005.7 | 758.2  | 642.5  | 606.6  | 586.6  | 566.7  | 562.7  | 566.7  | 566.7  |
| 30°   | 1859.7 | 1460.6 | 953.8  | 730.3  | 610.6  | 570.7  | 550.7  | 530.8  | 530.8  | 534.8  | 538.8  |
| 32.5° | 1700.1 | 1364.8 | 893.9  | 694.4  | 574.7  | 538.8  | 518.8  | 498.8  | 498.8  | 506.8  | 506.8  |
| 35°   | 1564.4 | 1289.0 | 834.1  | 658.5  | 542.7  | 502.8  | 486.9  | 470.9  | 466.9  | 474.9  | 478.9  |
| 37.5° | 1456.6 | 1221.2 | 770.2  | 622.6  | 510.8  | 474.9  | 458.9  | 439.0  | 435.0  | 443.0  | 451.0  |
| 40°   | 1344.9 | 1145.3 | 714.3  | 578.7  | 478.9  | 443.0  | 427.0  | 403.1  | 403.1  | 411.0  | 419.0  |
| 42.5° | 1237.1 | 1077.5 | 678.4  | 538.8  | 447.0  | 407.1  | 391.1  | 371.1  | 371.1  | 379.1  | 387.1  |
| 45°   | 1149.3 | 1013.6 | 658.5  | 498.8  | 411.0  | 375.1  | 355.2  | 339.2  | 343.2  | 351.2  | 359.2  |
| 47.5° | 1065.5 | 945.8  | 662.5  | 478.9  | 387.1  | 339.2  | 319.3  | 307.3  | 315.3  | 327.2  | 335.2  |
| 50°   | 1001.7 | 897.9  | 666.5  | 447.0  | 355.2  | 311.3  | 291.3  | 283.3  | 295.3  | 307.3  | 315.3  |
| 52.5° | 961.8  | 850.0  | 642.5  | 407.1  | 331.2  | 283.3  | 271.4  | 271.4  | 283.3  | 291.3  | 299.3  |
| 55°   | 921.9  | 770.2  | 590.6  | 363.2  | 307.3  | 263.4  | 255.4  | 255.4  | 267.4  | 275.4  | 279.4  |
| 57.5° | 889.9  | 686.4  | 530.8  | 327.2  | 279.4  | 243.4  | 243.4  | 243.4  | 247.4  | 251.4  | 259.4  |
| 60°   | 830.1  | 598.6  | 454.9  | 299.3  | 251.4  | 227.5  | 223.5  | 223.5  | 219.5  | 223.5  | 235.5  |
| 62.5° | 726.3  | 502.8  | 387.1  | 267.4  | 227.5  | 207.5  | 203.5  | 191.6  | 179.6  | 183.6  | 191.6  |
| 65°   | 614.6  | 399.1  | 323.3  | 231.5  | 195.5  | 183.6  | 179.6  | 159.6  | 143.7  | 147.7  | 159.6  |
| 67.5° | 490.9  | 299.3  | 271.4  | 199.5  | 167.6  | 155.6  | 155.6  | 143.7  | 131.7  | 131.7  | 139.7  |
| 70°   | 383.1  | 251.4  | 203.5  | 159.6  | 131.7  | 131.7  | 139.7  | 127.7  | 111.7  | 111.7  | 123.7  |
| 72.5° | 311.3  | 203.5  | 163.6  | 123.7  | 103.8  | 111.7  | 115.7  | 103.8  | 91.8   | 91.8   | 99.8   |
| 75°   | 243.4  | 159.6  | 127.7  | 91.8   | 79.8   | 83.8   | 91.8   | 83.8   | 71.8   | 75.8   | 79.8   |
| 77.5° | 167.6  | 107.8  | 83.8   | 67.8   | 59.9   | 63.9   | 63.9   | 59.9   | 55.9   | 55.9   | 59.9   |
| 80°   | 111.7  | 71.8   | 55.9   | 47.9   | 43.9   | 43.9   | 39.9   | 39.9   | 43.9   | 43.9   | 47.9   |
| 82.5° | 79.8   | 51.9   | 43.9   | 35.9   | 27.9   | 27.9   | 31.9   | 31.9   | 35.9   | 35.9   | 39.9   |
| 85°   | 47.9   | 35.9   | 31.9   | 23.9   | 20.0   | 23.9   | 23.9   | 27.9   | 31.9   | 31.9   | 35.9   |
| 87.5° | 35.9   | 27.9   | 23.9   | 20.0   | 16.0   | 16.0   | 20.0   | 20.0   | 23.9   | 27.9   | 27.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1386041  
 CATALOG NUMBER: VAL-T-SB3C-722-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 359°    | 360°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|
| 0°    | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8 | 2246.8  | 2246.8  |
| 2.5°  | 2015.3 | 2063.2 | 2131.1 | 2190.9 | 2262.8 | 2334.6 | 2402.4 | 2466.3 | 2470.3  | 2474.3  |
| 5°    | 1795.8 | 1891.6 | 2003.4 | 2139.0 | 2282.7 | 2422.4 | 2570.0 | 2689.8 | 2717.7  | 2733.7  |
| 7.5°  | 1552.4 | 1692.1 | 1863.7 | 2055.2 | 2270.7 | 2486.2 | 2693.8 | 2873.3 | 2941.2  | 2957.1  |
| 10°   | 1297.0 | 1468.6 | 1676.1 | 1923.5 | 2214.9 | 2502.2 | 2781.5 | 3001.0 | 3080.9  | 3096.8  |
| 12.5° | 1069.5 | 1209.2 | 1448.6 | 1747.9 | 2099.1 | 2478.3 | 2813.5 | 3056.9 | 3136.7  | 3156.7  |
| 15°   | 874.0  | 1005.7 | 1229.1 | 1544.4 | 1939.5 | 2394.4 | 2789.5 | 3068.9 | 3148.7  | 3164.7  |
| 17.5° | 722.3  | 806.1  | 1009.7 | 1352.9 | 1795.8 | 2286.7 | 2757.6 | 3076.9 | 3152.7  | 3164.7  |
| 20°   | 662.5  | 678.4  | 786.2  | 1121.4 | 1644.2 | 2206.9 | 2737.6 | 3088.8 | 3164.7  | 3176.6  |
| 22.5° | 634.5  | 634.5  | 658.5  | 854.0  | 1432.7 | 2123.1 | 2729.7 | 3124.8 | 3180.6  | 3192.6  |
| 25°   | 606.6  | 606.6  | 614.6  | 670.4  | 1181.3 | 2019.3 | 2745.6 | 3188.6 | 3224.5  | 3224.5  |
| 27.5° | 578.7  | 578.7  | 586.6  | 598.6  | 878.0  | 1847.7 | 2749.6 | 3260.4 | 3276.4  | 3264.4  |
| 30°   | 550.7  | 558.7  | 558.7  | 566.7  | 646.5  | 1632.2 | 2725.7 | 3340.3 | 3340.3  | 3316.3  |
| 32.5° | 522.8  | 526.8  | 534.8  | 538.8  | 562.7  | 1352.9 | 2685.8 | 3440.0 | 3420.1  | 3388.1  |
| 35°   | 498.8  | 502.8  | 502.8  | 510.8  | 534.8  | 1081.5 | 2641.9 | 3575.7 | 3519.8  | 3483.9  |
| 37.5° | 466.9  | 470.9  | 474.9  | 482.9  | 506.8  | 858.0  | 2578.0 | 3691.4 | 3651.5  | 3603.6  |
| 40°   | 439.0  | 443.0  | 447.0  | 454.9  | 478.9  | 738.3  | 2498.2 | 3867.0 | 3859.0  | 3803.2  |
| 42.5° | 407.1  | 415.0  | 419.0  | 423.0  | 454.9  | 674.4  | 2442.3 | 4150.4 | 4150.4  | 4082.5  |
| 45°   | 379.1  | 387.1  | 387.1  | 395.1  | 439.0  | 618.6  | 2566.0 | 4541.5 | 4573.4  | 4509.5  |
| 47.5° | 355.2  | 359.2  | 359.2  | 363.2  | 415.0  | 570.7  | 2897.3 | 5140.1 | 5100.2  | 5056.3  |
| 50°   | 331.2  | 339.2  | 331.2  | 335.2  | 395.1  | 598.6  | 3444.0 | 5906.3 | 6010.1  | 5934.2  |
| 52.5° | 315.3  | 319.3  | 303.3  | 303.3  | 367.1  | 634.5  | 3891.0 | 6884.0 | 7231.2  | 7139.4  |
| 55°   | 295.3  | 299.3  | 279.4  | 279.4  | 323.3  | 550.7  | 3918.9 | 7997.4 | 8759.7  | 8819.5  |
| 57.5° | 275.4  | 275.4  | 259.4  | 255.4  | 279.4  | 447.0  | 3475.9 | 8859.4 | 10587.4 | 10723.1 |
| 60°   | 251.4  | 247.4  | 239.4  | 231.5  | 255.4  | 411.0  | 2649.9 | 8743.7 | 11493.3 | 11964.2 |
| 62.5° | 215.5  | 223.5  | 219.5  | 203.5  | 231.5  | 383.1  | 1728.0 | 7566.4 | 10471.7 | 10886.7 |
| 65°   | 179.6  | 191.6  | 191.6  | 179.6  | 255.4  | 335.2  | 909.9  | 6057.9 | 8739.7  | 9238.6  |
| 67.5° | 159.6  | 167.6  | 163.6  | 155.6  | 227.5  | 211.5  | 439.0  | 4645.2 | 7482.6  | 7961.5  |
| 70°   | 139.7  | 147.7  | 135.7  | 127.7  | 183.6  | 151.6  | 259.4  | 3108.8 | 6177.7  | 6644.6  |
| 72.5° | 115.7  | 123.7  | 111.7  | 99.8   | 135.7  | 115.7  | 171.6  | 2023.3 | 5144.1  | 5662.9  |
| 75°   | 95.8   | 99.8   | 91.8   | 79.8   | 99.8   | 91.8   | 119.7  | 1320.9 | 4302.0  | 4685.1  |
| 77.5° | 67.8   | 75.8   | 71.8   | 59.9   | 71.8   | 63.9   | 83.8   | 754.3  | 3001.0  | 3288.4  |
| 80°   | 51.9   | 51.9   | 51.9   | 47.9   | 43.9   | 43.9   | 55.9   | 339.2  | 1456.6  | 1620.2  |
| 82.5° | 43.9   | 43.9   | 39.9   | 35.9   | 31.9   | 27.9   | 31.9   | 99.8   | 686.4   | 726.3   |
| 85°   | 39.9   | 31.9   | 27.9   | 23.9   | 20.0   | 12.0   | 12.0   | 27.9   | 139.7   | 115.7   |
| 87.5° | 23.9   | 20.0   | 16.0   | 8.0    | 4.0    | 4.0    | 0.0    | 4.0    | 4.0     | 4.0     |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-722-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 2200K CCT 26 LEDS

**Spectral Parameters**

CCT (K): 2160  
 CIE u': 0.2927  
 CIE v': 0.5388  
 Duv: 0.0015  
 CIE x: 0.5130  
 CIE y: 0.4197  
 CIE z: 0.0674  
 Peak Wavelength (nm): 609  
 Dominant Wavelength (nm): 587  
 Purity: 79.96089  
 Rf: 70.6  
 Rg: 97.6

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.9 |      |       |
| R1:       | 68.7 | R9:  | -17.8 |
| R2:       | 82.6 | R10: | 60.5  |
| R3:       | 95.5 | R11: | 60.2  |
| R4:       | 66.4 | R12: | 48.2  |
| R5:       | 65.4 | R13: | 70.7  |
| R6:       | 75.9 | R14: | 96.8  |
| R7:       | 77.2 | R15: | 61.8  |
| R8:       | 43.5 |      |       |



**Test Conditions**


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-2


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 27                       | NR            | 620    | 966                      | NR            | 750    | 46                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 42                       | NR            | 625    | 930                      | NR            | 755    | 39                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 67                       | NR            | 630    | 888                      | NR            | 760    | 34                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 101                      | NR            | 635    | 835                      | NR            | 765    | 30                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 139                      | NR            | 640    | 778                      | NR            | 770    | 26                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 183                      | NR            | 645    | 717                      | NR            | 775    | 22                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 224                      | NR            | 650    | 656                      | NR            | 780    | 19                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 262                      | NR            | 655    | 595                      | NR            | 785    | 17                       | NR            | 915    | 1                        | NR            |
| 400    | 1                        | NR            | 530    | 299                      | NR            | 660    | 536                      | NR            | 790    | 15                       | NR            | 920    | 1                        | NR            |
| 405    | 3                        | NR            | 535    | 332                      | NR            | 665    | 480                      | NR            | 795    | 13                       | NR            | 925    | 1                        | NR            |
| 410    | 7                        | NR            | 540    | 365                      | NR            | 670    | 425                      | NR            | 800    | 11                       | NR            | 930    | 1                        | NR            |
| 415    | 17                       | NR            | 545    | 400                      | NR            | 675    | 376                      | NR            | 805    | 10                       | NR            | 935    | 0                        | NR            |
| 420    | 36                       | NR            | 550    | 437                      | NR            | 680    | 332                      | NR            | 810    | 8                        | NR            | 940    | 0                        | NR            |
| 425    | 67                       | NR            | 555    | 479                      | NR            | 685    | 291                      | NR            | 815    | 8                        | NR            | 945    | 0                        | NR            |
| 430    | 105                      | NR            | 560    | 525                      | NR            | 690    | 255                      | NR            | 820    | 7                        | NR            | 950    | 0                        | NR            |
| 435    | 141                      | NR            | 565    | 579                      | NR            | 695    | 221                      | NR            | 825    | 6                        | NR            | 955    | 0                        | NR            |
| 440    | 169                      | NR            | 570    | 639                      | NR            | 700    | 192                      | NR            | 830    | 5                        | NR            | 960    | 0                        | NR            |
| 445    | 173                      | NR            | 575    | 703                      | NR            | 705    | 167                      | NR            | 835    | 4                        | NR            | 965    | 0                        | NR            |
| 450    | 136                      | NR            | 580    | 769                      | NR            | 710    | 144                      | NR            | 840    | 4                        | NR            | 970    | 0                        | NR            |
| 455    | 80                       | NR            | 585    | 832                      | NR            | 715    | 125                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 45                       | NR            | 590    | 890                      | NR            | 720    | 109                      | NR            | 850    | 3                        | NR            | 980    | 0                        | NR            |
| 465    | 32                       | NR            | 595    | 937                      | NR            | 725    | 94                       | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 23                       | NR            | 600    | 972                      | NR            | 730    | 81                       | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 18                       | NR            | 605    | 992                      | NR            | 735    | 70                       | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 18                       | NR            | 610    | 998                      | NR            | 740    | 61                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 20                       | NR            | 615    | 990                      | NR            | 745    | 53                       | NR            | 875    | 2                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-2

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 0.8**

| $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360               | 0                           | NR                      | 490               | 27                          | NR                      | 620               | 966                         | NR                      | 750               | 46                          | NR                      | 880               | 1                           | NR                      |
| 365               | 0                           | NR                      | 495               | 42                          | NR                      | 625               | 930                         | NR                      | 755               | 39                          | NR                      | 885               | 1                           | NR                      |
| 370               | 0                           | NR                      | 500               | 67                          | NR                      | 630               | 888                         | NR                      | 760               | 34                          | NR                      | 890               | 1                           | NR                      |
| 375               | 0                           | NR                      | 505               | 101                         | NR                      | 635               | 835                         | NR                      | 765               | 30                          | NR                      | 895               | 1                           | NR                      |
| 380               | 0                           | NR                      | 510               | 139                         | NR                      | 640               | 778                         | NR                      | 770               | 26                          | NR                      | 900               | 1                           | NR                      |
| 385               | 0                           | NR                      | 515               | 183                         | NR                      | 645               | 717                         | NR                      | 775               | 22                          | NR                      | 905               | 1                           | NR                      |
| 390               | 0                           | NR                      | 520               | 224                         | NR                      | 650               | 656                         | NR                      | 780               | 19                          | NR                      | 910               | 1                           | NR                      |
| 395               | 0                           | NR                      | 525               | 262                         | NR                      | 655               | 595                         | NR                      | 785               | 17                          | NR                      | 915               | 1                           | NR                      |
| 400               | 1                           | NR                      | 530               | 299                         | NR                      | 660               | 536                         | NR                      | 790               | 15                          | NR                      | 920               | 1                           | NR                      |
| 405               | 3                           | NR                      | 535               | 332                         | NR                      | 665               | 480                         | NR                      | 795               | 13                          | NR                      | 925               | 1                           | NR                      |
| 410               | 7                           | NR                      | 540               | 365                         | NR                      | 670               | 425                         | NR                      | 800               | 11                          | NR                      | 930               | 1                           | NR                      |
| 415               | 17                          | NR                      | 545               | 400                         | NR                      | 675               | 376                         | NR                      | 805               | 10                          | NR                      | 935               | 0                           | NR                      |
| 420               | 36                          | NR                      | 550               | 437                         | NR                      | 680               | 332                         | NR                      | 810               | 8                           | NR                      | 940               | 0                           | NR                      |
| 425               | 67                          | NR                      | 555               | 479                         | NR                      | 685               | 291                         | NR                      | 815               | 8                           | NR                      | 945               | 0                           | NR                      |
| 430               | 105                         | NR                      | 560               | 525                         | NR                      | 690               | 255                         | NR                      | 820               | 7                           | NR                      | 950               | 0                           | NR                      |
| 435               | 141                         | NR                      | 565               | 579                         | NR                      | 695               | 221                         | NR                      | 825               | 6                           | NR                      | 955               | 0                           | NR                      |
| 440               | 169                         | NR                      | 570               | 639                         | NR                      | 700               | 192                         | NR                      | 830               | 5                           | NR                      | 960               | 0                           | NR                      |
| 445               | 173                         | NR                      | 575               | 703                         | NR                      | 705               | 167                         | NR                      | 835               | 4                           | NR                      | 965               | 0                           | NR                      |
| 450               | 136                         | NR                      | 580               | 769                         | NR                      | 710               | 144                         | NR                      | 840               | 4                           | NR                      | 970               | 0                           | NR                      |
| 455               | 80                          | NR                      | 585               | 832                         | NR                      | 715               | 125                         | NR                      | 845               | 3                           | NR                      | 975               | 0                           | NR                      |
| 460               | 45                          | NR                      | 590               | 890                         | NR                      | 720               | 109                         | NR                      | 850               | 3                           | NR                      | 980               | 0                           | NR                      |
| 465               | 32                          | NR                      | 595               | 937                         | NR                      | 725               | 94                          | NR                      | 855               | 3                           | NR                      | 985               | 0                           | NR                      |
| 470               | 23                          | NR                      | 600               | 972                         | NR                      | 730               | 81                          | NR                      | 860               | 2                           | NR                      | 990               | 0                           | NR                      |
| 475               | 18                          | NR                      | 605               | 992                         | NR                      | 735               | 70                          | NR                      | 865               | 2                           | NR                      | 995               | 0                           | NR                      |
| 480               | 18                          | NR                      | 610               | 998                         | NR                      | 740               | 61                          | NR                      | 870               | 2                           | NR                      | 1000              | 0                           | NR                      |
| 485               | 20                          | NR                      | 615               | 990                         | NR                      | 745               | 53                          | NR                      | 875               | 2                           | NR                      |                   |                             |                         |

REPORT NUMBER: SP1-2407-184-2

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: NR**

**M/P: 1.21**





| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 27                       | NR            | 620    | 966                      | NR            | 750    | 46                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 42                       | NR            | 625    | 930                      | NR            | 755    | 39                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 67                       | NR            | 630    | 888                      | NR            | 760    | 34                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 101                      | NR            | 635    | 835                      | NR            | 765    | 30                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 139                      | NR            | 640    | 778                      | NR            | 770    | 26                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 183                      | NR            | 645    | 717                      | NR            | 775    | 22                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 224                      | NR            | 650    | 656                      | NR            | 780    | 19                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 262                      | NR            | 655    | 595                      | NR            | 785    | 17                       | NR            | 915    | 1                        | NR            |
| 400    | 1                        | NR            | 530    | 299                      | NR            | 660    | 536                      | NR            | 790    | 15                       | NR            | 920    | 1                        | NR            |
| 405    | 3                        | NR            | 535    | 332                      | NR            | 665    | 480                      | NR            | 795    | 13                       | NR            | 925    | 1                        | NR            |
| 410    | 7                        | NR            | 540    | 365                      | NR            | 670    | 425                      | NR            | 800    | 11                       | NR            | 930    | 1                        | NR            |
| 415    | 17                       | NR            | 545    | 400                      | NR            | 675    | 376                      | NR            | 805    | 10                       | NR            | 935    | 0                        | NR            |
| 420    | 36                       | NR            | 550    | 437                      | NR            | 680    | 332                      | NR            | 810    | 8                        | NR            | 940    | 0                        | NR            |
| 425    | 67                       | NR            | 555    | 479                      | NR            | 685    | 291                      | NR            | 815    | 8                        | NR            | 945    | 0                        | NR            |
| 430    | 105                      | NR            | 560    | 525                      | NR            | 690    | 255                      | NR            | 820    | 7                        | NR            | 950    | 0                        | NR            |
| 435    | 141                      | NR            | 565    | 579                      | NR            | 695    | 221                      | NR            | 825    | 6                        | NR            | 955    | 0                        | NR            |
| 440    | 169                      | NR            | 570    | 639                      | NR            | 700    | 192                      | NR            | 830    | 5                        | NR            | 960    | 0                        | NR            |
| 445    | 173                      | NR            | 575    | 703                      | NR            | 705    | 167                      | NR            | 835    | 4                        | NR            | 965    | 0                        | NR            |
| 450    | 136                      | NR            | 580    | 769                      | NR            | 710    | 144                      | NR            | 840    | 4                        | NR            | 970    | 0                        | NR            |
| 455    | 80                       | NR            | 585    | 832                      | NR            | 715    | 125                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 45                       | NR            | 590    | 890                      | NR            | 720    | 109                      | NR            | 850    | 3                        | NR            | 980    | 0                        | NR            |
| 465    | 32                       | NR            | 595    | 937                      | NR            | 725    | 94                       | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 23                       | NR            | 600    | 972                      | NR            | 730    | 81                       | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 18                       | NR            | 605    | 992                      | NR            | 735    | 70                       | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 18                       | NR            | 610    | 998                      | NR            | 740    | 61                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 20                       | NR            | 615    | 990                      | NR            | 745    | 53                       | NR            | 875    | 2                        | NR            |        |                          |               |

**Summary**

$R_f = 70.6$   
 $R_g = 97.6$   
 CIE  $R_a = 71.9$   
 $R_9 = -17.8$




**Color Vector Graphics**






Individual Sample Fidelity Index ( $R_{f,i}$ )



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 60 | CES51 = 74 | CES76 = 58 |
| CES02 = 65 | CES27 = 77 | CES52 = 77 | CES77 = 82 |
| CES03 = 32 | CES28 = 85 | CES53 = 65 | CES78 = 65 |
| CES04 = 72 | CES29 = 50 | CES54 = 77 | CES79 = 86 |
| CES05 = 52 | CES30 = 49 | CES55 = 74 | CES80 = 85 |
| CES06 = 53 | CES31 = 55 | CES56 = 64 | CES81 = 61 |
| CES07 = 44 | CES32 = 55 | CES57 = 60 | CES82 = 93 |
| CES08 = 43 | CES33 = 55 | CES58 = 64 | CES83 = 83 |
| CES09 = 29 | CES34 = 75 | CES59 = 84 | CES84 = 93 |
| CES10 = 79 | CES35 = 88 | CES60 = 89 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 55 |
| CES12 = 68 | CES37 = 82 | CES62 = 68 | CES87 = 79 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 86 | CES65 = 66 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 89 |
| CES17 = 51 | CES42 = 83 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 71 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 81 | CES94 = 52 |
| CES20 = 68 | CES45 = 76 | CES70 = 65 | CES95 = 76 |
| CES21 = 89 | CES46 = 68 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 88 | CES97 = 76 |
| CES23 = 92 | CES48 = 47 | CES73 = 59 | CES98 = 71 |
| CES24 = 92 | CES49 = 65 | CES74 = 85 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)