

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1384911

Luminaire Tested: **VAL-T-SB3A-727-U-SLR**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



Test Information

Test Method: LM-79-08
 Report Number: P1384911
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 02/18/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: VAL-T-SB3A-727-U-SLR
 Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 35 SQUARE 85W 70CRI
 2700K FIXTURE w/ 90° Spill Light Eliminator RIGHT OPTIC
 Light Source: (78) 2700K CCT, 70 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER
 Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
a	good	reflector
b	good	lens
c	good	housing
d	good	cord

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 11030 lumens
 Efficiency: N/A
 Efficacy: 129.8 lumens/watt
 Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
 IES Classification: Type IV - Short
 BUG Rating: B2 - U0 - G2

 Input Watts (W): 85
 Input Voltage (V): 120
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: 0.98
 Total Harmonic Distortion (THDi): 11.0%
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 28.75 FT

REPORT NUMBER: P1384911
 CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P1384911
CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P1384911
 CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2967.3	0.0	2967.3
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	8062.7	0.0	8062.7
	% Fixture	73.1	0.0	73.1
Total	Lumens	11030.0	0.0	11030.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.7	1.6
10°-20°	532.2	4.8
20°-30°	823.6	7.5
30°-40°	1021.9	9.3
40°-50°	1494.3	13.5
50°-60°	2340.6	21.2
60°-70°	2777.3	25.2
70°-80°	1619.9	14.7
80°-90°	246.4	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11030.0	100.0
0°-180°	11030.0	100.0




REPORT NUMBER: P1384911
 CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	829.0	7.5			
FM (30°-60°)	3355.5	30.4			
FH (60°-80°)	3676.6	33.3			G2/5000
FVH (80°-90°)	201.5	1.8			G2/225
BL (0°-30°)	700.5	6.4	B2/1000		
BM (30°-60°)	1501.3	13.6	B2/2500		
BH (60°-80°)	720.6	6.5	B2/1000		G2/1000
BVH (80°-90°)	44.9	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
 Type IV Short





REPORT NUMBER: P1384911

CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7
2.5°	1900.4	1883.1	1866.1	1850.5	1834.8	1819.2	1803.3	1788.1	1772.8	1757.4	1743.9
5°	2029.8	1999.4	1969.1	1937.3	1905.8	1874.7	1843.7	1814.3	1785.2	1754.7	1728.5
7.5°	2160.7	2109.4	2058.2	2009.9	1961.6	1918.4	1875.3	1836.7	1797.9	1757.4	1725.8
10°	2242.9	2181.7	2120.2	2060.3	2000.2	1947.0	1893.6	1849.1	1804.6	1761.4	1727.7
12.5°	2284.8	2223.8	2162.8	2095.7	2028.5	1968.9	1909.3	1860.2	1811.3	1764.1	1731.2
15°	2305.0	2243.2	2181.7	2113.5	2045.2	1981.0	1916.5	1861.3	1806.0	1753.4	1724.2
17.5°	2310.4	2252.7	2195.2	2122.4	2049.5	1976.2	1903.1	1838.6	1774.4	1712.9	1688.1
20°	2327.9	2269.6	2211.4	2133.2	2054.9	1968.9	1882.8	1798.1	1713.4	1632.0	1616.3
22.5°	2346.8	2293.4	2240.2	2154.2	2068.4	1963.2	1858.0	1751.7	1645.5	1548.3	1533.5
25°	2376.5	2330.3	2284.2	2190.3	2096.5	1962.7	1828.9	1696.4	1564.0	1452.6	1451.2
27.5°	2419.6	2384.3	2349.0	2243.2	2137.7	1967.8	1797.9	1639.8	1481.4	1367.6	1374.4
30°	2480.3	2452.5	2425.0	2305.8	2186.3	1978.9	1771.7	1590.4	1409.4	1298.8	1306.1
32.5°	2554.5	2537.2	2520.0	2379.4	2238.9	1991.3	1743.9	1547.3	1350.9	1248.9	1248.9
35°	2679.9	2658.4	2636.8	2457.7	2278.8	1988.3	1698.1	1498.2	1298.0	1219.3	1202.5
37.5°	2839.1	2813.5	2787.8	2553.2	2318.5	1979.9	1641.4	1443.7	1246.2	1184.2	1152.4
40°	3073.8	3023.3	2972.6	2662.4	2352.2	1961.1	1569.9	1378.7	1187.4	1138.3	1098.4
42.5°	3402.9	3296.0	3188.9	2783.2	2377.0	1928.4	1479.6	1301.3	1122.7	1088.4	1039.1
45°	3811.5	3640.2	3468.9	2947.3	2425.6	1906.0	1386.5	1222.5	1058.8	1027.7	978.6
47.5°	4202.7	3985.8	3768.9	3115.8	2462.8	1879.9	1296.9	1144.3	992.1	956.3	910.4
50°	4655.8	4361.8	4067.8	3262.9	2457.9	1835.4	1212.5	1074.7	936.6	887.5	842.1
52.5°	5237.1	4770.2	4303.0	3332.4	2361.6	1744.2	1127.0	1012.1	897.7	834.9	786.3
55°	5931.7	5180.5	4429.2	3314.1	2199.0	1623.3	1047.2	959.8	871.8	809.2	752.1
57.5°	6639.8	5524.9	4410.4	3214.0	2017.7	1496.8	975.9	915.5	855.1	802.5	732.4
60°	7171.2	5679.2	4187.0	2974.2	1761.4	1336.9	912.3	869.9	827.6	786.3	716.2
62.5°	6951.4	5336.9	3722.5	2581.2	1439.9	1134.0	828.1	804.4	780.9	763.4	696.5
65°	6209.6	4603.2	2996.9	2024.7	1052.6	891.2	729.7	724.5	719.7	714.8	659.5
67.5°	5513.6	3953.4	2393.2	1575.6	758.0	681.4	604.8	619.1	633.4	640.6	602.9
70°	4847.3	3358.6	1869.9	1207.4	544.9	517.9	490.9	512.2	533.6	531.4	513.1
72.5°	4160.8	2788.9	1416.7	907.7	398.7	398.1	397.9	414.1	430.2	408.7	420.3
75°	3406.9	2226.8	1046.6	672.7	298.9	297.0	295.4	314.5	333.9	342.6	350.1
77.5°	2265.9	1460.9	656.0	434.8	213.6	215.3	216.3	237.4	258.4	283.2	284.6
80°	1329.9	837.6	345.3	240.3	135.4	137.0	138.1	160.2	182.1	217.1	215.8
82.5°	664.9	419.7	174.8	129.2	83.6	83.9	84.2	95.0	105.7	125.4	130.8
85°	151.1	99.8	48.6	41.0	33.7	35.3	37.2	44.2	51.3	62.0	65.3
87.5°	12.1	11.9	11.3	11.1	10.8	11.3	12.1	13.5	14.8	16.2	18.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384911

CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7
2.5°	1729.3	1715.0	1703.7	1692.7	1682.9	1673.0	1661.4	1649.5	1641.1	1632.5	1626.8
5°	1702.6	1677.3	1656.2	1635.2	1617.9	1600.1	1584.5	1568.6	1556.2	1543.5	1533.2
7.5°	1694.3	1663.0	1635.7	1608.2	1585.0	1561.8	1542.4	1522.7	1504.1	1485.8	1473.9
10°	1694.5	1661.6	1633.6	1605.5	1581.0	1556.4	1530.8	1505.2	1484.7	1464.2	1446.4
12.5°	1703.7	1676.5	1656.8	1637.4	1614.7	1592.0	1561.6	1530.8	1503.0	1475.5	1453.7
15°	1706.4	1688.6	1687.0	1685.4	1677.6	1669.7	1641.4	1613.1	1574.8	1536.2	1504.9
17.5°	1685.6	1683.2	1709.9	1736.6	1752.0	1767.4	1747.7	1727.7	1673.8	1619.8	1573.2
20°	1631.7	1646.8	1699.1	1751.2	1792.7	1834.3	1832.1	1830.2	1759.8	1689.2	1627.9
22.5°	1556.2	1578.6	1646.8	1715.0	1774.9	1834.8	1850.2	1865.3	1796.2	1726.9	1651.4
25°	1475.8	1500.3	1563.5	1626.6	1691.0	1755.5	1784.1	1812.7	1755.8	1698.9	1625.5
27.5°	1397.8	1421.6	1468.5	1515.4	1567.2	1619.0	1651.1	1683.2	1648.4	1613.6	1554.3
30°	1324.5	1342.8	1376.8	1410.8	1445.8	1480.9	1506.5	1532.2	1509.2	1486.3	1443.7
32.5°	1256.7	1264.6	1286.7	1308.8	1335.0	1360.9	1375.2	1389.2	1371.4	1353.6	1325.5
35°	1196.1	1189.6	1204.1	1218.7	1239.8	1261.1	1271.9	1282.6	1267.8	1253.0	1227.9
37.5°	1135.1	1117.3	1124.3	1130.8	1148.9	1166.7	1182.0	1197.7	1186.9	1176.1	1154.8
40°	1072.5	1046.6	1046.1	1045.3	1062.5	1079.5	1098.9	1118.1	1116.2	1114.1	1093.8
42.5°	1006.2	973.2	969.7	966.2	983.2	1000.2	1020.7	1041.2	1045.3	1049.3	1032.6
45°	944.7	911.2	905.8	900.4	915.0	930.1	952.5	975.1	984.6	994.0	978.9
47.5°	881.5	852.4	849.2	845.7	861.0	876.7	901.5	926.6	936.6	946.8	936.6
50°	818.4	794.4	798.4	802.5	819.5	836.2	855.6	875.3	893.9	912.3	910.4
52.5°	768.5	750.4	763.1	775.5	790.9	806.5	826.8	847.0	866.4	886.1	889.1
55°	732.1	712.1	729.9	747.7	766.3	785.0	803.8	822.7	841.1	859.1	863.2
57.5°	704.3	676.5	694.3	712.1	732.4	752.6	771.5	790.4	811.7	833.0	836.2
60°	681.1	646.0	657.9	669.5	690.3	710.8	730.5	749.9	771.5	793.1	797.4
62.5°	650.6	604.8	606.4	607.5	630.9	654.1	670.3	686.5	707.0	727.8	734.0
65°	610.2	561.1	555.7	550.3	572.4	594.8	607.5	620.4	638.2	656.0	662.2
67.5°	559.5	515.8	504.7	493.6	514.1	534.6	545.2	555.7	567.8	580.0	587.0
70°	487.2	461.3	454.3	447.2	464.0	480.7	489.9	499.0	508.7	518.5	522.2
72.5°	414.3	408.7	403.5	398.7	411.4	424.0	431.9	439.7	448.9	458.0	460.2
75°	346.9	343.9	340.2	336.6	346.4	356.1	362.0	368.2	377.6	387.1	391.1
77.5°	277.6	270.3	266.5	262.2	271.1	280.0	285.7	291.3	299.1	307.0	308.1
80°	207.2	198.3	195.3	192.1	198.5	205.0	207.2	209.1	215.5	221.7	221.7
82.5°	130.8	130.8	128.9	126.8	125.4	124.1	121.4	118.7	125.2	131.6	133.8
85°	65.8	66.1	63.1	59.9	56.1	51.8	51.0	49.9	49.6	49.1	51.0
87.5°	20.5	22.1	23.7	24.8	26.4	27.5	26.7	25.6	24.5	23.7	21.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384911
 CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7
2.5°	1621.2	1618.5	1615.8	1613.6	1611.7	1610.4	1611.7	1613.6	1615.8	1618.5	1621.2
5°	1522.7	1518.4	1513.8	1510.9	1507.9	1505.2	1507.9	1510.9	1513.8	1518.4	1522.7
7.5°	1462.0	1455.0	1448.0	1442.9	1437.7	1435.1	1437.7	1442.9	1448.0	1455.0	1462.0
10°	1429.1	1419.1	1409.4	1404.0	1398.6	1394.6	1398.6	1404.0	1409.4	1419.1	1429.1
12.5°	1431.8	1419.4	1407.5	1399.4	1391.4	1386.5	1391.4	1399.4	1407.5	1419.4	1431.8
15°	1473.4	1456.1	1438.3	1428.3	1418.3	1410.8	1418.3	1428.3	1438.3	1456.1	1473.4
17.5°	1526.8	1501.4	1476.1	1467.2	1458.0	1453.9	1458.0	1467.2	1476.1	1501.4	1526.8
20°	1566.7	1532.7	1499.3	1485.8	1472.3	1467.4	1472.3	1485.8	1499.3	1532.7	1566.7
22.5°	1575.9	1535.9	1495.7	1483.1	1470.1	1464.7	1470.1	1483.1	1495.7	1535.9	1575.9
25°	1552.4	1510.3	1468.0	1455.0	1441.8	1437.7	1441.8	1455.0	1468.0	1510.3	1552.4
27.5°	1494.9	1457.7	1420.2	1406.5	1392.4	1383.8	1392.4	1406.5	1420.2	1457.7	1494.9
30°	1401.3	1373.5	1346.0	1337.4	1328.5	1324.5	1328.5	1337.4	1346.0	1373.5	1401.3
32.5°	1297.5	1280.2	1263.0	1257.3	1251.6	1248.9	1251.6	1257.3	1263.0	1280.2	1297.5
35°	1203.1	1190.7	1178.3	1173.7	1169.4	1165.3	1169.4	1173.7	1178.3	1190.7	1203.1
37.5°	1133.5	1118.9	1103.8	1095.7	1087.6	1081.7	1087.6	1095.7	1103.8	1118.9	1133.5
40°	1073.6	1052.6	1031.8	1020.7	1009.4	1003.5	1009.4	1020.7	1031.8	1052.6	1073.6
42.5°	1015.6	991.3	967.0	950.0	933.3	922.5	933.3	950.0	967.0	991.3	1015.6
45°	963.5	936.3	909.0	888.8	868.6	855.1	868.6	888.8	909.0	936.3	963.5
47.5°	926.6	903.1	879.4	861.6	843.8	830.8	843.8	861.6	879.4	903.1	926.6
50°	908.5	889.9	871.3	854.6	837.6	825.4	837.6	854.6	871.3	889.9	908.5
52.5°	892.3	878.8	865.3	850.8	836.2	825.4	836.2	850.8	865.3	878.8	892.3
55°	867.2	857.5	847.5	836.8	826.0	817.3	826.0	836.8	847.5	857.5	867.2
57.5°	839.5	829.2	818.7	810.6	802.5	798.4	802.5	810.6	818.7	829.2	839.5
60°	801.7	793.6	785.5	777.9	770.1	763.4	770.1	777.9	785.5	793.6	801.7
62.5°	740.5	736.7	733.2	724.5	716.2	706.7	716.2	724.5	733.2	736.7	740.5
65°	668.4	666.5	664.9	658.7	652.8	642.0	652.8	658.7	664.9	666.5	668.4
67.5°	594.0	590.5	586.7	580.2	574.0	571.9	574.0	580.2	586.7	590.5	594.0
70°	526.0	520.6	515.2	500.6	486.1	469.4	486.1	500.6	515.2	520.6	526.0
72.5°	462.6	454.3	445.6	428.6	411.4	393.8	411.4	428.6	445.6	454.3	462.6
75°	395.2	383.3	371.7	353.6	335.8	323.7	335.8	353.6	371.7	383.3	395.2
77.5°	309.7	299.4	289.2	278.4	267.6	261.7	267.6	278.4	289.2	299.4	309.7
80°	221.7	214.2	206.4	201.0	195.6	191.5	195.6	201.0	206.4	214.2	221.7
82.5°	136.2	132.7	129.5	123.5	117.3	113.3	117.3	123.5	129.5	132.7	136.2
85°	52.6	51.8	51.3	49.1	47.2	45.9	47.2	49.1	51.3	51.8	52.6
87.5°	19.4	17.8	16.2	15.1	14.0	13.5	14.0	15.1	16.2	17.8	19.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384911

CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7
2.5°	1626.8	1632.5	1641.1	1649.5	1661.4	1673.0	1682.9	1692.7	1703.7	1715.0	1729.3
5°	1533.2	1543.5	1556.2	1568.6	1584.5	1600.1	1617.9	1635.2	1656.2	1677.3	1702.6
7.5°	1473.9	1485.8	1504.1	1522.7	1542.4	1561.8	1585.0	1608.2	1635.7	1663.0	1694.3
10°	1446.4	1464.2	1484.7	1505.2	1530.8	1556.4	1581.0	1605.5	1633.6	1661.6	1694.5
12.5°	1453.7	1475.5	1503.0	1530.8	1561.6	1592.0	1614.7	1637.4	1656.8	1676.5	1703.7
15°	1504.9	1536.2	1574.8	1613.1	1641.4	1669.7	1677.6	1685.4	1687.0	1688.6	1706.4
17.5°	1573.2	1619.8	1673.8	1727.7	1747.7	1767.4	1752.0	1736.6	1709.9	1683.2	1685.6
20°	1627.9	1689.2	1759.8	1830.2	1832.1	1834.3	1792.7	1751.2	1699.1	1646.8	1631.7
22.5°	1651.4	1726.9	1796.2	1865.3	1850.2	1834.8	1774.9	1715.0	1646.8	1578.6	1556.2
25°	1625.5	1698.9	1755.8	1812.7	1784.1	1755.5	1691.0	1626.6	1563.5	1500.3	1475.8
27.5°	1554.3	1613.6	1648.4	1683.2	1651.1	1619.0	1567.2	1515.4	1468.5	1421.6	1397.8
30°	1443.7	1486.3	1509.2	1532.2	1506.5	1480.9	1445.8	1410.8	1376.8	1342.8	1324.5
32.5°	1325.5	1353.6	1371.4	1389.2	1375.2	1360.9	1335.0	1308.8	1286.7	1264.6	1256.7
35°	1227.9	1253.0	1267.8	1282.6	1271.9	1261.1	1239.8	1218.7	1204.1	1189.6	1196.1
37.5°	1154.8	1176.1	1186.9	1197.7	1182.0	1166.7	1148.9	1130.8	1124.3	1117.3	1135.1
40°	1093.8	1114.1	1116.2	1118.1	1098.9	1079.5	1062.5	1045.3	1046.1	1046.6	1072.5
42.5°	1032.6	1049.3	1045.3	1041.2	1020.7	1000.2	983.2	966.2	969.7	973.2	1006.2
45°	978.9	994.0	984.6	975.1	952.5	930.1	915.0	900.4	905.8	911.2	944.7
47.5°	936.6	946.8	936.6	926.6	901.5	876.7	861.0	845.7	849.2	852.4	881.5
50°	910.4	912.3	893.9	875.3	855.6	836.2	819.5	802.5	798.4	794.4	818.4
52.5°	889.1	886.1	866.4	847.0	826.8	806.5	790.9	775.5	763.1	750.4	768.5
55°	863.2	859.1	841.1	822.7	803.8	785.0	766.3	747.7	729.9	712.1	732.1
57.5°	836.2	833.0	811.7	790.4	771.5	752.6	732.4	712.1	694.3	676.5	704.3
60°	797.4	793.1	771.5	749.9	730.5	710.8	690.3	669.5	657.9	646.0	681.1
62.5°	734.0	727.8	707.0	686.5	670.3	654.1	630.9	607.5	606.4	604.8	650.6
65°	662.2	656.0	638.2	620.4	607.5	594.8	572.4	550.3	555.7	561.1	610.2
67.5°	587.0	580.0	567.8	555.7	545.2	534.6	514.1	493.6	504.7	515.8	559.5
70°	522.2	518.5	508.7	499.0	489.9	480.7	464.0	447.2	454.3	461.3	487.2
72.5°	460.2	458.0	448.9	439.7	431.9	424.0	411.4	398.7	403.5	408.7	414.3
75°	391.1	387.1	377.6	368.2	362.0	356.1	346.4	336.6	340.2	343.9	346.9
77.5°	308.1	307.0	299.1	291.3	285.7	280.0	271.1	262.2	266.5	270.3	277.6
80°	221.7	221.7	215.5	209.1	207.2	205.0	198.5	192.1	195.3	198.3	207.2
82.5°	133.8	131.6	125.2	118.7	121.4	124.1	125.4	126.8	128.9	130.8	130.8
85°	51.0	49.1	49.6	49.9	51.0	51.8	56.1	59.9	63.1	66.1	65.8
87.5°	21.6	23.7	24.5	25.6	26.7	27.5	26.4	24.8	23.7	22.1	20.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384911

CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7
2.5°	1743.9	1757.4	1772.8	1788.1	1803.3	1819.2	1834.8	1850.5	1866.1	1883.1	1900.4
5°	1728.5	1754.7	1785.2	1814.3	1843.7	1874.7	1905.8	1937.3	1969.1	1999.4	2029.8
7.5°	1725.8	1757.4	1797.9	1836.7	1875.3	1918.4	1961.6	2009.9	2058.2	2109.4	2160.7
10°	1727.7	1761.4	1804.6	1849.1	1893.6	1947.0	2000.2	2060.3	2120.2	2181.7	2242.9
12.5°	1731.2	1764.1	1811.3	1860.2	1909.3	1968.9	2028.5	2095.7	2162.8	2223.8	2284.8
15°	1724.2	1753.4	1806.0	1861.3	1916.5	1981.0	2045.2	2113.5	2181.7	2243.2	2305.0
17.5°	1688.1	1712.9	1774.4	1838.6	1903.1	1976.2	2049.5	2122.4	2195.2	2252.7	2310.4
20°	1616.3	1632.0	1713.4	1798.1	1882.8	1968.9	2054.9	2133.2	2211.4	2269.6	2327.9
22.5°	1533.5	1548.3	1645.5	1751.7	1858.0	1963.2	2068.4	2154.2	2240.2	2293.4	2346.8
25°	1451.2	1452.6	1564.0	1696.4	1828.9	1962.7	2096.5	2190.3	2284.2	2330.3	2376.5
27.5°	1374.4	1367.6	1481.4	1639.8	1797.9	1967.8	2137.7	2243.2	2349.0	2384.3	2419.6
30°	1306.1	1298.8	1409.4	1590.4	1771.7	1978.9	2186.3	2305.8	2425.0	2452.5	2480.3
32.5°	1248.9	1248.9	1350.9	1547.3	1743.9	1991.3	2238.9	2379.4	2520.0	2537.2	2554.5
35°	1202.5	1219.3	1298.0	1498.2	1698.1	1988.3	2278.8	2457.7	2636.8	2658.4	2679.9
37.5°	1152.4	1184.2	1246.2	1443.7	1641.4	1979.9	2318.5	2553.2	2787.8	2813.5	2839.1
40°	1098.4	1138.3	1187.4	1378.7	1569.9	1961.1	2352.2	2662.4	2972.6	3023.3	3073.8
42.5°	1039.1	1088.4	1122.7	1301.3	1479.6	1928.4	2377.0	2783.2	3188.9	3296.0	3402.9
45°	978.6	1027.7	1058.8	1222.5	1386.5	1906.0	2425.6	2947.3	3468.9	3640.2	3811.5
47.5°	910.4	956.3	992.1	1144.3	1296.9	1879.9	2462.8	3115.8	3768.9	3985.8	4202.7
50°	842.1	887.5	936.6	1074.7	1212.5	1835.4	2457.9	3262.9	4067.8	4361.8	4655.8
52.5°	786.3	834.9	897.7	1012.1	1127.0	1744.2	2361.6	3332.4	4303.0	4770.2	5237.1
55°	752.1	809.2	871.8	959.8	1047.2	1623.3	2199.0	3314.1	4429.2	5180.5	5931.7
57.5°	732.4	802.5	855.1	915.5	975.9	1496.8	2017.7	3214.0	4410.4	5524.9	6639.8
60°	716.2	786.3	827.6	869.9	912.3	1336.9	1761.4	2974.2	4187.0	5679.2	7171.2
62.5°	696.5	763.4	780.9	804.4	828.1	1134.0	1439.9	2581.2	3722.5	5336.9	6951.4
65°	659.5	714.8	719.7	724.5	729.7	891.2	1052.6	2024.7	2996.9	4603.2	6209.6
67.5°	602.9	640.6	633.4	619.1	604.8	681.4	758.0	1575.6	2393.2	3953.4	5513.6
70°	513.1	531.4	533.6	512.2	490.9	517.9	544.9	1207.4	1869.9	3358.6	4847.3
72.5°	420.3	408.7	430.2	414.1	397.9	398.1	398.7	907.7	1416.7	2788.9	4160.8
75°	350.1	342.6	333.9	314.5	295.4	297.0	298.9	672.7	1046.6	2226.8	3406.9
77.5°	284.6	283.2	258.4	237.4	216.3	215.3	213.6	434.8	656.0	1460.9	2265.9
80°	215.8	217.1	182.1	160.2	138.1	137.0	135.4	240.3	345.3	837.6	1329.9
82.5°	130.8	125.4	105.7	95.0	84.2	83.9	83.6	129.2	174.8	419.7	664.9
85°	65.3	62.0	51.3	44.2	37.2	35.3	33.7	41.0	48.6	99.8	151.1
87.5°	18.9	16.2	14.8	13.5	12.1	11.3	10.8	11.1	11.3	11.9	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384911
 CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7
2.5°	1907.1	1913.9	1921.1	1928.7	1933.0	1937.3	1941.9	1946.2	1950.3	1946.2	1941.9
5°	2060.3	2090.5	2111.0	2131.5	2147.2	2162.8	2171.7	2180.9	2182.2	2180.9	2171.7
7.5°	2196.8	2233.0	2264.3	2295.5	2315.5	2335.5	2347.1	2358.9	2363.0	2358.9	2347.1
10°	2285.3	2327.9	2358.1	2388.6	2407.2	2425.6	2434.7	2443.9	2446.6	2443.9	2434.7
12.5°	2325.5	2366.2	2389.7	2412.9	2424.8	2436.4	2440.7	2444.4	2441.2	2444.4	2440.7
15°	2329.0	2352.7	2362.7	2372.4	2366.8	2360.8	2352.5	2344.1	2338.7	2344.1	2352.5
17.5°	2318.7	2327.4	2309.3	2291.5	2259.1	2226.8	2202.5	2178.2	2160.7	2178.2	2202.5
20°	2314.4	2300.9	2252.9	2205.2	2144.5	2083.8	2043.1	2002.1	1977.2	2002.1	2043.1
22.5°	2308.8	2270.7	2190.1	2109.4	2026.3	1943.5	1896.6	1849.9	1823.5	1849.9	1896.6
25°	2311.2	2245.6	2136.7	2028.0	1930.3	1832.9	1781.9	1731.2	1702.1	1731.2	1781.9
27.5°	2319.8	2220.0	2085.1	1950.3	1844.5	1738.5	1690.0	1641.4	1615.8	1641.4	1690.0
30°	2347.9	2215.2	2053.9	1892.3	1781.7	1671.1	1623.6	1575.9	1548.3	1575.9	1623.6
32.5°	2387.3	2220.0	2039.3	1858.6	1745.8	1633.3	1587.7	1542.4	1518.7	1542.4	1587.7
35°	2468.2	2256.4	2056.0	1855.9	1751.2	1646.8	1613.4	1580.2	1567.2	1580.2	1613.4
37.5°	2591.7	2344.1	2137.7	1931.4	1860.2	1789.0	1789.0	1789.0	1799.2	1789.0	1789.0
40°	2795.9	2518.1	2322.8	2127.8	2123.4	2119.7	2165.0	2210.6	2230.8	2210.6	2165.0
42.5°	3109.1	2815.6	2658.1	2500.6	2595.0	2689.4	2820.5	2951.6	3037.3	2951.6	2820.5
45°	3525.6	3239.7	3129.6	3019.8	3229.9	3439.8	3671.5	3903.2	4067.8	3903.2	3671.5
47.5°	3962.0	3721.2	3658.3	3595.7	3945.0	4294.4	4634.0	4973.6	5173.7	4973.6	4634.0
50°	4439.5	4222.9	4210.7	4198.6	4663.9	5129.2	5567.6	6005.9	6250.0	6005.9	5567.6
52.5°	4999.5	4761.6	4771.3	4780.4	5333.2	5885.9	6415.9	6946.0	7221.1	6946.0	6415.9
55°	5633.7	5335.6	5334.0	5332.3	5967.3	6602.9	7254.0	7905.7	8273.1	7905.7	7254.0
57.5°	6360.6	6081.4	6015.1	5948.5	6612.6	7276.4	7995.6	8715.0	9101.2	8715.0	7995.6
60°	7017.5	6863.7	6757.4	6651.4	7333.3	8015.5	8758.4	9501.0	9886.2	9501.0	8758.4
62.5°	7226.2	7501.1	7493.3	7485.5	8221.6	8957.7	9730.3	10503.4	10849.2	10503.4	9730.3
65°	6647.9	7086.2	7387.8	7689.1	8579.0	9468.6	10273.6	11078.5	11431.9	11078.5	10273.6
67.5°	5899.9	6286.4	6533.3	6780.1	7782.7	8785.6	9699.0	10612.4	10976.0	10612.4	9699.0
70°	5275.2	5703.0	5879.4	6055.8	6907.7	7759.3	8481.9	9204.3	9346.7	9204.3	8481.9
72.5°	4669.6	5178.6	5253.3	5328.0	5947.9	6567.8	6952.7	7337.6	7026.9	7337.6	6952.7
75°	3980.9	4554.7	4604.6	4654.5	4847.6	5041.0	5138.9	5237.1	5060.4	5237.1	5138.9
77.5°	2762.7	3259.9	3371.8	3483.8	3612.4	3741.4	3734.6	3727.9	3479.7	3727.9	3734.6
80°	1718.6	2107.3	2121.8	2136.4	2233.0	2329.3	2427.7	2526.2	2368.4	2526.2	2427.7
82.5°	878.3	1091.9	1124.8	1157.8	1216.8	1275.9	1303.4	1331.2	1197.7	1331.2	1303.4
85°	206.6	262.2	315.9	369.6	431.6	493.6	486.6	479.6	404.6	479.6	486.6
87.5°	12.4	12.9	13.2	13.5	13.8	14.0	14.8	15.6	16.2	15.6	14.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1384911
 CATALOG NUMBER: VAL-T-SB3A-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7	1758.7
2.5°	1937.3	1933.0	1928.7	1921.1	1913.9	1907.1	1900.4
5°	2162.8	2147.2	2131.5	2111.0	2090.5	2060.3	2029.8
7.5°	2335.5	2315.5	2295.5	2264.3	2233.0	2196.8	2160.7
10°	2425.6	2407.2	2388.6	2358.1	2327.9	2285.3	2242.9
12.5°	2436.4	2424.8	2412.9	2389.7	2366.2	2325.5	2284.8
15°	2360.8	2366.8	2372.4	2362.7	2352.7	2329.0	2305.0
17.5°	2226.8	2259.1	2291.5	2309.3	2327.4	2318.7	2310.4
20°	2083.8	2144.5	2205.2	2252.9	2300.9	2314.4	2327.9
22.5°	1943.5	2026.3	2109.4	2190.1	2270.7	2308.8	2346.8
25°	1832.9	1930.3	2028.0	2136.7	2245.6	2311.2	2376.5
27.5°	1738.5	1844.5	1950.3	2085.1	2220.0	2319.8	2419.6
30°	1671.1	1781.7	1892.3	2053.9	2215.2	2347.9	2480.3
32.5°	1633.3	1745.8	1858.6	2039.3	2220.0	2387.3	2554.5
35°	1646.8	1751.2	1855.9	2056.0	2256.4	2468.2	2679.9
37.5°	1789.0	1860.2	1931.4	2137.7	2344.1	2591.7	2839.1
40°	2119.7	2123.4	2127.8	2322.8	2518.1	2795.9	3073.8
42.5°	2689.4	2595.0	2500.6	2658.1	2815.6	3109.1	3402.9
45°	3439.8	3229.9	3019.8	3129.6	3239.7	3525.6	3811.5
47.5°	4294.4	3945.0	3595.7	3658.3	3721.2	3962.0	4202.7
50°	5129.2	4663.9	4198.6	4210.7	4222.9	4439.5	4655.8
52.5°	5885.9	5333.2	4780.4	4771.3	4761.6	4999.5	5237.1
55°	6602.9	5967.3	5332.3	5334.0	5335.6	5633.7	5931.7
57.5°	7276.4	6612.6	5948.5	6015.1	6081.4	6360.6	6639.8
60°	8015.5	7333.3	6651.4	6757.4	6863.7	7017.5	7171.2
62.5°	8957.7	8221.6	7485.5	7493.3	7501.1	7226.2	6951.4
65°	9468.6	8579.0	7689.1	7387.8	7086.2	6647.9	6209.6
67.5°	8785.6	7782.7	6780.1	6533.3	6286.4	5899.9	5513.6
70°	7759.3	6907.7	6055.8	5879.4	5703.0	5275.2	4847.3
72.5°	6567.8	5947.9	5328.0	5253.3	5178.6	4669.6	4160.8
75°	5041.0	4847.6	4654.5	4604.6	4554.7	3980.9	3406.9
77.5°	3741.4	3612.4	3483.8	3371.8	3259.9	2762.7	2265.9
80°	2329.3	2233.0	2136.4	2121.8	2107.3	1718.6	1329.9
82.5°	1275.9	1216.8	1157.8	1124.8	1091.9	878.3	664.9
85°	493.6	431.6	369.6	315.9	262.2	206.6	151.1
87.5°	14.0	13.8	13.5	13.2	12.9	12.4	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ


Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.02

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.71

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

Summary

$R_f = 67.9$
 $R_g = 98.6$
 $CIE R_a = 71.1$
 $R_9 = -27.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)