

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1385699

Luminaire Tested: **VAL-T-SB2A-730-U-SLL**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been
influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P1385699
Test Lab: INNOVATION CENTER(G1)
Issue Date: 02/18/2026
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: VAL-T-SB2A-730-U-SLL
Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 25 SQUARE 58W 70CRI
3000K FIXTURE w/ 90° Spill Light Eliminator LEFT OPTIC
Light Source: (52) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
a	good	reflector
b	good	lens
c	good	housing
d	good	cord

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7889.7 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 58
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.98
Total Harmonic Distortion (THDi): 9.0%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 4.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P1385699
CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

Luminous Intensity Polar Plot



REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2122.5	0.0	2122.5
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	5767.2	0.0	5767.2
	% Fixture	73.1	0.0	73.1
Total	Lumens	7889.7	0.0	7889.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	1.6
10°-20°	380.7	4.8
20°-30°	589.1	7.5
30°-40°	730.9	9.3
40°-50°	1068.9	13.5
50°-60°	1674.3	21.2
60°-70°	1986.6	25.2
70°-80°	1158.7	14.7
80°-90°	176.3	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7889.7	100.0
0°-180°	7889.7	100.0

Coefficient of Utilization



REPORT NUMBER: P1385699


CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	593.0	7.5			
FM	(30°-60°)	2400.2	30.4			
FH	(60°-80°)	2629.8	33.3			G2/5000
FVH	(80°-90°)	144.2	1.8			G2/225
BL	(0°-30°)	501.1	6.4	B2/1000		
BM	(30°-60°)	1073.9	13.6	B2/2500		
BH	(60°-80°)	515.5	6.5	B2/1000		G2/1000
BVH	(80°-90°)	32.1	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2

Type IV Short





REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0
2.5°	1359.3	1364.1	1369.0	1374.2	1379.6	1382.7	1385.8	1389.0	1392.1	1395.0	1392.1
5°	1451.9	1473.7	1495.4	1510.0	1524.7	1535.9	1547.1	1553.4	1560.0	1561.0	1560.0
7.5°	1545.5	1571.4	1597.2	1619.6	1642.0	1656.3	1670.6	1678.8	1687.3	1690.2	1687.3
10°	1604.4	1634.7	1665.1	1686.8	1708.6	1721.9	1735.0	1741.6	1748.1	1750.0	1748.1
12.5°	1634.3	1663.4	1692.5	1709.3	1725.9	1734.4	1742.7	1745.8	1748.5	1746.2	1748.5
15°	1648.7	1665.9	1682.9	1690.0	1697.0	1692.9	1688.7	1682.7	1676.7	1672.9	1676.7
17.5°	1652.6	1658.6	1664.8	1651.8	1639.1	1615.9	1592.8	1575.4	1558.1	1545.5	1558.1
20°	1665.1	1655.5	1645.9	1611.5	1577.4	1533.9	1490.5	1461.4	1432.1	1414.3	1432.1
22.5°	1678.7	1651.4	1624.2	1566.6	1508.9	1449.4	1390.2	1356.6	1323.2	1304.3	1323.2
25°	1699.9	1653.2	1606.3	1528.3	1450.6	1380.7	1311.1	1274.6	1238.3	1217.5	1238.3
27.5°	1730.8	1659.4	1588.0	1491.5	1395.0	1319.4	1243.6	1208.8	1174.1	1155.8	1174.1
30°	1774.2	1679.4	1584.5	1469.1	1353.5	1274.4	1195.3	1161.4	1127.2	1107.5	1127.2
32.5°	1827.2	1707.6	1588.0	1458.7	1329.4	1248.8	1168.3	1135.7	1103.3	1086.3	1103.3
35°	1916.9	1765.5	1614.0	1470.7	1327.5	1252.6	1178.0	1154.0	1130.3	1121.0	1130.3
37.5°	2030.8	1853.9	1676.7	1529.1	1381.5	1330.6	1279.6	1279.6	1279.6	1287.0	1279.6
40°	2198.7	1999.9	1801.2	1661.5	1522.0	1518.9	1516.2	1548.6	1581.2	1595.7	1581.2
42.5°	2434.1	2223.9	2014.0	1901.3	1788.6	1856.2	1923.7	2017.5	2111.2	2172.6	2111.2
45°	2726.4	2521.8	2317.3	2238.6	2160.1	2310.4	2460.5	2626.2	2792.0	2909.7	2792.0
47.5°	3006.1	2834.0	2661.7	2616.8	2572.0	2821.9	3071.7	3314.7	3557.6	3700.8	3557.6
50°	3330.3	3175.6	3020.6	3011.9	3003.2	3336.1	3668.9	3982.5	4296.0	4470.6	4296.0
52.5°	3746.1	3576.1	3405.9	3412.9	3419.4	3814.8	4210.1	4589.3	4968.4	5165.2	4968.4
55°	4242.9	4029.7	3816.5	3815.4	3814.2	4268.4	4723.0	5188.8	5654.9	5917.7	5654.9
57.5°	4749.4	4549.7	4350.0	4302.6	4254.9	4729.9	5204.8	5719.2	6233.8	6510.1	6233.8
60°	5129.5	5019.6	4909.6	4833.6	4757.7	5245.5	5733.5	6264.9	6796.0	7071.6	6796.0
62.5°	4972.3	5168.9	5365.5	5359.9	5354.3	5880.9	6407.4	6960.1	7513.0	7760.4	7513.0
65°	4441.7	4755.2	5068.8	5284.5	5500.0	6136.5	6772.9	7348.7	7924.4	8177.2	7924.4
67.5°	3943.9	4220.2	4496.7	4673.2	4849.8	5567.0	6284.3	6937.7	7591.0	7851.1	7591.0
70°	3467.3	3773.3	4079.3	4205.5	4331.7	4941.0	5550.2	6067.1	6583.8	6685.7	6583.8
72.5°	2976.2	3340.1	3704.2	3757.7	3811.1	4254.5	4697.9	4973.3	5248.6	5026.3	5248.6
75°	2436.9	2847.5	3257.9	3293.6	3329.3	3467.5	3605.8	3675.9	3746.1	3619.7	3746.1
77.5°	1620.8	1976.2	2331.8	2411.9	2491.9	2584.0	2676.2	2671.4	2666.6	2489.0	2666.6
80°	951.2	1229.3	1507.3	1517.7	1528.2	1597.2	1666.1	1736.5	1807.0	1694.1	1807.0
82.5°	475.6	628.2	781.1	804.6	828.1	870.4	912.6	932.3	952.2	856.7	952.2
85°	108.1	147.8	187.5	225.9	264.3	308.7	353.1	348.1	343.1	289.4	343.1
87.5°	8.7	8.9	9.3	9.5	9.6	9.8	10.0	10.6	11.2	11.6	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0
2.5°	1389.0	1385.8	1382.7	1379.6	1374.2	1369.0	1364.1	1359.3	1347.0	1334.8	1323.6
5°	1553.4	1547.1	1535.9	1524.7	1510.0	1495.4	1473.7	1451.9	1430.1	1408.5	1385.8
7.5°	1678.8	1670.6	1656.3	1642.0	1619.6	1597.2	1571.4	1545.5	1508.9	1472.2	1437.7
10°	1741.6	1735.0	1721.9	1708.6	1686.8	1665.1	1634.7	1604.4	1560.6	1516.6	1473.7
12.5°	1745.8	1742.7	1734.4	1725.9	1709.3	1692.5	1663.4	1634.3	1590.7	1547.1	1499.0
15°	1682.7	1688.7	1692.9	1697.0	1690.0	1682.9	1665.9	1648.7	1604.6	1560.6	1511.8
17.5°	1575.4	1592.8	1615.9	1639.1	1651.8	1664.8	1658.6	1652.6	1611.3	1570.2	1518.1
20°	1461.4	1490.5	1533.9	1577.4	1611.5	1645.9	1655.5	1665.1	1623.5	1581.8	1525.8
22.5°	1356.6	1390.2	1449.4	1508.9	1566.6	1624.2	1651.4	1678.7	1640.5	1602.4	1540.9
25°	1274.6	1311.1	1380.7	1450.6	1528.3	1606.3	1653.2	1699.9	1666.9	1633.9	1566.7
27.5°	1208.8	1243.6	1319.4	1395.0	1491.5	1588.0	1659.4	1730.8	1705.5	1680.2	1604.6
30°	1161.4	1195.3	1274.4	1353.5	1469.1	1584.5	1679.4	1774.2	1754.3	1734.6	1649.3
32.5°	1135.7	1168.3	1248.8	1329.4	1458.7	1588.0	1707.6	1827.2	1814.9	1802.5	1702.0
35°	1154.0	1178.0	1252.6	1327.5	1470.7	1614.0	1765.5	1916.9	1901.5	1886.1	1758.0
37.5°	1279.6	1279.6	1330.6	1381.5	1529.1	1676.7	1853.9	2030.8	2012.5	1994.1	1826.3
40°	1548.6	1516.2	1518.9	1522.0	1661.5	1801.2	1999.9	2198.7	2162.6	2126.3	1904.4
42.5°	2017.5	1923.7	1856.2	1788.6	1901.3	2014.0	2223.9	2434.1	2357.6	2281.0	1990.8
45°	2626.2	2460.5	2310.4	2160.1	2238.6	2317.3	2521.8	2726.4	2603.8	2481.3	2108.2
47.5°	3314.7	3071.7	2821.9	2572.0	2616.8	2661.7	2834.0	3006.1	2851.0	2695.9	2228.8
50°	3982.5	3668.9	3336.1	3003.2	3011.9	3020.6	3175.6	3330.3	3120.0	2909.7	2333.9
52.5°	4589.3	4210.1	3814.8	3419.4	3412.9	3405.9	3576.1	3746.1	3412.1	3077.9	2383.7
55°	5188.8	4723.0	4268.4	3814.2	3815.4	3816.5	4029.7	4242.9	3705.6	3168.2	2370.6
57.5°	5719.2	5204.8	4729.9	4254.9	4302.6	4350.0	4549.7	4749.4	3952.0	3154.7	2299.0
60°	6264.9	5733.5	5245.5	4757.7	4833.6	4909.6	5019.6	5129.5	4062.3	2995.0	2127.5
62.5°	6960.1	6407.4	5880.9	5354.3	5359.9	5365.5	5168.9	4972.3	3817.5	2662.7	1846.3
65°	7348.7	6772.9	6136.5	5500.0	5284.5	5068.8	4755.2	4441.7	3292.7	2143.7	1448.3
67.5°	6937.7	6284.3	5567.0	4849.8	4673.2	4496.7	4220.2	3943.9	2827.9	1711.8	1127.0
70°	6067.1	5550.2	4941.0	4331.7	4205.5	4079.3	3773.3	3467.3	2402.4	1337.5	863.6
72.5°	4973.3	4697.9	4254.5	3811.1	3757.7	3704.2	3340.1	2976.2	1994.9	1013.4	649.3
75°	3675.9	3605.8	3467.5	3329.3	3293.6	3257.9	2847.5	2436.9	1592.8	748.6	481.2
77.5°	2671.4	2676.2	2584.0	2491.9	2411.9	2331.8	1976.2	1620.8	1045.0	469.3	311.0
80°	1736.5	1666.1	1597.2	1528.2	1517.7	1507.3	1229.3	951.2	599.1	247.0	171.9
82.5°	932.3	912.6	870.4	828.1	804.6	781.1	628.2	475.6	300.2	125.0	92.4
85°	348.1	353.1	308.7	264.3	225.9	187.5	147.8	108.1	71.4	34.7	29.3
87.5°	10.6	10.0	9.8	9.6	9.5	9.3	8.9	8.7	8.5	8.1	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0
2.5°	1312.4	1301.2	1289.9	1279.1	1268.1	1257.1	1247.4	1237.0	1226.8	1218.7	1210.8
5°	1363.2	1341.0	1318.8	1297.8	1276.9	1255.1	1236.4	1217.9	1199.8	1184.7	1169.7
7.5°	1403.1	1372.3	1341.4	1313.8	1286.0	1257.1	1234.5	1211.9	1189.5	1170.0	1150.4
10°	1430.7	1392.7	1354.5	1322.7	1290.8	1260.0	1235.8	1212.1	1188.6	1168.5	1148.4
12.5°	1451.0	1408.3	1365.7	1330.6	1295.7	1261.9	1238.3	1218.7	1199.2	1185.1	1171.2
15°	1462.9	1417.0	1370.9	1331.3	1291.8	1254.2	1233.3	1220.6	1207.9	1206.7	1205.5
17.5°	1466.0	1413.5	1361.3	1315.1	1269.2	1225.2	1207.5	1205.7	1204.0	1223.1	1242.2
20°	1469.9	1408.3	1346.8	1286.2	1225.6	1167.3	1156.1	1167.1	1178.0	1215.4	1252.6
22.5°	1479.5	1404.3	1329.0	1253.0	1177.0	1107.5	1096.9	1113.1	1129.1	1178.0	1226.8
25°	1499.6	1403.9	1308.2	1213.5	1118.7	1039.0	1038.1	1055.6	1073.2	1118.3	1163.5
27.5°	1529.1	1407.6	1286.0	1172.9	1059.7	978.3	983.1	999.9	1016.8	1050.4	1084.0
30°	1563.9	1415.5	1267.3	1137.6	1008.2	929.0	934.3	947.4	960.5	984.8	1009.1
32.5°	1601.5	1424.3	1247.4	1106.8	966.3	893.4	893.4	898.9	904.5	920.4	936.2
35°	1630.0	1422.2	1214.6	1071.6	928.5	872.1	860.2	855.5	850.9	861.3	871.7
37.5°	1658.4	1416.2	1174.1	1032.7	891.4	847.0	824.3	811.9	799.2	804.2	808.8
40°	1682.5	1402.7	1123.0	986.2	849.4	814.2	785.7	767.2	748.6	748.3	747.7
42.5°	1700.3	1379.4	1058.3	930.8	803.1	778.5	743.2	719.7	696.2	693.7	691.1
45°	1735.0	1363.4	991.8	874.4	757.3	735.1	700.0	675.7	651.8	647.9	644.1
47.5°	1761.6	1344.7	927.7	818.5	709.7	684.0	651.2	630.6	609.7	607.4	604.9
50°	1758.2	1312.8	867.3	768.7	669.9	634.8	602.4	585.4	568.2	571.1	574.0
52.5°	1689.3	1247.6	806.1	723.9	642.1	597.2	562.4	549.7	536.8	545.9	554.7
55°	1572.9	1161.2	749.0	686.5	623.6	578.8	537.9	523.7	509.4	522.1	534.9
57.5°	1443.3	1070.7	698.1	654.9	611.6	574.0	523.9	503.8	483.9	496.7	509.4
60°	1260.0	956.3	652.6	622.3	592.0	562.4	512.3	487.2	462.1	470.6	478.9
62.5°	1030.0	811.2	592.4	575.4	558.6	546.0	498.2	465.4	432.6	433.7	434.5
65°	752.9	637.5	521.9	518.3	514.8	511.3	471.8	436.5	401.3	397.5	393.6
67.5°	542.2	487.4	432.6	442.8	453.0	458.3	431.2	400.2	368.9	361.0	353.1
70°	389.8	370.5	351.2	366.4	381.7	380.1	367.0	348.5	329.9	324.9	319.9
72.5°	285.2	284.8	284.6	296.2	307.8	292.3	300.6	296.4	292.3	288.7	285.2
75°	213.8	212.4	211.3	225.0	238.9	245.0	250.4	248.1	246.0	243.3	240.8
77.5°	152.8	154.0	154.7	169.8	184.8	202.6	203.6	198.5	193.3	190.6	187.5
80°	96.9	98.0	98.8	114.6	130.2	155.3	154.4	148.2	141.8	139.7	137.4
82.5°	59.8	60.0	60.2	67.9	75.6	89.7	93.6	93.6	93.6	92.2	90.7
85°	24.1	25.3	26.6	31.6	36.7	44.4	46.7	47.1	47.3	45.2	42.8
87.5°	7.7	8.1	8.7	9.6	10.6	11.6	13.5	14.7	15.8	17.0	17.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0
2.5°	1203.8	1196.7	1188.4	1179.9	1173.9	1167.7	1163.7	1159.6	1157.7	1155.8	1154.2
5°	1157.3	1144.6	1133.4	1122.0	1113.1	1104.1	1096.7	1089.2	1086.1	1082.8	1080.7
7.5°	1133.8	1117.2	1103.3	1089.2	1075.9	1062.8	1054.3	1045.8	1040.8	1035.7	1032.1
10°	1130.9	1113.3	1095.0	1076.7	1062.0	1047.3	1034.6	1022.2	1015.1	1008.2	1004.3
12.5°	1155.0	1138.8	1117.0	1095.0	1075.1	1055.4	1039.8	1024.2	1015.3	1006.8	1001.0
15°	1199.9	1194.4	1174.1	1153.8	1126.4	1098.8	1076.5	1053.9	1041.5	1028.8	1021.7
17.5°	1253.2	1264.2	1250.1	1235.8	1197.2	1158.7	1125.3	1092.1	1074.0	1055.8	1049.4
20°	1282.3	1312.1	1310.5	1309.2	1258.8	1208.2	1164.4	1120.6	1096.3	1072.4	1062.8
22.5°	1269.6	1312.4	1323.4	1334.2	1284.8	1235.3	1181.2	1127.2	1098.7	1069.9	1060.8
25°	1209.6	1255.7	1276.2	1296.6	1255.9	1215.2	1162.7	1110.4	1080.3	1050.0	1040.8
27.5°	1121.0	1158.1	1181.0	1204.0	1179.1	1154.2	1111.8	1069.3	1042.7	1015.9	1006.0
30°	1034.2	1059.3	1077.6	1095.9	1079.5	1063.1	1032.7	1002.4	982.5	962.8	956.6
32.5°	954.9	973.4	983.7	993.7	981.0	968.2	948.2	928.1	915.7	903.4	899.3
35°	886.8	902.0	909.8	917.5	906.9	896.2	878.3	860.6	851.7	842.8	839.5
37.5°	821.8	834.5	845.5	856.7	849.0	841.3	826.0	810.8	800.4	789.5	783.8
40°	760.0	772.2	786.1	799.8	798.4	796.9	782.4	767.9	752.9	738.0	730.1
42.5°	703.3	715.5	730.1	744.8	747.7	750.6	738.6	726.5	709.1	691.7	679.6
45°	654.5	665.3	681.3	697.5	704.3	711.0	700.2	689.2	669.7	650.2	635.8
47.5°	615.9	627.1	644.8	662.8	669.9	677.3	669.9	662.8	646.0	629.0	616.3
50°	586.2	598.1	612.0	626.1	639.4	652.6	651.2	649.9	636.5	623.2	611.3
52.5°	565.7	576.9	591.4	605.9	619.8	633.8	636.0	638.3	628.6	619.0	608.6
55°	548.2	561.5	575.0	588.5	601.6	614.5	617.4	620.3	613.4	606.2	598.5
57.5°	523.9	538.3	551.8	565.3	580.6	595.8	598.1	600.5	593.1	585.6	579.8
60°	493.8	508.4	522.5	536.4	551.8	567.3	570.4	573.4	567.7	561.9	556.5
62.5°	451.3	467.9	479.5	491.1	505.7	520.6	525.0	529.6	526.9	524.4	518.3
65°	409.4	425.5	434.5	443.8	456.5	469.3	473.7	478.1	476.8	475.6	471.2
67.5°	367.8	382.4	389.9	397.5	406.2	414.8	419.9	424.9	422.4	419.7	415.0
70°	331.9	343.8	350.4	357.0	363.9	370.8	373.5	376.3	372.4	368.5	358.1
72.5°	294.2	303.3	308.9	314.5	321.1	327.6	329.2	330.9	324.9	318.8	306.6
75°	247.7	254.7	258.9	263.4	270.1	276.9	279.8	282.7	274.2	265.9	253.0
77.5°	193.9	200.3	204.3	208.4	214.0	219.6	220.3	221.5	214.2	206.8	199.1
80°	142.0	146.6	148.2	149.5	154.2	158.6	158.6	158.6	153.2	147.6	143.7
82.5°	89.7	88.8	86.8	84.9	89.5	94.2	95.7	97.4	94.9	92.6	88.4
85°	40.1	37.0	36.5	35.7	35.5	35.1	36.5	37.6	37.0	36.7	35.1
87.5°	18.9	19.7	19.1	18.3	17.6	17.0	15.4	13.9	12.7	11.6	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0
2.5°	1152.9	1151.9	1152.9	1154.2	1155.8	1157.7	1159.6	1163.7	1167.7	1173.9	1179.9
5°	1078.6	1076.7	1078.6	1080.7	1082.8	1086.1	1089.2	1096.7	1104.1	1113.1	1122.0
7.5°	1028.4	1026.5	1028.4	1032.1	1035.7	1040.8	1045.8	1054.3	1062.8	1075.9	1089.2
10°	1000.4	997.5	1000.4	1004.3	1008.2	1015.1	1022.2	1034.6	1047.3	1062.0	1076.7
12.5°	995.2	991.8	995.2	1001.0	1006.8	1015.3	1024.2	1039.8	1055.4	1075.1	1095.0
15°	1014.5	1009.1	1014.5	1021.7	1028.8	1041.5	1053.9	1076.5	1098.8	1126.4	1153.8
17.5°	1042.9	1040.0	1042.9	1049.4	1055.8	1074.0	1092.1	1125.3	1158.7	1197.2	1235.8
20°	1053.1	1049.6	1053.1	1062.8	1072.4	1096.3	1120.6	1164.4	1208.2	1258.8	1309.2
22.5°	1051.6	1047.7	1051.6	1060.8	1069.9	1098.7	1127.2	1181.2	1235.3	1284.8	1334.2
25°	1031.3	1028.4	1031.3	1040.8	1050.0	1080.3	1110.4	1162.7	1215.2	1255.9	1296.6
27.5°	996.0	989.8	996.0	1006.0	1015.9	1042.7	1069.3	1111.8	1154.2	1179.1	1204.0
30°	950.3	947.4	950.3	956.6	962.8	982.5	1002.4	1032.7	1063.1	1079.5	1095.9
32.5°	895.3	893.4	895.3	899.3	903.4	915.7	928.1	948.2	968.2	981.0	993.7
35°	836.4	833.5	836.4	839.5	842.8	851.7	860.6	878.3	896.2	906.9	917.5
37.5°	778.0	773.7	778.0	783.8	789.5	800.4	810.8	826.0	841.3	849.0	856.7
40°	722.0	717.8	722.0	730.1	738.0	752.9	767.9	782.4	796.9	798.4	799.8
42.5°	667.6	659.9	667.6	679.6	691.7	709.1	726.5	738.6	750.6	747.7	744.8
45°	621.3	611.6	621.3	635.8	650.2	669.7	689.2	700.2	711.0	704.3	697.5
47.5°	603.5	594.3	603.5	616.3	629.0	646.0	662.8	669.9	677.3	669.9	662.8
50°	599.1	590.4	599.1	611.3	623.2	636.5	649.9	651.2	652.6	639.4	626.1
52.5°	598.1	590.4	598.1	608.6	619.0	628.6	638.3	636.0	633.8	619.8	605.9
55°	590.8	584.6	590.8	598.5	606.2	613.4	620.3	617.4	614.5	601.6	588.5
57.5°	574.0	571.1	574.0	579.8	585.6	593.1	600.5	598.1	595.8	580.6	565.3
60°	550.9	546.0	550.9	556.5	561.9	567.7	573.4	570.4	567.3	551.8	536.4
62.5°	512.3	505.5	512.3	518.3	524.4	526.9	529.6	525.0	520.6	505.7	491.1
65°	466.9	459.2	466.9	471.2	475.6	476.8	478.1	473.7	469.3	456.5	443.8
67.5°	410.6	409.1	410.6	415.0	419.7	422.4	424.9	419.9	414.8	406.2	397.5
70°	347.7	335.7	347.7	358.1	368.5	372.4	376.3	373.5	370.8	363.9	357.0
72.5°	294.2	281.7	294.2	306.6	318.8	324.9	330.9	329.2	327.6	321.1	314.5
75°	240.2	231.5	240.2	253.0	265.9	274.2	282.7	279.8	276.9	270.1	263.4
77.5°	191.4	187.2	191.4	199.1	206.8	214.2	221.5	220.3	219.6	214.0	208.4
80°	139.9	137.0	139.9	143.7	147.6	153.2	158.6	158.6	158.6	154.2	149.5
82.5°	83.9	81.0	83.9	88.4	92.6	94.9	97.4	95.7	94.2	89.5	84.9
85°	33.8	32.8	33.8	35.1	36.7	37.0	37.6	36.5	35.1	35.5	35.7
87.5°	10.0	9.6	10.0	10.8	11.6	12.7	13.9	15.4	17.0	17.6	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0
2.5°	1188.4	1196.7	1203.8	1210.8	1218.7	1226.8	1237.0	1247.4	1257.1	1268.1	1279.1
5°	1133.4	1144.6	1157.3	1169.7	1184.7	1199.8	1217.9	1236.4	1255.1	1276.9	1297.8
7.5°	1103.3	1117.2	1133.8	1150.4	1170.0	1189.5	1211.9	1234.5	1257.1	1286.0	1313.8
10°	1095.0	1113.3	1130.9	1148.4	1168.5	1188.6	1212.1	1235.8	1260.0	1290.8	1322.7
12.5°	1117.0	1138.8	1155.0	1171.2	1185.1	1199.2	1218.7	1238.3	1261.9	1295.7	1330.6
15°	1174.1	1194.4	1199.9	1205.5	1206.7	1207.9	1220.6	1233.3	1254.2	1291.8	1331.3
17.5°	1250.1	1264.2	1253.2	1242.2	1223.1	1204.0	1205.7	1207.5	1225.2	1269.2	1315.1
20°	1310.5	1312.1	1282.3	1252.6	1215.4	1178.0	1167.1	1156.1	1167.3	1225.6	1286.2
22.5°	1323.4	1312.4	1269.6	1226.8	1178.0	1129.1	1113.1	1096.9	1107.5	1177.0	1253.0
25°	1276.2	1255.7	1209.6	1163.5	1118.3	1073.2	1055.6	1038.1	1039.0	1118.7	1213.5
27.5°	1181.0	1158.1	1121.0	1084.0	1050.4	1016.8	999.9	983.1	978.3	1059.7	1172.9
30°	1077.6	1059.3	1034.2	1009.1	984.8	960.5	947.4	934.3	929.0	1008.2	1137.6
32.5°	983.7	973.4	954.9	936.2	920.4	904.5	898.9	893.4	893.4	966.3	1106.8
35°	909.8	902.0	886.8	871.7	861.3	850.9	855.5	860.2	872.1	928.5	1071.6
37.5°	845.5	834.5	821.8	808.8	804.2	799.2	811.9	824.3	847.0	891.4	1032.7
40°	786.1	772.2	760.0	747.7	748.3	748.6	767.2	785.7	814.2	849.4	986.2
42.5°	730.1	715.5	703.3	691.1	693.7	696.2	719.7	743.2	778.5	803.1	930.8
45°	681.3	665.3	654.5	644.1	647.9	651.8	675.7	700.0	735.1	757.3	874.4
47.5°	644.8	627.1	615.9	604.9	607.4	609.7	630.6	651.2	684.0	709.7	818.5
50°	612.0	598.1	586.2	574.0	571.1	568.2	585.4	602.4	634.8	669.9	768.7
52.5°	591.4	576.9	565.7	554.7	545.9	536.8	549.7	562.4	597.2	642.1	723.9
55°	575.0	561.5	548.2	534.9	522.1	509.4	523.7	537.9	578.8	623.6	686.5
57.5°	551.8	538.3	523.9	509.4	496.7	483.9	503.8	523.9	574.0	611.6	654.9
60°	522.5	508.4	493.8	478.9	470.6	462.1	487.2	512.3	562.4	592.0	622.3
62.5°	479.5	467.9	451.3	434.5	433.7	432.6	465.4	498.2	546.0	558.6	575.4
65°	434.5	425.5	409.4	393.6	397.5	401.3	436.5	471.8	511.3	514.8	518.3
67.5°	389.9	382.4	367.8	353.1	361.0	368.9	400.2	431.2	458.3	453.0	442.8
70°	350.4	343.8	331.9	319.9	324.9	329.9	348.5	367.0	380.1	381.7	366.4
72.5°	308.9	303.3	294.2	285.2	288.7	292.3	296.4	300.6	292.3	307.8	296.2
75°	258.9	254.7	247.7	240.8	243.3	246.0	248.1	250.4	245.0	238.9	225.0
77.5°	204.3	200.3	193.9	187.5	190.6	193.3	198.5	203.6	202.6	184.8	169.8
80°	148.2	146.6	142.0	137.4	139.7	141.8	148.2	154.4	155.3	130.2	114.6
82.5°	86.8	88.8	89.7	90.7	92.2	93.6	93.6	93.6	89.7	75.6	67.9
85°	36.5	37.0	40.1	42.8	45.2	47.3	47.1	46.7	44.4	36.7	31.6
87.5°	19.1	19.7	18.9	17.8	17.0	15.8	14.7	13.5	11.6	10.6	9.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1385699

CATALOG NUMBER: VAL-T-SB2A-730-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0	1258.0
2.5°	1289.9	1301.2	1312.4	1323.6	1334.8	1347.0	1359.3
5°	1318.8	1341.0	1363.2	1385.8	1408.5	1430.1	1451.9
7.5°	1341.4	1372.3	1403.1	1437.7	1472.2	1508.9	1545.5
10°	1354.5	1392.7	1430.7	1473.7	1516.6	1560.6	1604.4
12.5°	1365.7	1408.3	1451.0	1499.0	1547.1	1590.7	1634.3
15°	1370.9	1417.0	1462.9	1511.8	1560.6	1604.6	1648.7
17.5°	1361.3	1413.5	1466.0	1518.1	1570.2	1611.3	1652.6
20°	1346.8	1408.3	1469.9	1525.8	1581.8	1623.5	1665.1
22.5°	1329.0	1404.3	1479.5	1540.9	1602.4	1640.5	1678.7
25°	1308.2	1403.9	1499.6	1566.7	1633.9	1666.9	1699.9
27.5°	1286.0	1407.6	1529.1	1604.6	1680.2	1705.5	1730.8
30°	1267.3	1415.5	1563.9	1649.3	1734.6	1754.3	1774.2
32.5°	1247.4	1424.3	1601.5	1702.0	1802.5	1814.9	1827.2
35°	1214.6	1422.2	1630.0	1758.0	1886.1	1901.5	1916.9
37.5°	1174.1	1416.2	1658.4	1826.3	1994.1	2012.5	2030.8
40°	1123.0	1402.7	1682.5	1904.4	2126.3	2162.6	2198.7
42.5°	1058.3	1379.4	1700.3	1990.8	2281.0	2357.6	2434.1
45°	991.8	1363.4	1735.0	2108.2	2481.3	2603.8	2726.4
47.5°	927.7	1344.7	1761.6	2228.8	2695.9	2851.0	3006.1
50°	867.3	1312.8	1758.2	2333.9	2909.7	3120.0	3330.3
52.5°	806.1	1247.6	1689.3	2383.7	3077.9	3412.1	3746.1
55°	749.0	1161.2	1572.9	2370.6	3168.2	3705.6	4242.9
57.5°	698.1	1070.7	1443.3	2299.0	3154.7	3952.0	4749.4
60°	652.6	956.3	1260.0	2127.5	2995.0	4062.3	5129.5
62.5°	592.4	811.2	1030.0	1846.3	2662.7	3817.5	4972.3
65°	521.9	637.5	752.9	1448.3	2143.7	3292.7	4441.7
67.5°	432.6	487.4	542.2	1127.0	1711.8	2827.9	3943.9
70°	351.2	370.5	389.8	863.6	1337.5	2402.4	3467.3
72.5°	284.6	284.8	285.2	649.3	1013.4	1994.9	2976.2
75°	211.3	212.4	213.8	481.2	748.6	1592.8	2436.9
77.5°	154.7	154.0	152.8	311.0	469.3	1045.0	1620.8
80°	98.8	98.0	96.9	171.9	247.0	599.1	951.2
82.5°	60.2	60.0	59.8	92.4	125.0	300.2	475.6
85°	26.6	25.3	24.1	29.3	34.7	71.4	108.1
87.5°	8.7	8.1	7.7	7.9	8.1	8.5	8.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-730-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 3000K CCT 26 LEDS

Spectral Parameters

CCT (K): 2985
 CIE u' : 0.2504
 CIE v' : 0.5243
 Duv: 0.0019
 CIE x: 0.4408
 CIE y: 0.4101
 CIE z: 0.1491
 Peak Wavelength (nm): 595
 Dominant Wavelength (nm): 582
 Purity: 55.41818
 R_f: 73.8
 R_g: 94.4

CRI (Ra): 70.8
 R1: 66.3
 R2: 80.6
 R3: 94.5
 R4: 68.2
 R5: 66.5
 R6: 74.7
 R7: 76.2
 R8: 39.6
 R9: -43.2
 R10: 57.6
 R11: 64.8
 R12: 53.5
 R13: 68.7
 R14: 97.0
 R15: 56.4



Test Conditions


Stabilization Time: 36M
 Operation Time: 1H 36M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.19

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.13


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	142	NR	620	803	NR	750	17	NR	880	0	NR
365	0	NR	495	189	NR	625	734	NR	755	15	NR	885	0	NR
370	0	NR	500	240	NR	630	670	NR	760	13	NR	890	0	NR
375	0	NR	505	290	NR	635	600	NR	765	11	NR	895	0	NR
380	0	NR	510	335	NR	640	535	NR	770	9	NR	900	0	NR
385	0	NR	515	375	NR	645	473	NR	775	8	NR	905	0	NR
390	1	NR	520	408	NR	650	415	NR	780	7	NR	910	0	NR
395	2	NR	525	434	NR	655	362	NR	785	6	NR	915	0	NR
400	4	NR	530	461	NR	660	313	NR	790	5	NR	920	0	NR
405	8	NR	535	486	NR	665	271	NR	795	4	NR	925	0	NR
410	16	NR	540	514	NR	670	231	NR	800	4	NR	930	0	NR
415	33	NR	545	549	NR	675	198	NR	805	3	NR	935	0	NR
420	69	NR	550	591	NR	680	169	NR	810	3	NR	940	0	NR
425	131	NR	555	640	NR	685	144	NR	815	2	NR	945	0	NR
430	227	NR	560	695	NR	690	123	NR	820	2	NR	950	0	NR
435	369	NR	565	757	NR	695	104	NR	825	2	NR	955	0	NR
440	517	NR	570	822	NR	700	88	NR	830	2	NR	960	0	NR
445	498	NR	575	882	NR	705	75	NR	835	1	NR	965	0	NR
450	315	NR	580	935	NR	710	63	NR	840	1	NR	970	0	NR
455	204	NR	585	972	NR	715	54	NR	845	1	NR	975	0	NR
460	145	NR	590	996	NR	720	46	NR	850	1	NR	980	0	NR
465	100	NR	595	1000	NR	725	39	NR	855	1	NR	985	0	NR
470	78	NR	600	989	NR	730	33	NR	860	1	NR	990	0	NR
475	76	NR	605	960	NR	735	28	NR	865	1	NR	995	0	NR
480	83	NR	610	918	NR	740	24	NR	870	1	NR	1000	0	NR
485	105	NR	615	864	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-4





TM-30-18

Summary

$R_f = 73.8$
 $R_g = 94.4$
 $CIE R_a = 70.8$
 $R_g = -43.2$




Color Vector Graphics






Individual Sample Fidelity Index (R_{fi})



CES01 = 86	CES26 = 63	CES51 = 86	CES76 = 61
CES02 = 62	CES27 = 83	CES52 = 86	CES77 = 81
CES03 = 31	CES28 = 86	CES53 = 75	CES78 = 64
CES04 = 71	CES29 = 58	CES54 = 81	CES79 = 86
CES05 = 49	CES30 = 61	CES55 = 80	CES80 = 86
CES06 = 51	CES31 = 63	CES56 = 71	CES81 = 70
CES07 = 41	CES32 = 61	CES57 = 69	CES82 = 94
CES08 = 40	CES33 = 65	CES58 = 72	CES83 = 88
CES09 = 29	CES34 = 77	CES59 = 85	CES84 = 90
CES10 = 76	CES35 = 88	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 86	CES86 = 60
CES12 = 65	CES37 = 85	CES62 = 81	CES87 = 78
CES13 = 43	CES38 = 69	CES63 = 73	CES88 = 75
CES14 = 74	CES39 = 93	CES64 = 72	CES89 = 66
CES15 = 71	CES40 = 89	CES65 = 67	CES90 = 72
CES16 = 47	CES41 = 83	CES66 = 70	CES91 = 95
CES17 = 50	CES42 = 87	CES67 = 68	CES92 = 59
CES18 = 56	CES43 = 77	CES68 = 73	CES93 = 76
CES19 = 73	CES44 = 99	CES69 = 83	CES94 = 48
CES20 = 66	CES45 = 83	CES70 = 66	CES95 = 70
CES21 = 87	CES46 = 77	CES71 = 66	CES96 = 76
CES22 = 79	CES47 = 74	CES72 = 88	CES97 = 82
CES23 = 92	CES48 = 62	CES73 = 59	CES98 = 73
CES24 = 91	CES49 = 77	CES74 = 93	CES99 = 60
CES25 = 73	CES50 = 85	CES75 = 67	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)