

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1386100

Luminaire Tested: **VAL-T-SB6B-730-U-SLL-HSS**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



**Test Information**

Test Method: LM-79-08  
 Report Number: P1386100  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 02/18/2026  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: VAL-T-SB6B-730-U-SLL-HSS  
 Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 65 SQUARE 219W 70CRI 3000K FIXTURE w/ 90° Spill Light Eliminator LETT OPTIC OPTIC AND HOUSE SIDE SHIELD  
 Light Source: (156) 3000K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER

Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a                 | good             | reflector          |
| b                 | good             | lens               |
| c                 | good             | housing            |
| d                 | good             | cord               |

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 24882.5 lumens  
 Efficiency: N/A  
 Efficacy: 113.6 lumens/watt  
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
 IES Classification: Type III - Short  
 BUG Rating: B3 - U0 - G4

Input Watts (W): 219  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: 0.98  
 Total Harmonic Distortion (THDi): 8.7%  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 28.75 FT

REPORT NUMBER: P1386100  
 CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 15.7 fc  
 Type III - Short - N/A

REPORT NUMBER: P1386100  
CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P1386100  
 CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5597.2   | 0.0    | 5597.2  |
|                    | % Fixture | 22.5     | 0.0    | 22.5    |
| <b>Street Side</b> | Lumens    | 19285.3  | 0.0    | 19285.3 |
|                    | % Fixture | 77.5     | 0.0    | 77.5    |
| <b>Total</b>       | Lumens    | 24882.5  | 0.0    | 24882.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 413.2   | 1.7       |
| 10°-20°   | 1142.6  | 4.6       |
| 20°-30°   | 1636.6  | 6.6       |
| 30°-40°   | 2052.9  | 8.3       |
| 40°-50°   | 3372.2  | 13.6      |
| 50°-60°   | 6088.7  | 24.5      |
| 60°-70°   | 6759.4  | 27.2      |
| 70°-80°   | 3055.4  | 12.3      |
| 80°-90°   | 361.6   | 1.5       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 24882.5 | 100.0     |
| 0°-180°   | 24882.5 | 100.0     |




REPORT NUMBER: P1386100  
 CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|--------|-----------|-------------------------|------|----------|
|      |             |        |           | B                       | U    | G        |
| FL   | (0°-30°)    | 1797.5 | 7.2       |                         |      |          |
| FM   | (30°-60°)   | 8382.0 | 33.7      |                         |      |          |
| FH   | (60°-80°)   | 8795.2 | 35.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 310.5  | 1.2       |                         |      | G3/500   |
| BL   | (0°-30°)    | 1394.8 | 5.6       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 3131.8 | 12.6      | B3/5000                 |      |          |
| BH   | (60°-80°)   | 1019.6 | 4.1       | B3/2500                 |      | G3/2500  |
| BVH  | (80°-90°)   | 51.1   | 0.2       |                         |      | G1/100   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G4**  
 Type III Short





REPORT NUMBER: P1386100

CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 1°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4298.8  | 4298.8  | 4298.8  | 4298.8  | 4298.8  | 4298.8  | 4298.8  | 4298.8  | 4298.8  | 4298.8  | 4298.8  |
| 2.5°  | 4734.0  | 4795.1  | 4787.4  | 4871.4  | 4947.8  | 5001.2  | 5047.0  | 5031.8  | 4993.6  | 4917.2  | 4863.8  |
| 5°    | 5230.3  | 5276.1  | 5352.5  | 5512.8  | 5635.0  | 5741.9  | 5726.6  | 5741.9  | 5627.3  | 5512.8  | 5375.4  |
| 7.5°  | 5657.9  | 5711.3  | 5818.2  | 6047.3  | 6200.0  | 6329.8  | 6314.5  | 6268.7  | 6138.9  | 5948.0  | 5741.9  |
| 10°   | 5925.1  | 5963.3  | 6077.8  | 6337.4  | 6513.0  | 6619.9  | 6581.8  | 6505.4  | 6337.4  | 6146.5  | 5902.2  |
| 12.5° | 6039.6  | 6085.5  | 6184.7  | 6390.9  | 6505.4  | 6482.5  | 6467.2  | 6452.0  | 6368.0  | 6222.9  | 6001.5  |
| 15°   | 6054.9  | 6085.5  | 6161.8  | 6253.4  | 6207.6  | 6077.8  | 6047.3  | 6161.8  | 6268.7  | 6238.2  | 6054.9  |
| 17.5° | 6054.9  | 6100.7  | 6116.0  | 6024.4  | 5787.7  | 5551.0  | 5520.4  | 5711.3  | 6009.1  | 6245.8  | 6138.9  |
| 20°   | 6077.8  | 6100.7  | 6070.2  | 5772.4  | 5329.5  | 5069.9  | 5016.5  | 5253.2  | 5696.0  | 6161.8  | 6222.9  |
| 22.5° | 6108.4  | 6131.3  | 6001.5  | 5474.6  | 4955.4  | 4680.5  | 4650.0  | 4825.6  | 5344.8  | 6039.6  | 6314.5  |
| 25°   | 6169.4  | 6154.2  | 5955.7  | 5215.0  | 4627.1  | 4367.5  | 4321.7  | 4550.7  | 5054.7  | 5917.5  | 6467.2  |
| 27.5° | 6245.8  | 6177.1  | 5894.6  | 5001.2  | 4390.4  | 4115.5  | 4085.0  | 4306.4  | 4810.3  | 5764.8  | 6597.0  |
| 30°   | 6345.1  | 6276.3  | 5886.9  | 4833.2  | 4214.8  | 3939.9  | 3901.7  | 4146.1  | 4642.4  | 5657.9  | 6780.3  |
| 32.5° | 6482.5  | 6383.2  | 5894.6  | 4703.4  | 4115.5  | 3855.9  | 3833.0  | 4092.6  | 4573.6  | 5596.8  | 6971.2  |
| 35°   | 6665.8  | 6520.7  | 5925.1  | 4657.6  | 4146.1  | 3970.4  | 4023.9  | 4222.4  | 4642.4  | 5642.6  | 7284.2  |
| 37.5° | 6894.8  | 6757.4  | 6077.8  | 4756.9  | 4482.0  | 4604.2  | 4741.6  | 4818.0  | 4970.7  | 5856.4  | 7788.2  |
| 40°   | 7276.6  | 7085.7  | 6306.9  | 5077.6  | 5383.0  | 5955.7  | 6222.9  | 6192.4  | 5841.1  | 6345.1  | 8498.3  |
| 42.5° | 7811.1  | 7635.5  | 6772.6  | 5894.6  | 6887.2  | 8101.2  | 8551.7  | 8292.1  | 7230.8  | 7123.9  | 9666.5  |
| 45°   | 8628.1  | 8337.9  | 7398.8  | 7108.6  | 8704.4  | 10697.3 | 11712.8 | 10819.4 | 8994.6  | 8353.2  | 11331.0 |
| 47.5° | 9674.1  | 9384.0  | 8376.1  | 8322.6  | 10735.4 | 13904.2 | 15110.6 | 13354.4 | 10743.1 | 9964.3  | 13323.9 |
| 50°   | 11353.9 | 11033.2 | 9811.6  | 9559.6  | 12980.3 | 17103.4 | 18714.5 | 15881.7 | 12522.1 | 11674.6 | 15782.5 |
| 52.5° | 13659.8 | 13446.0 | 12086.9 | 10834.7 | 14988.4 | 20631.0 | 22020.7 | 18523.6 | 13896.5 | 13629.3 | 18462.5 |
| 55°   | 16874.4 | 16668.2 | 15049.5 | 12254.9 | 16889.6 | 24166.2 | 25288.6 | 20928.8 | 15095.3 | 15919.9 | 21264.7 |
| 57.5° | 20516.5 | 20860.1 | 19103.9 | 14148.5 | 18890.1 | 27014.2 | 28579.5 | 23112.5 | 16714.0 | 18981.7 | 24380.0 |
| 60°   | 22891.1 | 23975.3 | 23753.9 | 17454.6 | 21997.7 | 30557.1 | 32259.8 | 26036.9 | 19081.0 | 21234.2 | 24311.3 |
| 62.5° | 20829.5 | 21913.8 | 23608.8 | 21287.6 | 24990.8 | 33764.0 | 35199.4 | 29114.0 | 21432.7 | 19439.9 | 20417.2 |
| 65°   | 17676.1 | 19027.6 | 20814.2 | 18493.1 | 24464.0 | 33863.2 | 35336.9 | 29228.5 | 19997.3 | 14369.9 | 14476.8 |
| 67.5° | 15232.7 | 16431.5 | 18630.5 | 15736.7 | 21684.7 | 30839.6 | 32000.2 | 26075.1 | 16530.8 | 9529.0  | 9445.1  |
| 70°   | 12713.0 | 13812.5 | 16591.8 | 14011.1 | 18997.0 | 26579.0 | 25578.8 | 21921.4 | 13972.9 | 6329.8  | 5245.6  |
| 72.5° | 10834.7 | 11850.2 | 14744.1 | 12590.9 | 15072.4 | 21539.6 | 17630.3 | 18187.7 | 11369.2 | 4023.9  | 3573.4  |
| 75°   | 8964.0  | 9895.5  | 12537.4 | 11399.7 | 12468.7 | 13438.4 | 12186.2 | 12919.2 | 9368.7  | 3413.0  | 2756.4  |
| 77.5° | 6291.6  | 6871.9  | 8796.0  | 9070.9  | 9704.7  | 7956.1  | 7727.1  | 9048.0  | 6665.8  | 1695.1  | 1160.6  |
| 80°   | 3100.0  | 3458.9  | 4588.9  | 5398.3  | 4588.9  | 4512.6  | 5146.3  | 6024.4  | 3458.9  | 1038.4  | 641.4   |
| 82.5° | 1389.7  | 1649.3  | 2115.0  | 3268.0  | 1656.9  | 1802.0  | 2275.4  | 3206.9  | 1572.9  | 618.5   | 274.9   |
| 85°   | 221.4   | 244.3   | 412.3   | 549.8   | 450.5   | 694.8   | 664.3   | 626.1   | 336.0   | 168.0   | 76.4    |
| 87.5° | 7.6     | 7.6     | 7.6     | 15.3    | 22.9    | 30.5    | 38.2    | 38.2    | 38.2    | 38.2    | 38.2    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1386100

CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°    | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4298.8  | 4298.8  | 4298.8  | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 |
| 2.5°  | 4848.5  | 4825.6  | 4711.1  | 4596.5 | 4497.3 | 4398.0 | 4298.8 | 4161.3 | 4054.4 | 3962.8 | 3924.6 |
| 5°    | 5306.6  | 5184.5  | 5008.9  | 4818.0 | 4650.0 | 4459.1 | 4275.9 | 4069.7 | 3901.7 | 3726.1 | 3634.5 |
| 7.5°  | 5619.7  | 5497.5  | 5207.4  | 4917.2 | 4711.1 | 4504.9 | 4314.0 | 4085.0 | 3863.5 | 3611.6 | 3474.1 |
| 10°   | 5764.8  | 5627.3  | 5314.3  | 4978.3 | 4726.3 | 4520.2 | 4344.6 | 4153.7 | 3932.3 | 3619.2 | 3436.0 |
| 12.5° | 5864.0  | 5696.0  | 5337.2  | 4993.6 | 4741.6 | 4527.8 | 4359.8 | 4222.4 | 4092.6 | 3787.2 | 3573.4 |
| 15°   | 5925.1  | 5772.4  | 5398.3  | 5001.2 | 4718.7 | 4466.7 | 4306.4 | 4260.6 | 4283.5 | 4138.4 | 3878.8 |
| 17.5° | 6016.7  | 5871.7  | 5474.6  | 5047.0 | 4680.5 | 4336.9 | 4161.3 | 4260.6 | 4466.7 | 4512.6 | 4306.4 |
| 20°   | 6138.9  | 5986.2  | 5573.9  | 5085.2 | 4566.0 | 4092.6 | 3924.6 | 4176.6 | 4520.2 | 4756.9 | 4642.4 |
| 22.5° | 6276.3  | 6154.2  | 5688.4  | 5123.4 | 4398.0 | 3771.9 | 3695.6 | 4001.0 | 4367.5 | 4672.9 | 4680.5 |
| 25°   | 6444.3  | 6329.8  | 5848.8  | 5161.6 | 4169.0 | 3497.0 | 3512.3 | 3771.9 | 4062.1 | 4375.1 | 4428.6 |
| 27.5° | 6673.4  | 6566.5  | 6047.3  | 5207.4 | 3932.3 | 3275.6 | 3352.0 | 3542.9 | 3741.4 | 3932.3 | 4008.6 |
| 30°   | 6925.4  | 6841.4  | 6284.0  | 5299.0 | 3710.8 | 3145.8 | 3191.6 | 3321.4 | 3481.8 | 3596.3 | 3634.5 |
| 32.5° | 7269.0  | 7131.5  | 6505.4  | 5291.4 | 3542.9 | 3084.7 | 3038.9 | 3077.1 | 3206.9 | 3321.4 | 3329.1 |
| 35°   | 7696.5  | 7589.6  | 6734.5  | 5153.9 | 3390.1 | 3054.2 | 2893.8 | 2870.9 | 2947.3 | 3061.8 | 3054.2 |
| 37.5° | 8322.6  | 8231.0  | 7108.6  | 4940.1 | 3199.3 | 2977.8 | 2741.1 | 2664.8 | 2718.2 | 2794.6 | 2817.5 |
| 40°   | 9261.8  | 9025.1  | 7536.2  | 4703.4 | 3008.4 | 2840.4 | 2557.9 | 2451.0 | 2489.2 | 2573.1 | 2588.4 |
| 42.5° | 10536.9 | 10086.4 | 8108.9  | 4382.8 | 2825.1 | 2634.2 | 2374.6 | 2260.1 | 2283.0 | 2359.4 | 2374.6 |
| 45°   | 12170.9 | 11491.4 | 8895.3  | 4046.8 | 2680.0 | 2420.4 | 2183.7 | 2061.6 | 2084.5 | 2168.5 | 2206.6 |
| 47.5° | 14079.8 | 13148.3 | 9719.9  | 3687.9 | 2596.1 | 2252.5 | 1992.9 | 1901.2 | 1954.7 | 2038.7 | 2053.9 |
| 50°   | 16332.2 | 15393.1 | 10246.8 | 3397.8 | 2542.6 | 2122.7 | 1817.2 | 1779.1 | 1847.8 | 1916.5 | 1931.8 |
| 52.5° | 18790.9 | 17454.6 | 9910.8  | 3161.1 | 2496.8 | 2076.8 | 1695.1 | 1710.3 | 1763.8 | 1832.5 | 1855.4 |
| 55°   | 21180.8 | 18210.6 | 8796.0  | 2855.7 | 2443.3 | 2107.4 | 1603.4 | 1641.6 | 1710.3 | 1763.8 | 1779.1 |
| 57.5° | 22738.4 | 17576.8 | 7085.7  | 2535.0 | 2382.3 | 2130.3 | 1557.6 | 1588.2 | 1664.5 | 1725.6 | 1733.2 |
| 60°   | 21379.3 | 16187.2 | 5306.6  | 2260.1 | 2252.5 | 2092.1 | 1542.4 | 1496.5 | 1603.4 | 1656.9 | 1664.5 |
| 62.5° | 17515.7 | 13239.9 | 3390.1  | 2000.5 | 2008.1 | 2008.1 | 1534.7 | 1343.8 | 1481.3 | 1527.1 | 1519.5 |
| 65°   | 12033.5 | 9361.1  | 2099.7  | 1634.0 | 1710.3 | 1824.9 | 1488.9 | 1183.5 | 1343.8 | 1389.7 | 1374.4 |
| 67.5° | 7910.3  | 5948.0  | 1298.0  | 1259.8 | 1404.9 | 1580.5 | 1397.3 | 1061.3 | 1206.4 | 1236.9 | 1191.1 |
| 70°   | 4291.1  | 2802.2  | 855.2   | 824.6  | 1099.5 | 1244.6 | 1183.5 | 954.4  | 1076.6 | 1107.1 | 1061.3 |
| 72.5° | 2832.8  | 1611.1  | 603.2   | 603.2  | 862.8  | 870.4  | 969.7  | 855.2  | 954.4  | 985.0  | 939.2  |
| 75°   | 2130.3  | 1038.4  | 419.9   | 465.8  | 549.8  | 679.6  | 694.8  | 717.7  | 809.4  | 847.5  | 801.7  |
| 77.5° | 977.3   | 381.8   | 252.0   | 343.6  | 381.8  | 519.2  | 442.9  | 534.5  | 603.2  | 618.5  | 580.3  |
| 80°   | 565.0   | 213.8   | 168.0   | 221.4  | 244.3  | 427.6  | 259.6  | 320.7  | 427.6  | 450.5  | 404.7  |
| 82.5° | 236.7   | 106.9   | 114.5   | 137.4  | 145.1  | 236.7  | 183.3  | 206.2  | 282.5  | 274.9  | 244.3  |
| 85°   | 68.7    | 68.7    | 76.4    | 84.0   | 84.0   | 137.4  | 129.8  | 122.2  | 129.8  | 129.8  | 106.9  |
| 87.5° | 45.8    | 45.8    | 45.8    | 53.4   | 53.4   | 61.1   | 68.7   | 76.4   | 76.4   | 76.4   | 68.7   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1386100  
 CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 |
| 2.5°  | 3871.2 | 3802.5 | 3703.2 | 3687.9 | 3634.5 | 3596.3 | 3634.5 | 3672.7 | 3741.4 | 3749.0 | 3779.5 |
| 5°    | 3550.5 | 3390.1 | 3268.0 | 3130.5 | 3061.8 | 3054.2 | 3038.9 | 3084.7 | 3184.0 | 3245.1 | 3290.9 |
| 7.5°  | 3336.7 | 3046.5 | 2832.8 | 2641.9 | 2573.1 | 2519.7 | 2565.5 | 2557.9 | 2687.7 | 2741.1 | 2786.9 |
| 10°   | 3222.2 | 2817.5 | 2496.8 | 2260.1 | 2168.5 | 2115.0 | 2107.4 | 2122.7 | 2199.0 | 2252.5 | 2305.9 |
| 12.5° | 3298.5 | 2725.9 | 2252.5 | 1977.6 | 1878.3 | 1817.2 | 1763.8 | 1763.8 | 1779.1 | 1847.8 | 1870.7 |
| 15°   | 3550.5 | 2779.3 | 2137.9 | 1840.1 | 1710.3 | 1611.1 | 1542.4 | 1488.9 | 1496.5 | 1504.2 | 1527.1 |
| 17.5° | 3917.0 | 2916.7 | 2099.7 | 1756.2 | 1618.7 | 1496.5 | 1427.8 | 1366.7 | 1351.5 | 1351.5 | 1343.8 |
| 20°   | 4268.2 | 3023.6 | 2069.2 | 1687.4 | 1511.8 | 1404.9 | 1343.8 | 1290.4 | 1267.5 | 1267.5 | 1267.5 |
| 22.5° | 4413.3 | 3115.3 | 2031.0 | 1603.4 | 1404.9 | 1305.7 | 1252.2 | 1214.0 | 1206.4 | 1206.4 | 1198.8 |
| 25°   | 4298.8 | 3084.7 | 1985.2 | 1519.5 | 1305.7 | 1229.3 | 1183.5 | 1145.3 | 1137.7 | 1145.3 | 1137.7 |
| 27.5° | 3939.9 | 2977.8 | 1924.1 | 1450.7 | 1229.3 | 1160.6 | 1122.4 | 1084.2 | 1076.6 | 1084.2 | 1084.2 |
| 30°   | 3558.1 | 2794.6 | 1824.9 | 1397.3 | 1168.2 | 1091.9 | 1053.7 | 1015.5 | 1015.5 | 1023.2 | 1030.8 |
| 32.5° | 3252.7 | 2611.3 | 1710.3 | 1328.6 | 1099.5 | 1030.8 | 992.6  | 954.4  | 954.4  | 969.7  | 969.7  |
| 35°   | 2993.1 | 2466.3 | 1595.8 | 1259.8 | 1038.4 | 962.1  | 931.5  | 901.0  | 893.3  | 908.6  | 916.3  |
| 37.5° | 2786.9 | 2336.4 | 1473.6 | 1191.1 | 977.3  | 908.6  | 878.1  | 839.9  | 832.3  | 847.5  | 862.8  |
| 40°   | 2573.1 | 2191.4 | 1366.7 | 1107.1 | 916.3  | 847.5  | 817.0  | 771.2  | 771.2  | 786.5  | 801.7  |
| 42.5° | 2367.0 | 2061.6 | 1298.0 | 1030.8 | 855.2  | 778.8  | 748.3  | 710.1  | 710.1  | 725.4  | 740.6  |
| 45°   | 2199.0 | 1939.4 | 1259.8 | 954.4  | 786.5  | 717.7  | 679.6  | 649.0  | 656.6  | 671.9  | 687.2  |
| 47.5° | 2038.7 | 1809.6 | 1267.5 | 916.3  | 740.6  | 649.0  | 610.8  | 587.9  | 603.2  | 626.1  | 641.4  |
| 50°   | 1916.5 | 1718.0 | 1275.1 | 855.2  | 679.6  | 595.6  | 557.4  | 542.1  | 565.0  | 587.9  | 603.2  |
| 52.5° | 1840.1 | 1626.4 | 1229.3 | 778.8  | 633.7  | 542.1  | 519.2  | 519.2  | 542.1  | 557.4  | 572.7  |
| 55°   | 1763.8 | 1473.6 | 1130.0 | 694.8  | 587.9  | 503.9  | 488.7  | 488.7  | 511.6  | 526.8  | 534.5  |
| 57.5° | 1702.7 | 1313.3 | 1015.5 | 626.1  | 534.5  | 465.8  | 465.8  | 465.8  | 473.4  | 481.0  | 496.3  |
| 60°   | 1588.2 | 1145.3 | 870.4  | 572.7  | 481.0  | 435.2  | 427.6  | 427.6  | 419.9  | 427.6  | 450.5  |
| 62.5° | 1389.7 | 962.1  | 740.6  | 511.6  | 435.2  | 397.0  | 389.4  | 366.5  | 343.6  | 351.2  | 366.5  |
| 65°   | 1175.9 | 763.5  | 618.5  | 442.9  | 374.1  | 351.2  | 343.6  | 305.4  | 274.9  | 282.5  | 305.4  |
| 67.5° | 939.2  | 572.7  | 519.2  | 381.8  | 320.7  | 297.8  | 297.8  | 274.9  | 252.0  | 252.0  | 267.2  |
| 70°   | 733.0  | 481.0  | 389.4  | 305.4  | 252.0  | 252.0  | 267.2  | 244.3  | 213.8  | 213.8  | 236.7  |
| 72.5° | 595.6  | 389.4  | 313.1  | 236.7  | 198.5  | 213.8  | 221.4  | 198.5  | 175.6  | 175.6  | 190.9  |
| 75°   | 465.8  | 305.4  | 244.3  | 175.6  | 152.7  | 160.3  | 175.6  | 160.3  | 137.4  | 145.1  | 152.7  |
| 77.5° | 320.7  | 206.2  | 160.3  | 129.8  | 114.5  | 122.2  | 122.2  | 114.5  | 106.9  | 106.9  | 114.5  |
| 80°   | 213.8  | 137.4  | 106.9  | 91.6   | 84.0   | 84.0   | 76.4   | 76.4   | 84.0   | 84.0   | 91.6   |
| 82.5° | 152.7  | 99.3   | 84.0   | 68.7   | 53.4   | 53.4   | 61.1   | 61.1   | 68.7   | 68.7   | 76.4   |
| 85°   | 91.6   | 68.7   | 61.1   | 45.8   | 38.2   | 45.8   | 45.8   | 53.4   | 61.1   | 61.1   | 68.7   |
| 87.5° | 68.7   | 53.4   | 45.8   | 38.2   | 30.5   | 30.5   | 38.2   | 38.2   | 45.8   | 53.4   | 53.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1386100

CATALOG NUMBER: VAL-T-SB6B-730-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°    | 359°    | 360°    |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0°    | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8 | 4298.8  | 4298.8  | 4298.8  |
| 2.5°  | 3855.9 | 3947.5 | 4077.3 | 4191.9 | 4329.3 | 4466.7 | 4596.5 | 4718.7  | 4726.3  | 4734.0  |
| 5°    | 3436.0 | 3619.2 | 3833.0 | 4092.6 | 4367.5 | 4634.7 | 4917.2 | 5146.3  | 5199.7  | 5230.3  |
| 7.5°  | 2970.2 | 3237.4 | 3565.8 | 3932.3 | 4344.6 | 4756.9 | 5153.9 | 5497.5  | 5627.3  | 5657.9  |
| 10°   | 2481.5 | 2809.8 | 3206.9 | 3680.3 | 4237.7 | 4787.4 | 5321.9 | 5741.9  | 5894.6  | 5925.1  |
| 12.5° | 2046.3 | 2313.5 | 2771.7 | 3344.3 | 4016.2 | 4741.6 | 5383.0 | 5848.8  | 6001.5  | 6039.6  |
| 15°   | 1672.2 | 1924.1 | 2351.7 | 2954.9 | 3710.8 | 4581.3 | 5337.2 | 5871.7  | 6024.4  | 6054.9  |
| 17.5° | 1382.0 | 1542.4 | 1931.8 | 2588.4 | 3436.0 | 4375.1 | 5276.1 | 5886.9  | 6032.0  | 6054.9  |
| 20°   | 1267.5 | 1298.0 | 1504.2 | 2145.6 | 3145.8 | 4222.4 | 5237.9 | 5909.8  | 6054.9  | 6077.8  |
| 22.5° | 1214.0 | 1214.0 | 1259.8 | 1634.0 | 2741.1 | 4062.1 | 5222.7 | 5978.6  | 6085.5  | 6108.4  |
| 25°   | 1160.6 | 1160.6 | 1175.9 | 1282.8 | 2260.1 | 3863.5 | 5253.2 | 6100.7  | 6169.4  | 6169.4  |
| 27.5° | 1107.1 | 1107.1 | 1122.4 | 1145.3 | 1679.8 | 3535.2 | 5260.8 | 6238.2  | 6268.7  | 6245.8  |
| 30°   | 1053.7 | 1069.0 | 1069.0 | 1084.2 | 1236.9 | 3122.9 | 5215.0 | 6390.9  | 6390.9  | 6345.1  |
| 32.5° | 1000.2 | 1007.9 | 1023.2 | 1030.8 | 1076.6 | 2588.4 | 5138.7 | 6581.8  | 6543.6  | 6482.5  |
| 35°   | 954.4  | 962.1  | 962.1  | 977.3  | 1023.2 | 2069.2 | 5054.7 | 6841.4  | 6734.5  | 6665.8  |
| 37.5° | 893.3  | 901.0  | 908.6  | 923.9  | 969.7  | 1641.6 | 4932.5 | 7062.8  | 6986.4  | 6894.8  |
| 40°   | 839.9  | 847.5  | 855.2  | 870.4  | 916.3  | 1412.6 | 4779.8 | 7398.8  | 7383.5  | 7276.6  |
| 42.5° | 778.8  | 794.1  | 801.7  | 809.4  | 870.4  | 1290.4 | 4672.9 | 7940.9  | 7940.9  | 7811.1  |
| 45°   | 725.4  | 740.6  | 740.6  | 755.9  | 839.9  | 1183.5 | 4909.6 | 8689.1  | 8750.2  | 8628.1  |
| 47.5° | 679.6  | 687.2  | 687.2  | 694.8  | 794.1  | 1091.9 | 5543.3 | 9834.5  | 9758.1  | 9674.1  |
| 50°   | 633.7  | 649.0  | 633.7  | 641.4  | 755.9  | 1145.3 | 6589.4 | 11300.5 | 11499.0 | 11353.9 |
| 52.5° | 603.2  | 610.8  | 580.3  | 580.3  | 702.5  | 1214.0 | 7444.6 | 13171.2 | 13835.4 | 13659.8 |
| 55°   | 565.0  | 572.7  | 534.5  | 534.5  | 618.5  | 1053.7 | 7498.0 | 15301.5 | 16759.8 | 16874.4 |
| 57.5° | 526.8  | 526.8  | 496.3  | 488.7  | 534.5  | 855.2  | 6650.5 | 16950.7 | 20256.9 | 20516.5 |
| 60°   | 481.0  | 473.4  | 458.1  | 442.9  | 488.7  | 786.5  | 5069.9 | 16729.3 | 21990.1 | 22891.1 |
| 62.5° | 412.3  | 427.6  | 419.9  | 389.4  | 442.9  | 733.0  | 3306.2 | 14476.8 | 20035.4 | 20829.5 |
| 65°   | 343.6  | 366.5  | 366.5  | 343.6  | 488.7  | 641.4  | 1740.9 | 11590.6 | 16721.6 | 17676.1 |
| 67.5° | 305.4  | 320.7  | 313.1  | 297.8  | 435.2  | 404.7  | 839.9  | 8887.7  | 14316.5 | 15232.7 |
| 70°   | 267.2  | 282.5  | 259.6  | 244.3  | 351.2  | 290.1  | 496.3  | 5948.0  | 11819.7 | 12713.0 |
| 72.5° | 221.4  | 236.7  | 213.8  | 190.9  | 259.6  | 221.4  | 328.3  | 3871.2  | 9842.1  | 10834.7 |
| 75°   | 183.3  | 190.9  | 175.6  | 152.7  | 190.9  | 175.6  | 229.1  | 2527.3  | 8231.0  | 8964.0  |
| 77.5° | 129.8  | 145.1  | 137.4  | 114.5  | 137.4  | 122.2  | 160.3  | 1443.1  | 5741.9  | 6291.6  |
| 80°   | 99.3   | 99.3   | 99.3   | 91.6   | 84.0   | 84.0   | 106.9  | 649.0   | 2786.9  | 3100.0  |
| 82.5° | 84.0   | 84.0   | 76.4   | 68.7   | 61.1   | 53.4   | 61.1   | 190.9   | 1313.3  | 1389.7  |
| 85°   | 76.4   | 61.1   | 53.4   | 45.8   | 38.2   | 22.9   | 22.9   | 53.4    | 267.2   | 221.4   |
| 87.5° | 45.8   | 38.2   | 30.5   | 15.3   | 7.6    | 7.6    | 0.0    | 7.6     | 7.6     | 7.6     |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-730-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

**Spectral Parameters**

CCT (K): 2985  
 CIE u': 0.2504  
 CIE v': 0.5243  
 Duv: 0.0019  
 CIE x: 0.4408  
 CIE y: 0.4101  
 CIE z: 0.1491  
 Peak Wavelength (nm): 595  
 Dominant Wavelength (nm): 582  
 Purity: 55.41818  
 Rf: 73.8  
 Rg: 94.4

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 70.8 |      |       |
| R1:       | 66.3 | R9:  | -43.2 |
| R2:       | 80.6 | R10: | 57.6  |
| R3:       | 94.5 | R11: | 64.8  |
| R4:       | 68.2 | R12: | 53.5  |
| R5:       | 66.5 | R13: | 68.7  |
| R6:       | 74.7 | R14: | 97.0  |
| R7:       | 76.2 | R15: | 56.4  |
| R8:       | 39.6 |      |       |



**Test Conditions**

Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 142                      | NR            | 620    | 803                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 189                      | NR            | 625    | 734                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 240                      | NR            | 630    | 670                      | NR            | 760    | 13                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 290                      | NR            | 635    | 600                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 335                      | NR            | 640    | 535                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 375                      | NR            | 645    | 473                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 408                      | NR            | 650    | 415                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 434                      | NR            | 655    | 362                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 461                      | NR            | 660    | 313                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 486                      | NR            | 665    | 271                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 16                       | NR            | 540    | 514                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 33                       | NR            | 545    | 549                      | NR            | 675    | 198                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 69                       | NR            | 550    | 591                      | NR            | 680    | 169                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 640                      | NR            | 685    | 144                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 227                      | NR            | 560    | 695                      | NR            | 690    | 123                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 369                      | NR            | 565    | 757                      | NR            | 695    | 104                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 822                      | NR            | 700    | 88                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 498                      | NR            | 575    | 882                      | NR            | 705    | 75                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 315                      | NR            | 580    | 935                      | NR            | 710    | 63                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 204                      | NR            | 585    | 972                      | NR            | 715    | 54                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 145                      | NR            | 590    | 996                      | NR            | 720    | 46                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 100                      | NR            | 595    | 1000                     | NR            | 725    | 39                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 78                       | NR            | 600    | 989                      | NR            | 730    | 33                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 76                       | NR            | 605    | 960                      | NR            | 735    | 28                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 83                       | NR            | 610    | 918                      | NR            | 740    | 24                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 105                      | NR            | 615    | 864                      | NR            | 745    | 20                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-4

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 1.19**

| $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360               | 0                           | NR                      | 490               | 142                         | NR                      | 620               | 803                         | NR                      | 750               | 17                          | NR                      | 880               | 0                           | NR                      |
| 365               | 0                           | NR                      | 495               | 189                         | NR                      | 625               | 734                         | NR                      | 755               | 15                          | NR                      | 885               | 0                           | NR                      |
| 370               | 0                           | NR                      | 500               | 240                         | NR                      | 630               | 670                         | NR                      | 760               | 13                          | NR                      | 890               | 0                           | NR                      |
| 375               | 0                           | NR                      | 505               | 290                         | NR                      | 635               | 600                         | NR                      | 765               | 11                          | NR                      | 895               | 0                           | NR                      |
| 380               | 0                           | NR                      | 510               | 335                         | NR                      | 640               | 535                         | NR                      | 770               | 9                           | NR                      | 900               | 0                           | NR                      |
| 385               | 0                           | NR                      | 515               | 375                         | NR                      | 645               | 473                         | NR                      | 775               | 8                           | NR                      | 905               | 0                           | NR                      |
| 390               | 1                           | NR                      | 520               | 408                         | NR                      | 650               | 415                         | NR                      | 780               | 7                           | NR                      | 910               | 0                           | NR                      |
| 395               | 2                           | NR                      | 525               | 434                         | NR                      | 655               | 362                         | NR                      | 785               | 6                           | NR                      | 915               | 0                           | NR                      |
| 400               | 4                           | NR                      | 530               | 461                         | NR                      | 660               | 313                         | NR                      | 790               | 5                           | NR                      | 920               | 0                           | NR                      |
| 405               | 8                           | NR                      | 535               | 486                         | NR                      | 665               | 271                         | NR                      | 795               | 4                           | NR                      | 925               | 0                           | NR                      |
| 410               | 16                          | NR                      | 540               | 514                         | NR                      | 670               | 231                         | NR                      | 800               | 4                           | NR                      | 930               | 0                           | NR                      |
| 415               | 33                          | NR                      | 545               | 549                         | NR                      | 675               | 198                         | NR                      | 805               | 3                           | NR                      | 935               | 0                           | NR                      |
| 420               | 69                          | NR                      | 550               | 591                         | NR                      | 680               | 169                         | NR                      | 810               | 3                           | NR                      | 940               | 0                           | NR                      |
| 425               | 131                         | NR                      | 555               | 640                         | NR                      | 685               | 144                         | NR                      | 815               | 2                           | NR                      | 945               | 0                           | NR                      |
| 430               | 227                         | NR                      | 560               | 695                         | NR                      | 690               | 123                         | NR                      | 820               | 2                           | NR                      | 950               | 0                           | NR                      |
| 435               | 369                         | NR                      | 565               | 757                         | NR                      | 695               | 104                         | NR                      | 825               | 2                           | NR                      | 955               | 0                           | NR                      |
| 440               | 517                         | NR                      | 570               | 822                         | NR                      | 700               | 88                          | NR                      | 830               | 2                           | NR                      | 960               | 0                           | NR                      |
| 445               | 498                         | NR                      | 575               | 882                         | NR                      | 705               | 75                          | NR                      | 835               | 1                           | NR                      | 965               | 0                           | NR                      |
| 450               | 315                         | NR                      | 580               | 935                         | NR                      | 710               | 63                          | NR                      | 840               | 1                           | NR                      | 970               | 0                           | NR                      |
| 455               | 204                         | NR                      | 585               | 972                         | NR                      | 715               | 54                          | NR                      | 845               | 1                           | NR                      | 975               | 0                           | NR                      |
| 460               | 145                         | NR                      | 590               | 996                         | NR                      | 720               | 46                          | NR                      | 850               | 1                           | NR                      | 980               | 0                           | NR                      |
| 465               | 100                         | NR                      | 595               | 1000                        | NR                      | 725               | 39                          | NR                      | 855               | 1                           | NR                      | 985               | 0                           | NR                      |
| 470               | 78                          | NR                      | 600               | 989                         | NR                      | 730               | 33                          | NR                      | 860               | 1                           | NR                      | 990               | 0                           | NR                      |
| 475               | 76                          | NR                      | 605               | 960                         | NR                      | 735               | 28                          | NR                      | 865               | 1                           | NR                      | 995               | 0                           | NR                      |
| 480               | 83                          | NR                      | 610               | 918                         | NR                      | 740               | 24                          | NR                      | 870               | 1                           | NR                      | 1000              | 0                           | NR                      |
| 485               | 105                         | NR                      | 615               | 864                         | NR                      | 745               | 20                          | NR                      | 875               | 1                           | NR                      |                   |                             |                         |

REPORT NUMBER: SP1-2407-184-4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 2.13**


| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 142                      | NR            | 620    | 803                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 189                      | NR            | 625    | 734                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 240                      | NR            | 630    | 670                      | NR            | 760    | 13                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 290                      | NR            | 635    | 600                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 335                      | NR            | 640    | 535                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 375                      | NR            | 645    | 473                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 408                      | NR            | 650    | 415                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 434                      | NR            | 655    | 362                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 461                      | NR            | 660    | 313                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 486                      | NR            | 665    | 271                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 16                       | NR            | 540    | 514                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 33                       | NR            | 545    | 549                      | NR            | 675    | 198                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 69                       | NR            | 550    | 591                      | NR            | 680    | 169                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 640                      | NR            | 685    | 144                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 227                      | NR            | 560    | 695                      | NR            | 690    | 123                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 369                      | NR            | 565    | 757                      | NR            | 695    | 104                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 822                      | NR            | 700    | 88                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 498                      | NR            | 575    | 882                      | NR            | 705    | 75                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 315                      | NR            | 580    | 935                      | NR            | 710    | 63                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 204                      | NR            | 585    | 972                      | NR            | 715    | 54                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 145                      | NR            | 590    | 996                      | NR            | 720    | 46                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 100                      | NR            | 595    | 1000                     | NR            | 725    | 39                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 78                       | NR            | 600    | 989                      | NR            | 730    | 33                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 76                       | NR            | 605    | 960                      | NR            | 735    | 28                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 83                       | NR            | 610    | 918                      | NR            | 740    | 24                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 105                      | NR            | 615    | 864                      | NR            | 745    | 20                       | NR            | 875    | 1                        | NR            |        |                          |               |

**Summary**

$R_f = 73.8$   
 $R_g = 94.4$   
 CIE  $R_a = 70.8$   
 $R_g = -43.2$




**Color Vector Graphics**






Individual Sample Fidelity Index ( $R_{f,i}$ )



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 63 | CES51 = 86 | CES76 = 61 |
| CES02 = 62 | CES27 = 83 | CES52 = 86 | CES77 = 81 |
| CES03 = 31 | CES28 = 86 | CES53 = 75 | CES78 = 64 |
| CES04 = 71 | CES29 = 58 | CES54 = 81 | CES79 = 86 |
| CES05 = 49 | CES30 = 61 | CES55 = 80 | CES80 = 86 |
| CES06 = 51 | CES31 = 63 | CES56 = 71 | CES81 = 70 |
| CES07 = 41 | CES32 = 61 | CES57 = 69 | CES82 = 94 |
| CES08 = 40 | CES33 = 65 | CES58 = 72 | CES83 = 88 |
| CES09 = 29 | CES34 = 77 | CES59 = 85 | CES84 = 90 |
| CES10 = 76 | CES35 = 88 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 89 | CES61 = 86 | CES86 = 60 |
| CES12 = 65 | CES37 = 85 | CES62 = 81 | CES87 = 78 |
| CES13 = 43 | CES38 = 69 | CES63 = 73 | CES88 = 75 |
| CES14 = 74 | CES39 = 93 | CES64 = 72 | CES89 = 66 |
| CES15 = 71 | CES40 = 89 | CES65 = 67 | CES90 = 72 |
| CES16 = 47 | CES41 = 83 | CES66 = 70 | CES91 = 95 |
| CES17 = 50 | CES42 = 87 | CES67 = 68 | CES92 = 59 |
| CES18 = 56 | CES43 = 77 | CES68 = 73 | CES93 = 76 |
| CES19 = 73 | CES44 = 99 | CES69 = 83 | CES94 = 48 |
| CES20 = 66 | CES45 = 83 | CES70 = 66 | CES95 = 70 |
| CES21 = 87 | CES46 = 77 | CES71 = 66 | CES96 = 76 |
| CES22 = 79 | CES47 = 74 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 62 | CES73 = 59 | CES98 = 73 |
| CES24 = 91 | CES49 = 77 | CES74 = 93 | CES99 = 60 |
| CES25 = 73 | CES50 = 85 | CES75 = 67 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)