

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P1385328

Luminaire Tested: **VAL-T-SB5B-730-U-SLR-HSS**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been  
influenced by sources from within Cooper Lighting Solutions or from external interests.

**Test Information**

Test Method: LM-79-08  
 Report Number: P1385328  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 02/18/2026  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: VAL-T-SB5B-730-U-SLR-HSS  
 Description: GALLEON II WALL SLIM HIGH DENSITY LED ARRAYS 55 SQUARE 184W 70CRI 3000K FIXTURE w/ 90° Spill Light Eliminator RIGHT OPTIC AND HOUSE SIDE SHIELD  
 Light Source: (130) 3000K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER  
 Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a                 | good             | reflector          |
| b                 | good             | lens               |
| c                 | good             | housing            |
| d                 | good             | cord               |


**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 20710.7 lumens  
 Efficiency: N/A  
 Efficacy: 112.6 lumens/watt  
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
 IES Classification: Type III - Short  
 BUG Rating: B2 - U0 - G3  
  
 Input Watts (W): 184  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: 0.98  
 Total Harmonic Distortion (THDi): 11.1%  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 28.75 FT

REPORT NUMBER: P1385328  
 CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 11.3 fc  
 Type III - Short - N/A

REPORT NUMBER: P1385328  
CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS

## Luminous Intensity Polar Plot



REPORT NUMBER: P1385328

CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3348.0   | 0.0    | 3348.0  |
|                    | % Fixture | 16.2     | 0.0    | 16.2    |
| <b>Street Side</b> | Lumens    | 17362.7  | 0.0    | 17362.7 |
|                    | % Fixture | 83.8     | 0.0    | 83.8    |
| <b>Total</b>       | Lumens    | 20710.7  | 0.0    | 20710.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 344.1   | 1.7       |
| 10°-20°   | 951.6   | 4.6       |
| 20°-30°   | 1363.0  | 6.6       |
| 30°-40°   | 1709.6  | 8.3       |
| 40°-50°   | 2808.4  | 13.6      |
| 50°-60°   | 5068.0  | 24.5      |
| 60°-70°   | 5624.4  | 27.2      |
| 70°-80°   | 2541.1  | 12.3      |
| 80°-90°   | 300.5   | 1.5       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20710.7 | 100.0     |
| 0°-180°   | 20710.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P1385328


CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1774.0 | 8.6       |                         |      |         |
| FM   | (30°-60°)   | 7864.4 | 38.0      |                         |      |         |
| FH   | (60°-80°)   | 7454.5 | 36.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 269.7  | 1.3       |                         |      | G3/500  |
| BL   | (0°-30°)    | 884.7  | 4.3       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 1721.5 | 8.3       | B2/2500                 |      |         |
| BH   | (60°-80°)   | 711.0  | 3.4       | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 30.7   | 0.1       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G3**

Type III Short





REPORT NUMBER: P1385328

CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 1°      | 5°      | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 3580.5  | 3580.5  | 3580.5  | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 |
| 2.5°  | 4038.3  | 4034.5  | 4019.3  | 3923.9 | 3828.5 | 3745.8 | 3663.1 | 3580.5 | 3466.0 | 3376.9 | 3300.6 |
| 5°    | 4419.9  | 4399.6  | 4318.2  | 4171.9 | 4012.9 | 3873.0 | 3714.0 | 3561.4 | 3389.7 | 3249.8 | 3103.5 |
| 7.5°  | 4680.7  | 4660.3  | 4578.9  | 4337.2 | 4095.6 | 3923.9 | 3752.2 | 3593.2 | 3402.4 | 3218.0 | 3008.1 |
| 10°   | 4801.5  | 4778.6  | 4687.0  | 4426.3 | 4146.5 | 3936.6 | 3764.9 | 3618.6 | 3459.6 | 3275.2 | 3014.4 |
| 12.5° | 4884.2  | 4856.2  | 4744.3  | 4445.4 | 4159.2 | 3949.3 | 3771.2 | 3631.3 | 3516.9 | 3408.7 | 3154.4 |
| 15°   | 4935.0  | 4909.6  | 4807.9  | 4496.2 | 4165.5 | 3930.2 | 3720.4 | 3586.8 | 3548.7 | 3567.7 | 3446.9 |
| 17.5° | 5011.4  | 4987.2  | 4890.5  | 4559.8 | 4203.7 | 3898.4 | 3612.3 | 3466.0 | 3548.7 | 3720.4 | 3758.5 |
| 20°   | 5113.1  | 5087.7  | 4985.9  | 4642.5 | 4235.5 | 3803.0 | 3408.7 | 3268.8 | 3478.7 | 3764.9 | 3962.0 |
| 22.5° | 5227.6  | 5207.2  | 5125.8  | 4737.9 | 4267.3 | 3663.1 | 3141.6 | 3078.0 | 3332.4 | 3637.7 | 3892.1 |
| 25°   | 5367.5  | 5348.4  | 5272.1  | 4871.5 | 4299.1 | 3472.3 | 2912.7 | 2925.4 | 3141.6 | 3383.3 | 3644.0 |
| 27.5° | 5558.3  | 5540.5  | 5469.3  | 5036.8 | 4337.2 | 3275.2 | 2728.3 | 2791.9 | 2950.9 | 3116.2 | 3275.2 |
| 30°   | 5768.2  | 5754.2  | 5698.2  | 5233.9 | 4413.6 | 3090.8 | 2620.2 | 2658.3 | 2766.4 | 2900.0 | 2995.4 |
| 32.5° | 6054.3  | 6031.4  | 5939.9  | 5418.4 | 4407.2 | 2950.9 | 2569.3 | 2531.1 | 2562.9 | 2671.0 | 2766.4 |
| 35°   | 6410.5  | 6392.7  | 6321.4  | 5609.2 | 4292.7 | 2823.7 | 2543.8 | 2410.3 | 2391.2 | 2454.8 | 2550.2 |
| 37.5° | 6932.0  | 6916.7  | 6855.6  | 5920.8 | 4114.7 | 2664.7 | 2480.2 | 2283.1 | 2219.5 | 2264.0 | 2327.6 |
| 40°   | 7714.2  | 7674.8  | 7517.0  | 6276.9 | 3917.5 | 2505.7 | 2365.8 | 2130.5 | 2041.4 | 2073.2 | 2143.2 |
| 42.5° | 8776.2  | 8701.2  | 8401.0  | 6753.9 | 3650.4 | 2353.1 | 2194.1 | 1977.8 | 1882.4 | 1901.5 | 1965.1 |
| 45°   | 10137.2 | 10024.0 | 9571.2  | 7408.9 | 3370.6 | 2232.2 | 2016.0 | 1818.8 | 1717.1 | 1736.2 | 1806.1 |
| 47.5° | 11727.1 | 11571.9 | 10951.2 | 8095.8 | 3071.7 | 2162.3 | 1876.1 | 1659.9 | 1583.5 | 1628.1 | 1698.0 |
| 50°   | 13603.2 | 13446.7 | 12820.9 | 8534.6 | 2830.0 | 2117.7 | 1768.0 | 1513.6 | 1481.8 | 1539.0 | 1596.3 |
| 52.5° | 15651.0 | 15428.4 | 14538.0 | 8254.8 | 2632.9 | 2079.6 | 1729.8 | 1411.8 | 1424.5 | 1469.1 | 1526.3 |
| 55°   | 17641.5 | 17146.7 | 15167.6 | 7326.3 | 2378.5 | 2035.1 | 1755.2 | 1335.5 | 1367.3 | 1424.5 | 1469.1 |
| 57.5° | 18938.9 | 18079.1 | 14639.8 | 5901.7 | 2111.4 | 1984.2 | 1774.3 | 1297.4 | 1322.8 | 1386.4 | 1437.3 |
| 60°   | 17806.9 | 16942.0 | 13482.3 | 4419.9 | 1882.4 | 1876.1 | 1742.5 | 1284.6 | 1246.5 | 1335.5 | 1380.0 |
| 62.5° | 14588.9 | 13876.6 | 11027.5 | 2823.7 | 1666.2 | 1672.6 | 1672.6 | 1278.3 | 1119.3 | 1233.8 | 1271.9 |
| 65°   | 10022.7 | 9577.6  | 7796.9  | 1748.9 | 1361.0 | 1424.5 | 1519.9 | 1240.1 | 985.7  | 1119.3 | 1157.4 |
| 67.5° | 6588.5  | 6261.7  | 4954.1  | 1081.1 | 1049.3 | 1170.2 | 1316.4 | 1163.8 | 884.0  | 1004.8 | 1030.3 |
| 70°   | 3574.1  | 3326.1  | 2334.0  | 712.3  | 686.8  | 915.8  | 1036.6 | 985.7  | 794.9  | 896.7  | 922.1  |
| 72.5° | 2359.4  | 2155.9  | 1341.9  | 502.4  | 502.4  | 718.6  | 725.0  | 807.7  | 712.3  | 794.9  | 820.4  |
| 75°   | 1774.3  | 1592.4  | 864.9   | 349.8  | 387.9  | 457.9  | 566.0  | 578.7  | 597.8  | 674.1  | 705.9  |
| 77.5° | 814.0   | 714.8   | 318.0   | 209.9  | 286.2  | 318.0  | 432.5  | 368.9  | 445.2  | 502.4  | 515.1  |
| 80°   | 470.6   | 412.1   | 178.1   | 139.9  | 184.4  | 203.5  | 356.1  | 216.2  | 267.1  | 356.1  | 375.2  |
| 82.5° | 197.1   | 175.5   | 89.0    | 95.4   | 114.5  | 120.8  | 197.1  | 152.6  | 171.7  | 235.3  | 228.9  |
| 85°   | 57.2    | 57.2    | 57.2    | 63.6   | 70.0   | 70.0   | 114.5  | 108.1  | 101.8  | 108.1  | 108.1  |
| 87.5° | 38.2    | 38.2    | 38.2    | 38.2   | 44.5   | 44.5   | 50.9   | 57.2   | 63.6   | 63.6   | 63.6   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1385328

CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 |
| 2.5°  | 3268.8 | 3224.3 | 3167.1 | 3084.4 | 3071.7 | 3027.2 | 2995.4 | 3027.2 | 3059.0 | 3116.2 | 3122.6 |
| 5°    | 3027.2 | 2957.2 | 2823.7 | 2721.9 | 2607.4 | 2550.2 | 2543.8 | 2531.1 | 2569.3 | 2652.0 | 2702.8 |
| 7.5°  | 2893.6 | 2779.1 | 2537.5 | 2359.4 | 2200.4 | 2143.2 | 2098.7 | 2136.8 | 2130.5 | 2238.6 | 2283.1 |
| 10°   | 2861.8 | 2683.8 | 2346.7 | 2079.6 | 1882.4 | 1806.1 | 1761.6 | 1755.2 | 1768.0 | 1831.6 | 1876.1 |
| 12.5° | 2976.3 | 2747.3 | 2270.4 | 1876.1 | 1647.1 | 1564.5 | 1513.6 | 1469.1 | 1469.1 | 1481.8 | 1539.0 |
| 15°   | 3230.7 | 2957.2 | 2314.9 | 1780.7 | 1532.7 | 1424.5 | 1341.9 | 1284.6 | 1240.1 | 1246.5 | 1252.8 |
| 17.5° | 3586.8 | 3262.5 | 2429.4 | 1748.9 | 1462.7 | 1348.2 | 1246.5 | 1189.2 | 1138.4 | 1125.6 | 1125.6 |
| 20°   | 3866.6 | 3555.0 | 2518.4 | 1723.5 | 1405.5 | 1259.2 | 1170.2 | 1119.3 | 1074.8 | 1055.7 | 1055.7 |
| 22.5° | 3898.4 | 3675.8 | 2594.7 | 1691.7 | 1335.5 | 1170.2 | 1087.5 | 1043.0 | 1011.2 | 1004.8 | 1004.8 |
| 25°   | 3688.6 | 3580.5 | 2569.3 | 1653.5 | 1265.6 | 1087.5 | 1023.9 | 985.7  | 953.9  | 947.6  | 953.9  |
| 27.5° | 3338.8 | 3281.6 | 2480.2 | 1602.6 | 1208.3 | 1023.9 | 966.7  | 934.9  | 903.1  | 896.7  | 903.1  |
| 30°   | 3027.2 | 2963.6 | 2327.6 | 1519.9 | 1163.8 | 973.0  | 909.4  | 877.6  | 845.8  | 845.8  | 852.2  |
| 32.5° | 2772.8 | 2709.2 | 2175.0 | 1424.5 | 1106.6 | 915.8  | 858.5  | 826.7  | 794.9  | 794.9  | 807.7  |
| 35°   | 2543.8 | 2493.0 | 2054.2 | 1329.2 | 1049.3 | 864.9  | 801.3  | 775.9  | 750.4  | 744.1  | 756.8  |
| 37.5° | 2346.7 | 2321.3 | 1946.0 | 1227.4 | 992.1  | 814.0  | 756.8  | 731.4  | 699.6  | 693.2  | 705.9  |
| 40°   | 2155.9 | 2143.2 | 1825.2 | 1138.4 | 922.1  | 763.2  | 705.9  | 680.5  | 642.3  | 642.3  | 655.0  |
| 42.5° | 1977.8 | 1971.5 | 1717.1 | 1081.1 | 858.5  | 712.3  | 648.7  | 623.2  | 591.4  | 591.4  | 604.2  |
| 45°   | 1837.9 | 1831.6 | 1615.3 | 1049.3 | 794.9  | 655.0  | 597.8  | 566.0  | 540.6  | 546.9  | 559.6  |
| 47.5° | 1710.7 | 1698.0 | 1507.2 | 1055.7 | 763.2  | 616.9  | 540.6  | 508.8  | 489.7  | 502.4  | 521.5  |
| 50°   | 1609.0 | 1596.3 | 1430.9 | 1062.1 | 712.3  | 566.0  | 496.0  | 464.3  | 451.5  | 470.6  | 489.7  |
| 52.5° | 1545.4 | 1532.7 | 1354.6 | 1023.9 | 648.7  | 527.8  | 451.5  | 432.5  | 432.5  | 451.5  | 464.3  |
| 55°   | 1481.8 | 1469.1 | 1227.4 | 941.2  | 578.7  | 489.7  | 419.7  | 407.0  | 407.0  | 426.1  | 438.8  |
| 57.5° | 1443.6 | 1418.2 | 1093.9 | 845.8  | 521.5  | 445.2  | 387.9  | 387.9  | 387.9  | 394.3  | 400.7  |
| 60°   | 1386.4 | 1322.8 | 953.9  | 725.0  | 477.0  | 400.7  | 362.5  | 356.1  | 356.1  | 349.8  | 356.1  |
| 62.5° | 1265.6 | 1157.4 | 801.3  | 616.9  | 426.1  | 362.5  | 330.7  | 324.3  | 305.3  | 286.2  | 292.5  |
| 65°   | 1144.7 | 979.4  | 636.0  | 515.1  | 368.9  | 311.6  | 292.5  | 286.2  | 254.4  | 228.9  | 235.3  |
| 67.5° | 992.1  | 782.2  | 477.0  | 432.5  | 318.0  | 267.1  | 248.0  | 248.0  | 228.9  | 209.9  | 209.9  |
| 70°   | 884.0  | 610.5  | 400.7  | 324.3  | 254.4  | 209.9  | 209.9  | 222.6  | 203.5  | 178.1  | 178.1  |
| 72.5° | 782.2  | 496.0  | 324.3  | 260.7  | 197.1  | 165.3  | 178.1  | 184.4  | 165.3  | 146.3  | 146.3  |
| 75°   | 667.8  | 387.9  | 254.4  | 203.5  | 146.3  | 127.2  | 133.6  | 146.3  | 133.6  | 114.5  | 120.8  |
| 77.5° | 483.3  | 267.1  | 171.7  | 133.6  | 108.1  | 95.4   | 101.8  | 101.8  | 95.4   | 89.0   | 89.0   |
| 80°   | 337.1  | 178.1  | 114.5  | 89.0   | 76.3   | 70.0   | 70.0   | 63.6   | 63.6   | 70.0   | 70.0   |
| 82.5° | 203.5  | 127.2  | 82.7   | 70.0   | 57.2   | 44.5   | 44.5   | 50.9   | 50.9   | 57.2   | 57.2   |
| 85°   | 89.0   | 76.3   | 57.2   | 50.9   | 38.2   | 31.8   | 38.2   | 38.2   | 44.5   | 50.9   | 50.9   |
| 87.5° | 57.2   | 57.2   | 44.5   | 38.2   | 31.8   | 25.4   | 25.4   | 31.8   | 31.8   | 38.2   | 44.5   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P1385328

CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°    | 270°    | 275°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0°    | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5 | 3580.5  | 3580.5  | 3580.5  |
| 2.5°  | 3148.0 | 3211.6 | 3287.9 | 3396.0 | 3491.4 | 3605.9 | 3720.4 | 3828.5 | 3930.2  | 3943.0  | 3987.5  |
| 5°    | 2741.0 | 2861.8 | 3014.4 | 3192.5 | 3408.7 | 3637.7 | 3860.3 | 4095.6 | 4286.4  | 4356.3  | 4458.1  |
| 7.5°  | 2321.3 | 2473.9 | 2696.5 | 2969.9 | 3275.2 | 3618.6 | 3962.0 | 4292.7 | 4578.9  | 4712.5  | 4846.0  |
| 10°   | 1920.6 | 2066.9 | 2340.3 | 2671.0 | 3065.3 | 3529.6 | 3987.5 | 4432.6 | 4782.4  | 4935.0  | 5062.2  |
| 12.5° | 1558.1 | 1704.4 | 1927.0 | 2308.5 | 2785.5 | 3345.1 | 3949.3 | 4483.5 | 4871.5  | 5030.4  | 5151.3  |
| 15°   | 1271.9 | 1392.8 | 1602.6 | 1958.8 | 2461.2 | 3090.8 | 3815.8 | 4445.4 | 4890.5  | 5043.2  | 5132.2  |
| 17.5° | 1119.3 | 1151.1 | 1284.6 | 1609.0 | 2155.9 | 2861.8 | 3644.0 | 4394.5 | 4903.3  | 5043.2  | 5094.0  |
| 20°   | 1055.7 | 1055.7 | 1081.1 | 1252.8 | 1787.0 | 2620.2 | 3516.9 | 4362.7 | 4922.3  | 5062.2  | 5055.9  |
| 22.5° | 998.5  | 1011.2 | 1011.2 | 1049.3 | 1361.0 | 2283.1 | 3383.3 | 4350.0 | 4979.6  | 5087.7  | 4998.6  |
| 25°   | 947.6  | 966.7  | 966.7  | 979.4  | 1068.4 | 1882.4 | 3218.0 | 4375.4 | 5081.3  | 5138.6  | 4960.5  |
| 27.5° | 903.1  | 922.1  | 922.1  | 934.9  | 953.9  | 1399.1 | 2944.5 | 4381.8 | 5195.8  | 5202.2  | 4909.6  |
| 30°   | 858.5  | 877.6  | 890.3  | 890.3  | 903.1  | 1030.3 | 2601.1 | 4343.6 | 5323.0  | 5284.8  | 4903.3  |
| 32.5° | 807.7  | 833.1  | 839.5  | 852.2  | 858.5  | 896.7  | 2155.9 | 4280.0 | 5482.0  | 5399.3  | 4909.6  |
| 35°   | 763.2  | 794.9  | 801.3  | 801.3  | 814.0  | 852.2  | 1723.5 | 4210.1 | 5698.2  | 5551.9  | 4935.0  |
| 37.5° | 718.6  | 744.1  | 750.4  | 756.8  | 769.5  | 807.7  | 1367.3 | 4108.3 | 5882.6  | 5742.7  | 5062.2  |
| 40°   | 667.8  | 699.6  | 705.9  | 712.3  | 725.0  | 763.2  | 1176.5 | 3981.1 | 6162.5  | 6060.7  | 5253.0  |
| 42.5° | 616.9  | 648.7  | 661.4  | 667.8  | 674.1  | 725.0  | 1074.8 | 3892.1 | 6614.0  | 6505.9  | 5641.0  |
| 45°   | 572.4  | 604.2  | 616.9  | 616.9  | 629.6  | 699.6  | 985.7  | 4089.2 | 7237.2  | 7186.3  | 6162.5  |
| 47.5° | 534.2  | 566.0  | 572.4  | 572.4  | 578.7  | 661.4  | 909.4  | 4617.1 | 8191.2  | 8057.6  | 6976.5  |
| 50°   | 502.4  | 527.8  | 540.6  | 527.8  | 534.2  | 629.6  | 953.9  | 5488.3 | 9412.2  | 9456.7  | 8172.1  |
| 52.5° | 477.0  | 502.4  | 508.8  | 483.3  | 483.3  | 585.1  | 1011.2 | 6200.6 | 10970.3 | 11377.3 | 10067.2 |
| 55°   | 445.2  | 470.6  | 477.0  | 445.2  | 445.2  | 515.1  | 877.6  | 6245.1 | 12744.6 | 14054.7 | 12534.8 |
| 57.5° | 413.4  | 438.8  | 438.8  | 413.4  | 407.0  | 445.2  | 712.3  | 5539.2 | 14118.3 | 17088.2 | 15911.7 |
| 60°   | 375.2  | 400.7  | 394.3  | 381.6  | 368.9  | 407.0  | 655.0  | 4222.8 | 13933.9 | 19066.1 | 19784.7 |
| 62.5° | 305.3  | 343.4  | 356.1  | 349.8  | 324.3  | 368.9  | 610.5  | 2753.7 | 12057.8 | 17349.0 | 19663.9 |
| 65°   | 254.4  | 286.2  | 305.3  | 305.3  | 286.2  | 407.0  | 534.2  | 1450.0 | 9653.9  | 14722.5 | 17336.3 |
| 67.5° | 222.6  | 254.4  | 267.1  | 260.7  | 248.0  | 362.5  | 337.1  | 699.6  | 7402.6  | 12687.4 | 15517.4 |
| 70°   | 197.1  | 222.6  | 235.3  | 216.2  | 203.5  | 292.5  | 241.7  | 413.4  | 4954.1  | 10588.7 | 13819.4 |
| 72.5° | 159.0  | 184.4  | 197.1  | 178.1  | 159.0  | 216.2  | 184.4  | 273.5  | 3224.3  | 9024.3  | 12280.4 |
| 75°   | 127.2  | 152.6  | 159.0  | 146.3  | 127.2  | 159.0  | 146.3  | 190.8  | 2105.0  | 7466.2  | 10442.5 |
| 77.5° | 95.4   | 108.1  | 120.8  | 114.5  | 95.4   | 114.5  | 101.8  | 133.6  | 1202.0  | 5240.3  | 7326.3  |
| 80°   | 76.3   | 82.7   | 82.7   | 82.7   | 76.3   | 70.0   | 70.0   | 89.0   | 540.6   | 2582.0  | 3822.1  |
| 82.5° | 63.6   | 70.0   | 70.0   | 63.6   | 57.2   | 50.9   | 44.5   | 50.9   | 159.0   | 1157.4  | 1761.6  |
| 85°   | 57.2   | 63.6   | 50.9   | 44.5   | 38.2   | 31.8   | 19.1   | 19.1   | 44.5    | 184.4   | 343.4   |
| 87.5° | 44.5   | 38.2   | 31.8   | 25.4   | 12.7   | 6.4    | 6.4    | 0.0    | 6.4     | 6.4     | 6.4     |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1385328

CATALOG NUMBER: VAL-T-SB5B-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 285°    | 295°    | 305°    | 315°    | 325°    | 335°    | 345°    | 355°    | 359°    | 360°    |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 3580.5  | 3580.5  | 3580.5  | 3580.5  | 3580.5  | 3580.5  | 3580.5  | 3580.5  | 3580.5  | 3580.5  |
| 2.5°  | 4057.4  | 4121.0  | 4165.5  | 4203.7  | 4191.0  | 4159.2  | 4095.6  | 4051.1  | 4040.9  | 4038.3  |
| 5°    | 4591.6  | 4693.4  | 4782.4  | 4769.7  | 4782.4  | 4687.0  | 4591.6  | 4477.2  | 4431.4  | 4419.9  |
| 7.5°  | 5036.8  | 5164.0  | 5272.1  | 5259.4  | 5221.2  | 5113.1  | 4954.1  | 4782.4  | 4701.0  | 4680.7  |
| 10°   | 5278.5  | 5424.7  | 5513.8  | 5482.0  | 5418.4  | 5278.5  | 5119.5  | 4916.0  | 4824.4  | 4801.5  |
| 12.5° | 5323.0  | 5418.4  | 5399.3  | 5386.6  | 5373.9  | 5303.9  | 5183.1  | 4998.6  | 4907.1  | 4884.2  |
| 15°   | 5208.5  | 5170.4  | 5062.2  | 5036.8  | 5132.2  | 5221.2  | 5195.8  | 5043.2  | 4956.7  | 4935.0  |
| 17.5° | 5017.7  | 4820.6  | 4623.4  | 4598.0  | 4757.0  | 5005.0  | 5202.2  | 5113.1  | 5031.7  | 5011.4  |
| 20°   | 4807.9  | 4439.0  | 4222.8  | 4178.3  | 4375.4  | 4744.3  | 5132.2  | 5183.1  | 5127.1  | 5113.1  |
| 22.5° | 4559.8  | 4127.4  | 3898.4  | 3873.0  | 4019.3  | 4451.7  | 5030.4  | 5259.4  | 5233.9  | 5227.6  |
| 25°   | 4343.6  | 3853.9  | 3637.7  | 3599.5  | 3790.3  | 4210.1  | 4928.7  | 5386.6  | 5371.3  | 5367.5  |
| 27.5° | 4165.5  | 3656.8  | 3427.8  | 3402.4  | 3586.8  | 4006.5  | 4801.5  | 5494.7  | 5545.6  | 5558.3  |
| 30°   | 4025.6  | 3510.5  | 3281.6  | 3249.8  | 3453.3  | 3866.6  | 4712.5  | 5647.3  | 5744.0  | 5768.2  |
| 32.5° | 3917.5  | 3427.8  | 3211.6  | 3192.5  | 3408.7  | 3809.4  | 4661.6  | 5806.3  | 6004.7  | 6054.3  |
| 35°   | 3879.4  | 3453.3  | 3307.0  | 3351.5  | 3516.9  | 3866.6  | 4699.7  | 6067.1  | 6341.8  | 6410.5  |
| 37.5° | 3962.0  | 3733.1  | 3834.8  | 3949.3  | 4012.9  | 4140.1  | 4877.8  | 6486.8  | 6842.9  | 6932.0  |
| 40°   | 4229.1  | 4483.5  | 4960.5  | 5183.1  | 5157.6  | 4865.1  | 5284.8  | 7078.2  | 7587.0  | 7714.2  |
| 42.5° | 4909.6  | 5736.4  | 6747.5  | 7122.7  | 6906.5  | 6022.5  | 5933.5  | 8051.3  | 8631.2  | 8776.2  |
| 45°   | 5920.8  | 7249.9  | 8909.8  | 9755.6  | 9011.6  | 7491.6  | 6957.4  | 9437.6  | 9997.3  | 10137.2 |
| 47.5° | 6932.0  | 8941.6  | 11580.8 | 12585.6 | 11122.9 | 8948.0  | 8299.3  | 11097.5 | 11601.2 | 11727.1 |
| 50°   | 7962.2  | 10811.3 | 14245.5 | 15587.4 | 13228.0 | 10429.7 | 9723.8  | 13145.3 | 13511.6 | 13603.2 |
| 52.5° | 9024.3  | 12483.9 | 17183.6 | 18341.1 | 15428.4 | 11574.5 | 11351.9 | 15377.5 | 15596.3 | 15651.0 |
| 55°   | 10207.2 | 14067.4 | 20128.1 | 21063.0 | 17431.7 | 12572.9 | 13259.8 | 17711.5 | 17655.5 | 17641.5 |
| 57.5° | 11784.3 | 15733.6 | 22500.3 | 23804.0 | 19250.5 | 13921.2 | 15810.0 | 20306.2 | 19212.3 | 18938.9 |
| 60°   | 14538.0 | 18322.0 | 25451.1 | 26869.3 | 21686.2 | 15892.6 | 17686.0 | 20249.0 | 18295.3 | 17806.9 |
| 62.5° | 17730.6 | 20815.0 | 28122.1 | 29317.7 | 24249.1 | 17851.4 | 16191.5 | 17005.6 | 15072.2 | 14588.9 |
| 65°   | 15402.9 | 20376.2 | 28204.8 | 29432.2 | 24344.5 | 16655.8 | 11968.8 | 12057.8 | 10429.7 | 10022.7 |
| 67.5° | 13107.1 | 18061.3 | 25686.4 | 26653.1 | 21718.0 | 13768.5 | 7936.8  | 7866.8  | 6844.2  | 6588.5  |
| 70°   | 11669.9 | 15822.7 | 22137.8 | 21304.7 | 18258.4 | 11638.1 | 5272.1  | 4369.0  | 3733.1  | 3574.1  |
| 72.5° | 10487.0 | 12553.8 | 17940.4 | 14684.3 | 15148.6 | 9469.4  | 3351.5  | 2976.3  | 2482.8  | 2359.4  |
| 75°   | 9494.9  | 10385.2 | 11192.9 | 10149.9 | 10760.4 | 7803.2  | 2842.7  | 2295.8  | 1878.6  | 1774.3  |
| 77.5° | 7555.2  | 8083.0  | 6626.7  | 6435.9  | 7536.1  | 5551.9  | 1411.8  | 966.7   | 844.6   | 814.0   |
| 80°   | 4496.2  | 3822.1  | 3758.5  | 4286.4  | 5017.7  | 2880.9  | 864.9   | 534.2   | 483.3   | 470.6   |
| 82.5° | 2721.9  | 1380.0  | 1500.9  | 1895.2  | 2671.0  | 1310.1  | 515.1   | 228.9   | 203.5   | 197.1   |
| 85°   | 457.9   | 375.2   | 578.7   | 553.3   | 521.5   | 279.8   | 139.9   | 63.6    | 58.5    | 57.2    |
| 87.5° | 12.7    | 19.1    | 25.4    | 31.8    | 31.8    | 31.8    | 31.8    | 31.8    | 36.9    | 38.2    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ


Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-730-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 3000K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 2985     | CRI (Ra): | 70.8 |      |       |
| CIE u':                   | 0.2504   | R1:       | 66.3 | R9:  | -43.2 |
| CIE v':                   | 0.5243   | R2:       | 80.6 | R10: | 57.6  |
| Duv:                      | 0.0019   | R3:       | 94.5 | R11: | 64.8  |
| CIE x:                    | 0.4408   | R4:       | 68.2 | R12: | 53.5  |
| CIE y:                    | 0.4101   | R5:       | 66.5 | R13: | 68.7  |
| CIE z:                    | 0.1491   | R6:       | 74.7 | R14: | 97.0  |
| Peak Wavelength (nm):     | 595      | R7:       | 76.2 | R15: | 56.4  |
| Dominant Wavelength (nm): | 582      | R8:       | 39.6 |      |       |
| Purity:                   | 55.41818 |           |      |      |       |
| Rf:                       | 73.8     |           |      |      |       |
| Rg:                       | 94.4     |           |      |      |       |



### Test Conditions

Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-4

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 142                      | NR            | 620    | 803                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 189                      | NR            | 625    | 734                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 240                      | NR            | 630    | 670                      | NR            | 760    | 13                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 290                      | NR            | 635    | 600                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 335                      | NR            | 640    | 535                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 375                      | NR            | 645    | 473                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 408                      | NR            | 650    | 415                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 434                      | NR            | 655    | 362                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 461                      | NR            | 660    | 313                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 486                      | NR            | 665    | 271                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 16                       | NR            | 540    | 514                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 33                       | NR            | 545    | 549                      | NR            | 675    | 198                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 69                       | NR            | 550    | 591                      | NR            | 680    | 169                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 640                      | NR            | 685    | 144                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 227                      | NR            | 560    | 695                      | NR            | 690    | 123                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 369                      | NR            | 565    | 757                      | NR            | 695    | 104                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 822                      | NR            | 700    | 88                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 498                      | NR            | 575    | 882                      | NR            | 705    | 75                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 315                      | NR            | 580    | 935                      | NR            | 710    | 63                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 204                      | NR            | 585    | 972                      | NR            | 715    | 54                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 145                      | NR            | 590    | 996                      | NR            | 720    | 46                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 100                      | NR            | 595    | 1000                     | NR            | 725    | 39                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 78                       | NR            | 600    | 989                      | NR            | 730    | 33                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 76                       | NR            | 605    | 960                      | NR            | 735    | 28                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 83                       | NR            | 610    | 918                      | NR            | 740    | 24                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 105                      | NR            | 615    | 864                      | NR            | 745    | 20                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-4

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.19

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 142                         | NR               | 620       | 803                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 189                         | NR               | 625       | 734                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 240                         | NR               | 630       | 670                         | NR               | 760       | 13                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 290                         | NR               | 635       | 600                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 335                         | NR               | 640       | 535                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 375                         | NR               | 645       | 473                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 408                         | NR               | 650       | 415                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 434                         | NR               | 655       | 362                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 461                         | NR               | 660       | 313                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 8                           | NR               | 535       | 486                         | NR               | 665       | 271                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 16                          | NR               | 540       | 514                         | NR               | 670       | 231                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 33                          | NR               | 545       | 549                         | NR               | 675       | 198                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 69                          | NR               | 550       | 591                         | NR               | 680       | 169                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 131                         | NR               | 555       | 640                         | NR               | 685       | 144                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 227                         | NR               | 560       | 695                         | NR               | 690       | 123                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 369                         | NR               | 565       | 757                         | NR               | 695       | 104                         | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 517                         | NR               | 570       | 822                         | NR               | 700       | 88                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 498                         | NR               | 575       | 882                         | NR               | 705       | 75                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 315                         | NR               | 580       | 935                         | NR               | 710       | 63                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 204                         | NR               | 585       | 972                         | NR               | 715       | 54                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 145                         | NR               | 590       | 996                         | NR               | 720       | 46                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 100                         | NR               | 595       | 1000                        | NR               | 725       | 39                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 78                          | NR               | 600       | 989                         | NR               | 730       | 33                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 76                          | NR               | 605       | 960                         | NR               | 735       | 28                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 83                          | NR               | 610       | 918                         | NR               | 740       | 24                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 105                         | NR               | 615       | 864                         | NR               | 745       | 20                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-4

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.13


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 142                                  | NR                             | 620               | 803                                  | NR                             | 750               | 17                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 189                                  | NR                             | 625               | 734                                  | NR                             | 755               | 15                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 240                                  | NR                             | 630               | 670                                  | NR                             | 760               | 13                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 290                                  | NR                             | 635               | 600                                  | NR                             | 765               | 11                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 335                                  | NR                             | 640               | 535                                  | NR                             | 770               | 9                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 375                                  | NR                             | 645               | 473                                  | NR                             | 775               | 8                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 408                                  | NR                             | 650               | 415                                  | NR                             | 780               | 7                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 434                                  | NR                             | 655               | 362                                  | NR                             | 785               | 6                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 461                                  | NR                             | 660               | 313                                  | NR                             | 790               | 5                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 8                                    | NR                             | 535               | 486                                  | NR                             | 665               | 271                                  | NR                             | 795               | 4                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 16                                   | NR                             | 540               | 514                                  | NR                             | 670               | 231                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 33                                   | NR                             | 545               | 549                                  | NR                             | 675               | 198                                  | NR                             | 805               | 3                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 69                                   | NR                             | 550               | 591                                  | NR                             | 680               | 169                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 131                                  | NR                             | 555               | 640                                  | NR                             | 685               | 144                                  | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 227                                  | NR                             | 560               | 695                                  | NR                             | 690               | 123                                  | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 369                                  | NR                             | 565               | 757                                  | NR                             | 695               | 104                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 517                                  | NR                             | 570               | 822                                  | NR                             | 700               | 88                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 498                                  | NR                             | 575               | 882                                  | NR                             | 705               | 75                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 315                                  | NR                             | 580               | 935                                  | NR                             | 710               | 63                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 204                                  | NR                             | 585               | 972                                  | NR                             | 715               | 54                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 145                                  | NR                             | 590               | 996                                  | NR                             | 720               | 46                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 100                                  | NR                             | 595               | 1000                                 | NR                             | 725               | 39                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 78                                   | NR                             | 600               | 989                                  | NR                             | 730               | 33                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 76                                   | NR                             | 605               | 960                                  | NR                             | 735               | 28                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 83                                   | NR                             | 610               | 918                                  | NR                             | 740               | 24                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 105                                  | NR                             | 615               | 864                                  | NR                             | 745               | 20                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-4




TM-30-18

### Summary

$R_f = 73.8$   
 $R_g = 94.4$   
 $CIE R_a = 70.8$   
 $R_g = -43.2$




### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 63 | CES51 = 86 | CES76 = 61 |
| CES02 = 62 | CES27 = 83 | CES52 = 86 | CES77 = 81 |
| CES03 = 31 | CES28 = 86 | CES53 = 75 | CES78 = 64 |
| CES04 = 71 | CES29 = 58 | CES54 = 81 | CES79 = 86 |
| CES05 = 49 | CES30 = 61 | CES55 = 80 | CES80 = 86 |
| CES06 = 51 | CES31 = 63 | CES56 = 71 | CES81 = 70 |
| CES07 = 41 | CES32 = 61 | CES57 = 69 | CES82 = 94 |
| CES08 = 40 | CES33 = 65 | CES58 = 72 | CES83 = 88 |
| CES09 = 29 | CES34 = 77 | CES59 = 85 | CES84 = 90 |
| CES10 = 76 | CES35 = 88 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 89 | CES61 = 86 | CES86 = 60 |
| CES12 = 65 | CES37 = 85 | CES62 = 81 | CES87 = 78 |
| CES13 = 43 | CES38 = 69 | CES63 = 73 | CES88 = 75 |
| CES14 = 74 | CES39 = 93 | CES64 = 72 | CES89 = 66 |
| CES15 = 71 | CES40 = 89 | CES65 = 67 | CES90 = 72 |
| CES16 = 47 | CES41 = 83 | CES66 = 70 | CES91 = 95 |
| CES17 = 50 | CES42 = 87 | CES67 = 68 | CES92 = 59 |
| CES18 = 56 | CES43 = 77 | CES68 = 73 | CES93 = 76 |
| CES19 = 73 | CES44 = 99 | CES69 = 83 | CES94 = 48 |
| CES20 = 66 | CES45 = 83 | CES70 = 66 | CES95 = 70 |
| CES21 = 87 | CES46 = 77 | CES71 = 66 | CES96 = 76 |
| CES22 = 79 | CES47 = 74 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 62 | CES73 = 59 | CES98 = 73 |
| CES24 = 91 | CES49 = 77 | CES74 = 93 | CES99 = 60 |
| CES25 = 73 | CES50 = 85 | CES75 = 67 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)