

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P1214887

Luminaire Tested: 22-ID2-70-CFD2-L940-U

Issue Date: 12/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P1214887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2506-458-13)
Test Lab: INNOVATION CENTER
Issue Date: 12/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: 22-ID2-70-CFD2-L940-U
Description: 2X2 IN DEPTH TROFFER WITH 2INCH CUBE DROP LENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6752.7 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.31
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 2' x H: 0.16')
CIE Type: Direct

Input Watts (W): 62.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P1214887
CATALOG NUMBER: 22-ID2-70-CFD2-L940-U

Luminous Intensity Polar Plot



TEST NUMBER: P1214887

CATALOG NUMBER: 22-ID2-70-CFD2-L940-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	118	118	118	118	115	115	115	115	109	109	109		103	103	103		98
1	107	102	98	94	104	100	95	92	95	91	88		90	87	85		86
2	97	89	82	76	94	87	80	75	83	77	73		79	74	70		75
3	89	78	70	63	86	76	69	62	73	66	61		69	64	59		66
4	81	69	60	54	79	68	59	53	65	58	52		62	56	51		59
5	75	62	53	46	72	61	52	46	58	51	45		56	49	44		53
6	69	56	47	40	67	55	46	40	52	45	39		50	44	39		48
7	64	51	42	36	62	50	41	36	48	40	35		46	39	34		44
8	60	46	38	32	58	45	37	32	44	37	31		42	36	31		41
9	56	43	34	29	54	42	34	29	40	33	28		39	33	28		38
10	52	39	31	26	51	39	31	26	37	30	26		36	30	25		35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6438	6438	6438
5°	6389	6364	6389
10°	6307	6264	6307
15°	6196	6129	6194
20°	6048	5976	6041
25°	5888	5792	5869
30°	5690	5583	5660
35°	5483	5368	5460
40°	5274	5132	5233
45°	5051	4909	5024
50°	4845	4667	4791
55°	4637	4445	4595
60°	4435	4211	4372
65°	4236	3977	4146
70°	3976	3705	3911
75°	3689	3375	3617
80°	3361	2984	3298
85°	3072	2666	2979

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5051 cd/sqm

TEST NUMBER: P1214887
 CATALOG NUMBER: 22-ID2-70-CFD2-L940-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.9	3.3
10°-20°	639.4	9.5
20°-30°	944.8	14.0
30°-40°	1101.1	16.3
40°-50°	1106.2	16.4
50°-60°	984.8	14.6
60°-70°	767.6	11.4
70°-80°	489.5	7.2
80°-90°	220.1	3.3
90°-100°	102.1	1.5
100°-110°	73.7	1.1
110°-120°	49.1	0.7
120°-130°	28.4	0.4
130°-140°	13.9	0.2
140°-150°	5.0	0.1
150°-160°	0.9	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1810.1	26.8
0°-40°	2911.2	43.1
0°-60°	5002.3	74.1
0°-90°	6479.5	96.0
90°-120°	224.9	3.3
90°-150°	272.3	4.0
90°-180°	273.0	4.0
0°-180°	6752.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2392	2392	2392	2392	2392	
5°	2382	2379	2379	2380	2382	226
15°	2272	2270	2267	2268	2271	640
25°	2057	2055	2054	2050	2050	947
35°	1763	1764	1764	1755	1755	1103
45°	1433	1440	1436	1430	1426	1107
55°	1101	1106	1100	1096	1091	987
65°	779	782	776	772	763	769
75°	461	468	462	460	452	489
85°	190	198	198	196	185	182
90°	103	112	116	113	105	60
95°	86	93	96	94	87	69
105°	68	69	72	70	67	72
115°	50	49	51	48	49	49
125°	33	31	32	30	32	30
135°	20	18	17	17	20	16
145°	11	8	5	8	10	7
155°	2	2	1	2	2	1
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

TEST NUMBER: P1214887

CATALOG NUMBER: 22-ID2-70-CFD2-L940-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2392.4	2392.4	2392.4	2392.4	2392.4
2.5°	2390.7	2389.1	2388.2	2389.9	2392.4
5°	2381.6	2379.1	2379.1	2379.9	2381.6
7.5°	2364.1	2362.4	2360.8	2363.3	2364.9
10°	2340.8	2339.1	2338.3	2339.1	2340.8
12.5°	2310.9	2306.7	2306.7	2308.4	2310.9
15°	2271.8	2270.1	2266.8	2268.4	2270.9
17.5°	2224.3	2226.0	2221.9	2222.7	2223.5
20°	2173.6	2172.8	2172.8	2171.9	2171.1
22.5°	2119.5	2116.2	2115.4	2112.0	2114.5
25°	2057.1	2054.7	2053.8	2049.7	2050.5
27.5°	1989.8	1986.4	1983.9	1982.3	1980.6
30°	1915.7	1915.7	1914.1	1910.7	1905.8
32.5°	1842.5	1841.7	1839.2	1835.0	1833.4
35°	1762.7	1764.3	1763.5	1755.2	1755.2
37.5°	1686.1	1686.1	1682.8	1677.8	1671.2
40°	1602.1	1603.8	1599.6	1593.8	1589.7
42.5°	1518.9	1520.6	1518.1	1514.0	1506.5
45°	1433.3	1439.9	1435.8	1429.9	1425.8
47.5°	1350.9	1356.7	1350.9	1346.8	1340.9
50°	1267.7	1271.9	1265.2	1261.9	1253.6
52.5°	1185.4	1189.5	1184.5	1181.2	1172.9
55°	1101.4	1105.5	1100.5	1096.4	1091.4
57.5°	1021.5	1024.8	1020.7	1018.2	1009.0
60°	938.3	943.3	935.8	933.3	925.0
62.5°	855.1	865.1	856.0	852.6	845.2
65°	779.4	781.9	776.1	771.9	762.8
67.5°	696.3	701.2	694.6	691.3	682.9
70°	616.4	622.2	617.2	613.9	606.4
72.5°	538.2	546.5	538.2	535.7	528.2
75°	460.8	467.5	461.7	460.0	451.7
77.5°	386.8	394.3	386.8	389.3	381.0
80°	315.3	323.6	316.1	317.8	309.4
82.5°	252.0	257.0	254.5	252.9	244.6
85°	190.5	198.0	198.0	195.5	184.7
87.5°	139.7	146.4	148.9	148.1	138.1
90°	103.1	112.3	115.6	113.1	104.8
92.5°	93.2	100.7	104.0	101.5	94.0
95°	86.5	93.2	95.7	94.0	87.3
97.5°	81.5	86.5	89.0	86.5	81.5
100°	77.4	80.7	83.2	80.7	76.5
102.5°	72.4	74.9	77.4	74.9	71.5
105°	68.2	69.0	71.5	69.9	67.4
107.5°	64.1	64.1	65.7	64.1	62.4
110°	59.1	59.1	60.7	59.1	57.4

TEST NUMBER: P1214887

CATALOG NUMBER: 22-ID2-70-CFD2-L940-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	54.1	54.1	55.7	53.2	53.2
115°	49.9	49.1	50.7	48.2	49.1
117.5°	44.9	44.1	45.8	43.3	44.1
120°	40.8	39.1	40.8	38.3	39.9
122.5°	37.4	34.9	36.6	34.1	35.8
125°	33.3	30.8	32.4	29.9	32.4
127.5°	29.9	26.6	28.3	25.8	28.3
130°	26.6	23.3	24.1	21.6	25.8
132.5°	23.3	20.0	20.8	19.1	22.5
135°	20.0	17.5	16.6	16.6	20.0
137.5°	17.5	15.0	13.3	14.1	16.6
140°	15.0	12.5	10.0	11.6	14.1
142.5°	12.5	10.0	7.5	10.0	12.5
145°	10.8	8.3	5.0	7.5	10.0
147.5°	8.3	6.7	2.5	5.8	7.5
150°	6.7	4.2	0.8	4.2	5.0
152.5°	4.2	3.3	0.8	2.5	3.3
155°	2.5	1.7	0.8	1.7	2.5
157.5°	0.8	0.8	0.8	0.8	0.8
160°	0.8	0.8	0.8	0.8	0.8
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1214887

CATALOG NUMBER: 22-ID2-70-CFD2-L940-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.89	18.44	17.32	18.84	19.26	16.84	18.39	17.27	18.79	19.20
	3H	18.73	20.14	19.17	20.55	21.00	18.65	20.06	19.09	20.47	20.93
	4H	19.46	20.78	19.92	21.21	21.69	19.37	20.69	19.83	21.12	21.60
	6H	20.04	21.27	20.52	21.72	22.20	19.95	21.18	20.42	21.62	22.11
	8H	20.26	21.44	20.75	21.91	22.40	20.16	21.34	20.65	21.81	22.30
	12H	20.45	21.57	20.94	22.04	22.56	20.34	21.47	20.84	21.93	22.46
4H	2H	17.49	18.82	17.95	19.25	19.72	17.45	18.77	17.91	19.20	19.68
	3H	19.56	20.67	20.03	21.15	21.65	19.49	20.60	19.96	21.08	21.58
	4H	20.42	21.44	20.91	21.92	22.45	20.34	21.36	20.83	21.84	22.37
	6H	21.15	22.04	21.66	22.55	23.10	21.06	21.95	21.58	22.47	23.01
	8H	21.43	22.27	21.95	22.78	23.34	21.34	22.17	21.86	22.69	23.25
	12H	21.68	22.43	22.22	22.98	23.54	21.58	22.33	22.12	22.88	23.44
8H	4H	20.74	21.57	21.26	22.09	22.65	20.67	21.50	21.19	22.02	22.58
	6H	21.61	22.31	22.16	22.87	23.43	21.53	22.23	22.08	22.79	23.35
	8H	21.98	22.62	22.55	23.19	23.77	21.90	22.53	22.47	23.10	23.68
	12H	22.34	22.90	22.90	23.46	24.10	22.24	22.80	22.81	23.36	24.01
12H	4H	20.78	21.53	21.32	22.08	22.64	20.71	21.46	21.25	22.01	22.57
	6H	21.68	22.31	22.25	22.88	23.46	21.60	22.24	22.17	22.81	23.39
	8H	22.12	22.68	22.69	23.24	23.89	22.04	22.60	22.61	23.16	23.81

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Corelite

Report Number: SP1-2506-458-11

Test Date: 08/26/2025

Luminaire Tested: 22ID2-55-CFR1-L940-U

Data in this report applies to families of products including 22ID2-55-CFR1-L940-U


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-458-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/27/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Corelite
 Catalog Number: **22ID2-55-CFR1-L940-U**
 Description: 2X2 CGTX WITH INDEPTH FRAME AND CFR1 LENS - 5500 LUMEN 4000K 90CRI

Spectral Parameters

CCT (K): 3910
 CIE u' : 0.2263
 CIE v' : 0.5043
 Duv: 0.0008
 CIE x: 0.3851
 CIE y: 0.3813
 CIE z: 0.2336
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 578
 Purity: 30.01895
 R_f: 90.8
 R_g: 98.8

CRI (Ra): 92.4
 R1: 92.5
 R2: 94.9
 R3: 95.8
 R4: 92.7
 R5: 91.7
 R6: 92.1
 R7: 94.3
 R8: 85.2
 R9: 62.0
 R10: 87.0
 R11: 92.8
 R12: 71.7
 R13: 93.2
 R14: 97.3
 R15: 89.6



Test Conditions


Stabilization Time: 31M
 Operation Time: 1H 31M
 Sphere Temperature (°C): 25.2.

REPORT NUMBER: SP1-2506-458-11


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-458-11

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-458-11

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.75

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.61


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	394	NR	620	868	NR	750	58	NR	880	1	NR
365	0	NR	495	449	NR	625	858	NR	755	49	NR	885	1	NR
370	0	NR	500	505	NR	630	839	NR	760	42	NR	890	1	NR
375	0	NR	505	553	NR	635	813	NR	765	36	NR	895	1	NR
380	0	NR	510	593	NR	640	783	NR	770	31	NR	900	1	NR
385	0	NR	515	628	NR	645	746	NR	775	26	NR	905	1	NR
390	1	NR	520	651	NR	650	702	NR	780	22	NR	910	0	NR
395	4	NR	525	670	NR	655	657	NR	785	19	NR	915	0	NR
400	5	NR	530	687	NR	660	607	NR	790	16	NR	920	0	NR
405	8	NR	535	705	NR	665	559	NR	795	14	NR	925	0	NR
410	12	NR	540	717	NR	670	507	NR	800	12	NR	930	0	NR
415	19	NR	545	731	NR	675	458	NR	805	10	NR	935	0	NR
420	34	NR	550	745	NR	680	413	NR	810	9	NR	940	0	NR
425	60	NR	555	757	NR	685	367	NR	815	7	NR	945	0	NR
430	107	NR	560	767	NR	690	328	NR	820	6	NR	950	0	NR
435	194	NR	565	777	NR	695	289	NR	825	5	NR	955	0	NR
440	349	NR	570	785	NR	700	253	NR	830	5	NR	960	0	NR
445	678	NR	575	794	NR	705	221	NR	835	4	NR	965	0	NR
450	997	NR	580	809	NR	710	192	NR	840	3	NR	970	0	NR
455	819	NR	585	820	NR	715	165	NR	845	3	NR	975	0	NR
460	581	NR	590	838	NR	720	144	NR	850	2	NR	980	0	NR
465	517	NR	595	851	NR	725	124	NR	855	2	NR	985	0	NR
470	406	NR	600	861	NR	730	107	NR	860	2	NR	990	0	NR
475	327	NR	605	873	NR	735	91	NR	865	2	NR	995	0	NR
480	330	NR	610	875	NR	740	78	NR	870	1	NR	1000	0	NR
485	356	NR	615	877	NR	745	67	NR	875	1	NR			

REPORT NUMBER: SP1-2506-458-11





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.8$
 $CIE R_a = 92.4$
 $R_9 = 62.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 85
CES02 = 62	CES27 = 90	CES52 = 98	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 96
CES05 = 49	CES30 = 90	CES55 = 90	CES80 = 93
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 91	CES57 = 91	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 93	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 96	CES60 = 91	CES85 = 83
CES11 = 57	CES36 = 79	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 84	CES87 = 91
CES13 = 43	CES38 = 85	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 95	CES67 = 83	CES92 = 79
CES18 = 56	CES43 = 95	CES68 = 86	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 84	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 97	CES72 = 93	CES97 = 96
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)