

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268518

Luminaire Tested: P3AS02R159740DE010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268518  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R159740DE010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 298.0 lumens  
Efficiency: N/A  
Efficacy: 82.8 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268518

CATALOG NUMBER: P3AS02R159740DE010 E3CB1MMS

### Luminous Intensity Polar Plot



TEST NUMBER: P1268518

CATALOG NUMBER: P3AS02R159740DE010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 |  | 104 | 103 | 103 |  | 101 |
| 2   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 101 |  | 102 | 101 | 99  |  | 99  |
| 3   | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 100 | 102 | 100 | 98  |  | 100 | 98  | 97  |  | 98  |
| 4   | 107 | 103 | 100 | 97  | 106 | 102 | 99  | 97  | 100 | 97  | 96  |  | 98  | 96  | 94  |  | 97  |
| 5   | 105 | 100 | 97  | 94  | 104 | 99  | 96  | 94  | 98  | 95  | 93  |  | 96  | 94  | 92  |  | 95  |
| 6   | 103 | 98  | 94  | 92  | 102 | 97  | 94  | 92  | 96  | 93  | 91  |  | 95  | 92  | 91  |  | 94  |
| 7   | 101 | 96  | 92  | 90  | 100 | 95  | 92  | 90  | 94  | 91  | 89  |  | 93  | 91  | 89  |  | 92  |
| 8   | 99  | 94  | 90  | 88  | 98  | 93  | 90  | 88  | 93  | 90  | 88  |  | 92  | 89  | 87  |  | 91  |
| 9   | 97  | 92  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 88  | 86  |  | 90  | 88  | 86  |  | 90  |
| 10  | 96  | 90  | 87  | 85  | 95  | 90  | 87  | 85  | 89  | 87  | 85  |  | 89  | 86  | 85  |  | 88  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 579230 |
| 5°  | 485471 |
| 10° | 228675 |
| 15° | 68945  |
| 20° | 25506  |
| 25° | 9920   |
| 30° | 3697   |
| 35° | 1124   |
| 40° | 401    |
| 45° | 217    |
| 50° | 171    |
| 55° | 191    |
| 60° | 219    |
| 65° | 104    |
| 70° | 128    |
| 75° | 169    |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 60°

Luminance: 219 cd/sqm

TEST NUMBER: P1268518

CATALOG NUMBER: P3AS02R159740DE010 E3CB1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 170.5  | 57.2      |
| 10°-20°   | 101.4  | 34.0      |
| 20°-30°   | 21.3   | 7.1       |
| 30°-40°   | 3.4    | 1.1       |
| 40°-50°   | 0.6    | 0.2       |
| 50°-60°   | 0.4    | 0.2       |
| 60°-70°   | 0.2    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 293.1  | 98.4      |
| 0°-40°    | 296.6  | 99.5      |
| 0°-60°    | 297.6  | 99.9      |
| 0°-90°    | 298.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 298.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2642 |      |
| 5°  | 2206 | 171  |
| 15° | 304  | 101  |
| 25° | 41   | 21   |
| 35° | 4    | 3    |
| 45° | 1    | 1    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1268518

CATALOG NUMBER: P3AS02R159740DE010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2641.5 |
| 1°    | 2633.3 |
| 2°    | 2591.4 |
| 3°    | 2507.5 |
| 4°    | 2384.5 |
| 5°    | 2205.5 |
| 6°    | 1995.1 |
| 7°    | 1754.5 |
| 8°    | 1524.8 |
| 9°    | 1264.7 |
| 10°   | 1027.0 |
| 12.5° | 554.1  |
| 15°   | 303.7  |
| 17.5° | 177.9  |
| 20°   | 109.3  |
| 22.5° | 66.9   |
| 25°   | 41.0   |
| 27.5° | 24.7   |
| 30°   | 14.6   |
| 32.5° | 8.2    |
| 35°   | 4.2    |
| 37.5° | 2.4    |
| 40°   | 1.4    |
| 42.5° | 0.9    |
| 45°   | 0.7    |
| 47.5° | 0.5    |
| 50°   | 0.5    |
| 52.5° | 0.5    |
| 55°   | 0.5    |
| 57.5° | 0.5    |
| 60°   | 0.5    |
| 62.5° | 0.2    |
| 65°   | 0.2    |
| 67.5° | 0.2    |
| 70°   | 0.2    |
| 72.5° | 0.2    |
| 75°   | 0.2    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)