

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284800

Luminaire Tested: P3AS13R30B2750DE010 E3DL1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3DL1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 814.9 lumens
Efficiency: N/A
Efficacy: 42.7 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284800

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284800

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95						
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90						
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86						
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82						
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78						
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75						
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71						
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69						
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66						
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	475576
5°	452651
10°	380732
15°	274576
20°	170325
25°	96852
30°	53806
35°	29259
40°	15429
45°	8342
50°	4469
55°	2944
60°	2719
65°	2802
70°	2436
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8342 cd/sqm

TEST NUMBER: P1284800

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.2	22.7
10°-20°	329.2	40.4
20°-30°	190.2	23.3
30°-40°	72.2	8.9
40°-50°	22.2	2.7
50°-60°	7.5	0.9
60°-70°	5.0	0.6
70°-80°	2.7	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.5	86.5
0°-40°	776.7	95.3
0°-60°	806.3	98.9
0°-90°	814.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	814.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2169	
5°	2056	185
15°	1210	329
25°	400	190
35°	109	72
45°	27	22
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1284800

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2168.8
1°	2167.3
2°	2154.2
3°	2129.5
4°	2098.7
5°	2056.4
6°	2002.5
7°	1942.5
8°	1875.5
9°	1795.4
10°	1709.9
11°	1617.6
12°	1519.8
13°	1417.4
14°	1313.4
15°	1209.5
17.5°	953.9
20°	729.9
22.5°	541.2
25°	400.3
27.5°	291.0
30°	212.5
32.5°	153.2
35°	109.3
37.5°	76.2
40°	53.9
42.5°	37.7
45°	26.9
47.5°	18.5
50°	13.1
52.5°	9.2
55°	7.7
57.5°	6.9
60°	6.2
62.5°	5.4
65°	5.4
67.5°	4.6
70°	3.8
72.5°	3.1
75°	2.3
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.0



TEST NUMBER: P1284800

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1WMH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)