

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250297

Luminaire Tested: P3A24R259027D010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250297
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R259027D010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1451.0 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250297

CATALOG NUMBER: P3A24R259027D010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1250297

CATALOG NUMBER: P3A24R259027D010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344841
5°	336627
10°	311929
15°	277822
20°	238744
25°	202923
30°	167064
35°	130179
40°	93661
45°	59417
50°	35137
55°	24200
60°	22191
65°	20651
70°	18529
75°	16860
80°	16037
85°	13586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 59417 cd/sqm

TEST NUMBER: P1250297

CATALOG NUMBER: P3A24R259027D010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.8	9.8
10°-20°	339.7	23.4
20°-30°	383.9	26.5
30°-40°	303.6	20.9
40°-50°	153.4	10.6
50°-60°	61.4	4.2
60°-70°	39.3	2.7
70°-80°	21.7	1.5
80°-90°	6.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	865.4	59.6
0°-40°	1169.0	80.6
0°-60°	1383.8	95.4
0°-90°	1451.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1451.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1573	
5°	1529	142
15°	1224	340
25°	839	384
35°	486	304
45°	192	153
55°	63	61
65°	40	39
75°	20	22
85°	5	6
90°	0	

TEST NUMBER: P1250297

CATALOG NUMBER: P3A24R259027D010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1572.6
1°	1572.6
2°	1567.2
3°	1558.2
4°	1545.5
5°	1529.3
6°	1509.4
7°	1485.9
8°	1460.6
9°	1431.7
10°	1400.9
11°	1366.6
12°	1334.0
13°	1296.1
14°	1259.9
15°	1223.8
17.5°	1122.5
20°	1023.1
22.5°	929.1
25°	838.7
27.5°	750.2
30°	659.8
32.5°	574.8
35°	486.3
37.5°	404.9
40°	327.2
42.5°	254.9
45°	191.6
47.5°	142.8
50°	103.0
52.5°	77.7
55°	63.3
57.5°	57.8
60°	50.6
62.5°	45.2
65°	39.8
67.5°	34.3
70°	28.9
72.5°	25.3
75°	19.9
77.5°	16.3
80°	12.7
82.5°	9.0
85°	5.4
87.5°	1.8



TEST NUMBER: P1250297

CATALOG NUMBER: P3A24R259027D010 E3DLD1WH

CANDELA DISTRIBUTION (continued):



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2508-518-1

Test Date: 09/09/2025

Luminaire Tested: LD3A24R159027D010 E3D1LI

Data in this report applies to families of products including LD3A24R159027D010 E3D1LI


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2508-518-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/16/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A24R159027D010 E3D1LI**
 Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3D1LI TRIM

Spectral Parameters

CCT (K): 2737
 CIE u': 0.2605
 CIE v': 0.5285
 Duv: 0.0013
 CIE x: 0.4590
 CIE y: 0.4138
 CIE z: 0.1272
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 62.00127
 Rf: 90.8
 Rg: 99.1

CRI (Ra): 91.4
 R1: 92.1
 R2: 95.0
 R3: 97.1
 R4: 93.2
 R5: 91.6
 R6: 95.8
 R7: 90.2
 R8: 76.6
 R9: 46.0
 R10: 87.1
 R11: 94.9
 R12: 83.0
 R13: 92.7
 R14: 97.1
 R15: 85.9



Test Conditions


Stabilization Time: 70M
 Operation Time: 2H 10M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2508-518-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2508-518-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2508-518-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	100	NR	620	447	NR	750	16	NR	880	0	NR
365	0	NR	495	123	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	148	NR	630	1000	NR	760	11	NR	890	0	NR
375	0	NR	505	173	NR	635	764	NR	765	10	NR	895	0	NR
380	0	NR	510	194	NR	640	317	NR	770	9	NR	900	0	NR
385	0	NR	515	211	NR	645	298	NR	775	7	NR	905	0	NR
390	0	NR	520	224	NR	650	271	NR	780	7	NR	910	0	NR
395	1	NR	525	235	NR	655	232	NR	785	6	NR	915	0	NR
400	1	NR	530	245	NR	660	202	NR	790	5	NR	920	0	NR
405	3	NR	535	255	NR	665	175	NR	795	4	NR	925	0	NR
410	5	NR	540	265	NR	670	160	NR	800	4	NR	930	0	NR
415	8	NR	545	273	NR	675	137	NR	805	3	NR	935	0	NR
420	15	NR	550	284	NR	680	119	NR	810	3	NR	940	0	NR
425	24	NR	555	295	NR	685	104	NR	815	2	NR	945	0	NR
430	38	NR	560	309	NR	690	91	NR	820	2	NR	950	0	NR
435	60	NR	565	321	NR	695	79	NR	825	2	NR	955	0	NR
440	88	NR	570	336	NR	700	68	NR	830	2	NR	960	0	NR
445	121	NR	575	350	NR	705	59	NR	835	1	NR	965	0	NR
450	158	NR	580	367	NR	710	51	NR	840	1	NR	970	0	NR
455	161	NR	585	384	NR	715	44	NR	845	1	NR	975	0	NR
460	128	NR	590	398	NR	720	38	NR	850	1	NR	980	0	NR
465	100	NR	595	407	NR	725	33	NR	855	1	NR	985	0	NR
470	83	NR	600	420	NR	730	28	NR	860	1	NR	990	0	NR
475	74	NR	605	431	NR	735	24	NR	865	1	NR	995	0	NR
480	73	NR	610	486	NR	740	20	NR	870	1	NR	1000	0	NR
485	82	NR	615	541	NR	745	17	NR	875	1	NR			

REPORT NUMBER: SP1-2508-518-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	100	NR	620	447	NR	750	16	NR	880	0	NR
365	0	NR	495	123	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	148	NR	630	1000	NR	760	11	NR	890	0	NR
375	0	NR	505	173	NR	635	764	NR	765	10	NR	895	0	NR
380	0	NR	510	194	NR	640	317	NR	770	9	NR	900	0	NR
385	0	NR	515	211	NR	645	298	NR	775	7	NR	905	0	NR
390	0	NR	520	224	NR	650	271	NR	780	7	NR	910	0	NR
395	1	NR	525	235	NR	655	232	NR	785	6	NR	915	0	NR
400	1	NR	530	245	NR	660	202	NR	790	5	NR	920	0	NR
405	3	NR	535	255	NR	665	175	NR	795	4	NR	925	0	NR
410	5	NR	540	265	NR	670	160	NR	800	4	NR	930	0	NR
415	8	NR	545	273	NR	675	137	NR	805	3	NR	935	0	NR
420	15	NR	550	284	NR	680	119	NR	810	3	NR	940	0	NR
425	24	NR	555	295	NR	685	104	NR	815	2	NR	945	0	NR
430	38	NR	560	309	NR	690	91	NR	820	2	NR	950	0	NR
435	60	NR	565	321	NR	695	79	NR	825	2	NR	955	0	NR
440	88	NR	570	336	NR	700	68	NR	830	2	NR	960	0	NR
445	121	NR	575	350	NR	705	59	NR	835	1	NR	965	0	NR
450	158	NR	580	367	NR	710	51	NR	840	1	NR	970	0	NR
455	161	NR	585	384	NR	715	44	NR	845	1	NR	975	0	NR
460	128	NR	590	398	NR	720	38	NR	850	1	NR	980	0	NR
465	100	NR	595	407	NR	725	33	NR	855	1	NR	985	0	NR
470	83	NR	600	420	NR	730	28	NR	860	1	NR	990	0	NR
475	74	NR	605	431	NR	735	24	NR	865	1	NR	995	0	NR
480	73	NR	610	486	NR	740	20	NR	870	1	NR	1000	0	NR
485	82	NR	615	541	NR	745	17	NR	875	1	NR			

REPORT NUMBER: SP1-2508-518-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.37


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	100	NR	620	447	NR	750	16	NR	880	0	NR
365	0	NR	495	123	NR	625	443	NR	755	13	NR	885	0	NR
370	0	NR	500	148	NR	630	1000	NR	760	11	NR	890	0	NR
375	0	NR	505	173	NR	635	764	NR	765	10	NR	895	0	NR
380	0	NR	510	194	NR	640	317	NR	770	9	NR	900	0	NR
385	0	NR	515	211	NR	645	298	NR	775	7	NR	905	0	NR
390	0	NR	520	224	NR	650	271	NR	780	7	NR	910	0	NR
395	1	NR	525	235	NR	655	232	NR	785	6	NR	915	0	NR
400	1	NR	530	245	NR	660	202	NR	790	5	NR	920	0	NR
405	3	NR	535	255	NR	665	175	NR	795	4	NR	925	0	NR
410	5	NR	540	265	NR	670	160	NR	800	4	NR	930	0	NR
415	8	NR	545	273	NR	675	137	NR	805	3	NR	935	0	NR
420	15	NR	550	284	NR	680	119	NR	810	3	NR	940	0	NR
425	24	NR	555	295	NR	685	104	NR	815	2	NR	945	0	NR
430	38	NR	560	309	NR	690	91	NR	820	2	NR	950	0	NR
435	60	NR	565	321	NR	695	79	NR	825	2	NR	955	0	NR
440	88	NR	570	336	NR	700	68	NR	830	2	NR	960	0	NR
445	121	NR	575	350	NR	705	59	NR	835	1	NR	965	0	NR
450	158	NR	580	367	NR	710	51	NR	840	1	NR	970	0	NR
455	161	NR	585	384	NR	715	44	NR	845	1	NR	975	0	NR
460	128	NR	590	398	NR	720	38	NR	850	1	NR	980	0	NR
465	100	NR	595	407	NR	725	33	NR	855	1	NR	985	0	NR
470	83	NR	600	420	NR	730	28	NR	860	1	NR	990	0	NR
475	74	NR	605	431	NR	735	24	NR	865	1	NR	995	0	NR
480	73	NR	610	486	NR	740	20	NR	870	1	NR	1000	0	NR
485	82	NR	615	541	NR	745	17	NR	875	1	NR			

REPORT NUMBER: SP1-2508-518-1





TM-30-18

Summary

$R_f = 90.8$
 $R_g = 99.1$
 $CIE R_a = 91.4$
 $R_9 = 46.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 91	CES51 = 98	CES76 = 89
CES02 = 64	CES27 = 96	CES52 = 98	CES77 = 85
CES03 = 32	CES28 = 96	CES53 = 95	CES78 = 87
CES04 = 71	CES29 = 91	CES54 = 97	CES79 = 89
CES05 = 51	CES30 = 97	CES55 = 97	CES80 = 91
CES06 = 51	CES31 = 92	CES56 = 94	CES81 = 70
CES07 = 44	CES32 = 85	CES57 = 93	CES82 = 96
CES08 = 42	CES33 = 94	CES58 = 95	CES83 = 93
CES09 = 29	CES34 = 94	CES59 = 97	CES84 = 96
CES10 = 77	CES35 = 97	CES60 = 97	CES85 = 80
CES11 = 59	CES36 = 91	CES61 = 95	CES86 = 74
CES12 = 66	CES37 = 94	CES62 = 95	CES87 = 92
CES13 = 44	CES38 = 98	CES63 = 92	CES88 = 95
CES14 = 74	CES39 = 97	CES64 = 93	CES89 = 81
CES15 = 72	CES40 = 95	CES65 = 88	CES90 = 96
CES16 = 48	CES41 = 95	CES66 = 91	CES91 = 86
CES17 = 50	CES42 = 93	CES67 = 90	CES92 = 76
CES18 = 57	CES43 = 93	CES68 = 92	CES93 = 85
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 70
CES20 = 68	CES45 = 96	CES70 = 89	CES95 = 85
CES21 = 87	CES46 = 94	CES71 = 88	CES96 = 91
CES22 = 79	CES47 = 88	CES72 = 96	CES97 = 94
CES23 = 92	CES48 = 92	CES73 = 85	CES98 = 92
CES24 = 91	CES49 = 93	CES74 = 89	CES99 = 89
CES25 = 72	CES50 = 98	CES75 = 88	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)