

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1432465

Luminaire Tested: EHBR1-48-UNV-ASM-L830-UPL40

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1432465
REPORT IS A COMBINATION OF REPORTS P1431842 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-48-UNV-ASM-L830-UPL40
Description: Elevate Round Highbay at, 48000 lumens, 3000K 80CRI LEDs with ASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 48102.0 lumens
Efficiency: N/A
Efficacy: 166.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.99 / 0.92
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 289.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1432465
CATALOG NUMBER: EHBR1-48-UNV-ASM-L830-UPL40

Luminous Intensity Polar Plot





TEST NUMBER: P1432465

CATALOG NUMBER: EHBR1-48-UNV-ASM-L830-UPL40

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	95	92
1	110	107	103	101	107	104	101	98	98	96	94	93	91	90	88	87	86	88	87	86	83
2	103	97	92	88	100	95	90	86	90	86	83	86	83	80	82	80	77	82	80	77	75
3	97	89	83	78	94	87	81	77	83	78	75	79	76	72	76	73	70	76	73	70	68
4	91	82	75	70	88	80	74	69	77	72	68	74	69	66	71	67	64	71	67	64	62
5	85	75	69	64	83	74	68	63	71	66	62	69	64	60	66	62	59	66	62	59	57
6	80	70	63	58	78	69	62	58	66	61	57	64	59	56	62	58	55	62	58	55	53
7	76	65	58	54	74	64	58	53	62	56	52	60	55	51	58	54	51	58	54	51	49
8	72	61	54	50	70	60	54	49	58	53	49	57	52	48	55	50	47	55	50	47	46
9	68	57	50	46	66	56	50	46	55	49	45	53	48	45	52	47	44	52	47	44	43
10	64	54	47	43	63	53	47	43	52	46	42	50	45	42	49	45	41	49	45	41	40

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	186761	186761	186761	186761	186761
5°	175992	178049	185625	194528	198027
10°	166562	170089	183343	200773	203111
15°	153858	157967	177930	198714	188754
20°	137044	141660	166409	182656	151354
25°	114849	119196	147285	153207	104867
30°	85930	90912	119590	118396	68223
35°	57206	60660	85773	84388	44183
40°	36077	38555	55456	55813	30454
45°	25705	26774	35186	36698	23590
50°	21411	21582	26130	26810	20045
55°	18900	18944	21333	21897	18260
60°	17500	17351	18473	18864	17394
65°	16704	16554	16840	17168	16776
70°	16224	15944	15961	16268	16437
75°	15425	14958	14927	15455	15901
80°	14034	13055	13112	14034	15011
85°	10221	8484	8484	9700	10719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 112.5°
 Vertical Angle: 45°
 Luminance: 49470 cd/sqm



TEST NUMBER: P1432465
 CATALOG NUMBER: EHBR1-48-UNV-ASM-L830-UPL40

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3781.5	7.9
10°-20°	10287.7	21.4
20°-30°	12065.4	25.1
30°-40°	8390.7	17.4
40°-50°	4169.8	8.7
50°-60°	2494.0	5.2
60°-70°	1755.4	3.6
70°-80°	1130.8	2.4
80°-90°	365.6	0.8
90°-100°	97.7	0.2
100°-110°	635.9	1.3
110°-120°	1174.3	2.4
120°-130°	698.3	1.5
130°-140°	422.8	0.9
140°-150°	293.0	0.6
150°-160°	191.7	0.4
160°-170°	110.6	0.2
170°-180°	36.9	0.1
0°-30°	26134.6	54.3
0°-40°	34525.4	71.8
0°-60°	41189.1	85.6
0°-90°	44440.9	92.4
90°-120°	1907.9	4.0
90°-150°	3321.9	6.9
90°-180°	3661.0	7.6
0°-180°	48102.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	39770	39770	39770	39770	39770	
5°	37577	38016	39634	41535	42282	3525
15°	32279	33141	37329	41689	39600	9002
25°	22935	23803	29413	30595	20942	10348
35°	10499	11133	15742	15488	8109	6688
45°	4159	4332	5693	5938	3817	3362
55°	2554	2560	2883	2959	2468	2317
65°	1744	1728	1758	1792	1751	1731
75°	1087	1054	1052	1089	1120	1147
85°	351	292	292	333	368	362
90°	27	73	27	79	32	30
95°	45	164	52	142	50	44
105°	222	1109	292	1184	150	296
115°	1015	1312	1250	1452	1068	935
125°	733	703	800	780	839	668
135°	536	540	507	565	586	419
145°	446	467	459	470	480	283
155°	398	410	410	410	427	185
165°	380	389	388	387	400	108
175°	381	387	387	386	395	36
180°	387	387	387	387	387	



TEST NUMBER: P1432465
 CATALOG NUMBER: EHBR1-48-UNV-ASM-L830-UPL40

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	39769.5	39769.5	39769.5	39769.5	39769.5	39769.5	39769.5	39769.5	39769.5
2.5°	38589.0	38614.3	38884.3	39235.6	39746.4	40260.2	40676.3	40950.8	41086.5
5°	37577.0	37717.2	38016.3	38661.4	39633.8	40662.9	41534.7	42105.2	42281.9
7.5°	36591.2	36672.4	37172.8	37988.0	39364.5	40967.9	42263.3	42929.2	43091.8
10°	35388.3	35572.5	36137.8	37099.0	38953.7	41160.3	42657.0	43134.3	43153.7
12.5°	33972.9	34216.8	34800.7	36013.3	38298.2	41091.7	42525.0	42368.4	42012.7
15°	32278.6	32492.6	33140.7	34547.1	37328.7	40685.3	41689.1	40414.6	39599.5
17.5°	30448.6	30642.5	31205.4	32754.4	35962.5	39924.6	39944.0	37422.6	35884.9
20°	28166.6	28318.7	29115.2	30635.0	34201.9	38704.6	37541.2	32929.6	31107.7
22.5°	25738.4	25880.9	26588.6	28170.3	31994.4	37059.5	34195.1	28409.6	25924.2
25°	22935.2	23012.8	23803.3	25233.5	29412.7	35043.8	30595.4	23484.8	20941.8
27.5°	19781.5	19913.5	20740.5	22201.4	26376.0	32488.9	26762.3	19190.8	16844.7
30°	16528.6	16747.0	17486.9	18794.9	23003.0	29213.6	22773.4	15283.2	13122.7
32.5°	13492.6	13650.0	14177.3	15544.2	19226.6	26003.1	18942.5	12245.8	10415.7
35°	10499.3	10656.7	11133.2	12475.5	15742.5	21986.6	15488.3	9622.2	8109.2
37.5°	8025.6	8303.8	8609.6	9699.1	12354.6	18191.5	12346.5	7748.3	6577.4
40°	6253.0	6297.8	6682.6	7379.9	9611.9	14224.2	9673.8	6185.2	5278.4
42.5°	5005.4	5127.0	5292.5	5814.5	7282.9	10876.6	7603.5	5076.2	4483.4
45°	4159.0	4206.8	4332.0	4682.5	5692.9	8004.0	5937.6	4282.8	3816.7
47.5°	3638.5	3617.6	3698.1	3960.6	4636.2	6185.9	4812.2	3673.5	3346.9
50°	3191.0	3178.3	3216.4	3391.6	3894.3	4746.6	3995.6	3206.6	2987.4
52.5°	2843.5	2854.7	2858.5	2967.3	3345.4	3871.1	3402.8	2857.7	2710.0
55°	2554.1	2568.4	2560.1	2640.7	2883.0	3254.4	2959.1	2569.9	2467.7
57.5°	2328.2	2317.8	2306.6	2349.8	2531.8	2760.8	2569.9	2324.4	2256.6
60°	2103.8	2094.0	2085.9	2114.2	2220.8	2390.9	2267.8	2110.4	2091.0
62.5°	1911.4	1905.4	1904.6	1899.4	1981.4	2088.9	2005.3	1918.0	1900.9
65°	1743.5	1736.8	1727.9	1719.7	1757.7	1857.7	1792.0	1745.0	1751.0
67.5°	1575.7	1575.7	1560.1	1547.4	1584.7	1636.9	1608.5	1581.7	1588.5
70°	1423.6	1424.4	1399.0	1389.3	1400.5	1456.4	1427.4	1431.1	1442.3
72.5°	1260.3	1242.4	1223.7	1223.0	1224.5	1267.7	1258.1	1267.0	1279.0
75°	1086.6	1065.7	1053.7	1040.3	1051.5	1084.3	1088.7	1101.5	1120.1
77.5°	918.7	886.7	876.9	870.3	862.8	900.1	914.3	931.5	959.0
80°	738.3	703.2	686.8	677.1	689.8	706.9	738.3	751.0	789.7
82.5°	545.9	519.8	499.6	498.9	504.9	520.5	547.4	571.2	593.6
85°	351.3	309.5	291.6	298.3	291.6	315.5	333.4	361.7	368.4
87.5°	126.7	99.2	94.7	104.4	102.2	109.6	125.2	136.5	137.2
90°	27.0	43.2	73.4	47.2	27.0	45.9	79.0	44.9	32.2
92.5°	39.1	65.4	117.8	61.3	35.0	62.0	111.3	59.0	42.3
95°	45.1	75.4	164.2	81.5	52.0	76.2	141.5	65.0	50.4
97.5°	58.0	83.5	188.5	99.7	80.2	94.3	159.7	69.1	60.5
100°	76.2	97.6	293.5	122.6	106.5	106.5	290.8	79.2	68.6
102.5°	128.7	206.6	622.4	229.6	160.9	208.1	673.1	156.6	82.7
105°	221.5	434.7	1108.9	479.9	292.2	474.5	1183.8	400.8	150.1
107.5°	383.0	777.8	1462.9	849.2	552.6	884.3	1524.9	788.4	345.8
110°	714.1	1032.2	1533.5	1166.1	883.6	1235.5	1664.2	1079.1	697.1



TEST NUMBER: P1432465
 CATALOG NUMBER: EHBR1-48-UNV-ASM-L830-UPL40

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	964.3	1108.9	1468.9	1287.2	1150.0	1376.8	1625.8	1196.2	963.5
115°	1014.7	1066.5	1311.5	1257.0	1249.7	1356.6	1452.3	1192.1	1068.4
117.5°	980.5	973.6	1113.7	1130.6	1207.2	1241.6	1254.4	1119.5	1074.5
120°	907.8	866.6	930.0	987.3	1090.2	1076.1	1057.4	1012.5	1014.0
122.5°	817.0	768.5	797.5	840.7	943.6	913.3	893.9	904.2	931.2
125°	732.9	683.7	703.4	714.2	800.3	770.0	779.6	811.4	839.1
127.5°	658.2	625.2	636.8	625.4	680.0	665.8	696.8	732.6	756.3
130°	607.8	579.5	595.2	567.6	593.9	597.2	638.3	668.8	683.7
132.5°	566.1	548.0	566.3	532.8	540.1	555.6	594.6	621.1	629.9
135°	535.9	520.4	540.1	509.4	506.6	529.3	565.1	582.0	585.5
137.5°	510.4	497.0	517.4	493.9	487.2	509.9	536.8	550.5	547.1
140°	487.7	476.3	498.0	479.8	475.8	498.5	510.6	526.2	523.7
142.5°	462.9	454.9	480.5	468.4	464.4	485.1	491.2	502.7	499.5
145°	446.2	440.2	467.1	460.4	459.1	474.5	469.8	484.6	480.0
147.5°	431.5	427.5	451.7	449.1	449.1	460.4	454.3	467.1	462.5
150°	418.9	414.9	438.3	435.6	437.5	445.6	436.9	451.7	451.2
152.5°	406.3	401.5	422.9	420.1	422.2	430.2	422.2	439.0	437.8
155°	397.6	392.9	410.3	408.8	409.5	413.6	409.5	426.4	427.1
157.5°	391.8	388.3	401.7	400.9	400.9	403.7	401.7	416.6	417.3
160°	387.2	384.5	395.9	395.1	393.9	397.9	396.6	409.4	410.2
162.5°	382.7	379.9	393.3	391.3	391.3	391.3	390.8	403.6	405.1
165°	380.2	379.5	388.7	388.7	387.5	389.5	387.0	396.5	400.1
167.5°	380.2	378.1	388.3	388.3	387.0	385.0	386.5	394.7	398.3
170°	379.6	378.9	387.0	385.7	383.7	384.4	384.0	392.2	395.8
172.5°	381.1	380.4	389.2	387.2	385.9	385.9	384.1	390.3	395.9
175°	380.7	379.9	386.7	386.7	387.4	386.2	385.6	389.9	395.4
177.5°	383.4	382.6	386.7	386.7	385.5	387.0	388.4	392.6	400.2
180°	387.0	387.0	387.0	387.0	387.0	387.0	387.0	387.0	387.0



TEST NUMBER: P1432465
 CATALOG NUMBER: EHBR1-48-UNV-ASM-L830-UPL40

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.06	19.15	18.55	19.62	20.12	18.82	19.91	19.32	20.38	20.89
	3H	19.87	20.84	20.38	21.33	21.88	20.38	21.35	20.89	21.84	22.39
	4H	20.61	21.51	21.14	22.02	22.58	21.03	21.93	21.56	22.44	23.00
	6H	21.17	22.01	21.72	22.53	23.11	21.52	22.36	22.07	22.87	23.45
	8H	21.36	22.15	21.92	22.68	23.27	21.68	22.47	22.24	23.00	23.59
	12H	21.46	22.21	22.02	22.74	23.35	21.76	22.51	22.32	23.04	23.65
4H	2H	18.57	19.48	19.11	19.98	20.55	19.20	20.11	19.74	20.61	21.18
	3H	20.61	21.36	21.15	21.91	22.49	21.01	21.76	21.55	22.30	22.89
	4H	21.47	22.15	22.04	22.70	23.33	21.79	22.47	22.36	23.02	23.65
	6H	22.17	22.75	22.76	23.33	23.97	22.43	23.01	23.02	23.59	24.23
	8H	22.39	22.93	22.99	23.52	24.16	22.63	23.17	23.23	23.75	24.40
	12H	22.53	23.01	23.14	23.62	24.27	22.75	23.22	23.36	23.84	24.49
8H	4H	21.73	22.27	22.33	22.86	23.50	22.03	22.58	22.63	23.16	23.80
	6H	22.55	22.99	23.17	23.62	24.27	22.80	23.24	23.42	23.87	24.52
	8H	22.85	23.24	23.49	23.88	24.55	23.08	23.47	23.72	24.11	24.78
	12H	23.05	23.39	23.69	24.02	24.76	23.26	23.61	23.90	24.23	24.97
12H	4H	21.74	22.22	22.35	22.83	23.48	22.04	22.52	22.66	23.14	23.78
	6H	22.59	22.98	23.23	23.62	24.29	22.84	23.23	23.49	23.88	24.54
	8H	22.93	23.28	23.57	23.90	24.64	23.17	23.51	23.81	24.14	24.88

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-2

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L830-N

Data in this report applies to families of products including EHBR-60-L830-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L830-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 2983
 CIE u': 0.2516
 CIE v': 0.5201
 Duv: -0.0012
 CIE x: 0.4364
 CIE y: 0.4010
 CIE z: 0.1626
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 51.34918
 Rf: 81.2
 Rg: 101.5

CRI (Ra):	83.4		
R1:	84.0	R9:	29.4
R2:	87.5	R10:	68.6
R3:	88.9	R11:	82.2
R4:	83.8	R12:	61.6
R5:	81.9	R13:	83.9
R6:	83.1	R14:	92.5
R7:	87.1	R15:	79.8
R8:	70.9		



Test Conditions

Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	43	NR	620	294	NR	750	6	NR	880	0	NR
365	0	NR	495	59	NR	625	294	NR	755	5	NR	885	0	NR
370	0	NR	500	81	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	109	NR	635	637	NR	765	4	NR	895	0	NR
380	0	NR	510	135	NR	640	175	NR	770	3	NR	900	0	NR
385	0	NR	515	160	NR	645	171	NR	775	3	NR	905	0	NR
390	1	NR	520	180	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	195	NR	655	119	NR	785	2	NR	915	0	NR
400	2	NR	530	207	NR	660	99	NR	790	2	NR	920	0	NR
405	3	NR	535	218	NR	665	82	NR	795	2	NR	925	0	NR
410	5	NR	540	227	NR	670	76	NR	800	1	NR	930	0	NR
415	10	NR	545	237	NR	675	61	NR	805	1	NR	935	0	NR
420	20	NR	550	247	NR	680	52	NR	810	1	NR	940	0	NR
425	35	NR	555	259	NR	685	44	NR	815	1	NR	945	0	NR
430	58	NR	560	271	NR	690	38	NR	820	1	NR	950	0	NR
435	90	NR	565	283	NR	695	33	NR	825	1	NR	955	0	NR
440	135	NR	570	293	NR	700	27	NR	830	1	NR	960	0	NR
445	204	NR	575	303	NR	705	24	NR	835	1	NR	965	0	NR
450	233	NR	580	310	NR	710	20	NR	840	0	NR	970	0	NR
455	153	NR	585	313	NR	715	17	NR	845	0	NR	975	0	NR
460	98	NR	590	314	NR	720	15	NR	850	0	NR	980	0	NR
465	76	NR	595	310	NR	725	13	NR	855	0	NR	985	0	NR
470	53	NR	600	307	NR	730	11	NR	860	0	NR	990	0	NR
475	39	NR	605	303	NR	735	9	NR	865	0	NR	995	0	NR
480	35	NR	610	331	NR	740	8	NR	870	0	NR	1000	0	NR
485	36	NR	615	353	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	43	NR	620	294	NR	750	6	NR	880	0	NR
365	0	NR	495	59	NR	625	294	NR	755	5	NR	885	0	NR
370	0	NR	500	81	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	109	NR	635	637	NR	765	4	NR	895	0	NR
380	0	NR	510	135	NR	640	175	NR	770	3	NR	900	0	NR
385	0	NR	515	160	NR	645	171	NR	775	3	NR	905	0	NR
390	1	NR	520	180	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	195	NR	655	119	NR	785	2	NR	915	0	NR
400	2	NR	530	207	NR	660	99	NR	790	2	NR	920	0	NR
405	3	NR	535	218	NR	665	82	NR	795	2	NR	925	0	NR
410	5	NR	540	227	NR	670	76	NR	800	1	NR	930	0	NR
415	10	NR	545	237	NR	675	61	NR	805	1	NR	935	0	NR
420	20	NR	550	247	NR	680	52	NR	810	1	NR	940	0	NR
425	35	NR	555	259	NR	685	44	NR	815	1	NR	945	0	NR
430	58	NR	560	271	NR	690	38	NR	820	1	NR	950	0	NR
435	90	NR	565	283	NR	695	33	NR	825	1	NR	955	0	NR
440	135	NR	570	293	NR	700	27	NR	830	1	NR	960	0	NR
445	204	NR	575	303	NR	705	24	NR	835	1	NR	965	0	NR
450	233	NR	580	310	NR	710	20	NR	840	0	NR	970	0	NR
455	153	NR	585	313	NR	715	17	NR	845	0	NR	975	0	NR
460	98	NR	590	314	NR	720	15	NR	850	0	NR	980	0	NR
465	76	NR	595	310	NR	725	13	NR	855	0	NR	985	0	NR
470	53	NR	600	307	NR	730	11	NR	860	0	NR	990	0	NR
475	39	NR	605	303	NR	735	9	NR	865	0	NR	995	0	NR
480	35	NR	610	331	NR	740	8	NR	870	0	NR	1000	0	NR
485	36	NR	615	353	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.34

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	43	NR	620	294	NR	750	6	NR	880	0	NR
365	0	NR	495	59	NR	625	294	NR	755	5	NR	885	0	NR
370	0	NR	500	81	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	109	NR	635	637	NR	765	4	NR	895	0	NR
380	0	NR	510	135	NR	640	175	NR	770	3	NR	900	0	NR
385	0	NR	515	160	NR	645	171	NR	775	3	NR	905	0	NR
390	1	NR	520	180	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	195	NR	655	119	NR	785	2	NR	915	0	NR
400	2	NR	530	207	NR	660	99	NR	790	2	NR	920	0	NR
405	3	NR	535	218	NR	665	82	NR	795	2	NR	925	0	NR
410	5	NR	540	227	NR	670	76	NR	800	1	NR	930	0	NR
415	10	NR	545	237	NR	675	61	NR	805	1	NR	935	0	NR
420	20	NR	550	247	NR	680	52	NR	810	1	NR	940	0	NR
425	35	NR	555	259	NR	685	44	NR	815	1	NR	945	0	NR
430	58	NR	560	271	NR	690	38	NR	820	1	NR	950	0	NR
435	90	NR	565	283	NR	695	33	NR	825	1	NR	955	0	NR
440	135	NR	570	293	NR	700	27	NR	830	1	NR	960	0	NR
445	204	NR	575	303	NR	705	24	NR	835	1	NR	965	0	NR
450	233	NR	580	310	NR	710	20	NR	840	0	NR	970	0	NR
455	153	NR	585	313	NR	715	17	NR	845	0	NR	975	0	NR
460	98	NR	590	314	NR	720	15	NR	850	0	NR	980	0	NR
465	76	NR	595	310	NR	725	13	NR	855	0	NR	985	0	NR
470	53	NR	600	307	NR	730	11	NR	860	0	NR	990	0	NR
475	39	NR	605	303	NR	735	9	NR	865	0	NR	995	0	NR
480	35	NR	610	331	NR	740	8	NR	870	0	NR	1000	0	NR
485	36	NR	615	353	NR	745	7	NR	875	0	NR			

Summary

$R_f = 81.2$
 $R_g = 101.5$
 CIE $R_a = 83.4$
 $R_9 = 29.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 71	CES51 = 89	CES76 = 65
CES02 = 63	CES27 = 89	CES52 = 89	CES77 = 82
CES03 = 31	CES28 = 86	CES53 = 80	CES78 = 67
CES04 = 70	CES29 = 68	CES54 = 92	CES79 = 89
CES05 = 50	CES30 = 77	CES55 = 90	CES80 = 85
CES06 = 51	CES31 = 70	CES56 = 81	CES81 = 75
CES07 = 43	CES32 = 64	CES57 = 79	CES82 = 93
CES08 = 41	CES33 = 74	CES58 = 81	CES83 = 89
CES09 = 29	CES34 = 76	CES59 = 92	CES84 = 91
CES10 = 76	CES35 = 87	CES60 = 96	CES85 = 81
CES11 = 59	CES36 = 99	CES61 = 91	CES86 = 74
CES12 = 65	CES37 = 81	CES62 = 93	CES87 = 83
CES13 = 44	CES38 = 83	CES63 = 79	CES88 = 86
CES14 = 74	CES39 = 94	CES64 = 81	CES89 = 74
CES15 = 72	CES40 = 89	CES65 = 78	CES90 = 85
CES16 = 48	CES41 = 88	CES66 = 76	CES91 = 87
CES17 = 50	CES42 = 80	CES67 = 74	CES92 = 73
CES18 = 57	CES43 = 75	CES68 = 79	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 67	CES45 = 83	CES70 = 72	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 70	CES96 = 86
CES22 = 79	CES47 = 79	CES72 = 90	CES97 = 85
CES23 = 92	CES48 = 78	CES73 = 65	CES98 = 83
CES24 = 91	CES49 = 79	CES74 = 94	CES99 = 82
CES25 = 72	CES50 = 88	CES75 = 70	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)