

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1436447

Luminaire Tested: EHBR1-36-UNV-M-L930-UPL30

Issue Date: 3/25/2026

Test Information

Test Method: LM-79-2019
Report Number: P1436447
REPORT IS A COMBINATION OF REPORTS P1436087 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/25/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-36-UNV-M-L930-UPL30
Description: Elevate Round Highbay at, 36000 lumens, 3000K 90CRI LEDs with M lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 34957.8 lumens
Efficiency: N/A
Efficacy: 163.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.15
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 213.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1436447
CATALOG NUMBER: EHBR1-36-UNV-M-L930-UPL30

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1436447

CATALOG NUMBER: EHBR1-36-UNV-M-L930-UPL30

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	95	92
1	110	106	103	100	106	103	100	98	98	95	93	93	91	89	88	87	85	88	87	85	83
2	102	96	91	86	99	93	89	85	89	85	82	85	82	79	81	78	76	81	78	76	74
3	95	87	81	76	92	85	79	74	81	76	72	78	73	70	74	71	68	74	71	68	66
4	89	79	72	67	86	77	71	66	74	69	64	71	67	63	68	64	61	68	64	61	59
5	83	72	65	60	80	71	64	59	68	62	58	66	61	57	63	59	55	63	59	55	53
6	78	67	59	54	75	65	58	53	63	57	52	61	55	51	58	54	50	58	54	50	48
7	73	61	54	49	71	60	53	48	58	52	48	56	51	47	54	50	46	54	50	46	44
8	68	57	49	44	66	56	49	44	54	48	43	52	47	43	51	46	42	51	46	42	40
9	64	53	46	41	62	52	45	40	50	44	40	49	43	39	47	42	39	47	42	39	37
10	60	49	42	38	59	48	42	37	47	41	37	45	40	36	44	39	36	44	39	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	89661	89661	89661
5°	89508	89508	89508
10°	89928	89928	89928
15°	90445	90445	90445
20°	90171	90171	90171
25°	88065	88065	88065
30°	82348	82348	82348
35°	71717	71717	71717
40°	54963	54963	54963
45°	35906	35906	35906
50°	22635	22635	22635
55°	16873	16873	16873
60°	14206	14206	14206
65°	12918	12918	12918
70°	11767	11767	11767
75°	10073	10073	10073
80°	7758	7758	7758
85°	4068	4068	4068

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35906 cd/sqm



TEST NUMBER: P1436447
 CATALOG NUMBER: EHBR1-36-UNV-M-L930-UPL30

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1823.6	5.2
10°-20°	5355.2	15.3
20°-30°	8035.2	23.0
30°-40°	8084.3	23.1
40°-50°	4627.6	13.2
50°-60°	2116.6	6.1
60°-70°	1342.9	3.8
70°-80°	753.3	2.2
80°-90°	181.5	0.5
90°-100°	75.2	0.2
100°-110°	471.2	1.3
110°-120°	842.7	2.4
120°-130°	494.5	1.4
130°-140°	303.3	0.9
140°-150°	210.4	0.6
150°-160°	136.7	0.4
160°-170°	77.9	0.2
170°-180°	25.7	0.1
0°-30°	15214.0	43.5
0°-40°	23298.3	66.6
0°-60°	30042.5	85.9
0°-90°	32320.2	92.5
90°-120°	1389.2	4.0
90°-150°	2397.3	6.9
90°-180°	2638.0	7.5
0°-180°	34957.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	19093	19093	19093	19093	19093	
5°	19111	19111	19111	19111	19111	1824
15°	18975	18975	18975	18975	18975	5355
25°	17587	17587	17587	17587	17587	8035
35°	13163	13163	13163	13163	13163	8084
45°	5809	5809	5809	5809	5809	4628
55°	2280	2280	2280	2280	2280	2117
65°	1348	1348	1348	1348	1348	1343
75°	710	710	710	710	710	753
85°	140	140	140	140	140	171
90°	20	32	54	35	20	15
95°	33	56	122	60	38	32
105°	165	325	829	358	217	220
115°	758	797	980	939	933	698
125°	546	510	524	532	596	498
135°	399	386	400	376	374	312
145°	328	323	343	338	337	208
155°	287	284	298	298	298	134
165°	269	269	276	276	275	77
175°	266	266	270	270	270	25
180°	269	269	269	269	269	



TEST NUMBER: P1436447

CATALOG NUMBER: EHBR1-36-UNV-M-L930-UPL30

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	19092.7	19092.7	19092.7	19092.7	19092.7
2.5°	19102.1	19102.1	19102.1	19102.1	19102.1
5°	19111.4	19111.4	19111.4	19111.4	19111.4
7.5°	19098.3	19098.3	19098.3	19098.3	19098.3
10°	19106.5	19106.5	19106.5	19106.5	19106.5
12.5°	19073.7	19073.7	19073.7	19073.7	19073.7
15°	18974.8	18974.8	18974.8	18974.8	18974.8
17.5°	18811.4	18811.4	18811.4	18811.4	18811.4
20°	18532.8	18532.8	18532.8	18532.8	18532.8
22.5°	18149.8	18149.8	18149.8	18149.8	18149.8
25°	17586.6	17586.6	17586.6	17586.6	17586.6
27.5°	16828.9	16828.9	16828.9	16828.9	16828.9
30°	15839.6	15839.6	15839.6	15839.6	15839.6
32.5°	14668.2	14668.2	14668.2	14668.2	14668.2
35°	13162.7	13162.7	13162.7	13162.7	13162.7
37.5°	11457.1	11457.1	11457.1	11457.1	11457.1
40°	9526.5	9526.5	9526.5	9526.5	9526.5
42.5°	7612.7	7612.7	7612.7	7612.7	7612.7
45°	5809.4	5809.4	5809.4	5809.4	5809.4
47.5°	4373.2	4373.2	4373.2	4373.2	4373.2
50°	3373.4	3373.4	3373.4	3373.4	3373.4
52.5°	2725.5	2725.5	2725.5	2725.5	2725.5
55°	2280.2	2280.2	2280.2	2280.2	2280.2
57.5°	1952.5	1952.5	1952.5	1952.5	1952.5
60°	1707.8	1707.8	1707.8	1707.8	1707.8
62.5°	1518.8	1518.8	1518.8	1518.8	1518.8
65°	1348.3	1348.3	1348.3	1348.3	1348.3
67.5°	1191.5	1191.5	1191.5	1191.5	1191.5
70°	1032.5	1032.5	1032.5	1032.5	1032.5
72.5°	872.4	872.4	872.4	872.4	872.4
75°	709.6	709.6	709.6	709.6	709.6
77.5°	555.0	555.0	555.0	555.0	555.0
80°	408.1	408.1	408.1	408.1	408.1
82.5°	266.1	266.1	266.1	266.1	266.1
85°	139.8	139.8	139.8	139.8	139.8
87.5°	39.9	39.9	39.9	39.9	39.9
90°	19.6	31.7	54.4	34.8	19.6
92.5°	28.7	48.3	87.6	45.3	25.7
95°	33.2	55.9	122.3	60.4	37.8
97.5°	42.2	61.9	140.4	74.0	58.9
100°	55.9	72.4	219.0	90.6	78.5
102.5°	95.1	154.0	465.0	170.7	119.3
105°	164.6	324.6	828.9	357.9	217.4
107.5°	285.3	581.3	1093.2	634.1	412.2
110°	533.0	771.5	1146.0	871.2	659.8



TEST NUMBER: P1436447

CATALOG NUMBER: EHBR1-36-UNV-M-L930-UPL30

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	720.2	828.9	1097.7	961.8	859.1
115°	757.9	797.2	979.9	939.2	933.1
117.5°	732.2	727.8	832.0	844.0	901.4
120°	677.9	647.8	694.6	736.8	813.8
122.5°	610.0	573.7	594.9	626.6	703.6
125°	546.5	510.4	523.9	531.5	596.4
127.5°	490.8	466.5	474.1	465.0	505.8
130°	453.0	431.8	442.4	421.2	440.8
132.5°	421.2	407.7	419.7	394.1	400.1
135°	398.6	386.5	400.1	376.0	374.5
137.5°	379.0	368.4	382.0	363.9	359.3
140°	360.8	351.8	366.9	353.3	350.3
142.5°	341.2	335.2	353.3	344.2	341.2
145°	327.7	323.1	342.7	338.2	336.7
147.5°	315.6	312.5	330.7	329.2	329.2
150°	305.0	302.0	320.1	318.6	320.1
152.5°	294.4	291.4	308.0	306.5	308.0
155°	286.9	283.8	297.5	297.5	297.5
157.5°	280.8	279.3	289.9	289.9	289.9
160°	276.3	274.8	283.8	283.8	282.3
162.5°	271.8	270.3	280.8	279.3	279.3
165°	268.8	268.8	276.3	276.3	274.8
167.5°	268.8	267.3	274.8	274.8	273.3
170°	267.3	267.3	273.3	271.8	270.3
172.5°	267.3	267.3	273.3	271.8	270.3
175°	265.7	265.7	270.3	270.3	270.3
177.5°	267.3	267.3	270.3	270.3	268.8
180°	268.8	268.8	268.8	268.8	268.8



TEST NUMBER: P1436447
 CATALOG NUMBER: EHBR1-36-UNV-M-L930-UPL30

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.90	19.05	18.40	19.52	20.02	17.90	19.05	18.40	19.52	20.02
	3H	19.38	20.41	19.89	20.89	21.44	19.38	20.41	19.89	20.89	21.44
	4H	19.91	20.86	20.44	21.36	21.93	19.91	20.86	20.44	21.36	21.93
	6H	20.23	21.11	20.78	21.62	22.20	20.23	21.11	20.78	21.62	22.20
	8H	20.30	21.13	20.86	21.66	22.25	20.30	21.13	20.86	21.66	22.25
	12H	20.31	21.10	20.87	21.63	22.24	20.31	21.10	20.87	21.63	22.24
4H	2H	18.34	19.29	18.87	19.79	20.36	18.34	19.29	18.87	19.79	20.36
	3H	20.03	20.82	20.58	21.36	21.94	20.03	20.82	20.58	21.36	21.94
	4H	20.66	21.37	21.22	21.92	22.54	20.66	21.37	21.22	21.92	22.54
	6H	21.09	21.69	21.67	22.27	22.91	21.09	21.69	21.67	22.27	22.91
	8H	21.18	21.75	21.77	22.33	22.97	21.18	21.75	21.77	22.33	22.97
	12H	21.21	21.71	21.82	22.32	22.97	21.21	21.71	21.82	22.32	22.97
8H	4H	20.84	21.40	21.43	21.98	22.63	20.84	21.40	21.43	21.98	22.63
	6H	21.35	21.81	21.97	22.44	23.09	21.35	21.81	21.97	22.44	23.09
	8H	21.49	21.90	22.13	22.54	23.20	21.49	21.90	22.13	22.54	23.20
	12H	21.55	21.92	22.19	22.54	23.27	21.55	21.92	22.19	22.54	23.27
12H	4H	20.82	21.32	21.44	21.94	22.58	20.82	21.32	21.44	21.94	22.58
	6H	21.35	21.76	21.99	22.40	23.07	21.35	21.76	21.99	22.40	23.07
	8H	21.52	21.88	22.16	22.50	23.24	21.52	21.88	22.16	22.50	23.24

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-5

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L930-N

Data in this report applies to families of products including EHBR-60-L930-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L930-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 2996
 CIE u': 0.2519
 CIE v': 0.5169
 Duv: -0.0033
 CIE x: 0.4325
 CIE y: 0.3945
 CIE z: 0.1730
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 48.21818
 Rf: 91.3
 Rg: 102

CRI (Ra):	94.4		
R1:	96.8	R9:	61.4
R2:	98.1	R10:	94.4
R3:	97.8	R11:	95.7
R4:	95.6	R12:	88.5
R5:	96.9	R13:	97.3
R6:	95.7	R14:	97.8
R7:	90.9	R15:	92.3
R8:	83.0		



Test Conditions

Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2506-472-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.85

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 102$
 $CIE R_a = 94.4$
 $R_9 = 61.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 96	CES76 = 89
CES02 = 63	CES27 = 96	CES52 = 95	CES77 = 85
CES03 = 32	CES28 = 96	CES53 = 93	CES78 = 86
CES04 = 70	CES29 = 90	CES54 = 98	CES79 = 89
CES05 = 51	CES30 = 96	CES55 = 98	CES80 = 91
CES06 = 51	CES31 = 90	CES56 = 95	CES81 = 72
CES07 = 44	CES32 = 84	CES57 = 95	CES82 = 95
CES08 = 42	CES33 = 91	CES58 = 95	CES83 = 93
CES09 = 29	CES34 = 92	CES59 = 99	CES84 = 96
CES10 = 76	CES35 = 96	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 77
CES12 = 65	CES37 = 94	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 99	CES63 = 94	CES88 = 96
CES14 = 74	CES39 = 97	CES64 = 96	CES89 = 82
CES15 = 72	CES40 = 94	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 94	CES66 = 95	CES91 = 82
CES17 = 50	CES42 = 91	CES67 = 94	CES92 = 78
CES18 = 57	CES43 = 88	CES68 = 93	CES93 = 87
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 73
CES20 = 67	CES45 = 93	CES70 = 90	CES95 = 85
CES21 = 86	CES46 = 93	CES71 = 90	CES96 = 92
CES22 = 79	CES47 = 86	CES72 = 96	CES97 = 93
CES23 = 92	CES48 = 95	CES73 = 85	CES98 = 94
CES24 = 91	CES49 = 91	CES74 = 90	CES99 = 93
CES25 = 72	CES50 = 96	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)