

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433310

Luminaire Tested: EHBR1-54-UNV-A1-L930-UPL30

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433310
REPORT IS A COMBINATION OF REPORTS P1431864 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-54-UNV-A1-L930-UPL30
Description: Elevate Round Highbay at, 53000 lumens, 3000K 90CRI LEDs with A lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 50517.8 lumens
Efficiency: N/A
Efficacy: 158.9 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 1.07 / 0.95
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 318
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433310
CATALOG NUMBER: EHBR1-54-UNV-A1-L930-UPL30

Luminous Intensity Polar Plot





TEST NUMBER: P1433310
 CATALOG NUMBER: EHBR1-54-UNV-A1-L930-UPL30

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	97	97	97	97	97	97	95	
1	110	107	104	101	107	104	101	99	99	97	95	94	92	91	90	88	87	87	87	87	85	
2	103	97	92	87	100	95	90	86	90	87	83	86	83	81	83	80	78	78	78	78	76	
3	96	88	82	77	94	86	81	76	83	78	74	80	76	72	76	73	70	70	70	70	68	
4	90	81	74	69	88	79	73	68	76	71	67	73	69	65	71	67	64	64	64	64	62	
5	84	74	67	62	82	73	66	61	70	65	60	68	63	59	66	62	58	58	58	58	56	
6	79	69	61	56	77	67	61	56	65	59	55	63	58	54	61	57	53	53	53	53	52	
7	75	64	57	52	73	63	56	51	61	55	51	59	54	50	57	53	49	49	49	49	47	
8	70	59	52	47	69	58	52	47	57	51	47	55	50	46	54	49	46	46	46	46	44	
9	67	55	49	44	65	55	48	44	53	47	43	52	47	43	51	46	42	42	42	42	41	
10	63	52	45	41	62	51	45	41	50	44	40	49	44	40	48	43	39	39	39	39	38	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	180689	180689	180689	180689	180689
5°	179494	179468	179475	179792	179683
10°	175058	177098	177379	176879	173912
15°	158924	170013	173513	168650	155275
20°	132435	155541	166166	152612	127278
25°	102419	134489	154149	129578	97113
30°	74655	109525	135409	105369	70859
35°	53814	84418	111285	80782	50301
40°	38716	62350	82012	59718	37521
45°	30507	45614	57279	43636	29451
50°	25312	34272	41457	33141	24928
55°	22106	27062	31396	26608	21808
60°	19936	22590	25017	22450	20077
65°	18646	19927	21024	19989	18823
70°	17707	18130	18691	18231	17881
75°	16520	16416	16520	16461	16680
80°	14920	13848	13542	14063	14920
85°	10341	8769	8676	8909	10646

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 67.5°
 Vertical Angle: 45°
 Luminance: 60014 cd/sqm



TEST NUMBER: P1433310
 CATALOG NUMBER: EHBR1-54-UNV-A1-L930-UPL30

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3633.5	7.2
10°-20°	9765.6	19.3
20°-30°	11874.8	23.5
30°-40°	9672.9	19.1
40°-50°	5807.6	11.5
50°-60°	3342.3	6.6
60°-70°	2091.8	4.1
70°-80°	1231.9	2.4
80°-90°	365.1	0.7
90°-100°	71.7	0.1
100°-110°	474.0	0.9
110°-120°	876.7	1.7
120°-130°	520.5	1.0
130°-140°	315.4	0.6
140°-150°	219.6	0.4
150°-160°	143.9	0.3
160°-170°	82.8	0.2
170°-180°	27.6	0.1
0°-30°	25273.9	50.0
0°-40°	34946.8	69.2
0°-60°	44096.8	87.3
0°-90°	47785.6	94.6
90°-120°	1422.4	2.8
90°-150°	2477.9	4.9
90°-180°	2732.0	5.4
0°-180°	50517.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	38476	38476	38476	38476	38476	
5°	38325	38319	38321	38388	38365	3622
15°	33341	35668	36402	35382	32576	9173
25°	20453	26857	30784	25877	19393	9319
35°	9877	15494	20425	14826	9232	6249
45°	4936	7380	9268	7060	4765	3894
55°	2987	3657	4243	3596	2947	2700
65°	1946	2080	2194	2086	1965	1935
75°	1164	1156	1164	1160	1175	1233
85°	355	301	298	306	366	379
90°	21	54	20	57	20	27
95°	35	122	38	104	34	33
105°	166	829	217	883	109	222
115°	760	980	933	1084	796	700
125°	549	524	596	581	624	500
135°	403	403	378	421	436	315
145°	335	349	343	353	360	212
155°	299	307	306	308	322	140
165°	287	292	289	289	299	82
175°	290	291	288	288	296	28
180°	290	290	290	290	290	



TEST NUMBER: P1433310
 CATALOG NUMBER: EHBR1-54-UNV-A1-L930-UPL30

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	38476.4	38476.4	38476.4	38476.4	38476.4	38476.4	38476.4	38476.4	38476.4
2.5°	38391.7	38426.4	38440.9	38448.9	38457.9	38482.0	38492.4	38475.6	38490.0
5°	38324.8	38327.3	38319.2	38355.5	38320.8	38345.0	38388.5	38371.6	38365.2
7.5°	37934.8	38015.4	38062.9	38075.0	38081.4	38111.3	38142.0	37968.6	37942.9
10°	37193.4	37328.0	37627.0	37712.4	37686.6	37735.0	37580.3	37127.3	36950.1
12.5°	35568.0	36041.0	36817.9	37163.6	37100.7	37143.4	36616.4	35660.7	35111.0
15°	33341.4	34035.2	35667.9	36349.7	36402.1	36349.7	35381.8	33519.4	32575.8
17.5°	30381.4	31662.7	34066.6	35389.8	35314.1	35339.1	33501.7	30748.9	29669.0
20°	27219.2	28585.1	31968.1	34175.4	34152.0	34011.9	31366.2	27735.7	26159.4
22.5°	23642.7	25404.4	29563.4	32682.1	32673.3	32439.5	28765.6	24445.3	22748.1
25°	20453.0	22180.8	26857.3	30852.8	30783.5	30517.5	25876.6	21163.0	19393.3
27.5°	17155.4	18951.7	23968.3	28709.2	28661.6	28371.5	23114.8	18095.0	16410.8
30°	14359.8	16002.2	21067.1	26350.4	26045.8	26012.7	20267.6	15254.4	13629.7
32.5°	11964.8	13372.6	18332.0	23883.6	23344.5	23498.4	17430.2	12878.7	11268.5
35°	9876.8	11117.0	15493.7	21030.8	20424.8	20623.9	14826.4	10567.4	9232.0
37.5°	8016.0	9208.7	13088.2	18256.3	17329.5	17705.0	12536.1	8825.1	7754.9
40°	6710.5	7656.6	10806.8	15211.7	14214.8	14826.4	10350.6	7360.8	6503.4
42.5°	5782.2	6399.5	8919.4	12304.9	11540.1	11973.6	8531.0	6153.7	5512.1
45°	4935.9	5428.4	7380.2	9710.0	9267.5	9669.7	7060.2	5247.0	4765.1
47.5°	4311.4	4691.0	6075.4	7841.1	7566.3	7693.7	5896.6	4578.9	4187.3
50°	3772.3	4065.6	5107.7	6328.5	6178.6	6256.8	4939.2	3984.2	3715.1
52.5°	3353.3	3568.4	4284.0	5201.1	5127.0	5139.0	4209.0	3504.8	3309.7
55°	2987.4	3137.3	3657.1	4260.6	4242.9	4246.1	3595.8	3105.8	2947.1
57.5°	2667.4	2791.6	3142.9	3578.9	3553.1	3558.8	3113.9	2758.5	2656.1
60°	2396.6	2479.7	2715.7	3024.4	3007.5	3000.3	2698.9	2449.0	2413.6
62.5°	2156.5	2209.7	2373.3	2592.5	2560.2	2567.6	2372.5	2212.1	2159.8
65°	1946.2	1964.7	2079.9	2215.4	2194.4	2212.1	2086.4	1976.8	1964.7
67.5°	1740.7	1759.2	1826.9	1918.0	1893.8	1908.3	1828.5	1764.0	1753.6
70°	1553.7	1552.9	1590.8	1640.0	1640.0	1642.4	1599.7	1561.0	1569.0
72.5°	1360.3	1355.5	1366.7	1399.8	1390.9	1421.5	1376.5	1364.3	1365.9
75°	1163.7	1150.0	1156.4	1173.4	1163.7	1179.8	1159.6	1175.0	1175.0
77.5°	978.3	952.5	944.5	946.9	929.2	953.3	958.2	968.7	992.8
80°	784.9	748.6	728.5	727.7	712.4	727.7	739.8	761.6	784.9
82.5°	582.6	551.3	517.4	510.9	501.3	510.1	526.2	552.1	589.9
85°	355.4	322.3	301.4	290.2	298.2	298.2	306.2	342.5	365.9
87.5°	128.1	112.0	91.9	92.7	95.1	98.3	102.3	128.9	141.1
90°	21.2	31.7	54.4	34.8	19.6	33.2	57.4	30.2	20.4
92.5°	29.5	48.3	87.6	45.3	25.7	45.3	81.5	40.7	28.0
95°	34.8	55.9	122.3	60.4	37.8	55.9	104.2	45.3	34.0
97.5°	43.8	61.9	140.4	74.0	58.9	69.4	117.8	48.3	41.5
100°	57.5	72.4	219.0	90.6	78.5	78.5	215.9	55.9	48.4
102.5°	96.7	154.0	465.0	170.7	119.3	154.0	501.3	113.3	59.0
105°	166.2	324.6	828.9	357.9	217.4	353.3	883.3	295.9	108.8
107.5°	286.9	581.3	1093.2	634.1	412.2	659.8	1138.4	585.8	255.2
110°	534.6	771.5	1146.0	871.2	659.8	922.5	1242.6	803.3	518.0



TEST NUMBER: P1433310
 CATALOG NUMBER: EHBR1-54-UNV-A1-L930-UPL30

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	721.8	828.9	1097.7	961.8	859.1	1028.2	1213.9	890.8	717.3
115°	759.5	797.2	979.9	939.2	933.1	1013.1	1084.1	887.8	795.8
117.5°	734.7	727.8	832.0	844.0	901.4	927.1	936.1	833.5	800.3
120°	679.5	647.8	694.6	736.8	813.8	803.3	788.1	754.3	755.1
122.5°	612.4	574.5	594.9	626.6	703.6	680.9	665.9	672.7	693.9
125°	548.9	511.2	523.9	531.5	596.4	573.7	580.6	603.2	624.5
127.5°	493.2	467.3	474.1	465.0	505.8	495.2	518.6	545.2	562.6
130°	455.4	433.5	443.2	421.2	441.6	444.7	475.7	496.8	508.2
132.5°	424.4	410.1	422.1	395.7	401.7	414.6	443.3	462.2	468.2
135°	402.6	389.7	403.3	378.4	377.7	395.8	421.4	433.5	435.9
137.5°	383.0	372.4	386.0	367.9	363.3	381.5	401.1	410.2	408.0
140°	366.4	356.6	371.7	358.1	355.1	373.2	382.3	393.6	390.7
142.5°	347.6	341.6	359.0	349.9	346.8	364.3	368.8	376.3	374.1
145°	334.9	330.3	349.1	344.6	343.1	356.0	353.0	364.4	359.8
147.5°	325.3	321.3	337.9	336.4	336.4	345.4	341.7	351.6	347.9
150°	315.6	311.7	328.1	326.6	328.1	334.2	328.9	341.2	340.5
152.5°	305.8	301.9	316.8	314.5	316.0	322.1	317.7	330.6	330.7
155°	299.0	295.1	307.2	305.5	305.5	309.3	308.0	321.6	322.4
157.5°	295.3	292.2	301.2	299.6	299.6	301.9	302.0	314.2	315.0
160°	292.5	289.4	296.7	295.1	293.6	297.5	297.6	308.2	309.0
162.5°	289.5	286.4	294.5	292.2	291.4	292.2	292.4	303.8	304.6
165°	287.3	285.7	291.7	290.1	288.6	290.1	289.4	297.0	299.3
167.5°	288.1	285.8	291.0	289.4	287.8	286.3	288.7	294.9	297.2
170°	287.4	286.6	290.2	287.1	284.8	285.6	286.5	292.7	295.0
172.5°	289.0	288.2	291.8	288.7	286.4	287.2	286.6	291.2	295.1
175°	289.9	288.3	291.2	288.8	288.0	287.3	288.2	291.3	295.9
177.5°	292.2	290.6	292.0	289.6	287.3	288.1	290.5	293.6	299.8
180°	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5



TEST NUMBER: P1433310
 CATALOG NUMBER: EHBR1-54-UNV-A1-L930-UPL30

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.54	20.71	20.00	21.14	21.59	20.52	21.69	20.98	22.12	22.57
	3H	21.01	22.06	21.49	22.50	23.00	21.78	22.82	22.25	23.27	23.77
	4H	21.62	22.59	22.11	23.05	23.57	22.28	23.25	22.78	23.72	24.23
	6H	22.08	22.98	22.59	23.46	23.98	22.63	23.53	23.14	24.01	24.54
	8H	22.23	23.08	22.75	23.58	24.11	22.73	23.58	23.26	24.08	24.61
	12H	22.31	23.12	22.83	23.61	24.17	22.77	23.58	23.30	24.07	24.63
4H	2H	20.05	21.03	20.55	21.49	22.01	20.83	21.81	21.33	22.27	22.79
	3H	21.74	22.54	22.25	23.05	23.59	22.32	23.13	22.83	23.64	24.17
	4H	22.46	23.18	22.98	23.70	24.27	22.95	23.67	23.48	24.19	24.76
	6H	23.04	23.66	23.59	24.20	24.80	23.42	24.05	23.98	24.59	25.18
	8H	23.22	23.80	23.78	24.35	24.95	23.56	24.14	24.12	24.69	25.28
	12H	23.33	23.84	23.91	24.42	25.02	23.63	24.14	24.20	24.72	25.32
8H	4H	22.68	23.26	23.24	23.81	24.40	23.13	23.71	23.69	24.25	24.85
	6H	23.37	23.84	23.96	24.44	25.04	23.71	24.18	24.30	24.78	25.38
	8H	23.62	24.05	24.23	24.65	25.27	23.90	24.33	24.51	24.93	25.55
	12H	23.79	24.16	24.39	24.75	25.44	24.02	24.40	24.63	24.98	25.68
12H	4H	22.68	23.19	23.26	23.77	24.37	23.12	23.64	23.70	24.22	24.82
	6H	23.39	23.82	24.00	24.42	25.04	23.73	24.15	24.34	24.76	25.38
	8H	23.69	24.06	24.29	24.65	25.34	23.97	24.34	24.57	24.93	25.62

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-5

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L930-N

Data in this report applies to families of products including EHBR-60-L930-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L930-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 2996
 CIE u': 0.2519
 CIE v': 0.5169
 Duv: -0.0033
 CIE x: 0.4325
 CIE y: 0.3945
 CIE z: 0.1730
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 48.21818
 Rf: 91.3
 Rg: 102

CRI (Ra):	94.4		
R1:	96.8	R9:	61.4
R2:	98.1	R10:	94.4
R3:	97.8	R11:	95.7
R4:	95.6	R12:	88.5
R5:	96.9	R13:	97.3
R6:	95.7	R14:	97.8
R7:	90.9	R15:	92.3
R8:	83.0		



Test Conditions

Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2506-472-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.85

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 102$
 $CIE R_a = 94.4$
 $R_9 = 61.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 96	CES76 = 89
CES02 = 63	CES27 = 96	CES52 = 95	CES77 = 85
CES03 = 32	CES28 = 96	CES53 = 93	CES78 = 86
CES04 = 70	CES29 = 90	CES54 = 98	CES79 = 89
CES05 = 51	CES30 = 96	CES55 = 98	CES80 = 91
CES06 = 51	CES31 = 90	CES56 = 95	CES81 = 72
CES07 = 44	CES32 = 84	CES57 = 95	CES82 = 95
CES08 = 42	CES33 = 91	CES58 = 95	CES83 = 93
CES09 = 29	CES34 = 92	CES59 = 99	CES84 = 96
CES10 = 76	CES35 = 96	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 77
CES12 = 65	CES37 = 94	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 99	CES63 = 94	CES88 = 96
CES14 = 74	CES39 = 97	CES64 = 96	CES89 = 82
CES15 = 72	CES40 = 94	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 94	CES66 = 95	CES91 = 82
CES17 = 50	CES42 = 91	CES67 = 94	CES92 = 78
CES18 = 57	CES43 = 88	CES68 = 93	CES93 = 87
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 73
CES20 = 67	CES45 = 93	CES70 = 90	CES95 = 85
CES21 = 86	CES46 = 93	CES71 = 90	CES96 = 92
CES22 = 79	CES47 = 86	CES72 = 96	CES97 = 93
CES23 = 92	CES48 = 95	CES73 = 85	CES98 = 94
CES24 = 91	CES49 = 91	CES74 = 90	CES99 = 93
CES25 = 72	CES50 = 96	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)