

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P859879

Luminaire Tested: **SPHB-12SE-W-L940-CD**

Issue Date: 7/11/2024

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P859879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2404-343-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/11/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SPHB-12SE-W-L940-CD
Description: 12000 Lumen Standard Efficacy Select Pro High Bay with Wide Lens
and, 4000K 90CRI LEDs
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10830.0 lumens
Efficiency: N/A
Efficacy: 141.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.5 / 1.51
Luminous Opening: Rectangular (W 1' x L: 1.38' x H: 0')
CIE Type: Direct

Input Watts (W): 76.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859879

CATALOG NUMBER: SPHB-12SE-W-L940-CD

Luminous Intensity Polar Plot





TEST NUMBER: P859879

CATALOG NUMBER: SPHB-12SE-W-L940-CD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85		
2	100	92	86	81	98	91	85	80	87	82	78	84	80	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	62		
4	84	73	64	58	82	71	63	57	69	62	57	66	61	56	64	59	55	53		
5	77	65	56	50	75	64	56	50	62	55	49	60	54	49	58	52	48	46		
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40		
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36		
8	62	48	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32		
9	58	44	36	31	56	44	36	31	43	36	31	42	35	30	41	35	30	29		
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26847	26847	26847
5°	26818	27324	27972
10°	26606	28766	30946
15°	26190	30907	34087
20°	25623	33366	35790
25°	24883	35165	36259
30°	24074	36266	36161
35°	23171	36630	33742
40°	22237	34976	31870
45°	21395	31704	30577
50°	20562	28827	27107
55°	19622	26635	22059
60°	18651	23745	18166
65°	17365	20403	15752
70°	15800	17421	14247
75°	13568	14619	13061
80°	10605	12541	12114
85°	7168	10641	9988



TEST NUMBER: P859879

CATALOG NUMBER: SPHB-12SE-W-L940-CD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.9	3.1
10°-20°	1071.6	9.9
20°-30°	1753.7	16.2
30°-40°	2139.4	19.8
40°-50°	2118.8	19.6
50°-60°	1694.4	15.6
60°-70°	1057.0	9.8
70°-80°	517.9	4.8
80°-90°	135.8	1.3
90°-100°	3.6	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3163.2	29.2
0°-40°	5302.6	49.0
0°-60°	9115.7	84.2
0°-90°	10826.4	100.0
90°-120°	3.6	0.0
90°-150°	3.6	0.0
90°-180°	4.0	0.0
0°-180°	10830.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3442	3442	3442	3442	3442	
5°	3425	3440	3490	3550	3572	325
15°	3243	3432	3828	4132	4221	914
25°	2891	3381	4086	4204	4213	1331
35°	2433	3252	3847	3641	3544	1522
45°	1940	3013	2874	2778	2772	1498
55°	1443	2314	1959	1769	1622	1293
65°	941	1298	1106	917	854	933
75°	450	552	485	444	433	478
85°	80	114	119	113	112	99
90°	0	12	21	27	28	5
95°	0	2	2	1	1	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P859879

CATALOG NUMBER: SPHB-12SE-W-L940-CD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3441.9	3441.9	3441.9	3441.9	3441.9
2.5°	3438.5	3437.2	3449.7	3472.5	3482.9
5°	3425.1	3440.2	3489.8	3550.5	3572.5
7.5°	3401.0	3441.5	3550.9	3662.5	3709.9
10°	3359.2	3442.4	3631.9	3828.8	3907.2
12.5°	3316.1	3439.4	3722.0	4000.7	4086.5
15°	3243.3	3432.0	3827.5	4132.1	4221.3
17.5°	3175.7	3423.4	3929.2	4243.7	4311.4
20°	3086.9	3410.9	4019.7	4277.8	4311.8
22.5°	2993.9	3401.0	4069.7	4254.9	4265.3
25°	2891.3	3380.8	4086.0	4204.5	4213.1
27.5°	2781.9	3362.7	4070.5	4142.0	4149.4
30°	2672.9	3329.9	4026.6	4044.7	4014.9
32.5°	2558.7	3297.2	3955.5	3874.1	3804.7
35°	2433.4	3251.5	3846.9	3641.4	3543.6
37.5°	2309.7	3207.6	3677.6	3381.2	3307.5
40°	2183.9	3153.3	3435.0	3138.2	3130.0
42.5°	2065.0	3094.7	3160.6	2949.1	2976.6
45°	1939.6	3013.3	2874.1	2777.6	2772.0
47.5°	1820.7	2900.8	2613.4	2588.0	2530.7
50°	1694.5	2745.7	2375.6	2351.5	2233.9
52.5°	1570.8	2548.0	2163.2	2072.7	1901.3
55°	1442.9	2313.6	1958.6	1769.4	1622.1
57.5°	1324.0	2055.9	1750.5	1505.3	1373.1
60°	1195.6	1794.9	1522.1	1273.5	1164.5
62.5°	1069.8	1537.6	1315.3	1076.2	1003.8
65°	940.9	1298.1	1105.5	916.8	853.5
67.5°	817.7	1090.9	924.1	772.9	730.7
70°	692.8	884.9	763.9	649.3	624.7
72.5°	564.0	707.0	617.8	548.0	529.5
75°	450.2	551.5	485.1	444.2	433.4
77.5°	335.2	410.2	379.1	355.0	352.0
80°	236.1	296.0	279.2	274.4	269.7
82.5°	150.8	193.4	198.6	195.6	192.2
85°	80.1	113.7	118.9	112.9	111.6
87.5°	32.3	49.5	53.4	59.0	60.7
90°	0.4	11.6	21.1	26.7	27.6
92.5°	0.4	2.6	3.0	3.0	2.6
95°	0.4	1.7	1.7	1.3	0.9
97.5°	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P859879

CATALOG NUMBER: SPHB-12SE-W-L940-CD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

METALUX

Report Number: SP1-2404-343-7

Test Date: 05/20/2024

Luminaire Tested: SPHB-24SE-M-UNV-L940-CD


Data in this report applies to families of products SPHB-24SE-M-UNV-L940-CD.

Test Information

Test Method: LM-79-2019
Report Number: SP1-2404-343-7
Test Lab: COOPER LIGHTING SOLUTIONS
Photometer: SP1 - 76IN SPHERE
Measurement Geometry: 4π
Issue Date: 05/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: **SPHB-24SE-M-UNV-L940-CD**
Description: 18IN SPHB WITH MEDIUM LENS, 4000K/90CRI, 24K LUMENS, SE

Spectral Parameters

CCT (K):	3941	CRI (Ra):	91.2		
CIE u':	0.2264	R1:	91.4	R9:	57.5
CIE v':	0.5022	R2:	93.9	R10:	84.4
Duv:	-0.0004	R3:	94.6	R11:	91.3
CIE x:	0.3827	R4:	91.6	R12:	71.8
CIE y:	0.3773	R5:	90.6	R13:	92.0
CIE z:	0.2400	R6:	90.6	R14:	96.7
Peak Wavelength (nm):	450	R7:	93.3		
Dominant Wavelength (nm):	579	R8:	83.5		
Purity:	28.3				
Rf:	90.1				
Rg:	99.4				



Test Conditions


Stabilization Time: 24M
Operation Time: 12H
Room Temperature (°C) / RH%: 25.0/41%
Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2404-343-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	2/12/2024	8/12/2024
Power Meter	XITRON 2801 IN0071	10/23/2023	10/23/2024
AC Power Source	CHROMA 61603 IN0063	10/24/2023	10/24/2024
DC Power Source	AGILENT E3634A IN0208	10/24/2023	10/24/2024
Sphere Thermometer	ONSET IN0085	10/24/2023	10/24/2024
Room Thermometer	ONSET IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2404-343-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2404-343-7

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	7212	NR	490	108829	NR	620	250576	NR	750	21248	NR	880	7254	NR
365	6095	NR	495	125088	NR	625	245705	NR	755	19109	NR	885	6272	NR
370	6022	NR	500	141971	NR	630	239404	NR	760	17593	NR	890	6410	NR
375	7076	NR	505	156633	NR	635	230449	NR	765	15401	NR	895	7000	NR
380	6674	NR	510	169197	NR	640	221008	NR	770	13743	NR	900	6176	NR
385	6019	NR	515	179365	NR	645	209690	NR	775	11948	NR	905	6118	NR
390	5440	NR	520	187018	NR	650	198297	NR	780	11421	NR	910	6132	NR
395	4835	NR	525	194159	NR	655	185669	NR	785	10432	NR	915	6202	NR
400	4236	NR	530	200071	NR	660	170891	NR	790	9515	NR	920	7026	NR
405	4501	NR	535	205570	NR	665	157591	NR	795	8800	NR	925	5915	NR
410	5834	NR	540	209259	NR	670	143731	NR	800	7939	NR	930	6549	NR
415	8990	NR	545	213260	NR	675	128798	NR	805	7431	NR	935	6547	NR
420	15076	NR	550	217506	NR	680	115773	NR	810	7034	NR	940	7527	NR
425	25851	NR	555	222032	NR	685	103063	NR	815	7070	NR	945	7157	NR
430	43228	NR	560	224902	NR	690	91359	NR	820	7449	NR	950	8630	NR
435	72792	NR	565	228152	NR	695	79831	NR	825	7107	NR	955	7432	NR
440	127912	NR	570	230769	NR	700	71164	NR	830	6871	NR	960	6594	NR
445	221467	NR	575	234150	NR	705	62968	NR	835	6778	NR	965	9518	NR
450	284796	NR	580	238181	NR	710	55738	NR	840	6431	NR	970	8910	NR
455	233729	NR	585	241075	NR	715	49805	NR	845	7189	NR	975	10074	NR
460	172720	NR	590	245594	NR	720	43740	NR	850	5642	NR	980	8847	NR
465	143757	NR	595	248900	NR	725	39092	NR	855	7250	NR	985	7969	NR
470	112827	NR	600	251233	NR	730	34044	NR	860	8091	NR	990	6557	NR
475	92779	NR	605	253490	NR	735	30057	NR	865	6978	NR	995	10421	NR
480	91420	NR	610	255123	NR	740	26868	NR	870	7631	NR	1000	7659	NR
485	97972	NR	615	254469	NR	745	23967	NR	875	5622	NR			

REPORT NUMBER: SP1-2404-343-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: 27133.5

S/P: 1.74

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	7212	NR	490	108829	NR	620	250576	NR	750	21248	NR	880	7254	NR
365	6095	NR	495	125088	NR	625	245705	NR	755	19109	NR	885	6272	NR
370	6022	NR	500	141971	NR	630	239404	NR	760	17593	NR	890	6410	NR
375	7076	NR	505	156633	NR	635	230449	NR	765	15401	NR	895	7000	NR
380	6674	NR	510	169197	NR	640	221008	NR	770	13743	NR	900	6176	NR
385	6019	NR	515	179365	NR	645	209690	NR	775	11948	NR	905	6118	NR
390	5440	NR	520	187018	NR	650	198297	NR	780	11421	NR	910	6132	NR
395	4835	NR	525	194159	NR	655	185669	NR	785	10432	NR	915	6202	NR
400	4236	NR	530	200071	NR	660	170891	NR	790	9515	NR	920	7026	NR
405	4501	NR	535	205570	NR	665	157591	NR	795	8800	NR	925	5915	NR
410	5834	NR	540	209259	NR	670	143731	NR	800	7939	NR	930	6549	NR
415	8990	NR	545	213260	NR	675	128798	NR	805	7431	NR	935	6547	NR
420	15076	NR	550	217506	NR	680	115773	NR	810	7034	NR	940	7527	NR
425	25851	NR	555	222032	NR	685	103063	NR	815	7070	NR	945	7157	NR
430	43228	NR	560	224902	NR	690	91359	NR	820	7449	NR	950	8630	NR
435	72792	NR	565	228152	NR	695	79831	NR	825	7107	NR	955	7432	NR
440	127912	NR	570	230769	NR	700	71164	NR	830	6871	NR	960	6594	NR
445	221467	NR	575	234150	NR	705	62968	NR	835	6778	NR	965	9518	NR
450	284796	NR	580	238181	NR	710	55738	NR	840	6431	NR	970	8910	NR
455	233729	NR	585	241075	NR	715	49805	NR	845	7189	NR	975	10074	NR
460	172720	NR	590	245594	NR	720	43740	NR	850	5642	NR	980	8847	NR
465	143757	NR	595	248900	NR	725	39092	NR	855	7250	NR	985	7969	NR
470	112827	NR	600	251233	NR	730	34044	NR	860	8091	NR	990	6557	NR
475	92779	NR	605	253490	NR	735	30057	NR	865	6978	NR	995	10421	NR
480	91420	NR	610	255123	NR	740	26868	NR	870	7631	NR	1000	7659	NR
485	97972	NR	615	254469	NR	745	23967	NR	875	5622	NR			

REPORT NUMBER: SP1-2404-343-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 11042.9 M/P: 0.71


λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	7212	NR	490	108829	NR	620	250576	NR	750	21248	NR	880	7254	NR
365	6095	NR	495	125088	NR	625	245705	NR	755	19109	NR	885	6272	NR
370	6022	NR	500	141971	NR	630	239404	NR	760	17593	NR	890	6410	NR
375	7076	NR	505	156633	NR	635	230449	NR	765	15401	NR	895	7000	NR
380	6674	NR	510	169197	NR	640	221008	NR	770	13743	NR	900	6176	NR
385	6019	NR	515	179365	NR	645	209690	NR	775	11948	NR	905	6118	NR
390	5440	NR	520	187018	NR	650	198297	NR	780	11421	NR	910	6132	NR
395	4835	NR	525	194159	NR	655	185669	NR	785	10432	NR	915	6202	NR
400	4236	NR	530	200071	NR	660	170891	NR	790	9515	NR	920	7026	NR
405	4501	NR	535	205570	NR	665	157591	NR	795	8800	NR	925	5915	NR
410	5834	NR	540	209259	NR	670	143731	NR	800	7939	NR	930	6549	NR
415	8990	NR	545	213260	NR	675	128798	NR	805	7431	NR	935	6547	NR
420	15076	NR	550	217506	NR	680	115773	NR	810	7034	NR	940	7527	NR
425	25851	NR	555	222032	NR	685	103063	NR	815	7070	NR	945	7157	NR
430	43228	NR	560	224902	NR	690	91359	NR	820	7449	NR	950	8630	NR
435	72792	NR	565	228152	NR	695	79831	NR	825	7107	NR	955	7432	NR
440	127912	NR	570	230769	NR	700	71164	NR	830	6871	NR	960	6594	NR
445	221467	NR	575	234150	NR	705	62968	NR	835	6778	NR	965	9518	NR
450	284796	NR	580	238181	NR	710	55738	NR	840	6431	NR	970	8910	NR
455	233729	NR	585	241075	NR	715	49805	NR	845	7189	NR	975	10074	NR
460	172720	NR	590	245594	NR	720	43740	NR	850	5642	NR	980	8847	NR
465	143757	NR	595	248900	NR	725	39092	NR	855	7250	NR	985	7969	NR
470	112827	NR	600	251233	NR	730	34044	NR	860	8091	NR	990	6557	NR
475	92779	NR	605	253490	NR	735	30057	NR	865	6978	NR	995	10421	NR
480	91420	NR	610	255123	NR	740	26868	NR	870	7631	NR	1000	7659	NR
485	97972	NR	615	254469	NR	745	23967	NR	875	5622	NR			

REPORT NUMBER: SP1-2404-343-7





TM-30-18

Summary

$R_f = 90.1$
 $R_g = 99.4$
 $CIE R_a = 91.2$
 $R_9 = 57.5$



Color Vector Graphics




REPORT NUMBER: SP1-2404-343-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 86	CES26 = 89	CES51 = 97	CES76 = 82
CES02 = 62	CES27 = 92	CES52 = 97	CES77 = 86
CES03 = 31	CES28 = 94	CES53 = 95	CES78 = 79
CES04 = 69	CES29 = 93	CES54 = 94	CES79 = 95
CES05 = 49	CES30 = 95	CES55 = 92	CES80 = 91
CES06 = 50	CES31 = 94	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 87	CES57 = 92	CES82 = 96
CES08 = 41	CES33 = 97	CES58 = 92	CES83 = 97
CES09 = 29	CES34 = 90	CES59 = 96	CES84 = 93
CES10 = 74	CES35 = 94	CES60 = 92	CES85 = 83
CES11 = 57	CES36 = 82	CES61 = 91	CES86 = 88
CES12 = 63	CES37 = 93	CES62 = 86	CES87 = 90
CES13 = 43	CES38 = 90	CES63 = 90	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 86
CES15 = 71	CES40 = 97	CES65 = 86	CES90 = 96
CES16 = 47	CES41 = 98	CES66 = 84	CES91 = 73
CES17 = 49	CES42 = 92	CES67 = 83	CES92 = 78
CES18 = 56	CES43 = 92	CES68 = 85	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 80
CES20 = 66	CES45 = 96	CES70 = 82	CES95 = 82
CES21 = 85	CES46 = 95	CES71 = 76	CES96 = 91
CES22 = 78	CES47 = 98	CES72 = 92	CES97 = 94
CES23 = 91	CES48 = 92	CES73 = 76	CES98 = 93
CES24 = 90	CES49 = 94	CES74 = 93	CES99 = 90
CES25 = 71	CES50 = 98	CES75 = 78	



REPORT NUMBER: SP1-2404-343-7

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2404-343-7

TM-30-18

Measure Comparisons



(END OF REPORT)