

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983179

Luminaire Tested: 24CZ-LD5-45SE-UNV-L840-SQP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983179  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-45SE-UNV-L840-SQP-CD1-U  
Description: METALUX CRUZE 2x4 4500LM STANDARD EFFICACY PACKAGE 80CRI 4000K TROFFER LENS WITH PATTERN INSERT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3432.0 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.31 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983179

CATALOG NUMBER: 24CZ-LD5-45SE-UNV-L840-SQP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983179

CATALOG NUMBER: 24CZ-LD5-45SE-UNV-L840-SQP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  | 93  | 90  | 87  | 89  | 87  | 85  | 83  |    |    |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 73  | 80  | 76  | 71  | 77  | 73  | 70  | 68  |    |    |
| 3   | 89  | 78  | 69  | 62  | 86  | 76  | 68  | 62  | 73  | 66  | 61  | 70  | 64  | 59  | 68  | 63  | 58  | 56  |    |    |
| 4   | 81  | 68  | 59  | 52  | 79  | 67  | 58  | 52  | 64  | 57  | 51  | 62  | 56  | 50  | 60  | 54  | 50  | 47  |    |    |
| 5   | 74  | 61  | 52  | 45  | 72  | 60  | 51  | 44  | 58  | 50  | 44  | 56  | 49  | 43  | 54  | 48  | 43  | 41  |    |    |
| 6   | 68  | 55  | 45  | 39  | 66  | 54  | 45  | 39  | 52  | 44  | 38  | 50  | 43  | 38  | 48  | 42  | 37  | 35  |    |    |
| 7   | 63  | 49  | 40  | 34  | 62  | 49  | 40  | 34  | 47  | 39  | 34  | 45  | 39  | 33  | 44  | 38  | 33  | 31  |    |    |
| 8   | 59  | 45  | 36  | 30  | 57  | 44  | 36  | 30  | 43  | 35  | 30  | 42  | 35  | 30  | 40  | 34  | 29  | 28  |    |    |
| 9   | 55  | 41  | 33  | 27  | 54  | 41  | 33  | 27  | 39  | 32  | 27  | 38  | 32  | 27  | 37  | 31  | 27  | 25  |    |    |
| 10  | 51  | 38  | 30  | 24  | 50  | 37  | 30  | 24  | 36  | 29  | 24  | 35  | 29  | 24  | 35  | 28  | 24  | 22  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1467 | 1467 | 1467 |
| 5°  | 1469 | 1479 | 1462 |
| 10° | 1464 | 1464 | 1464 |
| 15° | 1459 | 1466 | 1474 |
| 20° | 1454 | 1469 | 1477 |
| 25° | 1436 | 1460 | 1480 |
| 30° | 1425 | 1449 | 1491 |
| 35° | 1410 | 1449 | 1510 |
| 40° | 1395 | 1451 | 1545 |
| 45° | 1369 | 1455 | 1603 |
| 50° | 1339 | 1467 | 1679 |
| 55° | 1294 | 1507 | 1769 |
| 60° | 1234 | 1549 | 1872 |
| 65° | 1163 | 1604 | 1977 |
| 70° | 1038 | 1646 | 2065 |
| 75° | 900  | 1648 | 1635 |
| 80° | 764  | 1218 | 1322 |
| 85° | 658  | 823  | 739  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 70°

Luminance: 2065 cd/sqm

TEST NUMBER: P983179

CATALOG NUMBER: 24CZ-LD5-45SE-UNV-L840-SQP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 103.5  | 3.0       |
| 10°-20°   | 297.2  | 8.7       |
| 20°-30°   | 452.9  | 13.2      |
| 30°-40°   | 554.2  | 16.1      |
| 40°-50°   | 596.3  | 17.4      |
| 50°-60°   | 577.6  | 16.8      |
| 60°-70°   | 489.3  | 14.3      |
| 70°-80°   | 295.8  | 8.6       |
| 80°-90°   | 65.0   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 853.7  | 24.9      |
| 0°-40°    | 1407.9 | 41.0      |
| 0°-60°    | 2581.9 | 75.2      |
| 0°-90°    | 3432.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3432.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1090 | 1090  | 1090 | 1090  | 1090 |      |
| 5°  | 1087 | 1087  | 1095 | 1090  | 1082 | 103  |
| 15° | 1047 | 1050  | 1053 | 1055  | 1058 | 296  |
| 25° | 968  | 973   | 983  | 992   | 997  | 447  |
| 35° | 858  | 864   | 882  | 906   | 920  | 537  |
| 45° | 720  | 733   | 765  | 813   | 842  | 555  |
| 55° | 552  | 576   | 642  | 717   | 754  | 493  |
| 65° | 365  | 405   | 504  | 584   | 621  | 360  |
| 75° | 173  | 235   | 317  | 322   | 314  | 186  |
| 85° | 43   | 51    | 53   | 51    | 48   | 48   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P983179

CATALOG NUMBER: 24CZ-LD5-45SE-UNV-L840-SQP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1090.1 | 1090.1 | 1090.1 | 1090.1 | 1090.1 |
| 2.5°  | 1103.4 | 1100.8 | 1092.7 | 1087.4 | 1082.1 |
| 5°    | 1087.4 | 1087.4 | 1095.4 | 1090.1 | 1082.1 |
| 7.5°  | 1079.4 | 1079.4 | 1079.4 | 1092.7 | 1079.4 |
| 10°   | 1071.4 | 1074.1 | 1071.4 | 1082.1 | 1071.4 |
| 12.5° | 1063.4 | 1063.4 | 1063.4 | 1066.1 | 1066.1 |
| 15°   | 1047.4 | 1050.1 | 1052.7 | 1055.4 | 1058.1 |
| 17.5° | 1031.5 | 1034.1 | 1039.4 | 1042.1 | 1044.8 |
| 20°   | 1015.5 | 1018.1 | 1026.1 | 1026.1 | 1031.5 |
| 22.5° | 994.1  | 994.1  | 1004.8 | 1007.4 | 1015.5 |
| 25°   | 967.5  | 972.8  | 983.4  | 991.5  | 996.8  |
| 27.5° | 943.5  | 948.8  | 959.5  | 970.1  | 978.1  |
| 30°   | 916.9  | 922.2  | 932.8  | 948.8  | 959.5  |
| 32.5° | 887.5  | 892.9  | 908.8  | 927.5  | 938.1  |
| 35°   | 858.2  | 863.5  | 882.2  | 906.2  | 919.5  |
| 37.5° | 826.2  | 834.2  | 855.5  | 882.2  | 898.2  |
| 40°   | 794.2  | 802.3  | 826.2  | 855.5  | 879.5  |
| 42.5° | 756.9  | 767.6  | 794.2  | 834.2  | 860.9  |
| 45°   | 719.6  | 733.0  | 764.9  | 812.9  | 842.2  |
| 47.5° | 679.6  | 693.0  | 730.3  | 791.6  | 823.5  |
| 50°   | 639.6  | 655.6  | 700.9  | 767.6  | 802.3  |
| 52.5° | 597.0  | 613.0  | 671.6  | 743.6  | 780.9  |
| 55°   | 551.7  | 575.7  | 642.3  | 717.0  | 754.2  |
| 57.5° | 506.4  | 533.1  | 607.7  | 687.7  | 727.6  |
| 60°   | 458.4  | 490.4  | 575.7  | 655.6  | 695.6  |
| 62.5° | 413.1  | 447.8  | 541.0  | 621.0  | 661.0  |
| 65°   | 365.2  | 405.1  | 503.8  | 583.7  | 621.0  |
| 67.5° | 314.5  | 365.2  | 461.1  | 538.4  | 575.7  |
| 70°   | 263.9  | 322.5  | 418.5  | 490.4  | 525.0  |
| 72.5° | 218.5  | 279.9  | 370.5  | 431.7  | 431.7  |
| 75°   | 173.2  | 234.6  | 317.1  | 322.5  | 314.5  |
| 77.5° | 133.2  | 191.9  | 247.8  | 226.5  | 231.9  |
| 80°   | 98.6   | 146.6  | 157.2  | 165.3  | 170.6  |
| 82.5° | 66.7   | 98.6   | 101.3  | 106.6  | 106.6  |
| 85°   | 42.6   | 50.7   | 53.3   | 50.7   | 47.9   |
| 87.5° | 18.6   | 21.4   | 16.0   | 10.7   | 8.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-7

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L940-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L940-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L940-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 940 SMOOTH LENS

### Spectral Parameters

CCT (K): 3955  
 CIE  $u'$ : 0.2264  
 CIE  $v'$ : 0.5014  
 Duv: -0.0009  
 CIE x: 0.3818  
 CIE y: 0.3758  
 CIE z: 0.2424  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 579  
 Purity: 27.35334  
 R<sub>f</sub>: 90.3  
 R<sub>g</sub>: 99.3

CRI (Ra): 93.6  
 R1: 95.0  
 R2: 96.2  
 R3: 95.3  
 R4: 94.7  
 R5: 93.8  
 R6: 93.5  
 R7: 94.0  
 R8: 86.7  
 R9: 65.5  
 R10: 88.9  
 R11: 94.8  
 R12: 71.7  
 R13: 95.4  
 R14: 96.7  
 R15: 92.2



### Test Conditions

Stabilization Time: 22M  
 Operation Time: 1H 22M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-7

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-7

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 171                      | NR            | 620    | 355                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 199                      | NR            | 625    | 352                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 230                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 257                      | NR            | 635    | 711                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 278                      | NR            | 640    | 235                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 295                      | NR            | 645    | 222                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 305                      | NR            | 650    | 198                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 313                      | NR            | 655    | 165                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 3                        | NR            | 530    | 318                      | NR            | 660    | 142                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 4                        | NR            | 535    | 323                      | NR            | 665    | 120                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 6                        | NR            | 540    | 327                      | NR            | 670    | 110                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 9                        | NR            | 545    | 333                      | NR            | 675    | 91                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 15                       | NR            | 550    | 339                      | NR            | 680    | 77                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 27                       | NR            | 555    | 343                      | NR            | 685    | 67                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 48                       | NR            | 560    | 349                      | NR            | 690    | 57                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 87                       | NR            | 565    | 355                      | NR            | 695    | 49                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 155                      | NR            | 570    | 358                      | NR            | 700    | 42                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 291                      | NR            | 575    | 363                      | NR            | 705    | 36                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 475                      | NR            | 580    | 365                      | NR            | 710    | 30                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 466                      | NR            | 585    | 367                      | NR            | 715    | 26                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 308                      | NR            | 590    | 367                      | NR            | 720    | 22                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 246                      | NR            | 595    | 364                      | NR            | 725    | 19                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 202                      | NR            | 600    | 363                      | NR            | 730    | 16                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 152                      | NR            | 605    | 361                      | NR            | 735    | 14                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 140                      | NR            | 610    | 391                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 152                      | NR            | 615    | 418                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-7

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.77

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 171                                  | NR                             | 620               | 355                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 199                                  | NR                             | 625               | 352                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 257                                  | NR                             | 635               | 711                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 278                                  | NR                             | 640               | 235                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 295                                  | NR                             | 645               | 222                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 305                                  | NR                             | 650               | 198                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 313                                  | NR                             | 655               | 165                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 318                                  | NR                             | 660               | 142                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 323                                  | NR                             | 665               | 120                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 327                                  | NR                             | 670               | 110                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 9                                    | NR                             | 545               | 333                                  | NR                             | 675               | 91                                   | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 15                                   | NR                             | 550               | 339                                  | NR                             | 680               | 77                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 27                                   | NR                             | 555               | 343                                  | NR                             | 685               | 67                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 48                                   | NR                             | 560               | 349                                  | NR                             | 690               | 57                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 87                                   | NR                             | 565               | 355                                  | NR                             | 695               | 49                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 155                                  | NR                             | 570               | 358                                  | NR                             | 700               | 42                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 291                                  | NR                             | 575               | 363                                  | NR                             | 705               | 36                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 475                                  | NR                             | 580               | 365                                  | NR                             | 710               | 30                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 466                                  | NR                             | 585               | 367                                  | NR                             | 715               | 26                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 308                                  | NR                             | 590               | 367                                  | NR                             | 720               | 22                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 246                                  | NR                             | 595               | 364                                  | NR                             | 725               | 19                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 202                                  | NR                             | 600               | 363                                  | NR                             | 730               | 16                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 152                                  | NR                             | 605               | 361                                  | NR                             | 735               | 14                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 140                                  | NR                             | 610               | 391                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 152                                  | NR                             | 615               | 418                                  | NR                             | 745               | 10                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-7

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.69**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 171                                  | NR                             | 620               | 355                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 199                                  | NR                             | 625               | 352                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 257                                  | NR                             | 635               | 711                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 278                                  | NR                             | 640               | 235                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 295                                  | NR                             | 645               | 222                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 305                                  | NR                             | 650               | 198                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 313                                  | NR                             | 655               | 165                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 318                                  | NR                             | 660               | 142                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 323                                  | NR                             | 665               | 120                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 327                                  | NR                             | 670               | 110                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 9                                    | NR                             | 545               | 333                                  | NR                             | 675               | 91                                   | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 15                                   | NR                             | 550               | 339                                  | NR                             | 680               | 77                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 27                                   | NR                             | 555               | 343                                  | NR                             | 685               | 67                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 48                                   | NR                             | 560               | 349                                  | NR                             | 690               | 57                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 87                                   | NR                             | 565               | 355                                  | NR                             | 695               | 49                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 155                                  | NR                             | 570               | 358                                  | NR                             | 700               | 42                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 291                                  | NR                             | 575               | 363                                  | NR                             | 705               | 36                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 475                                  | NR                             | 580               | 365                                  | NR                             | 710               | 30                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 466                                  | NR                             | 585               | 367                                  | NR                             | 715               | 26                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 308                                  | NR                             | 590               | 367                                  | NR                             | 720               | 22                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 246                                  | NR                             | 595               | 364                                  | NR                             | 725               | 19                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 202                                  | NR                             | 600               | 363                                  | NR                             | 730               | 16                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 152                                  | NR                             | 605               | 361                                  | NR                             | 735               | 14                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 140                                  | NR                             | 610               | 391                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 152                                  | NR                             | 615               | 418                                  | NR                             | 745               | 10                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-7


TM-30-18

### Summary

$R_f = 90.3$   
 $R_g = 99.3$   
 $CIE R_a = 93.6$   
 $R_9 = 65.5$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 97 | CES76 = 85 |
| CES02 = 62 | CES27 = 90 | CES52 = 99 | CES77 = 87 |
| CES03 = 31 | CES28 = 95 | CES53 = 97 | CES78 = 82 |
| CES04 = 69 | CES29 = 96 | CES54 = 92 | CES79 = 93 |
| CES05 = 49 | CES30 = 89 | CES55 = 90 | CES80 = 92 |
| CES06 = 50 | CES31 = 97 | CES56 = 94 | CES81 = 80 |
| CES07 = 42 | CES32 = 89 | CES57 = 92 | CES82 = 96 |
| CES08 = 41 | CES33 = 98 | CES58 = 92 | CES83 = 96 |
| CES09 = 29 | CES34 = 93 | CES59 = 97 | CES84 = 93 |
| CES10 = 74 | CES35 = 95 | CES60 = 91 | CES85 = 80 |
| CES11 = 57 | CES36 = 77 | CES61 = 91 | CES86 = 84 |
| CES12 = 63 | CES37 = 94 | CES62 = 83 | CES87 = 91 |
| CES13 = 43 | CES38 = 83 | CES63 = 91 | CES88 = 98 |
| CES14 = 74 | CES39 = 99 | CES64 = 88 | CES89 = 85 |
| CES15 = 71 | CES40 = 98 | CES65 = 87 | CES90 = 96 |
| CES16 = 47 | CES41 = 96 | CES66 = 84 | CES91 = 70 |
| CES17 = 49 | CES42 = 92 | CES67 = 83 | CES92 = 76 |
| CES18 = 56 | CES43 = 93 | CES68 = 86 | CES93 = 85 |
| CES19 = 71 | CES44 = 99 | CES69 = 87 | CES94 = 76 |
| CES20 = 66 | CES45 = 97 | CES70 = 84 | CES95 = 81 |
| CES21 = 85 | CES46 = 97 | CES71 = 76 | CES96 = 92 |
| CES22 = 78 | CES47 = 94 | CES72 = 93 | CES97 = 95 |
| CES23 = 91 | CES48 = 89 | CES73 = 78 | CES98 = 95 |
| CES24 = 90 | CES49 = 96 | CES74 = 90 | CES99 = 93 |
| CES25 = 71 | CES50 = 98 | CES75 = 79 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)