

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983200

Luminaire Tested: 24CZ-LD5-55-UNV-L950-SQP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983200  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-55-UNV-L950-SQP-CD1-U  
Description: METALUX CRUZE 2x4 5500LM PACKAGE 90CRI 5000K TROFFER LENS WITH SQUARE PATTERN  
Light Source: 5000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4225.0 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.31 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983200

CATALOG NUMBER: 24CZ-LD5-55-UNV-L950-SQP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983200

CATALOG NUMBER: 24CZ-LD5-55-UNV-L950-SQP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 87  |  | 89  | 87  | 85  | 83  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 73  |  | 80  | 76  | 71  |  | 77  | 73  | 70  | 68  |
| 3   | 89  | 78  | 69  | 62  | 86  | 76  | 68  | 62  | 73  | 66  | 61  |  | 70  | 64  | 59  |  | 68  | 63  | 58  | 56  |
| 4   | 81  | 68  | 59  | 52  | 79  | 67  | 58  | 52  | 64  | 57  | 51  |  | 62  | 56  | 50  |  | 60  | 54  | 50  | 47  |
| 5   | 74  | 61  | 52  | 45  | 72  | 60  | 51  | 44  | 58  | 50  | 44  |  | 56  | 49  | 43  |  | 54  | 48  | 43  | 41  |
| 6   | 68  | 55  | 45  | 39  | 66  | 54  | 45  | 39  | 52  | 44  | 38  |  | 50  | 43  | 38  |  | 48  | 42  | 37  | 35  |
| 7   | 63  | 49  | 40  | 34  | 62  | 49  | 40  | 34  | 47  | 39  | 34  |  | 45  | 39  | 33  |  | 44  | 38  | 33  | 31  |
| 8   | 59  | 45  | 36  | 30  | 57  | 44  | 36  | 30  | 43  | 35  | 30  |  | 42  | 35  | 30  |  | 40  | 34  | 29  | 28  |
| 9   | 55  | 41  | 33  | 27  | 54  | 41  | 33  | 27  | 39  | 32  | 27  |  | 38  | 32  | 27  |  | 37  | 31  | 27  | 25  |
| 10  | 51  | 38  | 30  | 24  | 50  | 37  | 30  | 24  | 36  | 29  | 24  |  | 35  | 29  | 24  |  | 35  | 28  | 24  | 22  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1806 | 1806 | 1806 |
| 5°  | 1808 | 1821 | 1799 |
| 10° | 1802 | 1802 | 1802 |
| 15° | 1796 | 1805 | 1814 |
| 20° | 1790 | 1809 | 1818 |
| 25° | 1768 | 1797 | 1822 |
| 30° | 1754 | 1784 | 1835 |
| 35° | 1735 | 1784 | 1859 |
| 40° | 1717 | 1786 | 1902 |
| 45° | 1686 | 1792 | 1973 |
| 50° | 1648 | 1806 | 2067 |
| 55° | 1593 | 1855 | 2178 |
| 60° | 1519 | 1907 | 2304 |
| 65° | 1431 | 1975 | 2434 |
| 70° | 1278 | 2027 | 2543 |
| 75° | 1109 | 2030 | 2012 |
| 80° | 941  | 1500 | 1627 |
| 85° | 810  | 1013 | 911  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 70°

Luminance: 2543 cd/sqm

TEST NUMBER: P983200

CATALOG NUMBER: 24CZ-LD5-55-UNV-L950-SQP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 127.4  | 3.0       |
| 10°-20°   | 365.9  | 8.7       |
| 20°-30°   | 557.6  | 13.2      |
| 30°-40°   | 682.3  | 16.1      |
| 40°-50°   | 734.1  | 17.4      |
| 50°-60°   | 711.1  | 16.8      |
| 60°-70°   | 602.4  | 14.3      |
| 70°-80°   | 364.1  | 8.6       |
| 80°-90°   | 80.0   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1050.9 | 24.9      |
| 0°-40°    | 1733.2 | 41.0      |
| 0°-60°    | 3178.4 | 75.2      |
| 0°-90°    | 4225.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4225.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1342 | 1342  | 1342 | 1342  | 1342 |      |
| 5°  | 1339 | 1339  | 1348 | 1342  | 1332 | 127  |
| 15° | 1290 | 1293  | 1296 | 1299  | 1303 | 364  |
| 25° | 1191 | 1198  | 1211 | 1221  | 1227 | 550  |
| 35° | 1056 | 1063  | 1086 | 1116  | 1132 | 661  |
| 45° | 886  | 902   | 942  | 1001  | 1037 | 683  |
| 55° | 679  | 709   | 791  | 883   | 928  | 607  |
| 65° | 450  | 499   | 620  | 718   | 764  | 443  |
| 75° | 213  | 289   | 390  | 397   | 387  | 229  |
| 85° | 52   | 62    | 66   | 62    | 59   | 59   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P983200

CATALOG NUMBER: 24CZ-LD5-55-UNV-L950-SQP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1342.0 | 1342.0 | 1342.0 | 1342.0 | 1342.0 |
| 2.5°  | 1358.4 | 1355.1 | 1345.2 | 1338.7 | 1332.1 |
| 5°    | 1338.7 | 1338.7 | 1348.5 | 1342.0 | 1332.1 |
| 7.5°  | 1328.8 | 1328.8 | 1328.8 | 1345.2 | 1328.8 |
| 10°   | 1319.0 | 1322.3 | 1319.0 | 1332.1 | 1319.0 |
| 12.5° | 1309.1 | 1309.1 | 1309.1 | 1312.4 | 1312.4 |
| 15°   | 1289.5 | 1292.7 | 1296.0 | 1299.3 | 1302.6 |
| 17.5° | 1269.8 | 1273.1 | 1279.6 | 1282.9 | 1286.2 |
| 20°   | 1250.1 | 1253.4 | 1263.2 | 1263.2 | 1269.8 |
| 22.5° | 1223.8 | 1223.8 | 1237.0 | 1240.2 | 1250.1 |
| 25°   | 1191.0 | 1197.6 | 1210.7 | 1220.6 | 1227.1 |
| 27.5° | 1161.5 | 1168.1 | 1181.2 | 1194.3 | 1204.1 |
| 30°   | 1128.7 | 1135.2 | 1148.4 | 1168.1 | 1181.2 |
| 32.5° | 1092.6 | 1099.2 | 1118.8 | 1141.8 | 1154.9 |
| 35°   | 1056.5 | 1063.1 | 1086.0 | 1115.6 | 1132.0 |
| 37.5° | 1017.1 | 1027.0 | 1053.2 | 1086.0 | 1105.7 |
| 40°   | 977.8  | 987.6  | 1017.1 | 1053.2 | 1082.7 |
| 42.5° | 931.8  | 944.9  | 977.8  | 1027.0 | 1059.8 |
| 45°   | 885.9  | 902.3  | 941.7  | 1000.7 | 1036.8 |
| 47.5° | 836.7  | 853.1  | 899.0  | 974.5  | 1013.8 |
| 50°   | 787.4  | 807.1  | 862.9  | 944.9  | 987.6  |
| 52.5° | 734.9  | 754.6  | 826.8  | 915.4  | 961.3  |
| 55°   | 679.2  | 708.7  | 790.7  | 882.6  | 928.5  |
| 57.5° | 623.4  | 656.2  | 748.1  | 846.6  | 895.7  |
| 60°   | 564.3  | 603.7  | 708.7  | 807.1  | 856.3  |
| 62.5° | 508.6  | 551.3  | 666.0  | 764.5  | 813.7  |
| 65°   | 449.5  | 498.8  | 620.2  | 718.5  | 764.5  |
| 67.5° | 387.1  | 449.5  | 567.7  | 662.8  | 708.7  |
| 70°   | 324.9  | 397.0  | 515.2  | 603.7  | 646.4  |
| 72.5° | 269.0  | 344.5  | 456.1  | 531.5  | 531.5  |
| 75°   | 213.3  | 288.8  | 390.4  | 397.0  | 387.1  |
| 77.5° | 164.0  | 236.3  | 305.1  | 278.9  | 285.4  |
| 80°   | 121.4  | 180.4  | 193.6  | 203.5  | 210.0  |
| 82.5° | 82.1   | 121.4  | 124.7  | 131.3  | 131.3  |
| 85°   | 52.5   | 62.4   | 65.6   | 62.4   | 59.0   |
| 87.5° | 22.9   | 26.3   | 19.7   | 13.1   | 9.9    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-8

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L950-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L950-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-8  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L950-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 950 SMOOTH LENS

### Spectral Parameters

CCT (K): 5019  
 CIE  $u'$ : 0.2113  
 CIE  $v'$ : 0.4842  
 Duv: -0.0002  
 CIE x: 0.3445  
 CIE y: 0.3508  
 CIE z: 0.3046  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 572  
 Purity: 8.636369  
 R<sub>f</sub>: 89.8  
 R<sub>g</sub>: 98.5

CRI (Ra): 94.6  
 R1: 96.4  
 R2: 98.4  
 R3: 96.9  
 R4: 94.5  
 R5: 94.5  
 R6: 93.5  
 R7: 93.6  
 R8: 89.4  
 R9: 74.6  
 R10: 94.2  
 R11: 95.5  
 R12: 70.8  
 R13: 98.0  
 R14: 98.0  
 R15: 95.0



### Test Conditions

Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-8

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-8

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-8

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 249                      | NR            | 620    | 343                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 269                      | NR            | 625    | 339                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 296                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 325                      | NR            | 635    | 705                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 347                      | NR            | 640    | 221                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 363                      | NR            | 645    | 210                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 371                      | NR            | 650    | 186                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 378                      | NR            | 655    | 155                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 381                      | NR            | 660    | 132                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 5                        | NR            | 535    | 383                      | NR            | 665    | 111                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 385                      | NR            | 670    | 102                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 389                      | NR            | 675    | 84                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 17                       | NR            | 550    | 391                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 29                       | NR            | 555    | 392                      | NR            | 685    | 62                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 53                       | NR            | 560    | 393                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 97                       | NR            | 565    | 394                      | NR            | 695    | 45                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 173                      | NR            | 570    | 391                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 321                      | NR            | 575    | 389                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 597                      | NR            | 580    | 385                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 795                      | NR            | 585    | 382                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 615                      | NR            | 590    | 375                      | NR            | 720    | 21                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 438                      | NR            | 595    | 367                      | NR            | 725    | 17                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 372                      | NR            | 600    | 361                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 290                      | NR            | 605    | 355                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 236                      | NR            | 610    | 383                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 232                      | NR            | 615    | 408                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-8

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.11

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 249                                  | NR                             | 620               | 343                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 269                                  | NR                             | 625               | 339                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 296                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 325                                  | NR                             | 635               | 705                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 347                                  | NR                             | 640               | 221                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 363                                  | NR                             | 645               | 210                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 371                                  | NR                             | 650               | 186                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 3                                    | NR                             | 525               | 378                                  | NR                             | 655               | 155                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 381                                  | NR                             | 660               | 132                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 5                                    | NR                             | 535               | 383                                  | NR                             | 665               | 111                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 385                                  | NR                             | 670               | 102                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 389                                  | NR                             | 675               | 84                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 17                                   | NR                             | 550               | 391                                  | NR                             | 680               | 72                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 29                                   | NR                             | 555               | 392                                  | NR                             | 685               | 62                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 53                                   | NR                             | 560               | 393                                  | NR                             | 690               | 53                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 97                                   | NR                             | 565               | 394                                  | NR                             | 695               | 45                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 173                                  | NR                             | 570               | 391                                  | NR                             | 700               | 39                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 321                                  | NR                             | 575               | 389                                  | NR                             | 705               | 33                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 597                                  | NR                             | 580               | 385                                  | NR                             | 710               | 28                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 795                                  | NR                             | 585               | 382                                  | NR                             | 715               | 24                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 615                                  | NR                             | 590               | 375                                  | NR                             | 720               | 21                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 438                                  | NR                             | 595               | 367                                  | NR                             | 725               | 17                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 372                                  | NR                             | 600               | 361                                  | NR                             | 730               | 15                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 290                                  | NR                             | 605               | 355                                  | NR                             | 735               | 13                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 236                                  | NR                             | 610               | 383                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 232                                  | NR                             | 615               | 408                                  | NR                             | 745               | 9                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-8

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.62

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 249                                    | NR                             | 620               | 343                                    | NR                             | 750               | 8                                      | NR                             | 880               | 0                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 269                                    | NR                             | 625               | 339                                    | NR                             | 755               | 7                                      | NR                             | 885               | 0                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 296                                    | NR                             | 630               | 1000                                   | NR                             | 760               | 6                                      | NR                             | 890               | 0                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 325                                    | NR                             | 635               | 705                                    | NR                             | 765               | 5                                      | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 347                                    | NR                             | 640               | 221                                    | NR                             | 770               | 4                                      | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 363                                    | NR                             | 645               | 210                                    | NR                             | 775               | 4                                      | NR                             | 905               | 0                                      | NR                             |
| 390               | 1                                      | NR                             | 520               | 371                                    | NR                             | 650               | 186                                    | NR                             | 780               | 3                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 3                                      | NR                             | 525               | 378                                    | NR                             | 655               | 155                                    | NR                             | 785               | 3                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 4                                      | NR                             | 530               | 381                                    | NR                             | 660               | 132                                    | NR                             | 790               | 2                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 5                                      | NR                             | 535               | 383                                    | NR                             | 665               | 111                                    | NR                             | 795               | 2                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 7                                      | NR                             | 540               | 385                                    | NR                             | 670               | 102                                    | NR                             | 800               | 2                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 10                                     | NR                             | 545               | 389                                    | NR                             | 675               | 84                                     | NR                             | 805               | 1                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 17                                     | NR                             | 550               | 391                                    | NR                             | 680               | 72                                     | NR                             | 810               | 1                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 29                                     | NR                             | 555               | 392                                    | NR                             | 685               | 62                                     | NR                             | 815               | 1                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 53                                     | NR                             | 560               | 393                                    | NR                             | 690               | 53                                     | NR                             | 820               | 1                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 97                                     | NR                             | 565               | 394                                    | NR                             | 695               | 45                                     | NR                             | 825               | 1                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 173                                    | NR                             | 570               | 391                                    | NR                             | 700               | 39                                     | NR                             | 830               | 1                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 321                                    | NR                             | 575               | 389                                    | NR                             | 705               | 33                                     | NR                             | 835               | 1                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 597                                    | NR                             | 580               | 385                                    | NR                             | 710               | 28                                     | NR                             | 840               | 1                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 795                                    | NR                             | 585               | 382                                    | NR                             | 715               | 24                                     | NR                             | 845               | 1                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 615                                    | NR                             | 590               | 375                                    | NR                             | 720               | 21                                     | NR                             | 850               | 0                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 438                                    | NR                             | 595               | 367                                    | NR                             | 725               | 17                                     | NR                             | 855               | 0                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 372                                    | NR                             | 600               | 361                                    | NR                             | 730               | 15                                     | NR                             | 860               | 0                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 290                                    | NR                             | 605               | 355                                    | NR                             | 735               | 13                                     | NR                             | 865               | 0                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 236                                    | NR                             | 610               | 383                                    | NR                             | 740               | 11                                     | NR                             | 870               | 0                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 232                                    | NR                             | 615               | 408                                    | NR                             | 745               | 9                                      | NR                             | 875               | 0                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP3-2508-516-8

TM-30-18

### Summary

$R_f = 89.8$   
 $R_g = 98.5$   
 $\text{CIE } R_a = 94.6$   
 $R_9 = 74.6$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 85 | CES26 = 96  | CES51 = 93 | CES76 = 88 |
| CES02 = 61 | CES27 = 88  | CES52 = 97 | CES77 = 87 |
| CES03 = 31 | CES28 = 96  | CES53 = 95 | CES78 = 85 |
| CES04 = 69 | CES29 = 93  | CES54 = 89 | CES79 = 93 |
| CES05 = 48 | CES30 = 81  | CES55 = 86 | CES80 = 93 |
| CES06 = 50 | CES31 = 95  | CES56 = 90 | CES81 = 80 |
| CES07 = 41 | CES32 = 93  | CES57 = 87 | CES82 = 96 |
| CES08 = 40 | CES33 = 91  | CES58 = 87 | CES83 = 95 |
| CES09 = 29 | CES34 = 95  | CES59 = 96 | CES84 = 93 |
| CES10 = 73 | CES35 = 96  | CES60 = 89 | CES85 = 81 |
| CES11 = 56 | CES36 = 74  | CES61 = 89 | CES86 = 85 |
| CES12 = 62 | CES37 = 95  | CES62 = 78 | CES87 = 93 |
| CES13 = 42 | CES38 = 76  | CES63 = 89 | CES88 = 96 |
| CES14 = 74 | CES39 = 98  | CES64 = 84 | CES89 = 87 |
| CES15 = 71 | CES40 = 98  | CES65 = 86 | CES90 = 93 |
| CES16 = 47 | CES41 = 92  | CES66 = 81 | CES91 = 68 |
| CES17 = 48 | CES42 = 95  | CES67 = 80 | CES92 = 78 |
| CES18 = 56 | CES43 = 96  | CES68 = 85 | CES93 = 86 |
| CES19 = 70 | CES44 = 99  | CES69 = 85 | CES94 = 79 |
| CES20 = 65 | CES45 = 100 | CES70 = 84 | CES95 = 82 |
| CES21 = 85 | CES46 = 96  | CES71 = 75 | CES96 = 93 |
| CES22 = 77 | CES47 = 91  | CES72 = 92 | CES97 = 96 |
| CES23 = 91 | CES48 = 84  | CES73 = 80 | CES98 = 94 |
| CES24 = 90 | CES49 = 97  | CES74 = 89 | CES99 = 92 |
| CES25 = 70 | CES50 = 95  | CES75 = 78 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)