

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979920

Luminaire Tested: PRLX-242-927-LL3-C-U-S-BLAK-X

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2024
Report Number: P979920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-26)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-242-927-LL3-C-U-S-BLAK-X
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, BLACK 242 SHADE WITH CLEAR LENS
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2261.2 lumens
Efficiency: N/A
Efficacy: 150.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.39
Luminous Opening: Circular (Dia: 1.75' x H: 0')
CIE Type: Direct


Input Watts (W): 15
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P979920

CATALOG NUMBER: PRLX-242-927-LL3-C-U-S-BLAK-X

Luminous Intensity Polar Plot



TEST NUMBER: P979920

CATALOG NUMBER: PRLX-242-927-LL3-C-U-S-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51
6	73	61	52	46	71	60	52	46	58	51	46	56	50	45	55	49	45
7	68	55	47	41	66	54	46	41	53	46	40	51	45	40	50	44	40
8	63	50	42	36	62	49	42	36	48	41	36	47	41	36	46	40	36
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32
10	55	42	35	30	54	42	35	30	41	34	29	40	34	29	39	33	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4038
5°	4041
10°	4036
15°	3986
20°	3962
25°	3945
30°	3925
35°	3925
40°	3932
45°	3926
50°	3918
55°	3853
60°	3608
65°	1684
70°	567
75°	175
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3926 cd/sqm

TEST NUMBER: P979920

CATALOG NUMBER: PRLX-242-927-LL3-C-U-S-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	3.8
10°-20°	243.3	10.8
20°-30°	368.1	16.3
30°-40°	449.9	19.9
40°-50°	478.6	21.2
50°-60°	439.3	19.4
60°-70°	180.3	8.0
70°-80°	16.3	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	696.9	30.8
0°-40°	1146.8	50.7
0°-60°	2064.6	91.3
0°-90°	2261.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2261.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	902	
5°	900	86
15°	860	243
25°	799	368
35°	718	450
45°	620	479
55°	494	439
65°	159	180
75°	10	16
85°	0	0
90°	0	

TEST NUMBER: P979920

CATALOG NUMBER: PRLX-242-927-LL3-C-U-S-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	902.3
2.5°	901.7
5°	899.6
7.5°	895.6
10°	888.1
12.5°	878.0
15°	860.4
17.5°	846.2
20°	832.0
22.5°	815.8
25°	798.9
27.5°	779.2
30°	759.6
32.5°	740.0
35°	718.4
37.5°	696.7
40°	673.0
42.5°	647.3
45°	620.3
47.5°	592.5
50°	562.8
52.5°	529.6
55°	493.8
57.5°	457.9
60°	403.1
62.5°	290.9
65°	159.0
67.5°	63.6
70°	43.3
72.5°	29.8
75°	10.1
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

TEST NUMBER: P979920

CATALOG NUMBER: PRLX-242-927-LL3-C-U-S-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.64	19.18	18.00	19.49	19.80	17.64	19.18	18.00	19.49	19.80
	3H	17.62	18.99	18.00	19.32	19.68	17.62	18.99	18.00	19.32	19.68
	4H	17.57	18.85	17.97	19.19	19.57	17.57	18.85	17.97	19.19	19.57
	6H	17.51	18.68	17.92	19.05	19.44	17.51	18.68	17.92	19.05	19.44
	8H	17.48	18.59	17.90	18.98	19.38	17.48	18.59	17.90	18.98	19.38
	12H	17.44	18.51	17.87	18.89	19.32	17.44	18.51	17.87	18.89	19.32
4H	2H	17.69	18.97	18.09	19.31	19.69	17.69	18.97	18.09	19.31	19.69
	3H	17.71	18.74	18.12	19.14	19.54	17.71	18.74	18.12	19.14	19.54
	4H	17.65	18.57	18.08	18.99	19.43	17.65	18.57	18.08	18.99	19.43
	6H	17.59	18.38	18.05	18.83	19.29	17.59	18.38	18.05	18.83	19.29
	8H	17.54	18.28	18.01	18.73	19.20	17.54	18.28	18.01	18.73	19.20
	12H	17.51	18.17	17.99	18.65	19.12	17.51	18.17	17.99	18.65	19.12
8H	4H	17.55	18.29	18.01	18.73	19.20	17.55	18.29	18.01	18.73	19.20
	6H	17.46	18.07	17.96	18.56	19.04	17.46	18.07	17.96	18.56	19.04
	8H	17.41	17.96	17.93	18.47	18.96	17.41	17.96	17.93	18.47	18.96
	12H	17.37	17.86	17.88	18.35	18.92	17.37	17.86	17.88	18.35	18.92
12H	4H	17.51	18.17	18.00	18.65	19.12	17.51	18.17	18.00	18.65	19.12
	6H	17.41	17.96	17.93	18.47	18.96	17.41	17.96	17.93	18.47	18.96
	8H	17.37	17.86	17.88	18.35	18.92	17.37	17.86	17.88	18.35	18.92